

Basic Rack PDU


Overview

The American Power Conversion (APC[®]) Basic Rack Power Distribution Unit (PDU) distributes power to devices in the rack.

Outlets. The Rack PDU has twenty (20) IEC-320-C13 outlets and four (4) IEC-320-C19 outlets.

Power cord. The 10-foot (3.05-meter) power cord terminates with a IEC-309 16 A connector.

AP7554



Specifications for AP7554

Electrical

Input connector	IEC-309 16A plug
Output connectors	(20) IEC-320-C13 (4) IEC-320-C19 outlets
Nominal input voltage	230 VAC
Acceptable input voltage	± 10% of nominal voltage
Input frequency	47–63 Hz
Cord length	10 ft (3.05 m)

Physical

Dimensions (H × W × D)	63.75 × 2.19 × 1.73 in (161.92 × 5.56 × 4.39 cm)
Shipping dimensions (H × W × D)	84.00 × 6.00 × 5.00 in (213.36 × 15.24 × 12.70 cm)
Weight	12.25 lb (5.56 kg)
Shipping weight	14.25 lb (6.46 kg)

Environmental

Maximum elevation (above MSL)	
Operating	10,000 ft (3 000m)
Storage	50,000 ft (15 000m)
Temperature	
Operating	–5 to 45° C (23 to 115°F)
Storage	–25 to 65° C (–13 to 149°F)
Humidity	
Operating	5–95% RH, non-condensing
Storage	5–95% RH, non-condensing

Compliance

Safety verifications	VDE 0805, CE, EN 60950-1, IEC 60950-1
----------------------	--

