

Basic Rack PDU


Overview

The American Power Conversion (APC[®]) Basic Rack Power Distribution Unit (PDU) distributes power to devices in the rack.

Outlets. The Rack PDU has twenty (20) IEC-320-C13 outlets and four (4) IEC-320-C19 outlets.

Power cord. The 10-foot (3.05-meter) power cord terminates with a IEC-309 16A connector.

AP7554



Specifications for AP7554

Electrical

| | |
|--------------------------|---|
| Input connector | IEC-309 16A plug |
| Output connectors | (20) IEC-320-C13 (4) IEC-320-C19 outlets |
| Nominal input voltage | 230 VAC |
| Acceptable input voltage | ± 10% of nominal voltage |
| Input frequency | 47–63 Hz |
| Cord length | 10 ft (3.05 m) |

Physical

| | |
|------------------------------------|---|
| Dimensions (H × W × D) | 63.75 × 2.19 × 1.73 in (161.92 × 5.56 × 4.39 cm) |
| Shipping dimensions (H × W × D) | 84.00 × 6.00 × 5.00 in (213.36 × 15.24 × 12.70 cm) |
| Weight | 12.25 lb (5.56 kg) |
| Shipping weight | 14.25 lb (6.46 kg) |

Environmental

| | |
|----------------------------------|-----------------------------|
| Maximum elevation (above MSL) | |
| Operating | 10,000 ft (3 000 m) |
| Storage | 50,000 ft (15 000 m) |
| Temperature | |
| Operating | –5 to 45° C (23 to 115°F) |
| Storage | –25 to 65° C (–13 to 149°F) |
| Humidity | |
| Operating | 5–95% RH, non-condensing |
| Storage | 5–95% RH, non-condensing |

Compliance

| | |
|----------------------|--|
| Safety verifications | VDE 0805, CE, EN 60950-1, IEC 60950-1 |
|----------------------|--|

