


JD250S



SYMBOL	KNOCKOUTS			
	CONDUIT SIZE		DIAMETER	
	IN	MM	IN	MM
A	.50	13	.88	22
B	.75	19	1.13	29
C	1.00	25	1.38	35
D	1.25	32	1.75	45
E	1.50	38	2.00	51
F	2.00	51	2.50	64
G	2.50	64	3.00	76
H	3.00	76	3.63	92
I	3.50	89	4.13	105

FIELD INSTALLABLE SOLID NEUTRAL ASSEMBLIES AND GROUND KIT						
CATALOG NUMBER	MAXIMUM AMPERE RATING	NUMBER OF TERMINALS	CONDUCTORS PER TERMINAL	WIRE SIZE (AWG/KCMIL)		TYPE
				MAX	MIN	
SN225KA	225A	2	2	300	#4	CU ONLY
SN400LA	250A	2	2	600	#1	CU ONLY
PKOGTA-2	-	2	1	2/0	#10	CU ONLY

CIRCUIT BREAKER TERMINAL LUG DATA					
CIRCUIT BREAKER CATALOG NO PREFIX	AMPERE RATING	CONDUCTORS PER PHASE	WIRE SIZE (AWG/KCMIL)		TYPE
			MAX	MIN	
JDL	150-175	1	4/0	#4	CU
JDL	200-250	1	350	3/0	CU
HDL	15-150	1	3/0	#14	CU

DUAL DIMENSIONS: INCHES
MILLIMETERS

FIELD INSTALLABLE CIRCUIT BREAKER DATA					
CIRCUIT BREAKER CATALOG NO. PREFIX	WIRING DIA	AMPERE RATING	UL LISTED INTERRUPTING RATING RMS SYMMETRICAL AMPERES		
			AC VOLTAGE		
			120/240	480Y/277	480
JDL	A	150-250	18K	18K	18K
HDL	A	15-150	18K	18K	18K

NOTES:
 FINISH - GRAY BAKED ENAMEL ELECTRODEPOSITED OVER CLEANED PHOSPHATIZED STEEL.
 cULus LISTED - FILE E-136861.
 SUITABLE FOR USE AS SERVICE EQUIPMENT WHEN NEUTRAL ASSEMBLY IS INSTALLED. (US ONLY).
 NEUTRAL - INSULATED GROUNDABLE.
 ACCEPTS STANDARD 80% RATED CIRCUIT BREAKERS ONLY. NOT RATED FOR 100% RATED CIRCUIT BREAKERS.

CIRCUIT BREAKER ENCLOSURES
 250 AMPERE
 NEMA/EEMAC TYPE 1 GENERAL PURPOSE



DWG# 3457
NO.