


Note:  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:

**BMH0703T06A2A**



Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

Technical Information:

|   |                                   |
|---|-----------------------------------|
| Frame Size (mm):                        | 70                                |
| Degree of Protection (Shaft / housing): | IP54 / IP65                       |
| Maximum Current (Arms):                 | 17.84                             |
| Holding brake:                          | No                                |
| Encoder Type:                           | ABS Single turn 16 Sin/Cos period |
| Torque Constant (Nm/A):                 | 0.61                              |
| CSA:                                    | Yes                               |
| RoHS:                                   | Yes                               |
| Weight without brake (kg / lb):         | 6.61 / 3.0                        |

|  |              |
|--|--------------|
| Description:                           |              |
| Family:                                | BMH          |
| Maximum Permissible Speed (rpm):       | 8000         |
| Continuous Stall Torque (Nm / lbs-in): | 3.40 / 30.1  |
| Peak Torque (Nm / lbs-in):             | 10.2 / 90.28 |

Specification: