



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

SSM1A16P7



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

Approvals:	UL, CSA, CE, RoHS
Current Rating:	6
Motor Load Rating (UL Hp) at 40C:	0.17hp at 240 VAC
Motor Load Rating (IEC KW) at 40C:	N/A
Transient Overvoltage:	600 Vpk
Surge Current (PK MAX):	300 A for 20ms
On-State Voltage Drop at Rated Current (MAX):	1.3 V
Thermal Resistance Junction to Case :	N/A
Maximum I ² T for Fusing (A2 SEC):	375
Max. Off-State Leakage Current at Rated Voltage:	Auto tuning, PID
Min. Off-State DV/DT at MAX Rated Voltage:	500 V/μsec
Minimum On-State Resistance:	N/A
Maximum Turn-On Time:	1/2 cycle
Maximum Turn-Off Time:	1/2 cycle
Control (Input) Voltage Range:	200-265VAC
Minimum Turn-On Voltage:	200 VAC
Minimum Turn-Off Voltage:	90 VAC
Input Current (Typical):	2.5 - 3.5 mA

Specification:

Description:	SSR 1 CHANNEL, 6A@24-280VAC ZC, 200-265VAC
Operating Temperature [°C]:	-30 to +80
Storage Temperature [°C]:	-30 to +100
Weight [g]:	50
Mounting Style :	DIN Rail
Switching Device:	SCR
Switching Type:	Zero Voltage Switching
Contact Configuration:	SPST-NO
Outputs Channel:	1
Operating (Switching) Voltage:	24-280 VAC