



**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:  
**LC1D115S7**

**Schneider Electric**  
 Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

Rating: 600V / 115A  
 UL File/CCN: E164862 / NLDX  
 CSA File: LR43364 3211 04  
 Meets Standards: IEC 60647-4  
 Weight: 2.5 lb (1.13 kg)  
 Termination Method: Screw Clamp  
 Wire Size: Power: #8 AWG - 250MCM  
 Control: #14 - #18 AWG  
 Terminal torque: Power: 100 lb-in (12 Nm)  
 Control: 10 lb-in (1.2 Nm)  
 Mounting Hwd.: 2 x 35mm DIN Rail, M6 screw

**Specification:**

Description: TeSys D IEC Contactor - 115A - Vac Coil  
 Type: TeSys D IEC Contactor - 115A - 500Vac Coil  
 Voltages Code: S7 at 500Vac 50/60 Hz

Coil Consumption: Inrush 280 - 350 VA  
 Sealed 2 - 18 VA

| Single Phase |      | Three Phase |       |       |        |
|--------------|------|-------------|-------|-------|--------|
| 115V         | 230V | 200V        | 230V  | 460V  | 575V   |
| N/A          | N/A  | 30 HP       | 40 HP | 75 HP | 100 HP |