



Description:

Note:

- Drawings Not To Scale

- Drawings Subject to Change Without Notice

- Dimensions are inches next to [Millimeters]

Part No.:

## SSM1A36BDR



Schneider Electric United States North American Division **Boston One Campus** 800 Federal Street Andover, MA 01810, USA Phone:+1 8773425173 Email: CCC@us.schneider-electric.com

Specification:

SSR 1 CHANNEL, 6A@48-600VAC RANDOM, 4-32VDC -30 to +80

Operating Temperature [°C]:
Storage Temperature [°C]:
Weight [g]:
Mounting Style:
Switching Device: -30 to +100 50 **DIN Rail** SCR

Switching Type: Contact Configuration: Random AC Switching

SPST-NO Outputs Channel:

Operating (Switching) Voltage: 48-600 VAC

**Technical Information:** 

UL, CSA, CE, RoHS

Approvals:
Current Rating:
Motor Load Rating ( UL Hp) at 40C:
Motor Load Rating ( IEC KW) at 40C:
Transient Overvoltage: 0.17hp at 240 VAC N/A 1200 Vpk Surge Current (PK MAX):
On-State Voltage Drop at Rated Current (MAX): 300 A for 20ms 1.3 V

On-State Voltage Drop at Rated Current (WCV).
Thermal Resistance Junction to Case:
M/A
Maximum I2T for Fusing (A2 SEC):
Max. Off-State Leakage Current at Rated Voltage: Auto tuning, PID
Min. Off-State DV/DT at MAX Rated Voltage:

500 V/µsec
N/A

1/2 cyclo Maximum Turn-On Time: 1/2 cycle Maximum Turn-Off Time: 1/2 cycle Control (Input) Voltage Range: 4-32VDC Minimum Turn-On Voltage: Minimum Turn-Off Voltage: 4 VDC 1 VDC Input Current (Typical): 8-11 mA