

Drawings Not To Scale
Drawings Subject to Change Without Notice
Dimensions are inches next to [Millimeters]

Note:

RM35JA32MR

Schneider Electric United States
North American Division
Boston One Campus
800 Federal Street
Andover, MA 01810, USA
Phone:+1 8773425173
Email: CCC@us.schneider-electric.com

Technical Information:

Max. Switching Current:
Max. Switching Voltage:
Max. Power Consuption:
Type of Output:
Output Configuration:

Relay DPDT

Function(s): Time Delay:

Measurement Range: Sensitivity Threashold:

8A 250 V 3.5 VA (AC), 1.5 W (DC)

Over Current, Under Current Off-Delay: 0.1 to 30s

0.15-15 Á N/A

Specification:

Description: Current Monitoring Relay, 24-240 VAC/VDC Input, 8A DPDT Output, 0.15-15 A Measurement Range, Function: Over Current And Under Current Dial Settings:

Memory Yes / Memory No: <I, >I, >I>, I%: 10 to 100%, Hys / >I>: 5 to 50%, Tt: 0.1 to 30s

Indication LED:

R

Max. Operating Temps:

-20 to +50 °C (-4 to +122 °F) -40 to +70 °C (-40 to +158 °F)

Max. Operating Temp.: -20 to
Max. Storage Temp.: -40 to
Degree of Protection Term. Block: IP20
Degree of Protection Housing: IP40
Electrical Life @ Rated Load: 100,00
Mechanical Life @ Rated Load: 10,000
Mayorting: 25 mg

100,000 cycles 10,000,000 cycles 35 mm DIN Rail Mounting: