



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
T36AN13G7

Schneider Electric
 Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:
 Max. Continuous Current Rating: 600V / 9A
 Certifications: UL Listed, CSA, CE
 RoHS: Yes
 Termination Method: Power Line: Screw Clamp, Power Load: Lug, Control Circuit: Screw Clamp
 Weight (lbs): 5.92
 Power Line Size (AWG): #8 - #18
 Power Load Size (AWG): #4 - #14
 Control Wire Size (AWG): #10 - #18
 Thermal Overload Type: Motor Logic Solid State
 Thermal Overload Trip Class: Class 10/20 Selectable
 Mounting: Panel

Specification:
 Description: TeSys N Sz 00 open starter, 3 pole, 120 VAC
 Type: FVNR
 Voltages Code: G7 at 120VAC
 Control Type: Common control
 Coil Consumption: Inrush 70 VA
 Sealed 7 VA

Single Phase			Three Phase		
115V	230V	200V	230V	460V	575V
1/3 HP	1 HP	1.5 HP	1.5 HP	2 HP	2 HP