



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
XB6ETN521P

Schneider Electric
 Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:
 Degree of Protection: IP 65
 Storage Temperature Range: -40 to +70 °C
 Operating Temperature Range: -10 to +55 °C
 Contact Type: 2NC
 AC Supply Utilization Category: AC12, 120V-1.5A; 240V-1A; AC15, 120V-0.3A; 240V-0.3A
 Certifications: EN 60947-5-1, EN 60947-5-5, UL 508, GB 14048.5, CSA C22.2 No 14, JIS C8201-5-1

Specification:
 Description: Emergency stop, no illum, IP65, 32mm, 2xNC
 Vibration Resistance: +/- 0.7 mm (10...500 Hz)
 Mechanical Shock Resistance: 500 m/s? for mechanical durability
 Mechanical Life (in operating cycles): 100000