



NOTES:

- ENCLOSURE IS MADE OF THERMOPLASTIC NORYL, RATED TYPE 1.
- ALL WIRES 18.50 ± 0.50 OUT OF CASE.
PHASE A-C, N, GND ARE 12 AWG, 600V, 105°C COPPER WIRE.
NO, NC, COM ARE 18 AWG, 600V, 105°C COPPER WIRE.
FORM C RELAY RATED 5A @ 125VAC.
- THREE PHASE CONFIGURATION SHOWN.
OTHER CONFIGURATIONS ARE AVAILABLE.
- REQUIRED OVERCURRENT PROTECTION: 15A-20A
- APPROXIMATE WEIGHT: 5 LBS [2.3KGS].

PROJECT NAME:			REV. TO SHEET	ECN NO.	BY	APP.	DATE
SERIES 300			MODEL 320			 THIRD ANGLE PROJECTION	
DRAWN BY	BY	DATE	MANUFACTURING TOLERANCES TO BE IN ACCORDANCE WITH ASCO PROCEDURE MP-1-003. FOR PLASTIC PARTS SEE MP-1-055		ASSEM. REF. NO.		COMPUTER GENERATED DRAWING
CHECKED	ALG	1/02	PROPERTY OF ASCO POWER TECHNOLOGIES. USE PERMITTED FOR OUR WORK ONLY. ALL RIGHTS OF DESIGN OR INVENTION ARE RESERVED.		SCALE	NONE	SIZE BS
PROJECT APPROVAL	---	2001	 ASCO® ASCO POWER TECHNOLOGIES, L.P. FLORHAM PARK, NEW JERSEY 07932 U.S.A.		DWG. NO.		DD-82078
FINAL APPROVAL					DRAWING REV.	0	ECN NO.