



Room temperature controller 230 V with two way contact and central plate



Version	Art. no.
Thermoplastic	
<input type="checkbox"/> lotus white	MTN5762-6035
<input checked="" type="checkbox"/> anthracite	MTN5762-6034
<input type="checkbox"/> sahara	MTN5762-6033
<input type="checkbox"/> stainless steel	MTN5762-6036
Metal	
<input type="checkbox"/> nickel metallic	MTN5762-6050
<input type="checkbox"/> champagne metallic	MTN5762-6051
<input checked="" type="checkbox"/> mocca metallic	MTN5762-6052

For System Design.

For electric underfloor heating if the additional heater has to be interlocked, air conditioning (cooling), valve drives (de-energised open or closed).

Range limiting integrated into setting knob.

With plug-in terminals.

With screw fixing.

Functions:

- 1 x changeover contact
- Differential gap 0.5 K
- Temperature range approx. 5-30 °C
- With thermal recirculation

Nominal voltage: AC 230 V

Heating nominal current: 10 A (4 A, cos φ = 0.6)

Heating switching capacity: 2200 W

Cooling nominal current: 5 A (2 A, cos φ = 0.6)

Cooling switching capacity: 1100 W

Room temperature controller 24 V with two way contact and central plate



Version	Art. no.
Thermoplastic	
<input type="checkbox"/> lotus white	MTN5763-6035
<input checked="" type="checkbox"/> anthracite	MTN5763-6034
<input type="checkbox"/> sahara	MTN5763-6033
<input type="checkbox"/> stainless steel	MTN5763-6036
Metal	
<input type="checkbox"/> nickel metallic	MTN5763-6050
<input type="checkbox"/> champagne metallic	MTN5763-6051
<input checked="" type="checkbox"/> mocca metallic	MTN5763-6052

For System Design.

For electric underfloor heating if the additional heater has to be interlocked, air conditioning (cooling), valve drives (de-energised open or closed).

Range limiting integrated into setting knob.

With plug-in terminals.

With screw fixing.

Functions:

- 1 x changeover contact
- Differential gap 0.5 K
- Temperature range approx. 5-30 °C
- With thermal recirculation

Nominal voltage: AC 24 V

Heating nominal current: 10 A (DC 4 A)

Heating switching capacity: 240 W (DC 100 W)

Cooling nominal current: 5 A (DC 2 A)

Cooling switching capacity: 120 W (DC 30 W)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.