



# Green Flexible Digital

ECOFIT™ modernization solutions

## Greater sustainability

- Efficient use of natural resources by replacing only active components
- Recycling of obsolete equipment
- Enabled energy efficiency monitoring

## Improved efficiency

- Lifetime extension for existing switchboards
- Less downtime than with a full panel replacement
- Reduced plant shutdown time from days to hours
- No change of cables and no civil work
- Improved safety of people and surrounding equipment

## Resiliency with digital capabilities

- Enabled asset condition monitoring
- Remote operation ability
- Access to digital energy management solutions and connected service plans

## Benefits

- Digitization giving access to energy management
- Enhanced process dependability
- Optimized maintenance service costs
- New ECOFIT spare parts availability

## Expert help from Schneider Electric

- Worldwide support with Schneider Electric's warranty
- Skilled installation and commissioning experts available locally
- Access to the know-how of a global leader in energy management solutions

[se.com/ecofitselector](https://se.com/ecofitselector)

Life Is On


**Schneider**  
Electric

# DPU 445 with MiCOM P123 Original brand: ABB


## ECOFIT™ proposal

DPU 445  
Protection relay

MiCOM P123  
Protection relay



With ECOFIT™, a true extended life time



## Main technical characteristics

	DPU 445	MiCOM P123
Case	DPU 445	Fit existing cutout
Replacement Type	-	1 for 1 with minimal rewiring
Type	Digital	Numerical
Functionality	3 phase feeder	3 phase + ground feeder overcurrent
Power supply	24 VDC - 125 VDC	24 VDC - 250 VDC
Communication	-	Courier, DNP 3.0, IEC 60870-5-103, Modbus RTU