



The ASCO Model 3012 are resistive, AC load banks designed for static or moveable installation when up to 120 kW of electrical load is required.

LOAD BANK RATINGS

Standard capacity rating up to:

- 120 kW

Standard load step resolution:

- 1 kW

Standard voltage ratings:

Voltage*	Hz	Max. Capacity
380	50	100 kW
400	50	100 kW
415	50	120 kW
440	60	120 kW
480	60	120 kW

*NOTE: Other voltages are available. Please contact sales for further information.

Airflow and Noise Level

Forced-air cooling is by a propeller type metal fan, giving vertical discharge. Fan motor is rated at 50Hz (DOL). 0.95kW at 1 phase and airflow is 2.1 m³/s (4,450 CFM).

Typical noise level is 69dBA at 50Hz. Measurements are taken 3 metres from the load bank and at 90° to the airflow direction. Noise readings are subject to a tolerance of ±3dBA.

Load Control

The load contactors are actuated by the specified load control system. Options range from simple switches to the comprehensive SIGMA system, please see separate data sheet and system layout diagram for further details.

Construction

The frame of the load bank is constructed from 2mm 'Zintec' steel, folded and welded to form a monocoque construction.

A double skinned recessed door allows easy access to the separate enclosures for control, switchgear and power connections.

The double skinned, vertical discharge duct with aluminised steel heat shield contains the resistive load elements and the cooling fan below.

A powder coated air inlet and a stainless steel mesh screen on the hot air discharge provide protection against hazardous parts to IP2X.

All electrical enclosures are to IP54.

Finish

High quality two-pack industrial acrylic paint system applied to an electro-plated zinc base and low-bake finish. Standard colour is grey (RAL7042). Other colours are available on request. Stainless steel construction is also available as an option.

Warranty

The equipment is covered by a 12-month warranty as detailed in our Conditions of Trade.

Model 3012 Specifications

Resistor Elements

The 3012 load banks use replaceable, non-finned sheathed elements. The outer sheath is made from stainless steel to give good corrosion resistance. The heating element is an 80/20 nickel-chrome wire embedded in compacted magnesium oxide powder, giving good thermal and insulation properties.

The elements are very conservatively rated and there is no need for cooling fins to dissipate the heat into the airflow. This ensures that foreign matter or a loosely fitting fin cannot possibly cause hot spots and therefore ensures high reliability.

The elements are designed to operate continuously at up to 800°C (red/orange). The actual temperature is below 500°C (dull red). This gives a wide margin of safety and very long life.

Load tolerance is within 2½ % of total capacity.

Elements are continuously rated at the specific voltage. Short-term tests with fluctuations up to 10% above rated voltage are permissible. Tests at lower voltages, with a corresponding reduction in overall rating, may be carried out. Power is proportional to voltage squared.

Safety Features

An emergency stop/disconnect switch gives full isolation of the fan and control supply.

A 110 Volt AC control circuit transformer provides isolation and operator safety.

Stop/start buttons ensure the load bank will not automatically restart. On static load banks provision is also made for the connection of remote stop/start buttons.

The fan motor is fully protected with fuses and a thermal overload.

Thermal detectors are fitted to protect against overheating in the resistive duct and switchgear enclosure.

Over voltage protection for the control and load circuit is provided by SIGMA load control if specified.

Each element group and its associated contactor are protected by an HRC fuse. This is very important when testing large capacity power supplies, due to the possible high fault currents.


The load contactors are interlocked with the fan controls to ensure load can be applied only when the fan is running.

Internal access is restricted by key operated door catches. Polycarbonate screens behind the doors prevent accidental contact with live parts.

Ambient Temperature and Humidity

Standard load banks are rated at 35°C, when protected from solar radiation. Load banks rated at 50°C are also available. Average air temperature rise 60°C.

Ambient humidity may be up to 90% RH, non-condensing.



All dimensions are in millimeters. Specifications subject to change without notice.

Mounting

The load bank is mounted on to galvanised mounting rails.

Power Terminals & Cable Entry

Power terminals are located behind a dedicated door.

Static load banks are fitted with a non-ferrous gland plates.

Moveable load banks are fitted with a pre-punched, non-metallic gland plate with a flexible rubber shutter, to enable safe temporary power connections to be easily made in a controlled test environment. A blank non-ferrous gland plate is also supplied to enable a fully compliant installation to IP54 if necessary.

There are two gland plates within the load bank. One on the front and one in the bottom, both with a clear opening size of 280 x 80mm.

Auxiliary Supply

The fan and control circuit may be powered from an external auxiliary supply or from the supply on test, provided it is of the correct voltage and frequency. Lower voltages and other frequencies must be tested using the external supply.

On static load banks, connection is by internal terminals.

On moveable load banks, an IEC 60309-2 plug and socket with a three-position switch enables quick and easy connection.

Optional Accessories

- Anti-Condensation Heater
- Castor Sets
- Special Paint Finish

Please see system layout diagram for further details.

Documentation – Operator Handbook

A comprehensive illustrated operator's manual is supplied. Sections cover safety, installation, commissioning, operation, calibration, maintenance and fault finding.

Testing and Standards

Functional operation and load tests are completed on all load banks, before despatch, in line with our ISO 9001:2008 procedures.

ASCO load banks comply with international standards and are CE marked to confirm compliance with both the EMC and Low Voltage Directives.

Weight and Dimensions

Measurements: mm/in. and kg/lbs.

Model	3012
Length	980/38.58
Width across airflow	740/29.14
Height (on base)	1065/41.93
Approximate weight	150/330

Additional Information

An extensive range of resistive, inductive, capacitive or combined load banks of varying capacities are also available. For further information on this model or any other 3000 SERIES load bank, please contact a member of our sales team.