

INDEX

A

Active Port Status, 5-10
Addition, 14-21, 14-22
Addressing I/O, 7-17 to 7-28
 P451, 9-1 to 9-10,
Alphabetic Keyboard, 10-2, 10-12
Alternate Screen, 14-5
Analog Modules, 8-1, 8-3, 8-4, 8-6, 8-8
AND, 16-6, 16-7
ASCII Function Block Menu, 18-23
 Character Set, 18-35
 Editorial Menu, 18-8 to 18-20
 Error Detection, 18-3, 18-33, 18-34
 Function Blocks, 18-3, 18-24
 to 18-29
 Hardware Configuration, 18-1
 Message Formatting, 18-21, 18-22
 Overview, 18-30
 Programmer Tape, 18-5 to 18-22
 Programmer Tape Menu, 18-36
 Programming Messages, 18-2
 Read, 18-27 to 18-29
 Report Generation, 18-3, 18-4
 Software, 18-2
 System Operating Parameters,
 18-3
 Terminal Input and Editing
 Features, 18-31
 Video Terminal Layout Form,
 18-37
 Write, 18-24 to 18-26
Asynchronous, 1-3
Attach, 12-9, 14-1, 21-2
Auxiliary Contact, 2-2

B

Battery Back-up, 4-2, 4-3
Battery Coil, 12-6
Battery Status, 4-1
Baud, 1-3
BCD, 1-5
Binary, 1-5
Bit, 1-1
Bit Modify, 16-14, 16-15
Bit Rotate, 16-19, 16-20
Bit Sense, 16-16 to 16-18
Bit Shift, 16-19, 16-20
Block Move, 15-10, 15-11
Brightness Control, 10-2, 10-3

BROT, 16-19, 16-20
Buffer Addresses, 5-10
Byte, 1-1

C

Cables, 10-5 to 10-8
Cable Connectors, 7-3 to 7-5
Cabling Remote I/O, 6-17, 6-18
Calculates, 14-3, 14-20
CATV Cable, 7-1 to 7-3
Central Processor, 2-1, 2-2
Change Node, 10-11, 14-2
Change Screen, 14-5
Channel Configuration, 6-2, 9-1
Clear Memory, 14-2, 18-6, 21-3
CMPR, 16-12, 16-13
Coils, 14-12, 14-13
Communication Counters, 5-11
Compare (CMPR), 16-12, 16-13
Complement (COMP), 16-4, 16-5
Composite Video, 10-3
Configuration, 12-1
 ASCII, 5-15 to 5-17
 Modules, 12-6, 12-7
 No Skips/Skips, 12-2
 Port 1/Port 2, 12-3 to 12-5
 Set Size, 12-2
 Specials, 12-6
 Write Config, 12-6
Configurator Tape, 10-13, 12-1
Constant Sweep, 14-33 to 14-36
Continue Search, 14-40
Contrast, 10-2, 10-3
Controller Operations (Start, Stop,
 Clear), 14-2, 18-6, 21-3
Counter Power History Tables, 5-19
Counters, 14-2, 14-3, 14-15, 14-18
CPU (Central Processing Unit), 2-1, 2-2
CRT, 2-4, 10-1
Cursor Control, 10-11

D

Data Transfer (DX) Functions, 15-1, 16-1
Data Transfer Move Function Menu, 15-1
Data Transfer Matrix Function Menu,
 16-1
dB — see decibel
DCTR, 14-15, 14-18, 14-19
Deadcodes, 5-7
Decibel loss over cable, 7-1 to 7-4, 7-6,
 7-10 to 7-13
Decimal, 1-5

INDEX (Continued)

Delete Network, 10-11
Delete Node, 10-11
Diagnostics (External), 22-1
Diagnostics (Internal), 13-10
Digital Word Format, 1-4
Dim Awareness Codes, 5-7, 11-1
Discrete Functions, 2-4
Divide (DIV), 14-27
Double Precision Math, 14-25, 14-27
Dump, 20-1
DX (Data Transfer) Functions, 15-1, 16-1

E

Editing Networks, 14-37
Enter, 10-11
Error Messages, 10-18, 20-3, 22-6
to 22-10
Evaluate Tape, 20-1
Event Logs, 5-11
Exclusive OR, 16-10, 16-11
Executive, 2-2
Executive ID, 5-12
Exit Level, 14-36, 14-44
Extended Memory, 17-1
File, 17-1
Map, 17-2
Read, 17-6 to 17-8
Status Word, 17-9, 17-10
Write, 17-3 to 17-5

F

Failure Modes for 584 System, 22-4
Fault Detection, 22-1
FIN, 15-12
Fixed Function Keys, 10-11
FOUT, 15-14
Function Blocks, 14-14, 15-1, 16-1

G

Get, 10-11
Get Next, 10-11
Get Previous, 10-11

H

Hexadecimal, 1-5

I

I425, 6-3, 1-5
I427, 6-3
Identification Plate, 4-4
Increasing the Number of Segments,
12-13
Information Display Screen, 14-2
INIT, 10-12
INIT Lock, 10-12
Initial Start Up 548, 11-1 to 11-3
Input Register, 2-4
Input/Output Modules, 2-3, 3-4, 8-1
I/O Addressing, 9-1
I/O Channel Configuration, 6-2, 6-6
I/O Characteristics, 8-1
I/O Housings, 6-2
I/O Bound, 13-5
I/O Reference Numbers, 2-4, 2-5

J

J200, 6-7, 7-16, 7-29
J540, 6-2

K

Keyboard, 10-2, 10-11
Keylock, 10-2, 10-3

L

Ladder Lister, 21-1
Ladder Lister Example, 21-7 to 21-9
Line Splitters, 7-4
Line Taps, 7-3, 7-4
Load Procedure, 20-1
Local I/O Configurations, 6-3, 6-4
Logic Area, 14-4
Logic Bound, 13-5
Logic Screen, 14-4
Logout, 5-10

M

Mainframe, 3-3, 4-1
Master Tapes, 10-13
Matrix, 16-2
Matrix Functions, 16-2, 16-3
MBIT, 16-14
Memory Map, 2-6

INDEX (Continued)

Memory Size, 4-4
Memory Protect, 10-2, 10-3
Minimize Scan, Hints, 13-11
Miscompares, 20-2
MODBUS, 24-1
MODBUS Port Parameters, 5-9
Model Numbers, 4-5 to 4-12
 584A, 4-5, 4-10, 4-12
 584L, 4-7, 4-11
 584L (XMEM), 4-8, 4-11
 584M, 4-6, 4-11
Motor Starter, 2-2
Multiply (MUL), 14-25

N

Network, 13-1
Network Structure, 13-1
Number Systems, 1-5
Numeric Keyboard, 10-2, 10-12

O

OR, 16-8
Output (Holding) Register, 2-4

P

P190 Features, 10-1, 10-2
P190 Keyboard, 10-2, 10-11, 10-12
P190 Port Settings, 10-4
P190 Programmer, 3-5, 10-1
P190 Tapes, 10-13 to 10-17
P421, 6-5
P451, 6-8, 6-9, 7-30
P451 Addressing, 7-16, 7-17
P452, 6-5
P453, 6-10, 7-31
P453 Model Numbers, 6-11 to 6-16
Parity, 1-3
PC Block Diagram, 2-2, 2-3
PC Board/Model Number Chart, 4-9
 to 4-11
PC Definition, 2-2
Percentage of Sweep Time, 5-19
Phone Line Communications, 10-8

PID (Proportional-Integral-Derivative), 19-1
 Configuration, 19-9, to 19-11
 Derivative Control Action, 19-7
 Integral Control Action, 19-5, 19-6
 Offset, 19-5
 Formula, 19-8
 Function Block, 19-13 to 19-20
 Menu, 19-12
 Proportional Band, 19-3
 Proportional Control, 19-3, 19-4
 Reset, 19-5
 Tuning Guidelines, 19-21
 Typical Analog Loop, 19-1
 Typical Process Loop Diagram, 19-2

Pointer, 15-3
Ports, 5-12 to 5-14, 11-2
Power Loss, 13-7
Power Supply, 2-4
Print, 10-11
Programmer, 2-4
Programmer Tape, 14-1
Programming, 14-1
Programming at a Remote Location,
 10-6, 10-8
Programming Worksheet, 14-42
Proportional-Integral-Derivative, 19-1
Proportional Control, 19-1

R

RAM (See Random Access Memory)
Random Access Memory, 2-6 to 2-8
RAP (Register Access Panel), 4-1, 5-2
Read, 18-27
Redundancy, 23-1
Reference Numbers, 2-4, 2-5
Reference Area, 14-4
Registers, 5-1
Register Access Panel (RAP), 4-1, 5-2
 ASCII Information, 5-15 to 5-17
 Configuration, 5-12 to 5-14
 Disable Feature, 5-5, 5-6
 Forcing I/O, 5-5
 General Capabilities, 5-3
 Keypad Error Codes, 5-8
 Operation, 5-4, 5-5

INDEX (Continued)

Relay Logic, 14-3, 14-6 to 14-8
Relocate Logic Procedure, 20-2
Remote I/O, 6-6 to 6-18, 7-1
Remote I/O Cabling, 6-17, 6-18, 7-1
Remote I/O Configurations, 6-6
Remote I/O Media, 7-1
Reset Level, 14-43
Retrace, 10-11
Revision Levels, 4-4
RS-232C, 1-2
R→T, 15-4
RTU, 1-3
Run Light, 4-1

S

Safe84, 5-7
Scan, 13-2 to 13-4, 13-11
Scratch Pad Memory, 2-2
Screen, 2-4, 10-1
Seal Circuit, 2-2
Search, 10-11, 14-40
Search Function, 15-16, 15-17
Segmentation 12-12, 12-15, 13-6
SENS, 16-16
Segmentation Numbers, 4-4
Skip, 14-30
Slot Addressing, 9-1
Splitter, 7-4
Start 584, 14-2, 18-6, 21-3
Start Bit, 1-4
Start Up, 11-1 to 11-3, 13-8
Start/Stop Circuit, 2-2
State RAM, 2-6 to 2-8
Status, 22-5
Status Line, 14-4
Stop 584, 14-2, 18-6, 21-3
Stop Bit, 1-4
Subtraction (Sub), 14-23
System Status Words, 5-18

T

Table, Definition, 15-2
Tap, 7-3, 7-4

Tap, 7-3, 7-4
Tape Loader, 20-1
 Dump Procedure, 20-1
 Error Messages, 20-3 to 20-6
 Information Messages, 20-3 to 20-6
 Load Procedure, 20-1
 Menu — Exit Level, 20-7
 Menu — Reset Level, 20-8
 Tape, 20-1
Tape Duplication, 10-14
Tape Insertion & Removal, 10-16
Tape Labeling, 10-14
Tape Storage and Shipment, 10-17
Tapes, 10-13
Timers, 14-2, 14-3, 14-15, 14-16
T→R, 15-6
T→T, 15-8
Trace, 10-11
Traffic Cop, 12-9
Trouble Shooting, 22-1

U

UCTR, 14-15, 14-18, 14-19
Up Counter, 14-15, 14-18, 14-19
User Memory, 2-2
User Logic Tapes, 10-13
Utility Tape (Ladder Lister), 21-1

V

Verify Procedure, 20-2

W

W190, 10-5 to 10-8
W191, 10-5 to 10-8
W192, 10-5 to 10-8
W193, 10-5 to 10-8
W194, 10-5 to 10-8
Word, 1-1
Writ, 18-24

X

XMRD, 17-6 to 17-8
XMWT, 17-3 to 17-5
XOR, 16-10, 16-11