

GOULD

Modicon Division

**184/384
MANUAL**

382A

382B - DX ^{ASCII} ~~to~~ added functionality

Copyright 1981 Gould Inc., Modicon Division
All Rights Reserved

No part of this document may be reproduced in any
form without the expressed written permission of
Gould Inc., Modicon Division

CONTENTS

	Page
PREFACE	1
WARRANTIES	2
I. INTRODUCTION	3
General	3
Processor	5
Power Supply	6
Input/Output Section	6
Programming Panel	8
CRT Programming Panel	9
II. CONFIGURATION	11
System Requirements	11
Hardware Configuration	16
System	16
Processor	16
Power Supplies	18
Input/Output	24
Maintenance Aids	28
III. BASIC CONTROL DESIGN	31
3.1 IMPORTANT MACHINE CONCEPTS	31
3.1.1 Controller Reference Numbers	31
3.1.2 The MODICON Ladder Line	33
3.1.3 Scan	36
3.1.4 Memory Protect	36
3.1.5 Disable/Enable	37
3.2 BASIC PROGRAMMING	38
3.2.1 Relays	38
Example Relay Logic	39
Extended Logic	40
Latches	41
Redundant Contacts	43
Watchdog Timer Line	43
Processor Fault Indications	44
Null Data	44
One-Shots	45
First Scan Indicator	46
Entering a Relay with the P112 Programming Panel	46

CONTENTS (Continued)

	Page
Programming Example (Memory Protect OFF)	46
EXAMPLE I – Shift Register	47
3.2.2 Timers	50
Specifying Time	50
Storing Time	51
ON-Delay Energizing Timer	52
ON-Delay De-Energizing Timer	53
OFF-Delay Energizing Timer	54
OFF-Delay De-Energizing Timer	54
Accumulator Timer	55
Self-Resetting Timers (Oscillators)	55
3.2.3 Counters	56
Cascaded Counters	56
Entering a Timer or a Counter Line	57
Example of a Timer Line 53	57
Example of a Counter Line	58
EXAMPLE II – Scan Time Evaluator	58
Summary	59
3.3 ADVANCED CONCEPTS	60
3.3.1 Registers	60
3.3.2 184 Executive Program (MOPS)	61
3.3.3 Additional Programming Panel Features	64
3.4 REMOTE SET AND CALCULATE CAPABILITY	65
3.4.1 Remote Set Timers and Counters	65
Example of a Remote Set Timer	67
Example of a Remote Set Counter	67
3.4.2 Addition (B + C) and Subtraction (B – C)	68
Coil Activation	69
Set Points (Compare)	69
Register-to-Register Move	70
Clearing a Register to Zero	70
Double-Precision Add	70
Detecting Equality with B + C Overflow	
Coil Option	71
Detecting Overflow with B + C Equal	
Coil Option	72
Entering a Calculate Line	72
Entry of a B + C Calculate	73
EXAMPLE III – Time-Shared Display	75
3.5 DATA TRANSFER	75
3.5.1 Move (Group 1YXX)	76

CONTENTS (Continued)

	Page
10XX — Table-to-Register Move (Incremental)	81
11XX — Table-to-Register Move (Continuous)	82
12XX — Register-to-Table Move (Incremental)	82
13XX — Register-to-Table Move (Continuous)	83
14XX — Table-to-Table Move (Incremental)	83
17XX — Table-to-Table Move (Continuous)	85
15XX — First In, First Out (FIFO) Load	85
16XX — First In, First Out (FIFO) Remove	86
EXAMPLE IV — Operator Monitor and Change of Registers	87
3.5.2 Matrix Handling (Group 2YXX)	88
20XX — Logical AND of Two Matrices	90
21XX — Logical OR (Inclusive) of Two Matrices	92
22XX — Matrix Compare of Two Matrices ...	92
23XX — Clear Bit or Sense Bit	94
24XX — Sense Bit or Set Bit	96
25XX — Matrix Complement	96
26XX — Logical Exclusive OR of Two Matrices	97
27XX — Rotate Left	98
28XX — Rotate Right	99
Additional 30XX References	99
EXAMPLE V — Monitoring of Discrete Inputs Versus Outputs	100
EXAMPLE VI — Matrix Retentive Shift Register	102
3.5.3 Extended Arithmetic (Group 3YXX)	103
3000 — General Multiply	103
3100 — General Divide	104
32XX — Fixed Multiply	105
33XX — Fixed Divide	105
3400 — PID (Proportional, Integral, Derivative) Control	105
Programming PID Control	106
Output Table (6 Registers)	107

CONTENTS (Continued)

	Page
Additional Application Notes	107
3.5.4 Entering a Data Transfer Line	107
3.6 P500 PRINTER/D285 DISPLAY UNIT	108
3.6.1 Introduction	108
3.6.2 Formatting Messages	111
3.6.3 Programming DX Lines	116
40PL — Print Numerical Data	117
41XX — Print Specified Stored Message	117
4200 — Print Variable Stored Message	119
3.6.4 Connecting Printer to 184/384 Controller	119
3.6.5 D285 Connections and Programming	121
3.6.6 Programming Busy, Form Busy, and Abort Inputs	123
3.7 IMPROVED DATA TRANSFER CAPABILITIES	125
3.7.1 Privileged Registers (5XXX references)	126
18XX — 4XXX/30XX to 5XXX Move (Block)	127
19XX — 5XXX to 4XXX Move (Block)	128
3.7.2 Matrix Sequencer Move	128
29XX — Matrix Sequencer Move	129
3.7.3 Improved PID	130
35XX — PID (Minutes)	130
3.7.4 Sort	131
36XX — SORT (Ascending order)	131
37XX — SORT (Descending Order)	132
3.7.5 Guarded Lines	132
3.7.6 Input/Output Communication Status	133
3.8 ASCII I/O Communications (384B)	134
3.8.1 Introduction to ASCII Communications	134
3.8.2 Programming DX ASCII Functions	136
43XX — ASCII Output	136
44XX — ASCII Input	138
45LF — ASCII Numerical Output	139
46XX — ASCII Numerical Input	141
Delimiters	142
IV. INTERNAL PRINCIPLES AND AUXILIARY EQUIPMENT	143
4.1 THEORY OF OPERATION	143

CONTENTS (Continued)

	Page
4.1.1 Introduction	143
4.1.2 Scan	143
4.1.3 Data Base	145
Data Base Description	145
Data Base Formats	146
Discrete References	147
Section 1	147
Section 2	148
Section 3	148
Register References	148
Word Formats	150
4.1.4 I/O Allocation Table	150
Table Description	150
Word Format	157
Discrete Data Addresses	157
Register Data Addresses	157
Modifications to I/O Allocation Table	158
4.1.5 Power-Up/Power-Down Sequence	159
4.2 SERVICE CENTER	160
4.2.1 Services	160
4.2.2 Ladder Diagram Documentation	162
4.2.3 System Maintenance Support	163
4.3 COMMUNICATIONS WITH A COMPUTER	165
Introduction	165
RS-232C Details of Operation	165
Communications	168
TO Mode	168
FROM Mode	169
Controller Response	170
Options	170
System Design Recommendations	171
V. INSTALLATION	173
Specifications	173
Installation Procedure	173
Mounting and Check-Out Procedures	175
First Power-Up	175
Mounting Procedure	179
Input/Output Connections	181
Channel Cabling	181
Module Addressing	183
Additional Channel Cabling	184

CONTENTS (Continued)

	Page
I/O Housing and Module Wiring	184
Inductive Loads	185
Setup and Run Switch	190
Connecting Output to Input Circuits	190
VI. TROUBLESHOOTING	193
Introduction	193
System Assembly and Cabling	193
Indicator Lights	193
Power Supply	194
Processor	194
Input/Output Housings & Modules	195
Common Faults	197
Auxiliary Units	198
APPENDIX A AUXILIARY UNITS	A-1
APPENDIX B I/O MODULES	B-1
APPENDIX C NUMBER THEORY	C-1
APPENDIX D GLOSSARY OF TERMS	D-1
APPENDIX E ESTIMATING SYSTEM REQUIREMENTS	E-1
APPENDIX F SUMMARY OF MODEL DIFFERENCES 384 CONTROLLER COMPARED TO 184 CONTROLLER	F-1

ILLUSTRATIONS

Figure	Page
1. Typical Industrial Control System, Block Diagram	4
2. Typical Relay and Solid State Electronics Installations for Industrial Control	4
3. MODICON 184/384 Programmable Controller	5
4. Basic System Configuraton	6
5. Programming Panel	7
6. Typical I/O Module	11
7. Expanded 184/384 System	13
8. Auxiliary Power Supply and Remote Interface	14
9. Typical Mounting Plan	17
10. Processor, Showing Cable Connections	19
11. Main Power Supply (Model P420)	20
12. Connections to Main Power Supply	22
13. Model 184/384 Controller Typical Power Connections .	22
14. Auxiliary Power Supply (Model P421)	23
15. Connections to Auxiliary Power Supply	24
16. I/O Housing, Showing Module Address Selection	24
17. I/O Housing Overview, Showing Module Index Pins	25
18. I/O Housing, Showing Conduit and Terminals for Wiring	26
19. I/O Housing, Showing Relationship Between Terminals and I/O Module Terminal Identification Strip	27
20. MODICON 184/384 System Block Diagram	29
21. Location of Fuses on B244 and B246 Isolated Output Modules	30
22. Block Diagram, Operation of I/O with Core Memory	33
23. General Four Element Line Format	33
24. Typical MODICON Ladder Line	34
25. MODICON 184/384 Controller Programming Panel	35
26. Sample Relay Logic	39
27. Sample Relay Program	39
28. Definition of Output and Internal Logic Lines	40
29. Sample Extended Relay Logic	41
30. Sample Extended Relay Program	41
31. Sample Latch Program	42
32. Latch Timing Diagram	42
33. Sample Redundant Contacts	43
34. Sample Watchdog Timer Line	43
35. Sample Fault Indicator	44
36. Null Data	44
37. Typical One-Shots	45
38. Sample First Scan Indicator	46
39. Relay Line Example	47
40. Example: Shift Register	48
41. Timing Diagram for Shift Register	49
42. Typical Timer Line	50
43. User Area of Core Memory	51

ILLUSTRATIONS (Continued)

Figure		Page
44.	Example: Timing Line	52
45.	ON-Delay Energizing Timer	53
46.	ON-Delay De-Energizing Timer	53
47.	OFF-Delay Energizing Timer	54
48.	OFF-Delay De-Energizing Timer	54
49.	Accumulator Timer	55
50.	Self-Resetting Timer	55
51.	Cascaded Counters	56
52.	Timer Line	57
53.	Counter Line	58
54.	Example: Scan Time Evaluator	59
55.	Wiring of Input/Output Registers	62
56.	Block Diagram of Core Memory	63
57.	Core Memory Allocation	64
58.	Typical Remote Set	66
59.	Remote Set Timer Line	67
60.	Remote Set Counter Line	67
61.	Typical Arithmetic Line	68
62.	Sample Set Points	69
63.	Sample Register to Register Move	70
64.	Sample Clearing of a Register	70
65.	Sample Double-Precision Add	71
66.	Sample Detection of Equality with B+C Overflow Coil Option	71
67.	Sample Detection of Overflow with B+C Equal Coil Option	72
68.	Calculate B+C Line	73
69.	Example of Time Shared Display	74
70.	Typical DX Line	76
71.	Sample Table to Register Move	82
72.	Sample Register to Table Move	83
73.	Sample Table to Table Move	84
74.	Sample FIFO Stack	86
75.	Example: Operator Monitor and Change of Registers	87
76.	Typical Matrix Bit Numbering	89
77.	Programming Panel Display of Binary Data	91
78.	Sample Matrix AND and OR	92
79.	Sample Matrix Compare	94
80.	Sample Matrix Clear Line	95
81.	Sample Matrix Complement	96
82.	Sample Matrix Exclusive OR	97
83.	Sample Matrix Rotate Left	98
84.	Example: Monitoring of Discretes	101
85.	Example: Matrix Shift Register	102
86.	Sample Multiply	104
87.	Sample Divide	104

ILLUSTRATIONS (Continued)

Figure		Page
88.	Sample PID Logic Line	106
89.	Data Transfer (Move) Line	108
90.	Programmable Printer	109
91.	Sample Printout	109
92.	Sample P500 PROM Specification	112
93.	Blanks for Specifying P500 PROM Messages	113
94.	Sample Fixed Format Print	118
95.	Sample PROM Format Print	119
96.	Typical Printer Control Lines using Discrete Inputs	124
97.	Typical Printer Control Lines using Matrix Register Inputs	125
98.	Typical Printer Control Lines using Register Inputs	126
99.	Typical Printer Control Lines with Multiple Printers	127
100.	Sample 4XXX to 5XXX Move	128
101.	Sample 5XXX to 4XXX Move	129
102.	Example: Matrix Sequencer Move	130
103.	Example: Sort	132
104.	Example: I/O Monitoring	134
105.	ASCII I/O	137
106.	ASCII Numerical I/O	140
107.	General Format of Logic Lines Data Base	146
108.	RAM Definition	147
109.	Definition of Register Table	149
110.	Relay Line Word Format	151
111.	Counter Line Word Format	152
112.	Timer Line Word Format	153
113.	Calculate Line Word Format	154
114.	Data Transfer Line Word Format	155
115.	Word Definition in I/O Allocation Table	156
116.	Block Diagram of I/O Transfers	156
117.	Word Format in I/O Allocation Table	158
118.	Telephone Interface	160
119.	Typical Ladder Diagram Printout	161
120.	Ladder Diagram with Mnemonics	162
121.	Form for Specifying Mnemonics	164
122.	Computer Interface	166
123.	Format of RS-232C Serial Transmission	167
124.	Format of Controller's 16-Bit Word Transmission	167
125.	Pin Assignments on 1646 Connector	171
126.	Typical Mounting Plan	174
127.	Main Power Supply AC Connections	176
128.	Cable Connection, Power Supply to Processor	176
129.	Power Supply Indicators	177
130.	Typical I/O Channel Cable Connector and Housing Receptacle	178
131.	Cable Connector, Showing Locking Cam	178
132.	Typical Mounted Basic System	180
133.	Mounted Housing, Showing Protective Tape	179

ILLUSTRATIONS (Continued)

Figure		Page
134.	Expanded System Configuration, Mounted	182
135.	Processor, Top View	183
136.	I/O Housing, Showing Module Address Selector	184
137.	Processor, Bottom View	185
138.	I/O Housing Overview, Showing Module Selection Switches	186
139.	Housing, Showing Channel and Terminals for Wiring	187
140.	Housing, Showing Relationship Between Terminals and I/O Module Signal Identification Strip	187
141a.	Model 184/384 Controller Typical Wiring	188
141b.	Model 184/384 Controller Typical Input Wiring	189
142.	Example of Poor Input Circuit Wiring	190
143.	Inductive Load in Parallel with B231 Input Point	191
144.	Protecting a B231 Input Print from a Parallel Inductive Load	191
145.	Inductive Load Operated by Both a B230 Outputs and a Set of Contacts	192
146.	Connection of B230 Output to B231 Input Point	192
147.	Location of Fuses on B244 & B246 Isolated Output Modules	196
A-1.	Typical Ladder Diagram	A-3
A-2.	Program Loader (Mounted).....	A-7
A-3.	Cartridge Insertion.....	A-8
A-4.	Hanger.....	A-9
A-5.	Program Loader Controls and Indicators.....	A-10
A-6.	1646-1, 2, 3, or 4 Connected to 184/384 Service Port .	A-15
A-7.	Remote Computer Communication through an 1642 or 1643	A-16
A-8.	Cable A	A-17
A-9.	Connectors Between 1646-1, 2, 3, and 4 And Data Set	A-19
A-10.	Auxiliary Power Supply	A-21
A-11.	Auxiliary Power Supply System Options	A-22
A-12.	1425 Remote Driver	A-23
A-13.	Wiring Details (1425 and 1430 Interface)	A-24
A-14.	Program Loader Model 206.....	A-25
A-15.	Controls and Indicators	A-26
A-16.	Model P140	A-30
A-17.	Model P145	A-30
A-18.	Multi-Node Format	A-31
A-19.	Multi-Node with Non-Relay	A-31
A-20.	Four Node Format	A-32
A-21.	D285 CRT Display Unit	A-35
A-22.	J540 Interface with 500 Series I/O	A-37
E-1.	MODICON 184/384 System Configuration	E-5
F-1.	384 Controller	F-2
F-2.	Core Memory Allocation	F-4
F-2a.	184 Controller	F-4
F-2b.	384 Controller	F-4
F-3.	384 Executive Numbering	F-6

TABLES

Table	Page
1. Basic MODICON 184/384 Controller Specifications	8
2. Processor to I/O Cable Options	12
3. Internal I/O Power Loads	15
4. Summary of Required AC Power	21
5. I/O Housing, Showing Relationship Between Terminals and I/O Module Terminal Identification Strip	27
6. Fuse Requirements	28
7. Typical I/O Configuration — 352 Discrete I/O	32
8. Error Codes	35
9. Model 184 Controller Executive Program	60
10. I/O Channels III & IV, Optional Register Assignments	63
11. Model 184 Controller Executive Program	66
12. Model 184 Controller Executive Programs	77
13. P112 Hexadecimal Symbols	90
14. Example Additional 30XX References (608 Lines, 256 Discrete Inputs)	100
15. P500 Printer Specifications	110
16. Standard Character Set	111
17. P500 Printer Data Format	118
18. Printer Output Register Connections	120
18A. D285 Connections Via W280 Cables	122
19. Line Assignments for Printer Control Functions	124
20. Sample Scan	144
21. Minimum Times for Single Character or Bit Transmis- sions	166
22. Starting Addresses vs. Address Sent	169
23. List of Replaceable Output Fuses	196
24. Printer Command Values	199
B-1. I/O Module Terminal Assignments	B-3
E-1. Output Modules	E-6
F-1. Typical 384 Tradeoffs with 30XX Additional References	F-5
F-2. Special Options	F-6
F-3. Available TEF04 Configurations	F-8
F-4. Available TEF08 Configurations	F-9
F-5. Available TEF10 Configurations	F-9