




1 CONTENTS




2 CONNECT BATTERY CARTRIDGE



3 OPERATING ENVIRONMENT



4 CONNECT EQUIPMENT / POWER




5 CHECK BUILDING WIRING FAULT INDICATOR

If the rear panel Building Wiring Fault (red) indicator is lit, a potential shock hazard exists due to one of the following conditions:


- Open or high resistance ground
- Hot or neutral polarity reversed
- Overloaded neutral circuit

Improper building wiring should be corrected by a qualified electrician. Do not use the Back-UPS until the condition that caused the fault is corrected.


Note: Improper building wiring will not prevent the Back-UPS from operating, but will limit its protection capability.



6 CONNECT MODEM/PHONE/FAX



7 CONNECT COAXIAL CABLES




8 SWITCH ON THE BACK-UPS

Note: Allow the Back-UPS to charge for a full sixteen (16) hours prior to using it.


Press the front panel Power ON/OFF switch and observe that the following events occur after pressing and releasing the switch:

- The green On Line indicator flashes.
- The yellow On Battery indicator lights while a Self-Test is being performed.
- When Self-Test has successfully completed, only the green On Line indicator will be lit.
- If the internal battery cartridge is not connected (shown in Step 2 above), the green On Line indicator and red Replace Battery indicators will light. The Back-UPS will also emit a chirping sound.



9 CONNECT TVSS GROUND


The Back-UPS features a Transient Voltage Surge Suppression (TVSS) Ground Screw for connecting the ground lead of additional surge suppression devices such as network and data line surge protectors.



1. Loosen the TVSS Ground Screw far enough to allow placement of the Ground Lug on the Grounding Wire to slip under the Ground Screw.
2. Tighten the Ground Screw on the Back-UPS.
3. Ensure the other end of the Ground Wire is connected to the Network or Data Line TVSS.

STATUS INDICATORS, ALARMS and CIRCUIT BREAKER

There are four status indicators (lights) on the front panel of the Back-UPS (On Line, On Battery, Overload, and Replace Battery).



- On Line (green)** - is lit whenever utility power is powering the Battery Backup outlets.
- On Battery (yellow)** - is lit whenever the battery of the Back-UPS is powering equipment connected to the Battery Backup Outlets.
- Four Beeps Every 30 Seconds** - this alarm is sounded whenever the Back-UPS is running On Battery. Consider saving work in progress.
- Continuous Beeping** - this alarm is sounded whenever a low battery condition is reached. Battery run-time is very low. Promptly save any work in progress and exit all open applications. Shutdown the operating system, computer and the Back-UPS.

Overload (red) - is lit whenever power demand has exceeded the capacity of the Back-UPS.

Continuous Tone - this alarm is sounded whenever the Battery Backup outlets are overloaded.

Replace Battery (red) - is lit whenever the battery is near the end of its useful life, or if the battery is not connected (see above). A battery that is near the end of its useful life has insufficient run-time and should be replaced.

Chirps for 1 Minute Every 5 Hours - this alarm is sounded whenever the battery has failed the automatic diagnostic test.

Circuit Breaker - the circuit breaker button located on the rear panel of the Back-UPS will stick out if an overload condition forces the Back-UPS to disconnect itself from utility power. If the button sticks out, disconnect non-essential equipment. Reset the circuit breaker by pushing the button inward.

TRANSFER VOLTAGE and SENSITIVITY ADJUSTMENT

In situations where the Back-UPS or connected equipment appears too sensitive to input voltage, it may be necessary to adjust the transfer voltage. This is a simple task requiring use of the front panel pushbutton. To adjust the transfer voltage, proceed as follows:

1. Plug the Back-UPS into the utility power source, but do not turn the unit on. The Back-UPS will be in Standby Mode (no indicators lit).
2. Press and hold the front panel ON/OFF pushbutton switch fully inward for 10 seconds until all LED indicators on the Back-UPS flash to acknowledge it has entered Programming Mode.
3. The Back-UPS indicates its current Sensitivity Setting, as described in the table below.

Indicators Flashing	Sensitivity Setting	Input Voltage Range (for utility operation)	Use When
1 (yellow)	Low	78 to 142 Vac	Input voltage is extremely low or high. Not recommended for computer loads.
2 (yellow, and red)	Medium (factory default)	88 to 139 Vac	Back-UPS frequently goes On Battery.
3 (yellow, red, and red)	High	88 to 136 Vac	Connected equipment is sensitive to voltage fluctuations.

4. To select the *Low Sensitivity* setting, press the pushbutton until the yellow indicator is flashing.
5. To select the *Medium Sensitivity* setting, press the pushbutton until the yellow and red indicators (second and third from the top) are flashing.
6. To select the *High Sensitivity* setting, press the pushbutton until yellow and both red indicators (bottom three) are flashing.
7. To exit without changing the Sensitivity Setting, press the pushbutton until the green indicator is flashing.
8. Once in Programming Mode, if the pushbutton is not pressed within five seconds, the Back-UPS will exit Programming Mode, and all indicators will be off (unlit).

ORDER REPLACEMENT BATTERY


The battery cartridge typically lasts 3-6 years, and less time if it is subjected to frequent outages or elevated temperatures. To replace a DL1000VNT battery, order part number **RBC5**. Please recycle spent batteries.



TROUBLESHOOTING

Problem	Possible Cause	Corrective Action
Back-UPS will not switch on.	Back-UPS is not connected to AC power source.	Ensure the Back-UPS is securely connected to an AC outlet.
	Back-UPS circuit breaker "tripped".	Disconnect non-essential equipment from the Back-UPS. Reset (push in) the rear panel circuit breaker. Switch on the Back-UPS and plug in devices one at a time. If the circuit breaker trips again, disconnect the device that caused the breaker to trip.
	Utility input voltage quality is out of range.	Consider adjusting the transfer voltage and sensitivity (see <i>Transfer Voltage and Sensitivity Adjustment</i>).
Back-UPS does not power essential equipment during an outage.	Equipment was plugged into a Surge Only outlet.	Unplug device from 'Surge Only' outlet, and move to a 'Battery Backup' outlet.
Back-UPS operates on battery although utility power exists.	Back-UPS's circuit breaker has tripped.	Disconnect non-essential devices from the Back-UPS. Reset (push in) the rear panel circuit breaker. Switch the Back-UPS on and plug the devices in one-at-a-time. If the circuit breaker trips again, disconnect the device that caused the breaker to trip.
	Utility input voltage quality is out of range.	Consider adjusting the transfer voltage and sensitivity, as described in the <i>Transfer Voltage and Sensitivity Adjustment</i> section.
Back-UPS does not provide expected backup time.	Back-UPS is heavily loaded.	Unplug non-essential equipment (printers, scanners, etc) from the Battery Backup outlets, and plug into 'Surge Only' outlets.
	Back-UPS battery cartridge is discharged due to recent power outage and has not had time to recharge.	Charge the battery cartridge for 16 hours. Back-UPS runtime is reduced until the battery cartridge is fully charged.
	Battery has reached the end of its life.	Refer to <i>Replace Battery Cartridge</i> ; Replace the battery cartridge.
Red Replace Battery indicator is flashing. Green, On Line indicator is on.	Internal battery cartridge is not connected.	Refer to <i>Connect Battery Cartridge</i> , and connect the battery cartridge.
Red Replace Battery indicator is on.	Battery has reached the end of its life.	Refer to <i>Replace Battery Cartridge</i> ; replace the battery cartridge.
Red Overload indicator is on or flashing.	Connected equipment is drawing more power than the Back-UPS can provide.	Move one or more equipment power plugs from Battery Backup outlets to Surge Only outlets.
Green On Line indicator is on and all other front panel LEDs are flashing.	Internal UPS fault.	Contact APC Technical Support (refer to <i>Contact Information</i>).

REPLACE BATTERY CARTRIDGE



SPECIFICATIONS

Item	DL1000VNT
On-line Input Voltage Range (default settings)	88 to 139 VAC
Automatic Voltage Regulation (AVR)	+12% (Boost Only)
On-line Frequency Range	57 to 63 Hz (Autosensing)
On-battery Waveshape	Stepped Sine Wave
Maximum Load	1000 VA - 600 W
Typical Recharge Time	16 Hours
Operating Temperature	32° to 104°F 0° to 40°C
Storage Temperature	23° to 113°F -5° to 45°C
Operating / Storage Relative Humidity	0 to 95% non-condensing
Size (H x W x D)	8.7 in x 5.1 in x 13.8 in 220 mm x 130 mm x 350 mm
Weight	22 lbs (10 kg)
Shipping Weight	23 lbs (11 kg)
EMI Classification	FCC / DOC Class B Certified
On Battery Run-Time	See http://www.apc.com/product
Notice: This device complies with parts 68 and 15 of the FCC rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference. (2) This device must accept any interference received, including interference that may cause undesired operation.	
On the bottom of this equipment is a label that contains, among other information, the FCC registration number and ringer equivalence number (REN) for this equipment. If requested, this information must be provided to the telephone company.	

LIMITED WARRANTY

The standard warranty is two (2) years from the date of purchase. APC's standard procedure is to replace the original unit with a factory reconditioned unit. Customers who must have the original unit back due to the assignment of asset tags and set depreciation schedules must declare such a need at first contact with an APC Technical Support representative. APC will ship the replacement unit once the defective unit has been received by the repair department, or cross-ship upon the receipt of a valid credit card number. The customer pays for shipping the unit to APC. APC pays ground freight transportation costs to ship the replacement unit to the customer.

SERVICE

If the Back-UPS arrived damaged, notify the carrier.

If the Back-UPS requires service, do not return it to the dealer. The following steps should be taken:

1. Consult the Troubleshooting section to eliminate common problems.
2. If the problem persists, go to <http://www.apc.com/support/>.
3. If the problem still persists, contact APC Technical Support.
 - Have the Back-UPS model number, serial number and date of purchase available. Be prepared to troubleshoot the problem with an APC Technical Support representative. If this is not successful, APC will issue a Return Merchandise Authorization (RMA) number and a shipping address.

CONTACT INFORMATION

Technical Support	http://www.apc.com/support
Internet	http://www.apc.com
USA / Canada	1.800.800.4272
Mexico	292.0253 / 292.0255
Brazil	0800.12.72.1
Worldwide	+1.401.789.5735