

# Easergy MiCOM P746

Numerical Busbar Protection Relay

P746/EN PC/L72

Software Version	B3/C3
Hardware Suffix	M
IEC61850	Edition 2

Protocol Implementation Conformance Statement (PICS)

**Note**

The technical manual for this device gives instructions for its installation, commissioning, and operation. However, the manual cannot cover all conceivable circumstances or include detailed information on all topics. In the event of questions or specific problems, do not take any action without proper authorization. Contact the appropriate Schneider Electric technical sales office and request the necessary information.

Any agreements, commitments, and legal relationships and any obligations on the part of Schneider Electric including settlements of warranties, result solely from the applicable purchase contract, which is not affected by the contents of the technical manual.

This device **MUST NOT** be modified. If any modification is made without the express permission of Schneider Electric, it will invalidate the warranty, and may render the product unsafe.

Easergy MiCOM and the Schneider Electric logo and any alternative version thereof are trademarks and service marks of Schneider Electric.

All trade names or trademarks mentioned herein whether registered or not, are the property of their owners.

This manual is provided for informational use only and is subject to change without notice.

© 2016, Schneider Electric. All rights reserved.

PROTOCOL IMPLEMENTATION  
CONFORMANCE STATEMENT  
(PICS)

Date (month/year):	10/2016
Products covered by this chapter:	This chapter covers the specific versions of the MiCOM products listed below. This includes <b>only</b> the following combinations of Software Version and Hardware Suffix.
Hardware suffix:	M
Software version:	B3/C3
IEC61850 Edition:	2
Connection diagrams:	This includes a list of the Connection Diagrams for the Products covered by this document. 10P746xx (xx = 00 to 21)

---

**CONTENTS**

---

	Page-
<b>1 Introduction</b>	<b>5</b>
<b>2 ACSI Basic Conformance Statement</b>	<b>6</b>
<b>3 ACSI Models Conformance Statement</b>	<b>7</b>
<b>4 ACSI Service Conformance Statement</b>	<b>9</b>

# *Notes:*

## 1 INTRODUCTION

This specification is the Protocol Implementation Conformance Statement (PICS) and shows the Abstract Communication Service Interface (ACSI) conformance statements as defined in Annex A of Part 7-2 of the IEC 61850 standard specifications. The following ACSI conformance statements used to provide an overview and details about Protocol Implementation Conformance Statement (PICS) with firmware **Error! Unknown document property name.**

- ACSI basic conformance statement,
- ACSI models conformance statement,
- ACSI service conformance statement

The statements specify the communication features mapped to IEC 61850-8-1.

**2 ACSI BASIC CONFORMANCE STATEMENT**

The basic conformance statement is defined in **Table 1**.

		Client /Subscriber	Server /Publisher	Value /Comments
Client-Server roles				
B11	Server side (of Two-Party- Application- Association)		Y	
B12	Client side of (Two-Party- Application- Association)			
SCSMs supported				
B21	SCSM: IEC 61850-8-1 used		Y	
B22	SCSM: IEC 61850-9-1 used			
B23	SCSM: IEC 61850-9-2 used			
B24	SCSM: other			
Generic Substation Event model (GSE)				
B31	Publisher side		Y	
B32	Subscriber side	Y		
Transmission of Sampled Value Model (SVC)				
B41	Publisher side			
B42	Subscriber side			
– Y = Yes (supported) N or empty = No (not supported)				

**Table 1 -Basic Conformance Statement**



**3 ACSI MODELS CONFORMANCE STATEMENT**

The ACSI models conformance statement is defined in Table 2.

		Client/ Subscriber	Server/ Publisher	Value/ Comments
If Server or Client side (B11/12) supported				
M1	Logical device		Y	
M2	Logical node		Y	
M3	Data		Y	
M4	Data set		Y	
M5	Substitution			
M6	Setting group control		Y	
Reporting				
M7	Buffered report control		Y	
M7-1	sequence-number		Y	
M7-2	report-time-stamp		Y	
M7-3	reason-for-inclusion		Y	
M7-4	data-set-name		Y	
M7-5	data-reference		Y	
M7-6	buffer-overflow		Y	
M7-7	entryID		Y	
M7-8	BufTim		Y	
M7-9	IntgPd		Y	
M7-10	GI		Y	
M7-11	conf-revision		Y	
M8	Unbuffered report control		Y	
M8-1	sequence-number		Y	
M8-2	report-time-stamp		Y	
M8-3	reason-for-inclusion		Y	
M8-4	data-set-name		Y	
M8-5	data-reference		Y	
M8-6	BufTim		Y	
M8-7	IntgPd		Y	
M8-8	GI		Y	
M8-9	conf-revision		Y	
Logging				
M9	Log control			
M9-1	IntgPd			
M10	Log			
Control				
M11	Control		Y	
If GSE (B31/32) is supported				
M12	GOOSE	Y	Y	
M13	GSSE			
If SVC (41/42) is supported				

		Client/ Subscriber	Server/ Publisher	Value/ Comments
M14	Multicast SVC			
M15	Unicast SVC			
If Server or Client side (B11/12) supported				
M16	Time	Y	Y	Time source with required accuracy shall be available.
M17	File Transfer		Y	
M18	Application association		Y	
M19	GOOSE Control Block	Y	Y	
M20	Sampled Value Control Block			
Y = service is supported N or empty = service is not supported				

**Table 2 – ACSI Models Conformance Statement**

## 4 ACSI SERVICE CONFORMANCE STATEMENT

The ACSI service conformance statement is defined in Table 3 (depending on the statements in **Table 1**).

	Services	AA:TP/MC	Client (C)	Server (S)	Comments
<b>Server</b>					
S1	GetServerDirectory	TP		Y	
<b>Application association</b>					
S2	Associate			Y	
S3	Abort			Y	
S4	Release			Y	
<b>Logical device</b>					
S5	GetLogicalDeviceDirectory	TP		Y	
<b>Logical node</b>					
S6	GetLogicalNodeDirectory	TP		Y	
S7	GetAllDataValues	TP		Y	
<b>Data</b>					
S8	GetDataValues	TP		Y	
S9	SetDataValues	TP		Y	
S10	GetDataDirectory	TP		Y	
S11	GetDataDefinition	TP		Y	
<b>Data set</b>					
S12	GetDataSetValues	TP		Y	
S13	SetDataSetValues	TP			
S14	CreateDataSet	TP			
S15	DeleteDataSet	TP			
S16	GetDataSetDirectory	TP		Y	
<b>Substitution</b>					
S17	SetDataValues	TP			
<b>Setting group control</b>					
S18	SelectActiveSG	TP		Y	
S19	SelectEditSG	TP			
S20	SetSGValues	TP			
S21	ConfirmEditSGValues	TP			
S22	GetSGValues	TP			
S23	GetSGCBValues	TP		Y	
<b>Reporting</b>					
<b>Buffered report control block (BRCB)</b>					
S24	Report	TP		Y	
S24-1	data-change (dchg)			Y	
S24-2	quality-change (qchg)			Y	
S24-3	data-update (dupd)				
S25	GetBRCBValues	TP		Y	
S26	SetBRCBValues	TP		Y	
<b>Unbuffered report control block (URCB)</b>					

	Services	AA:TP/MC	Client (C)	Server (S)	Comments
S27	Report	TP		Y	
S27-1	data-change (dchg)			Y	
S27-2	quality-change (qchg)			Y	
S27-3	data-update (dupd)				
S28	GetURCBValues	TP		Y	
S29	SetURCBValues	TP		Y	
<b>Logging</b>					
<b>Log control block</b>					
S30	GetLCBValues	TP			
S31	SetLCBValues	TP			
Log					
S32	QueryLogByTime	TP			
S33	QueryLogByEntry	TP			
S34	GetLogStatusValues	TP			
<b>Generic substation event model (GSE)</b>					
<b>GOOSE-CONTROL-BLOCK</b>					
S35	SendGOOSEMessage	MC		Y	IED supports GOOSE Publisher and Subscriber.
S36	GetGoReference	TP			
S37	GetGOOSEElementNumber	TP			
S38	GetGoCBValues	TP		Y	
S39	SetGoCBValues	TP		Y	
<b>GSSE-CONTROL-BLOCK</b>					
S40	SendGSSEMessage	MC			
S41	GetGsReference	TP			
S42	GetGSSEDataOffset	TP			
S43	GetGsCBValues	TP			
S44	SetGsCBValues	TP			
<b>Transmission of sampled value model (SVC)</b>					
<b>Multicast SVC</b>					
S45	SendMSVMessage	MC			
S46	GetMSVCBValues	TP			
S47	SetMSVCBValues	TP			
Unicast SVC					
S48	SendUSVMessage	TP			
S49	GetUSVCBValues	TP			
S50	SetUSVCBValues	TP			
<b>Control</b>					
S51	Select			Y	
S52	SelectWithValue	TP		Y	
S53	Cancel	TP		Y	
S54	Operate	TP		Y	
S55	Command-Termination	TP		Y	
S56	TimeActivated-Operate	TP			

	Services	AA:TP/MC	Client (C)	Server (S)	Comments
<b>File transfer</b>					
S57	GetFile	TP		Y	
S58	SetFile	TP			
S59	DeleteFile	TP		Y	Only from /COMTRADE/ operation may only be performed on .cfg files.
S60	GetFileAttributeValues	TP		Y	
S61	GetServerDirectory (FILE-SYSTEM)	TP		Y	
<b>Time</b>					
T1	Time resolution of internal clock		10	10	nearest negative power of 2 in seconds
T2	Time accuracy of internal clock				T0
			1ms	1ms	T1
					T2
					T3
					T4
					T5
T3	Supported TimeStamp resolution	-	10	10	nearest value of 2 <sup>**</sup> -n in seconds

**Table 3 – ACSI Service Conformance Statement**

AA: Application Association type

MC: Multicast (for GOOSE and SMV)

MMS: Manufacturing Message Specification

TP: Two part (for MMS)

# *Notes:*





## Customer Care Centre

<http://www.schneider-electric.com/cc>

### **Schneider Electric**

35 rue Joseph Monier  
92506 Rueil-Malmaison  
FRANCE

Phone: +33 (0) 1 41 29 70 00  
Fax: +33 (0) 1 41 29 71 00

[www.schneider-electric.com](http://www.schneider-electric.com)

Publisher: Schneider Electric

**Publication: Easergy MiCOM P746/EN PC/L72 Numerical Busbar Protection Relay Software Version: B3/C3 Hardware Suffix: M IEC61850 Edition: 2**

10/2016