

Easergy MiCOM P841

Multifunctional Line Terminal IED

P841/EN PC/Kc2 – Ed. 2

Software Version	L3/K3
Hardware Suffix	M
IEC61850 Edition	2
Issue Date	03/2021

Protocol Implementation Conformance Statement (PICS)

Note

The technical manual for this device gives instructions for its installation, commissioning, and operation. However, the manual cannot cover all conceivable circumstances or include detailed information on all topics. In the event of questions or specific problems, do not take any action without proper authorization. Contact the appropriate Schneider Electric technical sales office and request the necessary information.

Any agreements, commitments, and legal relationships and any obligations on the part of Schneider Electric including settlements of warranties, result solely from the applicable purchase contract, which is not affected by the contents of the technical manual.

This device **MUST NOT** be modified. If any modification is made without the express permission of Schneider Electric, it will invalidate the warranty, and may render the product unsafe.

Easergy MiCOM and the Schneider Electric logo and any alternative version thereof are trademarks and service marks of Schneider Electric.

All trade names or trademarks mentioned herein whether registered or not, are the property of their owners.

This manual is provided for informational use only and is subject to change without notice.

© 2021, Schneider Electric. All rights reserved.

**PROTOCOL IMPLEMENTATION
CONFORMANCE STATEMENT
(PICS)**

Date (month/year):	03/2021
Products covered by this chapter:	This chapter covers the specific versions of the MiCOM products listed below. This includes only the following combinations of Software Version and Hardware Suffix.
Hardware suffix:	M
Software version:	L3/K3
Connection diagrams:	This includes a list of the Connection Diagrams for the Products covered by this document. 10P84100 10P84101 (SH 1 to 2) 10P84102 (SH 1 to 2) 10P84103 (SH 1 to 2) 10P84104 (SH 1 to 2) 10P84105 (SH 1 to 2)

CONTENTS

	Page-
1 Introduction	5
2 ACSI Basic Conformance Statement	6
3 ACSI Models Conformance Statement	7
4 ACSI Service Conformance Statement	9

TABLES

	Page-
Table 1 - Basic Conformance Statement	6
Table 2 - ACSI Models Conformance Statement	8
Table 3 - ACSI Service Conformance Statement	11

Notes:

1 INTRODUCTION

The following ACSI conformance statements are used to provide an overview and details about MiCOM P841 with firmware L3/K3:

- ACSI basic conformance statement,
- ACSI models conformance statement,
- ACSI service conformance statement

The statements specify the communication features mapped to IEC 61850-8-1 and IEC 61850-9-2.

2 ACSI BASIC CONFORMANCE STATEMENT

The basic conformance statement is defined in Table 1:

		Client/ Subscriber	Server/ Publisher	Value/ Comments
Client-Server roles				
B11	Server side (of TWO-PARTY-APPLICATION-ASSOCIATION)		Y	
B12	Client side of (TWO-PARTY-APPLICATION-ASSOCIATION)			
SCSMs supported				
B21	SCSM : IEC 61850-8-1 used		Y	
B22	SCSM : IEC 61850-9-1 used			Deprecated Ed2
B23	SCSM : IEC 61850-9-2 used	Y		
B24	SCSM : other			
Generic substation event model (GSE)				
B31	Publisher side		Y	
B32	Subscriber side	Y		
Transmission of sampled value model (SVC)				
B41	Publisher side			
B42	Subscriber side	Y		
– = not applicable Y = supported N or empty = not supported				

Table 1 - Basic Conformance Statement

3 ACSI MODELS CONFORMANCE STATEMENT

The ACSI models conformance statement is defined in Table 2.

		Client/ Subscriber	Server/ Publisher	Value/ Comments
If Server side (B11) and/or Client side (B12) supported				
M1	Logical device		Y	c1
M2	Logical node		Y	c1
M3	Data		Y	c1
M4	Data set		Y	c2
M5	Substitution			
M6	Setting group control		Y	
	Reporting			
M7	Buffered report control		Y	
M7-1	sequence-number		Y	
M7-2	report-time-stamp		Y	
M7-3	reason-for-inclusion		Y	
M7-4	data-set-name		Y	
M7-5	data-reference		Y	
M7-6	buffer-overflow		Y	
M7-7	entryID		Y	
M7-8	BufTm		Y	
M7-9	IntgPd		Y	
M7-10	GI		Y	
M7-11	conf-revision		Y	
M8	Unbuffered report control		Y	
M8-1	sequence-number		Y	
M8-2	report-time-stamp		Y	
M8-3	reason-for-inclusion		Y	
M8-4	data-set-name		Y	
M8-5	data-reference		Y	
M8-6	BufTm		Y	
M8-7	IntgPd		Y	
M8-8	GI		Y	
M8-9	conf-revision		Y	
	Logging			
M9	Log control			
M9-1	IntgPd			
M10	Log			
M11	Control		Y	
M17	File Transfer		Y	
M18	Application association		Y	c1
M19	GOOSE Control Block	Y	Y	
M20	Sampled Value Control Block			
c1 Server must be Y if B11=Yes; Client must be Y if B12=Y				
c2 Server must be Y if M7=Y or M8=Y or M9=Y or M19=Y or M20=Y				

		Client/ Subscriber	Server/ Publisher	Value/ Comments
If GSE (B31/32) is supported				
M12	GOOSE	Y	Y	
M13	GSSE			Deprecated Ed2
If SVC (B41/42) is supported				
M14	Multicast SVC	Y		
M15	Unicast SVC			
For all IEDs				
M16	Time	Y	Y	Time source with required accuracy shall be available. Only Time Master are SNTP (Mode 4 response) time server. All other Client / Server devices require SNTP (Mode 3 request) clients
Y = service is supported N or empty = service is not supported				

Table 2 - ACSI Models Conformance Statement

4 ACSI SERVICE CONFORMANCE STATEMENT

The ACSI service conformance statement is defined in Table 3 (depending on the statements in Table 1).

	Ed.	Services	AA: TP/MC	Client (C)	Server (S)	Comments
Server: if B11=Y or B12=Y						
S1	1,2	GetServerDirectory (LOGICAL-DEVICE)	TP		Y	S must be Y if B11=Yes
Application association: if B11=Y or B12=Y						
S2	1,2	Associate			Y	S must be Y if B11=Yes
S3	1,2	Abort			Y	C must support S3 if S4=N
S4	1,2	Release			Y	C must support S4 if S3=N
Logical device: if M1=Y						
S5	1,2	GetLogicalDeviceDirectory	TP		Y	S must be Y if B11=Yes
Logical node: if M2=Y						
S6	1,2	GetLogicalNodeDirectory	TP		Y	S must be Y if B11=Yes
S7	1,2	GetAllDataValues	TP		Y	
Data: if M3=Y						
S8	1,2	GetDataValues	TP		Y	
S9	1,2	SetDataValues	TP		Y	
S10	1,2	GetDataDirectory	TP		Y	
S11	1,2	GetDataDefinition	TP		Y	
Data set: if M4=Y						
S12	1,2	GetDataSetValues	TP		Y	
S13	1,2	SetDataSetValues	TP			Deprecated in Ed2
S14	1,2	CreateDataSet	TP			
S15	1,2	DeleteDataSet	TP			
S16	1,2	GetDataSetDirectory	TP		Y	
Substitution: if M5=Y						
S17	1,2	SetDataValues	TP			
Setting group control: if M6=Y						
S18	1,2	SelectActiveSG	TP		Y	
S19	1,2	SelectEditSG	TP			
S20	1,2	SetEditSGValues	TP			
S21	1,2	ConfirmEditSGValues	TP			
S22	1,2	GetEditSGValues	TP			
S23	1,2	GetSGCBValues	TP		Y	
Reporting: If M7=Y or M8=Y						
Buffered report control block (BRCB); If M7=Y						

	Ed.	Services	AA: TP/MC	Client (C)	Server (S)	Comments
S24	1,2	Report	TP		Y	
S24-1	1,2	data-change (dchg)			Y	
S24-2	1,2	quality-change (qchg)			Y	
S24-3	1,2	data-update (dupd)				
S25	1,2	GetBRCBValues	TP		Y	
S26	1,2	SetBRCBValues	TP		Y	
Unbuffered report control block (URCB) If M8=Y						
S27	1,2	Report	TP		Y	
S27-1	1,2	data-change (dchg)			Y	
S27-2	1,2	quality-change (qchg)			Y	
S27-3	1,2	data-update (dupd)				
S28	1,2	GetURCBValues	TP		Y	
S29	1,2	SetURCBValues	TP		Y	
Logging: If M9=Y or M10=Y						
Log control block; If M9=Y						
S30	1,2	GetLCBValues	TP			
S31	1,2	SetLCBValues	TP			
Log; If M10=Y						
S32	1,2	QueryLogByTime	TP			
S33	1,2	QueryLogAfter	TP			
S34	1,2	GetLogStatusValues	TP			
Generic substation event model (GSE): If M19=Y						
GOOSE						
S35	1,2	SendGOOSEMessage	MC		Y	
GOOSE-CONTROL-BLOCK						
S36	1,2	GetGoReference	TP			
S37	1,2	GetGOOSEElementNumber	TP			
S38	1,2	GetGoCBValues	TP		Y	
S39	1,2	SetGoCBValues	TP		Y	
GSSE						
S40	1	SendGSSEMessage	MC			Deprecated in Edition 2
GSSE-CONTROL-BLOCK						
S41	1	GetReference	TP			Deprecated in Edition 2
S42	1	GetGSSEElementNumber	TP			Deprecated in Edition 2
S43	1	GetGsCBValues	TP			Deprecated in Edition 2
S44	1	SetGsCBValues	TP			Deprecated in Edition 2
Transmission of sampled value model (SVC): If M20=Y						
Multicast SV						
S45	1,2	SendMSVMessage	MC			
Multicast Sampled Value Control Block						
S46	1,2	GetMSVCBValues	TP			
S47	1,2	SetMSVCBValues	TP			
Unicast SV						

	Ed.	Services	AA: TP/MC	Client (C)	Server (S)	Comments
S48	1,2	SendUSVMessage	TP			
Unicast Sampled Value Control Block						
S49	1,2	GetUSVCBValues	TP			
S50	1,2	SetUSVCBValues	TP			
Control: If M11=Y						
S51	1,2	Select			Y	
S52	1,2	SelectWithValue	TP		Y	
S53	1,2	Cancel	TP		Y	
S54	1,2	Operate	TP		Y	
S55	1,2	CommandTermination	TP		Y	
S56	1,2	TimeActivatedOperate	TP			
File transfer: If M17=Y						
S57	1,2	GetFile	TP		Y	
S58	1,2	SetFile	TP			
S59	1,2	DeleteFile	TP		Y	
S60	1,2	GetFileAttributeValues	TP		Y	
S61	1,2	GetServerDirectory (FILE-SYSTEM)	TP		Y	
Time						
T1	1,2	Time resolution of internal clock		10	10	Nearest negative power of 2 ⁿ in seconds (number 0 .. 24)
T2	1,2	Time accuracy of internal clock		T1	T1	TL (ms) (low accuracy), T3 < 7) (c1) T0 (ms) (<= 10 ms), 7 <= T3 < 10 (c1) T1 (µs) (<= 1 ms), 10 <= T3 < 13 T2 (µs) (<= 100 µS), 13 <= T3 < 15 T3 (µs) (<= 25 µS), 15 <= T3 < 18 T4 (µs) (<= 4 µS), 18 <= T3 < 20 T5 (µs) (<= 1 µS), 20 <= T3 < 25
T3	1,2	Supported TimeStamp resolution	-	10	10	Nearest value of 2 ⁿ in seconds (number 0 .. 24)
c1 TL may only be specified for Ed2. If Ed1 has accuracy which is better than 1 second but is not T1 then declare T0.						

Table 3 - ACSI Service Conformance Statement

AA: Application Association type
 MC: Multicast (for GOOSE and SMV)
 MMS: Manufacturing Message Specification
 TP: Two part (for MMS)



Customer Care Centre

<http://www.schneider-electric.com/cc>

Schneider Electric

35 rue Joseph Monier
92506 Rueil-Malmaison
FRANCE

Phone: +33 (0) 1 41 29 70 00
Fax: +33 (0) 1 41 29 71 00

www.schneider-electric.com

Publisher: Schneider Electric

Publication: Easergy MiCOM P841/EN PC/Kc2 Multifunctional Line Terminal IED Software Version: L3/K3 Hardware Suffix: M IEC61850 Edition: 2

03/2021