Catalog | January 2024



Modicon M171/M172/M173

Logic controllers for HVAC and Pumping applications





Discover **Modicon**

Edge control for Industrial IoT

Modicon IIoT-native edge controllers manage complex interfaces across assets and devices or directly into the cloud, with embedded functional safety and cybersecurity. Modicon provides performance and scalability for a wide range of industrial applications up to high-performance multi-axis machines and high-available redundant processes.

Explore our offer

- Modicon HVAC Controllers
- Modicon PLC
- Modicon Motion Controllers
- Modicon PAC
- Modicon I/O
- Modicon Networking
- Modicon Power Supply
- Modicon Wiring
- Modicon Safety




Quick access to product information

Get technical information about your product



Each commercial reference presented in a catalog contains a hyperlink. Click on it to obtain the technical information of the product:

- Characteristics, Dimensions and drawings, Mounting and clearance,
 Connections and schemas, Performance curves
- Product image, Instruction sheet, User guide, Product certifications, End of life manual



Find your catalog



- > With just 3 clicks, you can access the Industrial Automation and Control catalogs, in both English and French
- > Consult digital automation catalogs at Digi-Cat Online



- Up-to-date catalogs
- Embedded product selectors,360° pictures
- Optimized search by commercial references

Select your training



- > Find the right <u>Training</u> for your needs on our Global website
- > Locate the training center with the selector tool, using this link





General content

Modicon M171/M172/M173


Logic controllers for HVAC and Pumping applications

	introduction to Ecostruxure machine HVAC	2
	General overview	
	- Maximize business and machine Performance	4
	- Flexible	5
	- Efficient	
	- Connected, Cybersecurity	
	- Modicon M171/M172/M173 range	
	- System components	
	- Configuration software	
	- Ethernet connection	
	- Architectures	12 & 13
G	eneral selection: logic controllers	14 & 15
	Modicon M173 Optimized logic controllers	
	Selection guide: controllers and remote displays	. 16 & 17
	- Presentation, Description	18
	- References	19
	Modicon M172 logic controllers	
	Selection guide: controllers and remote displays	. 20 & 21
	Controllers	
	- Presentation	22
	- Description	
	- References	
	I/O Expansion modules	
	- Presentation, Description	
	- References	<mark>27</mark>
	Remote displays	
	- Presentation, Description	
	- References	29
	Modicon M171 Optimized logic controllers	
	Selection guide of controllers and remote displays	. 30 & 31
	Controllers	
	- Presentation, Description	32
	- References	33
	I/O Expansion modules	
	- Presentation, Description, References	34
	Remote displays, Connection accessories	
	- Presentation, References	35
	Modicon M171 Performance logic controllers	
	Controllers	
	- Presentation, Description	
	- References	37
Ш	I/O Expansion modules - Presentation, Description	20
	- References	
	Secure Interfaces - Presentation, Description	40
	- References	
		41
	Communication modules	40
	- Presentation, Description	
	- References	43
	Electronic expansion valve drivers	
	- Presentation, Description	
	- References	45
	Measurement accessories: Temperature & Humidity control	46
	Compatibility with Variable speed drives and machines	47
_		
	EcoStruxure [™] Machine Expert – HVAC programming software - Presentation, Characteristics	ΛΩ
	- Product offer, References	
	Product reference index.	
	FIOUUCI IEIEIEIICE IIIUEX	50

Our solution for Smart HVAC Control Systems

EcoStruxure™ Machine, our open, interoperable, IoT-enabled system architecture, helps OEMs quickly build smarter cost-optimized HVAC control systems with onboard energy-efficiency solutions while reducing maintenance and improving reliability. EcoStruxure Machine encompasses key technologies for product technology and edge control on premises, using cloud technologies to provide analytics and digital services.





General presentation

Modicon M171/M172/M173

Logic controllers for HVAC and Pumping applications

Maximize business and machine performance with EcoStruxure[™] Machine


Maximize business and machine performance with EcoStruxure Machine To be competitive in today's digital era, machine builders must be innovative. Smart machines, those that are better connected, more flexible, more efficient, and safe, are enabling machine builders to innovate in ways never before possible.

- > EcoStruxure Machine, our open, interoperable, IoT-enabled system architecture helps you build smarter machines and equipment faster, making your business more efficient, profitable, and sustainable.
- > EcoStruxure Machine brings together key technologies for product connectivity and edge control on premises, and cloud technologies to provide analytics and digital services.
- > EcoStruxure Machine helps you bring more innovation and added value to your customers throughout the entire machine life cycle

Ready-to-use architectures and function blocks

- > Tested, Validated, and Documented Architectures (TVDAs) are just one of the ways we help to reduce design time.
- > Whether machines are simple or complex, Application Function Blocks (AFBs) make system design fast and easy.

Modicon M171/M172/M173 is part of EcoStruxure Machine



HVAC/Chiller/Modbus SL/Modicon M172 Performance logic controller

Solution breakdown

- Compact NSX circuit breaker
- iEM3000 energy meter
- TeSys Deca contactor
- Multi9 circuit breaker Modicon Power supply
- Multi9 circuit breaker
- Modicon M172 IIoT Secure Interface
- Modicon M172 performance logic controller
- Modicon M172 Electronic expansion valve driver module for single valve
- 10 Modicon M171 remote display
- 11 Harmony XALK Emergency stop push button
- 12 TeSys Deca magnetic circuit breaker
- 13 TeSys Deca contactor
- Altivar 212 variable speed drive, for 0.75 to 7**5** kW (1.0 to 100 hp) motors
- Modicon TM1S • humidity and temperature probes
- 16 Pressure transmitter
- 17 Electronic expansion valve
- 18 Harmony XB4, Harmony XB5 signaling units

Logic controllers for HVAC and Pumping applications Flexible

Flexible

Flexible and scalable Performance

Whether you specialize in chillers, Air Handling Units for commercial buildings, residential, industrial and Pumping applications, etc.

With Modicon M171/M172/M173 range, EcoStruxure™ Machine is well positioned. Multiple BMS (Building Management System) connectivity, embedded or as an option, and an embedded web server make remote control and remote access simple to implement, while a unique software environment supports the development of algorithms and functions that can be used on any platform.





M172 Performance and Optimized





M173 Optimized





Performance and connectivity

- > M173 and M171 Optimized: logic controllers for simple and compact machines, also available for flush mounting, they requires minimal installation time and offers tremendous versatility. M173 provide high level of field connectivity.
- M172 Performance and Optimized: logic controllers for any size of connectable or connected HVAC machine: manage small to large HVAC machines, and boosters for buildings, connectable to BMS or the cloud.



- Best-in-class versatility and compact size
- > Best-in-class Performance


Logic controllers for HVAC and Pumping applications Efficient

Efficient


Everything needed is embedded

The high degree of flexibility makes it very easy to install additional modules and still keep everything in just one configuration:

- > IIoT Edge unit (1)
- > Controllers
- > Remote displays
- > Expansion modules
- > Communication modules
- > Wide range of humidity and temperature probes



(1) IIoT: Industrial Internet of Things.



Intuitive automation with EcoStruxure Machine Expert - HVAC

- EcoStruxure Machine Expert HVAC is the universal programming software for machines automated by Modicon M171, M172 and M173 logic controllers
- Simplified navigation that requires only a few clicks delivers a more efficient engineering process
- > EcoStruxure Machine Expert HVAC simplifies each of the steps in machine design and commissioning

General presentation (continued)

Modicon M171/M172/M173

Logic controllers for HVAC and Pumping applications

Connected

Cybersecurity

Connected



- FTPs
 - HTTPs
 - SMTPs
 - SNMT
 - MQTT
 - Cybersecure VPN

Connected everywhere

> M172 Optimized and M172 Performance:

- Modbus RTU
- Modbus TCP
- BACnet MS/TP (B-AAC Profile certified BTL)
- BACnet /IP (B-AAC Profile certified BTL)
- ASCII support for GSM Modem
- CAN Expansion Bus
- LonWorks (FFT-10)
- Webserver, FTP Client/Server, Email, Proxy management, Allow list, SNTP

> M173 Optimized:

- Modbus RTU
- CAN Expansion Bus
- LAN Expansion Bus

> M171 Optimized:

- Modbus RTU
- LAN Expansion Bus

Customization and services

Our experts help you every step of the way, from perfecting machine design to on-site servicing of the finished machine

Global support, 24/7 hotline services, and replacement parts centers around the world enable you to deliver superior customer support and satisfaction

Fully customized solution and co-design with our Application Design Experts (ADE)

> Design an Optimized solution for your machine to create added value, with the help of our experienced ADEs

Turnkey control panel

- > Engineering expertise for codes and standards compliance
- > Custom engineering to provide the optimum solution and meet specific needs

Collaboration from design to commissioning

Recruited directly from the industries they serve, ADEs collaborate with you from design through to programming, as well as in the commissioning of turnkey installations

Expert support throughout your system's life cycle

 A dedicated team of Schneider Electric application design experts provides worldwide support for your HVAC solution

Cybersecurity fo HVAC systems

IIoT-enabled systems are exposed to other devices and networks, which potentialy increases the risk of cyberattacks and data privacy breaches.

HVAC machine builders need to implement mechanisms and cybersecurity best practices

- > Ensure data protection: Authentification Authorization Encryption
- > Prohibit unauthorized access: violations logging and notification
- Comply with evolving regulations: IEC 62443 standard for cybersecure control system components

Our cybersecurity solutions

- > Secure Development Life cycle process (SDL)
- > A framework for secure product design
- > Allows the controller to connect to secured netwoks

VPN (Virtual Private Network)

- > Enables secure connection to the cloud
- > Alternative to more complex and expensive gateway



Cybersecurity



Logic controllers for HVAC and Pumping applications Modicon M171/M172/M173 range

HVAC



Heat pump



Chiller



Air handling unit

Modicon M171/M172/M173 range

The range has been developed to manage digital and analog inputs and outputs for controling HVAC machines, Pumping applications, and to offer numerous possibilities for connection to different Building Management System communication networks

- The offer is made up of:
 - several types of controller depending on the requested performance and connectivity
 - a variety of communication modules to connect them to the BMS
 - Secure Interfaces (Plug and Use IIoT Gateway) to perform Cybersecure communications based on HTTPs and TLS
 - a choice of expansion modules to increase and adapt the number and type of I/O
 - monochrome and color displays
 - EcoStruxure Machine Expert HVAC, the dedicated software used to program, commission and debug applications
 - and a set of sensors.
- Applications
 - M173 logic controllers are suitable for:
 - Heat pumps (up to two circuits)
 - Process chillers
 - Pumping
 - Boilers/Heaters
 - and any small and compact machines
 - M171 and M172 logic controllers are suitable for:
 - Air/water-cooled chiller
 - Rooftop unit
 - Heat pump
 - Compressor rack
 - Ventilation unit
 - Precision air conditioner
 - Heat recovery unit
 - Air handling unit
 - Small chillers (up to two circuits)
 - Process chillers
- The offer is flexible and scalable, depending on the application requirements. Any existing controller can evolve later as all M171, M172, and M173 logic controllers are programmed with the same EcoStruxure Machine Expert - HVAC software
- M171 Optimized logic controllers: up to 44 I/O, when only Modbus SL is needed
- M173 Optimized logic controllers: from 22 I/O (stand alone) to 78 I/O (with expansion modules)
- M172 logic controllers: from 7 to 238 I/O (with expansion modules)

Logic controllers for HVAC and Pumping applications System components

Color touch screen display M173 Optimized logic controller

I/O expansion module

- Color touch screen display Secure Interface (Plug-in version) M172 Optimized logic controller
- I/O expansion module
- Electronic expansion valve driver



- Color touch screen display
- M172 Performance logic controller Electronic expansion valve driver



- Remote flush mounting display (1)
- Remote wall mounting display (1) LAN-RS485 Communication adaptor
- M171 Optimized logic controller
- I/O expansion module



EcoStruxure Machine Expert - HVAC programming software



System components

M171, M172 and M173 logic controllers are available with or without an embedded display, with or without SSR output depending on the base product.

- M171 and M172 logic controllers, are available in both an Optimized and Performance version
- M173 logic controllers are available in Optimized version
- M172 Performance controllers embed connectivity, and M172 Optimized controllers offer optional connectivity.
- I/O expansion modules are mixed digital and analog I/O types
- M173 Optimized logic controllers, see page 18 and TM172E●●R I/O expansion module, see page 26 and TM172DC ••• remote color touch screen displays, see page 28
- M172 Optimized and M172 Performance logic controllers, see page 22 and TM172E●●R I/O expansion module, see page 26 and TM172DC •• • remote color touch screen displays, see page 28
- M171 Optimized logic controllers, see page 32 and TM171EO●●R I/O expansion modules, see page 34 and TM171D •• ee remote displays, see page 35
- M171 Performance logic controllers, see page 36 and TM171EP●●R I/O expansion modules, see page 38
- TM172SI• Secure Interfaces, designed to establish secure internet connections with Plug-in and Gateway versions, see page 40
- TM171A • • communication modules (BMS fieldbus Interfaces) provide the M171 Performance, M172 Optimized, M172 Performance, and M173 Optimized logic controllers with a connection to:
 - BACnet MS/TP (B-AAC profile) or IP
 - Modbus SL (Serial Link)
 - Modbus TCP
 - LonWorks (FFT-10)
 - Profibus
 - CAN bus

See page 42


- TM172EVEV● •: electronic expansion valve drivers compatible with M172 and M173 Optimized logic controllers, and also with third party controllers and electronic expansion valves, see page 44
- TM171VEVM4: An autonomous expansion valve driver compatible with M171, M172, and M173 logic controllers, and also with third party controllers and electronic expansion valves, see page 44
- Specific measurement accessories **TM1S** • •: humidity and temperature probes, see page 46
- EcoStruxure Machine Expert HVAC programming software, and programming accessories, see page 48
- Adapted connection accessories: I/O connectors and cables, see page 35

(1) Remote display can also be used with M171 Optimized with embedded display.

Logic controllers for HVAC and Pumping applications
Configuration software

Machine Caper - HOIC

EcoStruxure Machine Expert - HVAC



5 languages compliant with IEC 61131-3

Configuration software

M171, M172 and M173 logic controllers are supported by an intuitive software package: EcoStruxure Machine Expert - HVAC, see page 48.

This software follows a simple drag-and-drop function block approach to configuration and is completed with a library of Application Function Blocks (AFBs) and logic functions.

EcoStruxure Machine Expert - HVAC uses five languages compliant with IEC 61131-3.

Examples:




Structured Text language (ST)




Function Block Diagram language (FBD)



Ladder Diagram language (LD)



Instruction List language (IL)




Sequential Function Chart language (SFC)

Available resources on logic controllers for IEC programming									
	Logic controller type								
	M173 Optimized	M172 Optimized and Performance	M171 Optimized	M171 Performance					
CPU	160 MHz	120 MHz, 32 MB RAM	14.7 MHz	72 MHz, 32 MB RAM					
Available memory for application	1.0 MB	1.0 MB	188 kB	1.0 MB					
Available memory for user Interface	– (Shared with application)	1.5 MB	-	1.5 MB					
Flash memory data	(External flash memory is not available to the user)	5 MB	_	126 MB					
RAM memory (automatic mapping)	378 kB	512 kB (256000 words)	2048 B (1024 words)	512 kB (256000 words)					
RAM memory (Modbus mapping)	10 kB (5000 words)	10 kB (5000 words)	1024 B (512 words)	10 kB (5000 words)					
Parameters	10 kB (5000 words)	_	_	_					
EEPROM variables	-	28 kB (14000 words)	1024 B (512 words)	28 kB (14000 words)					

Logic controllers for HVAC and Pumping applications

Ethernet connection



M172 Performance logic controllers linked to Ethernet via the embedded RJ45 ports

AVEVA IIOT

M172 Optimized, M173 Optimized, and M171 Performance logic controllers managed by **AVEVA** industrial software via the Secure Interface (IIoT gateway)

Ethernet connection

Ethernet access is:

- embedded in M172 Performance logic controllers
- optional with M173 Optimized, M171 Performance and M172 Optimized logic controllers by means of a communication module or Secure Interface (Ilot gateway)

Ethernet access enables several functions such as:

- HTTP Webserver (Webvisu)
- Remote access
- Download program
- Display program download
- Download, upload parameters
- Download firmware
- Debug
- File management
- Bridge: specific function allowing controllers connected in Modbus SL to the same controller to be programmed via Modbus
- FTP client/server

These services are not always available:

- the service can be enabled or disabled via the controller programming
- an allowlist is used to provide access (no allowlist defined by default)


Logic controllers for HVAC and Pumping applications

M173 Optimized logic controllers

M171 Optimized logic controllers


Logic controllers for simple and compact machines

M173 Optimized logic controllers



- TM172SIG Secure Interface, see page 40
- TM173O●●● logic controller, see page 16TM172E12R I/O expansion module 4 (12 I/O in 4 DIN), see page 26
- 3 Altivar 212 variable speed drive (1)
- TM1SH●● humidity sensor, see page 47
 - 5 TM1ST temperature sensor PT1000 or NTC, see page 46

M171 Optimized logic controllers




- TM1710FM22R Optimized logic controller flush mounting, see page 33
- TM171EO I/O expansion module, see page 38
- TM171DLED remote display, see page 35

- TM171DWAL●● remote wall mounting display, see page 35
- Altivar 212 variable speed drive (1)
- TM1SH●● humidity sensor, see page 47
- TM1ST●● temperature sensor PT1000 or NTC, see page 46

⁽¹⁾ Consult this offer on our website.

Logic controllers for HVAC and Pumping applications M172 logic controllers



- 1 TM172DCLF● flush mounting display, see page 28
- 2 spaceLYnk gateway (1)
- 3 Harmony STO/STU HMI (1)
- 4 TM172SIG Secure Interface see page 40
- 5 TM1710D••• Optimized logic controller (18 I/O in 4 DIN), see page 33
- 6 TM172PB••• Performance logic controller (7 or 18 I/O in 4 DIN), see page 25
- 7 TM172PD••• Performance logic controller (28 or 42 I/O in 8 DIN), see page 25
- 8 TM172E12R I/O expansion module (12 I/O in 4 DIN), see page 26
- 9 TM172E28R I/O expansion module (28 I/O in 4 DIN, see page 26
- 10 TM172DCLWT● wall mounting remote display, see page 28
- 11 TeSys D motor starter (1)
- 12 Electromechanical relays, solid state relays (1)
- 13 Pressure transmitter (third-party product)
- **14 TM1ST●●** temperature sensor PT1000 or NTC, see page 46
- 15 SPD310 Differential pressure sensor (1)
- 16 H721LC-S6 current transducer (1)
- 17 iEM 3000 energy meter (1)
- 18 Altivar 212 variable speed drive (1)
- 19 TM171VEVM4 electronic expansion valve driver, see page 44
- 20 SE8000 room controller (thermostat) (1)
- 21 TM1SH●● humidity sensor, see page 47

(1) Consult this offer on our website.

Logic controllers for HVAC and Pumping applications

M173 Optimized, M172 Optimized / Performance, and M171 Optimized logic controllers

Application		Logic controllers for Compact and simple machines	Logic controllers for any size of connectable of	or connected HVAC machines	Logic controllers for sim	ple and compact machines
Product name		M173 Optimized	M172 Optimized	M172 Performance	M171 Optimized	
					\$\frac{1}{2}\frac{1}{2	7 238 C
HVAC unit type		Heat pumps (up to two circuits) Process chillers Pumping Boilers/Heaters and any small and compact machines	 Air/water-cooled chiller Rooftop unit Heat pump Shelters Compressor rack Ventilation unit Precision air conditioner Heat recovery unit Packaged unit AHU and many more 		- Air/water-cooled chiller - Rooftop unit - Heat pump - Shelters - Compressor rack - Ventilation unit - Precision air conditioner - Heat recovery unit - Packaged unit - AHU and many more	
Programming Software		EcoStruxure Machine Expert - HVAC V1.6 or higher	EcoStruxure Machine Expert - HVAC V1.0 or higher			
Secure comunication on the Internet		Yes, - with TM172SIG Gateway Secure Interface - with TM172SIP Plug-in Secure Interface	Yes, - with TM172SIG Gateway Secure Interface - with TM172SIP Plug-in Secure Interface	Yes, with TM172SIG Gateway Secure Interface		
Maximum number of I/O with expansion modules		78	238		28	44
Power Supply		24 Vac/dc	24 Vac/dc		100240 Vac, isolated	24 Vac/dc (except for TM1710DM22S: 12-24 Vac)
Embedded I/Os	Analog Input	7	8 or 12	2, 8 or 12	5	5
Imbedded I/Os	Digital Input	6	2, 8 or 12	2, 8 or 12	2	6
	Analog Output	4	2, 4 or 6	0, 2, 4 or 6	5	5
	Digital Output	5	6, 8 or 12	3, 6, 8 or 12	4	6
Communication fieldbus and networks	Embedded communication port	1 CAN expansion bus 2 RS485 (Modbus SL) 1 Secure Interface Wifi (Modbus TCP/IP, HTTPs,MQTTs) (1)	- 2 RS485 (Modbus SL or BACnet MS/TP) - 1 CAN expansion bus	- 2 RS485 (Modbus SL or BACnet MS/TP) - 1 CAN expansion bus - RJ45 connector - Ethernet	- 1 RS485 - 1 LAN expansion bus	
	Optional communication port	None except with a gateway	With TM171A • • • communication modules: - RS485 (Modbus SL or BACnet MS/TP) - CAN bus - RS232 - LonWorks (FFT-10) - Modbus TCP, BACnet /IP, - Ethernet	With TM171A • • • communication modules: - RS485 (Modbus SL or BACnet MS/TP) - CAN bus - RS232 - LonWorks (FFT-10)	None except with a gateway	
	USB port	Yes, 1 USB-C	Yes, 1 USB-Mini-B	Yes, 1 USB-A and 1 USB-Mini-B	No (program can be downloaded v TM171ADMI programming cable)	vith the TM171AMFK programming stick and
	Services	Remote download via Modbus SL Download program and firmware via USB-C	 Download the program via USB-A or Modbus SL Optional services depending on the Ethernet communication module 	Download the program through USB-A or Modbus SL Remote access HTTP Webserver (Webvisu) FTP client/server SNPT	Remote download via Modbus SL	
Display	Built-in	Built-in versions available	Built-in versions available	Built-in versions available	Built-in versions available	
Remote		Yes - with with TM172DCL●●●● color touch screen displays - with HMI Harmony STU/STO offer, see on our website	Yes, - with TM172DGRP display - with TM172DCL•••• color touch screen displays - with HMI Harmony STU/STO offer, see on our website		Yes, - with TM171DLED, TM171DLCD - with TM172DCLeeee color touc - with HMI Harmony STU/STO off	h screen displays
Mounting		35 mm (1.38 in) DIN rail	35 mm (1.38 in) DIN rail, or on panel with TM172AP12PM mounti	ting accessory	35 mm (1.38 in) DIN rail or Flush m	nounting
Product certifications		(¢, cURus (UL Recognized), CSA, EAC, RCM, RoHS China, UKCA	C€, cURus (UL Recognized), CSA, EAC, RCM, RoHS China, BA	Cnet BTL	CE, cURus (UL Recognized), CSA	, EAC, RCM, RoHS China
Reference		TM173O•••	TM172O•••	TM172P•••	TM1710•••	
Page		16	20		30	

⁽¹⁾ Secure Interface Wifi is scheduled to be commercialized for Q2 2024.(2) Special brackets provided with logic controllers and remote display.

Schneider Electric

Logic controllers for HVAC and Pumping applications

M173 Optimized logic controllers

Application	Logic controllers for compact and simple machines
Product name	M173 Ontimized







Reference		TM1730BM22R	TM173ODM22S	TM1730DM22R
Power supply		24 Vac/dc	24 Vac/dc	24 Vac/dc
ype of mounting		4 DIN, 35 mm/1.38 in ∟r rail mounting	4 DIN, 35 mm/1.38 in ட rail mounting	4 DIN, 35 mm/1.38 in பாrail mounting
Embedded display		-	Yes	Yes
otal I/Os		22	22	22
nalog Inputs	Total	7	7	7
NTC (β3435 - 10 I 0-10 V	kW at 25 °C), or PT1000, or digital inputs, or	1	1	1
NTC (β3435 - 10 l or 10 V, or digital i	kW at 25 °C), or PT1000, or 4-20 mA, or 5 V, inputs	6	6	6
igital Inputs	Total	6	6	6
volt-free or pulse	reading - up to 2 kHz	2	2	2
volt-free		4	4	4
nalog Outputs	Total	4	4	4
0-10 V/ 4-20 mA		1	1	1
0-10 V/PWM - 10	Hz2 kHz	3	3	3
igital Outputs	Total	5	5	5
Relay 3 A SPST 3	x 1 common, 100 k cycles- no UL derating	3	3	3
Relay 3 A SPST 2	x 1 common, 100 k cycles- no UL derating	2	-	2
2 SSR 2x 110/240) Vac and 24 Vac	-	2	-
laximum I/Os expa	nded	78	78	78
ompatible Secure	Interface	TM172SIG, TM172SIP	TM172SIG, TM172SIP	TM172SIG, TM172SIP
ompatible expansi	ion module	TM172E12R, TM172E28R, TM171EP14R, TM171EP27R	TM172E12R, TM172E28R, TM171EP14R, TM171EP27R	TM172E12R, TM172E28R, TM171EP14R, TM171EP27R
	RS485 serial ports	-	2	2
ommunication C	CAN expansion bus	2	1	1
C	Connector for remote display	1	1	1
C	Connector to communication module	1	1	1
Ū	JSB-C	1	1	1


Schneider Belectric

Logic controllers for HVAC and Pumping applications M173 Optimized logic controllers

M173 Optimized logic controllers

M173 Optimized logic controllers comprise 3 models that can be used to control up to 22 embedded I/O (digital and analog).

- Power supply: 24 V ≂
- Two types of housing:
 - with built-in display
 - without display
- One type of mounting: on 35 mm/1.38 in ¬ rail mounting: controllers to be mounted inside a cabinet
- Communication ports on M173 Optimized logic controllers:
 - One Modbus SL client/server
 - One USB
 - One CAN expansion bus
 - On flush mounting version:
 - One Modbus SL client/server
 - One CAN expansion bus
- M173 Optimized logic controllers can be connected to I/O expansion modules, see page 26.
- M173 Optimized logic controllers are certified C€, cURus (UL Recognized), CSA, EAC, RCM, RoHS China, UKCA.



35 mm/1.38 in ∟ rail mounting

M173 Optimized logic controllers (1)

- 1 Connector for removable terminal block for digital outputs CN6
- 2 Connector for removable terminal block for isolated power supply CN7
- 3 Connector clip
- 4 Display (except for TM173OBM22R model)
- 5 4 control keys for setting controller parameters (Enter, Escape, Navigation)
- 6 USB-C p ort to connect a PC (CN11)
- 7 Connector for removable terminal block for analog inputs CN10
- 8 Remote display connector CN4
- 9 Connector for removable terminal block for digital inputs CN9
- 10 Clip-on lock for 35 mm/1.38 in _r rail mounting
- 11 Connector for removable terminal block for analog outputs CN8
- 12 Connector for removable terminal block for CAN expansion bus CN1
- 13 Serial port RS-485 (Modbus SL) for removable terminal block CN2, CN3

(1) M173 Optimized logic controllers are provided with removable terminal blocks for IO, power connections.

Logic controllers for HVAC and Pumping applications M173 Optimized logic controllers

M17	3 Optimized logic	controllers: Power sup	oply: 24 V ≂			
No. of I/O	Number and type of cha Inputs	annels Outputs	Embedded communication port	Display	Reference	Weight kg/lb
35 mr	n/1.38 in ∟r rail mount	ting <i>(1)</i>				
22	6 digital inputs: 2 Volt-free or pulse reading - up to 2 kHz 4x volt-free 7 analog inputs:	5 digital outputs: ■ 3 Relay 3 A SPST 3x 1 common (2) ■ 2 SSR 2x 110/240 Vac and 24 Vac		■ 2 RS485 display	TM173ODM22S	0,178 <i>0.3</i> 92
	7 analog inputs: ■ 1 NTC (β3435 - 10 kW at 25°C), or PT1000, or digital input, or 0-10 V ■ 6 NTC (b3435 - 10 kW at 25°C), or PT1000, or 4-20 mA, or 5 V, or 10 V, or digital inputs	4 analog outputs: ■ 1x 0-10 V/ 4-20 mA ■ 3x 0-10 V/PWM (10Hz2kHz)				
		5 digital outputs: ■ 3 Relay 3 A SPST 3x 1 common (2) ■ 2 Relay 3 A SPST 2x 1 common (2)		Built-in display	TM173ODM22R	0,182 <i>0.401</i>
		4 analog outputs: ■ 1x 0-10 V/ 4-20 mA ■ 3x 0-10 V/PWM (10Hz2kHz)		Remote display (optional)	TM173OBM22R	0,172 0.268



TM173ODM22S TM173ODM22R



TM173OBM22R

⁽¹⁾ Removable terminal blocks are supplied with TM173 Optimized logic controllers. (2) 100 k cycles- no UL derating.

Logic controllers for HVAC and Pumping applications

M172 Optimized and Performance logic controllers, Remote displays

			r any size of connectab													
Product nam	е	M172 Performance	M172 Optimized		M172 Performanc	e		M172 Optimized	I	M172 Performano	e	M172 Optimize	ed	M172 Performan	ce	
					Mid minin					munun nunum p						
eference		400	PPDG07R TM172OBM18R (1) (1)	TM172ODM18R (1)	TM172PBG18R (1)	TM172PDG18R <i>(1)</i>	TM172PDG18S (1)	TM172OBM28R (1)		TM172PBG28R, T TM172PBG28RI T (1)	M172PDG28R, TM172PDG28 M172PDG28RI (1)	TM172OBM42F (1)	TM172ODM42R (1)	TM172PBG42R, 1 TM172PBG42RI 1 <i>(1)</i>		
wer supply	у			24 Vac/dc						(7	1.7	Vac/dc		(7)	(7)	('/
pe of mour	nting	4 DIN, 35 mm/1.38 in	பா rail mounting Performance c	ntrollers, and Panel	mounting with TM17	72AP12PM mounting	accessory(2)			m/1.38 in ∟r rail mo	ounting Performance controllers	s, and Panel mount			cessory (2)	
mbedded di	isplay	128	n display No k64 LCD backlight	Built-in display 128x64 LCD with backlight	No	Built-in 128x6- with ba	4 LCD	No	Built-in display 128x64 LCD with backlight	No	Built-in display 128x64 LCD with backlight	No	Built-in display 128x64 LCD with backlight	No	Built-in d 128x64 with bac	LCD
otal I/Os		7		8		18			g.n.	28	man bashingin		- man basinigini	42		g
nalog Input	Total	2		3		8				8				12		
or 4-20 mA hOhm, or d	1000, or PTC, or 0-20 mA, , or 0-5 V, or 0-10 V, or aOhm, or digital input	2		3		8				8				12		
i gital Inputs High sp contact	peed counter (2 kHz), dry	2 2		2		2 2				8 2				12 2		
24 Vac/		_		-						6				10		
nalog Outpi		-		2		2				4				6		
or PWN	or 4-20 mA, // (2 kHz, 24 Vdc)	-				2				2				2		
0-10 V igital Outpu		3		2		2 6				2 8				4 12		
Relay 3		3		, S		6	4		8	o 3	6			12		10
SSR 0,		_		-		_	2			-	2			_		2
ompatible S	Secure Interface		<u> </u>	M172SIG, TM172SI	IP						TM172S	G, TM172SIP				
ompatible e	expansion module		172E12R, TM172E28R, TM171								R, TM172E28R, TM171EP14R					
	xpansion valve driver	TI	M172EVEV1U, TM172EVEV1B,	TM172EVEV2B (up	to 4 expansion valv	e drivers max.)				TM172EVE	V1U, TM172EVEV1B, TM172	EVEV2B (up to 4 e	xpansion valve dri	vers max.)		
mmunication ort	Ethernet (Modbus TCP, BACnet IP (B-AAC profile), WebVisu)	1		-		1		-	-		1		_		1	
	RS485 (Modbus SL or BACnet MS/TP (B-AAC profile)	2		2		2		2	2		2		2		2	
	CAN expansion bus	1		<u> </u>		1					1		1		1	
	Communication module port	1		l		1		1	1		1		1		1	
	USB-B	1				1			1		1		1		1	
	USB-A	1		-		1		-	-		1		-		1	
ptional ommunication ort	μSD Card slot With communication module (see page 42)	- CAN expansion bus - Modbus TCP - Modbus SL(RS485) - BACnet MS/TP (B-AAC profile - RS232 Serial link - LonWorks (FFT-10)	rofile)			1		-			1		_		1	
	With Secure Interfaces (see page 40)	- FTPs - HTTPs - SMTPs - SMTP - SMTT - MQTT - Cybersecure VPN														
			5 ports. (2) Accessories to be ord													

Application	Remote displays (compatible	with each M172 Logic controller)				
References	TM172DGRP	TM172DCLWT	TM172DCLWTH	TM172DCLWTHP	TM172DCLFW	TM172DCLFG
Type of mounting	Remote wall	Remote wall	Remote wall	Remote wall	Remote flush	Remote flush
Description	LCD display with backlight	LCD display, Color touchscreen Temperature	LCD display, Color touchscreen Temperature, Relative humidity	LCD display, Color touchscreen Temperature, Relative humidity, Presence PIR	LCD display, Color touchscreen IP65 (front face)	LCD display, Color touchscreen IP65 (front face)
Programming software	EcoStruxure Machine Expert - HVAC V1	.0 or higher			-	
Product certifications	C€, cURus (UL Recognized), CSA, EAC	, RCM, RoHS China				
Communication	CAN expansion hus	Modbus SI		Modbus SI		

Logic controllers for HVAC and Pumping applications

M172 logic controllers





4 DIN - with display

8 DIN - without display

M172 Optimized logic controller





4 DIN - without display

8 DIN - with display

M172 Performance logic controller

M172 Optimized and Performance logic controllers

M172 Optimized and M172 Performance logic controllers are differentiated by the connectivity: embedded on M172 Performance, optional on M172 Optimized. M172 logic controllers embed 7, 18, 28 or 42 I/O, and can be fitted with a display, with relay outputs, and with SSR outputs, depending on the model.

- The M172 logic controller offer comprises:
 - a M172 model to control from 7 up to 18 embedded I/O (digital and analog), in 4 DIN (controller width is 72 mm /2.83 in)
 - and M172 models to control from 28 up to 42 embedded I/O (digital and analog), in 8 DIN (controller width 144 mm /5.66 in)
- Power supply: 24 V ≂
- Two types of housing:
 - with built-in display
 - without display
- Two types of mounting:
 - On 35 mm/1.38 in ¬¬ rail mounting: for M172 logic controller to be mounted inside a cabinet
 - On panel: with TM172AP12PM fixing accessory
- Communication ports on M172 Optimized logic controllers:
 - Two RS485 for Modbus SL (client/server) (only 1 client) or 1 for BACnet MS/ TP (B-AAC profile, BACnet BTL certified)
 - One for CAN expansion bus
 - Plus one communication module connector
- Communication ports on M172 Performance logic controllers: same as M171 Optimized, plus one RJ45 for Modbus TCP, BACnet IP (B-AAC profile, BACnet BTL certified) and Ethernet
- M172 logic controllers can be connected to communication modules, offering another connection to a CAN expansion bus, Modbus SL or LonWorks, etc., see page 42.
- M172 logic controllers are certified C€, cURus (UL Recognized), CSA, EAC, RCM, RoHS China, and BACnet BTL certified.
- Micro SD card: a slot for a micro SD memory card is available on the front face of the M172 Performance logic controllers (1).
 The micro SD card is used for
 - The micro SD card is used for:
 - Data logging
 - Webserver storage
- USB programming ports
 - The USB-A port is available on M172 Performance logic controllers, used to transfer programs with a memory stick.
 - USB mini B is available on M172 Optimized and Performance logic controllers, used to connect to a PC for programming, see page 49.

(1) M172 Optimized logic controllers do not have a slot for a micro SD card (no slot can be added later).

Logic controllers for HVAC and Pumping applications M172 logic controllers

16 15 14 13 12 10 9 8 7 6 5 4

4 DIN controller



8 DIN controller

M172 Optimized and Performance logic controllers

logic controllers with 7 or 18 I/O (in 4 DIN: controller width is 72 mm /2.83 in) (1)

- 1 RJ45 connector for Ethernet Modbus TCP, BACnet IP (B-AAC profile) (2)
- 2 Connector for removable terminal block for digital outputs
- 3 Connector for removable terminal block for power supply (24 V ≈) (3)
- 4 Connector for removable terminal block for analog inputs
- 5 Connector for removable terminal block for digital intputs
- 6 Connector for removable terminal block for fast digital inputs (high speed counter)
- 7 Connector for removable terminal block for analog outputs
- 8 Connector for removable terminal block for RS485-1 (Modbus SL or BACnet MS/TP) (3)
- 9 Connector for removable terminal block for RS485-2 (Modbus SL or BACnet MS/TP) (3)
- 10 Connector for removable terminal block for CAN expansion bus
- 11 Slot for micro SD card (2)
- 12 Slot for battery (behind the front flap)
- 13 On TM17•D•••: Built-in display, 4 status LEDs and 5 control keys for setting controller parameters
 - On TM17•B•••: 4 status LEDs and 5 control keys for setting controller parameters, behind a front panel
- 14 Connector for communication module
- 15 USB-B port to link a PC
- 16 USB-A port for USB stick (2)
- 17 Clip-on lock for 35 mm/1.38 in _r rail mounting
- 18 Two slots for the TM172AP12PM fixing accessory

M172 logic controllers with 28 or 42 I/O (in 8 DIN: controller width is 144 mm/5.66 in) (1)

- 1 RJ45 connector for Ethernet Modbus TCP and BACnet IP (B-AAC profile) (2)
- 2 Connector for removable terminal block for digital outputs
- 3 Connector for removable terminal block for power supply (24 V 元) (3)
- 4 Connector for removable terminal block for analog inputs
- 5 Connector for removable terminal block for digital intputs
- 6 Connector for removable terminal block for fast digital inputs (high speed counter)
- 7 Connector for removable terminal block for analog outputs
- 8 Connector for removable terminal block for RS485-1 (Modbus SL or BACnet MS/TP) (3)
- 9 Connector for removable terminal block for RS485-2 (Modbus SL or BACnet MS/TP) (3)
- 10 Connector for removable terminal block for CAN expansion bus
- 11 Slot for micro SD card (2)
- 12 Slot for battery (behind the front flap)
- 13 On TM172•D••••: Built-in display, 4 status LEDs and 5 control keys for setting controller parameters
 - On TM172•B••••: 4 status LEDs and 5 control keys for setting controller parameters, behind a front panel
- 14 Connector for communication modules
- 15 USB-B port to connect a PC
- 16 USB-A port for USB stick (2)
- 17 Clip-on lock for 35 mm/1.38 in _r rail mounting
- 18 Two slots for the TM172AP12PM fixing accessory
- (1) TM172ASCTB••• removable terminal blocks to be ordered separately, see page 27.
- (2) Only for M172 Performance.
- (3) TM172O••••, TM172P•G07R, TM172P•G18•, TM172P•G28•I and TM172P•G42•I have an isolated power supply and two isolated RS485 ports.

Logic controllers	s for HVAC and I	Pumping ap∣	olications
M172 Optimized lo	gic controllers		





TM172ODM18R



TM172OBM28R



TM172ODM28R



TM1720BM42R



TM1720DM42R



TM172AP12PM

	′2 Optimized logio nm/1.38 in ጊr rail mou					
No.	Number and type of cha	nnels	Embedded	Display	Reference	Weight
of I/C	Inputs	Outputs	communication port			kg/ <i>lb</i>
18	2 digital inputs: ■ 2 high speed counter (2 kHz), dry contact 8 analog inputs (configurable in pairs): ■ 8 NTC, or PT1000, or PTC, or 0-20 mA, or 4-20 mA, or 0-5 V, or 0-10 V, or hOhm, or daOhm, or digital input	6 digital outputs: ■ 1 SPDT relay 3 A ■ 2 SPST 3 A with the same common ■ 1 SPST 3 A ■ 2 SPST 3 A with independent common 2 analog outputs:	■ 1 CAN expansion bus ■ 2 RS485 ■ 1 USB-B ■ 1 Communication module port	Remote display (optional)	TM172OBM18R (1)	0.170/ <i>0.375</i>
		■ 2 x 0-10 V, or 4-20 mA, or PWM (2 kHz, 24 V)		Built-in display 128x64 LCD with backlight	TM172ODM18R (1)	0.195/ 0.430

28	8 digital inputs:
	\blacksquare 6 24 V \sim or $=$
	2 high speed counters,
	dry contact
	8 analog inputs

(configurable in pairs): ■ 8 NTC, or PT1000, or PTC, or 0-20 mA, or 4-20 mA, or 0-5 V, or 0-10 V, or digital input 4 analog outputs

8 digital outputs: ■ 1 SPDT Relay 3 A

■ 3 SPST 3 A with the same common ■ 2 SPST 3 A with the

same common
■ 2 SPST 3 A with independent common

■ 2 x 0-10 V, or 4-20 mA or PWM (2 kHz, 24 V =

■ 1 CAN expansion bus Remote display ■ 2 RS485 (optional)

■ 1 USB-B ■ 1 Communication module port

(1)

TM172OBM28R

0.390/

0.859

0.390/

0.859

Built-in display TM 128x64 LCD with (1) TM172ODM28R backlight ■ 2 x 0-10 V

42 12 digital inputs:

- 10 24 V ~ or ===
- 2 high speed counters, dry contact

12 analog inputs (configurable in pairs):

■ 12 NTC, or PT1000, or PTC, or 0-20 mA, or 4-20 mA, or 0-5 V, or 0-10 V, or digital input

12 digital outputs:

■ 2 SPDT Relay 3 A ■ 3 SPST 3 A with the same common

■ 3 SPST 3 A with the same common

■ 2 SPST 3 A with the same common

■ 2 SPST 3 A with independent common

6 analog outputs:

or 4-20 mA, or PWM (2 kHz, 24 V ---) ■ 4 x 0-10 V

■ 2 RS485

■ 1 USB-B ■ 1 Communication module port

■ 1 CAN expansion bus Remote display TM172OBM42R 0.480/ (optional) 1.058

> Built-in display TM172ODM42R 0.480/ 128x64 LCD with (1) backlight

Accessories to be orde	red separately		
Designation	Use for	Reference	Weight kg/lb
I/O screw terminal blocks	TM172●●●07R logic controllers	TM172ASCTB07	0.025/ <i>0.055</i>
	TM172●●●18● logic controllers	TM172ASCTB18	0.040/ 0.088
	TM172P•••28•, TM172P•••28•I logic controllers	TM172ASCTB28	0.100/ 0.220
	TM172P•••42•, TM172P•••42•I logic controllers	TM172ASCTB42	0.150/ <i>0.331</i>
Fixing accessory: 12 clip-on locks for panel mounting	For mounting M172 logic controllers and M172 expansion modules on panel	TM172AP12PM	0.050/ 0.110

(1) Products equipped with an isolated power supply, and two isolated RS485 ports.

Logic controllers for HVAC and Pumping applications

M172 Performance logic controllers



TM172PBG07R



TM172PDG18R



TM172PBG28RI



TM172PDG28RI



TM172PBG42RI



TM172PDG42SI

No.	Number and type of ch	unting, and panel mou	Embedded Embedded	Display	Reference	Weight
	Inputs	Outputs	communication port	Display	Reference	kg/lb
7	2 digital inputs: ■ 2 high speed counter	3 digital outputs: ■ 1 SPDT relay 3 A ■ 2 SPST 3 A with the same common	■ 1 Ethernet ■ 1 CAN expansion bus ■ 2 RS485 ■ 1 USB-A	Remote display (optional)	TM172PBG07R (1)	0.175 0.386
(configurable in pairs): ■ 2 NTC, or PT1000, or PTC, or 0-20 mA, or 4-20 mA, or 0-5 V, or 0-10 V, or hOhm, or daOhm, or digital input		■ 1 Communication 12	Built-in display 128x64 LCD with backlight	TM172PDG07R (1)	0.200/ 0.441	
18	2 digital inputs: ■ 2 high speed counters, dry contact	■ 2 SPST 3 A with independent common Optional 2 SSR 0.5 A	■ 1 Ethernet ■ 1 CAN expansion bus ■ 2 RS485	Remote display (optional)	TM172PBG18R (1)	0.200/ <i>0.441</i>
	8 analog inputs (configurable in pairs): ■ 8 NTC, or PT1000, or PTC, or 0-20 mA, or 4-20 mA, or 0-5 V,		■ 1 USB-A ■ 1 USB-B ■ 1 Communication module port ■ 1 µSD Card slot	Built-in display 128x64 LCD with backlight	TM172PDG18R (1)	0.225/ 0.496
	or 0-10 V, or hOhm, or daOhm, or digital input	with independent common for TM172PDG18S only			TM172PDG18S (1)	0.225/ 0.496
		2 Analog outputs: ■ 2 x 0-10 V, or 4-20 mA, or PWM (2 kHz, 24 V ==-)				
28	8 digital inputs: ■ 6 24 V ~ or === ■ 2 high speed counters, dry contact	8 digital outputs: ■ 1 SPDT Relay 1 A or 3 A for TM172P●G28●I ■ 3 SPST 3 A with the	■ 1 Ethernet ■ 1 CAN expansion bus ■ 2 RS485 ■ 1 USB-A	Remote display (optional)	TM172PBG28R	0.300/ 0.661
	8 analog inputs, (configurable in pairs): ■ 8 NTC, or PT1000, or PTC, or 0-20 mA,	same common ■ 2 SPST 3 A with the same common ■ 2 SPST 3 A with	1 USB-B1 Communication module port1 µSD Card slot	Built-in display 128x64 LCD with backlight	TM172PDG28R	0.300/ 0.661
	or 4-20 mA, or 0-5 V, or 0-10 V, or digital	independent common ■ Optional 2 SSR 0.5 A		Remote display	TM172PBG28RI (1)	0.390/ 0.859

12	12	digital	inputs
-		aigita.	putt

input

- 10 24 V ==
- 2 high speed counter, dry contact

12 analog inputs, (configurable in pairs):

■ 12 NTC, or PT1000, or PTC, or 0-20 mA, or 4-20 mA, or 0-5 V, or 0-10 V, or digital input

- 12 digital outputs:
- 2 SPDT relay 1 A or 3 A for TM172P•G42•I

with independent

common for TM172PDG28SI only

4 analog outputs:

■ 2 x 0-10 V

■ 2 x 0-10 V, or 4-20 mA,

or PWM (2 kHz, 24 V ===)

- 3 SPST 3 A with the same common ■ 3 SPST 3 A with the
- same common
- 2 SPST 3 A with the same common
- 2 SPST 3 A with
- independent common ■ Optional 2 SSR 0.5 A with independent common for TM172PDG42S and TM172PDG42SI only

- 6 analog outputs: 2 x 0-10 V, or 4-20 mA, or PWM (2 kHz, 24 V ===)
- 4 x 0-10 V

- 1 Ethernet ■ 1 CAN expansion b
- 2 RS485
- 1 USB-A
- 1 USB-B
- 1 Communication module port
- 1 µSD Card slot

bus	Remote display (optional)	TM172PBG42R	0.385/ 0.849	
	Built-in display 128x64 LCD	TM172PDG42R	0.385/ 0.849	

Built-in display TM172PDG28RI 128x64 LCD (1)

(1)

(1)

TM172PDG28SI

0.390/

0.859

0.390/

0.859

0.385/

0.849

(optional)

with backlight

with backlight

Remote display (optional)	TM172PBG42RI (1)	0.480 1.058
Built-in display 128x64 LCD	TM172PDG42RI	0.480

TM172PDG42S

with backlight	()	
	TM172PDG42SI	0.480/
	(1)	1 058

Accessories to be ordered separately	
I/O screw terminal blocks, Fixing accessory	See page 27

(1) Products equipped with an isolated power supply, and two isolated RS485 ports.

Logic controllers for HVAC and Pumping applications


I/O expansion modules for M173 and M172 logic controllers

I/O expansion modules


Two I/O expansion modules are available to increase the number of I/O up to 78 on M173 logic controllers, and up to 238 on M172 logic controllers.

- Expanded I/O types are digital and analog; the mix between inputs and outputs differs according to the module, making it easier to adapt the configuration to each need
- They are connected via the CAN expansion bus of the logic controllers.
- The maximum number of expansion modules on the CAN expansion bus is 7, in any combination (if more expansions are needed, please contact our Customer Care Centre).
- The expansion modules are equipped with DIP switches which can be used to set the baud rate, the network address and also to incorporate a 120 ohm terminal resistor.
- The I/O can be configured in pairs, like M172 controllers.
- I/O expansion modules compatibility:

Logic controllers	Compatible I/O expansion module (reference)
M172 Optimized (TM172O••••) M172 Performance (TM172P••••)	TM172E12R TM172E28R Legacy TM171EP expansion modules are also compatible with M172.
M173 Optimized (TM173O••••)	TM172E12R TM172E28R



TM172E12R TM172E28R



- 2 Removable terminal block for digital outputs
- 3 Connector for removable terminal block for CAN expansion bus
- 4 DIP switches
- 5 Clip-on lock for 35 mm/1.38 in ⊥r rail mounting
- 6 Connector for removable terminal block for digital inputs
- 7 Connector for removable terminal block for analog inputs with 5 V $\frac{1}{2}$ /24 V $\frac{1}{2}$ output power supply

TM172E28R expansion module (1)

- 8 Connector for removable terminal block for analog outputs
- 9 Two slots for TM172AP12PM fixing accessory



(1) Removable terminal blocks to be ordered separately, see page 27.

Logic controllers for HVAC and Pumping applications
I/O expansion modules for M173 and M172 logic controllers



TM172E12R



TM172E28R

1/0	expansion module	es en				
35 m	nm/1.38 in 🖵 rail mount	ting				
No. of I/O	Number and type of cha	nnels	Compatibility	Embedded	Reference	Weight
	Inputs (1)	Outputs (1)		communication port		kg/ <i>lb</i>
12	2 digital inputs: ■ 2 high speed counters, dry contact 4 analog inputs: ■ 4 NTC or PT1000, or PTC. or 0-20 mA, or 4-20 mA, or 0-5 V, or 0-10 V, or hOhm, or daOhm, or digital inputs	6 digital outputs: ■ 3 SPST 3 A with the same common ■ 3 SPST 3 A with the same common	TM1730•••• TM1720•••• TM172P••••	■ 1 CAN expansion bus	TM172E12R	0.140/ 0.308
28	6 digital inputs: ■ 4 ~ or 24 V ■ 2 high speed counters, dry contact	10 digital outputs: ■ 3 SPST 3 A with the same common ■ 3 SPST 3 A with the	TM1730•••• TM1720•••• TM172P••••	■ 1 CAN expansion bus	TM172E28R	0.190/ 0.418
	10 analog inputs: ■ 10 NTCor PT1000, or PTC, or 0-20 mA, or 4-20 mA, or 0-5 V, or 0-10 V, or hOhm, or daOhm, or digital inputs	same common ■ 2 SPST 3 A with the same common ■ 2 SPST 3 A with the same common 2 analog outputs: ■ 2 x 0-10 V, or 4-20 mA,or PWM (2 kHz, 24 V :)				







Accessories to be ordered s	separately		
Designation	Compatibility	Reference	Weight kg/lb
Screw terminal blocks (inputs, outputs, and communication bus)	TM172E12R expansion module	TM172ASCTB12E	0.070/ <i>0.154</i>
	TM172E28R expansion module	TM172ASCTB28E	0.100/ 0.220
Fixing accessory: 12 clip-on locks for panel mounting	TM172E●●R expansion modules	TM172AP12PM	0.055/ 0.110

⁽¹⁾ Removable terminal blocks to be ordered separately.

Logic controllers for HVAC and Pumping applications

Remote displays for M172 logic controllers

Remote displays

Remote color touch screen displays

Six remote color touch screen displays are dedicated to the M172 Optimized and Performance logic controllers, distinguished by use and type of mounting. These displays can be also used with M171 controllers with Modbus SL or with third-party products equipped via Modbus SL.

They are all programmable with EcoStruxure Machine Expert - HVAC. The remote color touch screen displays have the same firmware, meaning they can be swapped interchangeably.

- TM172DCLWT•• are designed for wall mounting and indoor use, depending on the reference, for controlling temperature, relative humidity and PIR presence with built-in sensor
- TM172DCLF
 are designed for flush mounting, and wall mounting with an accessory, and either indoor or outdoor uses, with a or dark gray housing. An installation on a wall with TM172ABKP
 accessories, useful for a plant room.
- TM172DCLWT● and TM172DCLF● displays can be mounted vertically (portrait) or horizontally (landscape) (1). They can be configured for Modbus SL as client or server, by means of the software.
 - On Modbus SL Server, up to 8 displays can be installed in the same network.
 - On Modbus SL Client, up to 8 devices can be managed via the display.

Remote monochrome display

■ TM172DGRP monochrome display is dedicated to the M172 Optimized and M172 Performance logic controllers. It is designed for flush mounting, and wall mounting with an accessory, and indoor use. It is programmable with EcoStruxure Machine Expert - HVAC.



- 1 3.5" color touch screen LCD (320 x 240 pixels)
- 2 Holes for presence (motion) detection
- 3 Input connector (USB Micro-B port)
- 4 Power Supply (24 V ≂)
- 5 RS485 Modbus serial line
- 6 Holes for temperature and humidity measurement



TM172DCLFW, TM172DCLFG

- 1 3.5" color touch screen LCD (320 x 240 pixels)
- 2 Input connector (USB Micro-B port)
- 3 Power Supply (24 V ≂)
- 5 RS485 Modbus serial line





TM172DGRF

TM172DCLWT • •

TM172DCI FW

TM172DGRP

- 1 Backlight monochrome LCD screen (240 x 140 pixels)
- 2 5 control kevs
- 3 CAN bus connector

(1) With landscape mounting, temperature and humidity sensors cannot be used as they are not accurate.



Logic controllers for HVAC and Pumping applications

Remote displays for M172 logic controllers



TM172DCLWT●●

Туре	Description	Housing	Built-in sensor for	Reference	Weight kg/lb	
Remote color touch screet wall mounting displays	■ Color touchscreen■ Size: 3.5"■ Resolution: 320 x 240 pixels	White	■ Temperature	TM172DCLWT	0.340 0.749	
	■ IP20 ■ Communication port: 1 RS485, Modbus SL with terminal blocks		■ Temperature ■ Relative humidity	TM172DCLWTH	0.340/ 0.749	
			■ Temperature ■ Relative humidity ■ Presence PIR	TM172DCLWTHP	0.340/ 0.749	



TM172DCLFW



TM172DCLFG









TM172ABKPG



TM171ABKPG

■ Size: ■ Reso ■ IP65 ■ Com: 1 RS-	r touchscreen	White –	TM172DCLFW	0.205 0.452
		Grey –	TM172DCLFG	0.205 0.452

Remote display	■ 5 control keys	Grey	TM172DGRP	0.197/
monochrome	■ Backlit LCD,	-		0.430
	■ 240 x 140 pixels,			
	■ Monochrome,			
	■ With real time clock			

Accessories to be orde	ered separately		
Туре	Use	Reference	Weight kg/ <i>lb</i>
Mounting accessories (1)	White wall support for TM172DCLFW display	TM172ABKPW	0.060/ <i>0.132</i>
	Grey wall support for TM172DCLFG display	TM172ABKPG	0.060/ 0.132
	Wall bracket For TM172DGRP display	TM171ABKPG	0.015/ 0.030

(1) With the use of TM172ABKP•• accessories, the degree of protection for the TM172DCLF• displays is IP20.

Logic controllers for HVAC and Pumping applications

M171 Optimized logic controllers and Remote displays

Application	Logic controllers for Sim	ple and compact machines							
Product name	M171 Optimized								
	100 A	9 2981 6	G 2301 G	79		C COOL C	G ESSEL S	- E99 - E	() () () () () () () () () ()
Reference	TM171OBM14R (1)	TM1710D14R (1)	TM1710DM14R (1)	TM1710BM22R	TM1710D22R	TM1710DM22R	TM1710DM22S	TM1710F22R	TM1710FM22R
Power supply		100-240 Vac				24 Vac/	dc (3) (4)		
Type of mounting		4 DIN, 35 mm/1.38 in _r rail mounting	ng		4 DIN, 35 mm/1.3	8 in பாrail mounting		Flush	mounting
Embedded display	-	Built-i	n display	-		Built-in display			
Total I/Os		14				2	2		
Analog Inputs Total		5					5		
NTC, or PT1000, or digital inputs		2					-		
NTC, or 0-20 mA, or 4-20 mA, or 0-10 V, or 0-5 V, or 0-1 V, or digital inputs		2				:	2		
NTC, or PT1000, or 0-20 mA, or 4-20 mA, or 0-10 V, or 0-5 V, or 0-1 V, or digital input		1				-			
NTC or digital inputs		_				;	3		
Digital Inputs Total		2					6		
open collector or digital inputs (2)		2					-		
volt-free in 1 group		_				(6		
Analog Outputs Total		5					5		
open collector (2) for 12 V PWM/PPM or digital inputs		2					-		
open collector for 12 V PWM/PPM		-					2		
0-10 V		2				;	3		
4-20 mA		1					_		
Digital Outputs Total		4				(6		
Relay 2 A, 230 Vac		4			5		3		5
open collector		-			1		1		1
SSR (3 A, 230 Vac)		-			-		2		-
Maximum I/Os expanded		22				4	4		
Compatible Secure Interface	TM172SIG	TM172SIG (5)	TM172SIG	TM172SIG	TM172SIG (5)	TM172SIG	TM172SIG	TM172SIG (5)	TM172SIG
Compatible expansion module		TM171EO14R				TM171EO15R	TM171EO22R		
Embeded RS485	1	-	1	1	-	1	1	-	1
communication LAN expansion bus portS		1					1		
Connection accessories references (sold in lots of 5)									
Low voltage connector		_				TM171ACB4OI1M			
Analog output connector		-				TM171ACB4OAO1M			
Modbus SL connector		-		TM171ACB4ORS485	-	TM171ACB4ORS485	TM171ACB4ORS485	-	TM171ACB4ORS485
LAN expansion bus connector		TM171ACB4OLAN				TM171A0	CB4OLAN		
				_					

- (1) Terminal blocks are supplied with TM1710BM14R, TM1710D14R, and TM1710DM14R.

 (2) Both I/O are the same. On the same channel: 2 digital inputs or 2 analog outputs (depending on the configuration).

 (3) Except for for TM1710DM22S: 12-24 Vac.

 (4) Connectors to be ordered separately, see page 35.

 (5) When controller is associated to a TM171AMB Communication module.

Application	Remote Displays (comp	eatible with each M171 Logic co	ontroller)						
	Constant	1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1		20					
Reference	TM171DLED	TM171DLCD2U	TM171DWAL2U	TM171DWAL2L	TM172DCLWT	TM172DCLWTH	TM172DCLWTHP	TM172DCLFW	TM172DCLFG
Type of mounting	Remote flush	Remote flush	Remote wall	Remote wall	Remote wall	Remote wall	Remote wall	Remote wall	Remote flush
Description	LED display Keyboard: 4 buttons	LCD display Keyboard: 7 buttons	LCD display Keyboard: 4 buttons Without backlight	LCD display Keyboard: 4 buttons With backlight	LCD display Color touchscreen Temperature	LCD display Color touchscreen Temperature, Relative humidity	LCD display Color touchscreen Temperature, Relative humidity Presence PIR	LCD display Color touchscreen IP65 (front face)	LCD display Color touchscreen IP65 (front face)
Programming software	EcoStru:	xure Machine Expert - HVAC V1.0	O or higher	EcoStruxure Machine Expert - HVAC V1.0 or higher					
Product certifications	C€, UL (reco	gnized), cURus, CSA, EAC, RCM	I, RoHS China.	CE, UL (recognized), cURus, CSA, EAC, RCM, RoHS China.					
Communication LAN expansion has			I AN expansion hus	LAN expansion hus Modhus SI					

Logic controllers for HVAC and Pumping applications

M171 Optimized logic controllers

M171 Optimized logic controllers

The M171 Optimized logic controllers comprise 10 models that can be used to control from 14 up to 22 embedded I/O (digital and analog).

- Two types of power supply are available:
 - 100-240 V \sim
 - 12-24 V \sim or 24 V =
- Two types of housing:
 - with built-in display
 - with remote display that can be added by means of the LAN expansion bus
- Two types of mounting:
 - Flush mounting: controllers to be mounted on a cabinet door
 - On 35 mm/1.38 in ur rail mounting: controllers to be mounted inside a cabinet
- Communication ports on M171 Optimized logic controllers:
 - One optional Modbus SL bus
 - One LAN expansion bus
- M171 Optimized logic controllers are certified C€, UL (recognized), cURus, CSA, EAC, RCM, RoHS China.

35 mm/1.38 in ∟r rail mounting

TM171O●14R Optimized logic controllers

- Display
- 2 Four navigation keys for setting controller parameters
- 3 Programming port (TTL)
- 4 Removable terminal block for RS 485 serial port (TM171O●M14R)
- 5 Wired connector for LAN expansion bus
- 6 Clip-on lock for 35 mm/1.38 in ∟ rail mounting
- 7 Removable terminal block for digital outputs
- 8 Removable terminal block for 100...240 V ∼ power supply
- 9 Removable terminal block for I/O



- 1 Display
- Four navigation keys for setting controller parameters
- 3 Programming port (TTL)
- Wired connector for RS 485 serial port (TM1710•M14R)
- 5 Clip-on lock for 35 mm/1.38 in __rail mounting
- 6 Removable terminal block for outputs
- 7 Wired connector for 12-24 V \sim or 24 V = power supply, and for low voltage I/O
- 8 Wired connector for analog output
- Wired connector for LAN expansion bus



Flush mounting

TM171OF●22R● Optimized logic controllers (1)

- 1 Displa
- 2 Four navigation keys for setting controller parameters
- Wired connector for RS 485 serial port (TM1710F•M22R)
- Wired connector for analog outputs
- 5 Wired connector for LAN expansion bus
- 6 Programming port (TTL)

⁽¹⁾ Connectors to be ordered separately, see page 35.



Logic controllers for HVAC and Pumping applications

M171 Optimized logic controllers



TM1710BM14R



TM1710D14R



TM1710DM14R



TM1710BM22R





TM1710DM22R



M17	71 Optimized logi	c controllers: Pov	ver supply: 100-2	240 V \sim		
No.	31.		Embedded	Display	Reference	Weight
of I/O	Inputs	Outputs	communication			kg/ <i>lb</i>
35 n	nm/1.38 in 🖵 rail moເ	ınting (1)				
14	2 digital inputs: ■ 2 open collector or digital inputs (2) 5 configurable analog	4 digital outputs: ■ 3 SPST (2 A, 230 V ∼) with the same common ■ 1 SPDT (2 A, 230 V ∼)		Remote display (optional)	TM171OBM14R	0.190/ <i>0.420</i>
	inputs: 3 NTC, or PT1000, or digital inputs	5 analog outputs: ■ 2 open collector (2) for 12 V PWM/PPM				
	■ 2 NTC, or 0-20 mA, or 4-20 mA, or 0-10 V, or 0-5 V, or 0-1 V, or digital inputs	or digital inputs ■ 2 x 0-10 V ■ 1 x 4-20 mA	■ 1 LAN expansion bus	Built-in display	TM1710D14R	0.190/ <i>0.420</i>
			■ 1 RS485 ■ 1 LAN expansion bus	Built-in display	TM171ODM14R	0.190/ <i>0.420</i>

35 r	nm/1.38 in ∟r rail mou	nting				
22	6 digital inputs: ■ 6 volt-free in 1 group 5 configurable analog inputs: ■ 3 NTC or digital inputs	■ 3 SPST (2A, 230 V ∼) with the same common ■ 2 SPST (2A, 230 V ∼) with independent		Remote display (optional)	TM171OBM22R	0.190/ 0.420
	■ 2 NTC, or 0-20 mA, or 4-20 mA, or 0-10 V, or 0-5 V, or 0-1 V, or digital inputs	common 1 open collector 5 analog outputs: 2 open collector for 12 V PWM/PPM 3 x 0-10 V	■ 1 LAN expansion bus	Built-in display	TM171OD22R	0.190/ 0.420
			■ 1 RS485 ■ 1 LAN expansion bus	Built-in display	TM171ODM22R	0.190/ 0.420
		6 digital outputs: ■ 3 SPST (2 A, 230 V ~) with the same common ■ 2 SSR (3 A, 230 V ~) ■ 1 open collector		Built-in display	TM171ODM22S	0.190/ 0.420
		5 analog outputs: ■ 2 open collector for 12 V PWM/PPM ■ 3 x 0-10 V				
Flu	sh mounting					
22	6 digital inputs:	6 digital outputs:	■ 1 LAN expansion bus	Built-in display	TM1710F22R	0.164/

22	6 digital inputs: ■ 6 volt-free in 1 group	6 digital outputs: ■ 3 SPST (2 A, 230 V ~)	■ 1 LAN expansion bus	Built-in display	TM171OF22R	0.164 <i>i</i> 0.360
	5 configurable analog inputs: ■ 3 NTC	with the same common ■ 2 SPST (2 A, 230 V ~) with independent				
	or digital input ■ 2 NTC, or 0-20 mA, or 4-20 mA, or 0-10 V, or 0-5 V, or 0-1 V, or digital inputs	common 1 open collector	■ 1 RS485 ■ 1 LAN expansion bus	Built-in display	TM171OFM22R	0.164/ 0.360
		5 analog outputs: ■ 2 open collector for 12 V PWM/PPM ■ 3 x 0-10 V				

Remote display to	i with Optimized logic controllers							
Remote displays	See page 35							
Connection accessories for M171 Optimized logic controllers								
Connectors	Low voltage connector, Analog output connector, Modbus SL connector, LAN expansion bus connector	See page 35						

- (1) Terminal blocks are supplied with TM1710BM14R, TM1710D14R, and TM1710DM14R.
- (2) Both I/O are the same. On the same channel: 2 digital inputs or 2 analog outputs (depending on the configuration).
 (3) Except for for TM1710DM22S: 12-24 V ~.
 (4) Connectors to be ordered separately, see page 35.

Logic controllers for HVAC and Pumping applications

I/O expansion modules for M171 Optimized controllers

I/O expansion modules

Three I/O expansion modules are available to increase the number of I/O up to 44 on M171 Optimized logic controllers:

- Expanded I/O types are digital and analog
- I/O expansion modules are connected via the LAN expansion bus on M171 Optimized logic controllers
- I/O expansion modules compatibilty:

Logic controller type	Reference	Compatible I/O expansion module (reference)
M171 Optimized	TM1710BM14R, TM1710D14R, TM1710DM14R	TM171EO14R
	TM171OBM22R, TM171OD22R, TM171ODM22R,	TM171EO15R
	TM1710DM22S, TM1710F22R, TM1710FM22R	TM171EO22R



TM171EO●●R expansion modules (1)

35 mm/1.38 in ∟ rail mounting

- 1 Service port (TTL)
- Wired connector for removable terminal block for Modbus SL
- 3 Connector for removable terminal block for digital outputs
- 4 Wired connector for removable terminal block for power supply (12-24 V ~ or 24 V ==),
- 5 Wired connector for low voltage I/O
- 6 Clip-on lock for 35 mm/1.38 in _r rail mounting
- 7 Wired connector for removable terminal block for analog outputs
- Wired connector for removable terminal block for LAN expansion bus

(1) Removable terminal blocks to be ordered separately, except for TM171EO14R.



TM171EO14R



TM171EO15R



TM171EO22R



Connection accessories (2) for expansion modules: TM171EO15R, M171EO22R

35 n	nm/1.38 in 🖵 rail mour	nting				
No. of I/O	Number and type of channels		Compatibility	Embedded	Reference	Weight
	Inputs	Outputs		communication port		kg/ <i>lb</i>
14	2 digital inputs: 2 open collector or digital inputs (1) 5 configurable analog	■ 4 digital outputs: ■ 3 SPST (2 A, 230 V ∼) with the same common ■ 1 SPDT (2 A, 230 V ∼)	TM1710BM14R, TM1710D14R, TM1710DM14R	■ 1 LAN expansion bus	TM171EO14R	0.190/ <i>0.420</i>
	inputs: ■ 3 NTC or digital inputs ■ 2 NTC, or 0-20 mA, or 4-20 mA, or 0-10 V, or 0-5 V, or 0-1 V, or digital inputs	5 analog outputs: ■ 2 open collector for 12 V PWM/PPM or digital inputs (1) ■ 2 x 0-10 V ■ 1 x 4-20 mA				
15	6 digital inputs: volt-free 3 analog inputs: NTC or digital inputs	4 digital outputs: ■ 3 2 A, 250 V ~ ■ 1 open collector 2 analog outputs:	TM1710BM22R, TM1710D22R, TM1710DM22R, TM1710DM22S,	expansion bus	TM171EO15R	0.190/ <i>0.420</i>
22	6 digital inputs:	open collector (PPM/PWM) 6 digital outputs:	TM1710F22R, TM1710FM22R TM1710BM22R,	= 11 AN	TM171EO22R	0.190/
22	volt-free	■ 5 2 A, 250 V ∼ ■ 1 open collector	TM1710DM22R, TM1710DM22R, TM1710DM22R,	expansion bus	TWITT IEO22K	0.190/
	5 analog inputs: ■ 3 NTC or digital inputs ■ 2 NTC, or 0-20 mA, or 4-20 mA, or 0-10 V, or	5 analog outputs: 2 open collector (PPM/PWM)	TM1710DM22S, TM1710F22R, TM1710FM22R			

Accessories for I/O expans	sion modules			
Designation	Description	Cable length (m/ft.)	Unit reference	Weight kg/lb
Accessories to be ordered sep	parately			
Analog output connector (0-10 V outputs)	Cordset equipped with a 4-pin connector at one end	1/3.3	TM171ACB4OAO1M	0.075/ <i>0.170</i>
Sold in lots of 5 (item 1)		2/6.6	TM171ACB4OAO2M	0.125/ <i>0.280</i>
Low voltage connector Sold in lots of 5 (item 2)	Screw terminal block and a cordset equipped with a 20-pin connector at one end	1/3.3	TM171ACB4OI1M	0.575/ 1.270
		2/ 6.6	TM171ACB4OI2M	1.120/ 2.470
Accessory - Supplied with each	ch expansion module			
LAN expansion bus connector Sold in lots of 5 (item 3)	Cordset equipped with a 3-pin connector at each end	2/6.6	TM171ACB4OLAN	0.060/ <i>0.130</i>

⁽¹⁾ On the same channel: 2 digital inputs or 2 analog outputs (depending on the configuration).

■ 3 x 0-10 V

(2) Minimum set for operating controllers.

digital inputs

Presentation, references

Modicon M171/M172/M173

Logic controllers for HVAC and Pumping applications

Remote displays, Connection accessories for M171 Optimized logic controllers

Remote displays for M171 Optimized logic controllers

The four available remote displays are distinguished by technology and type of mounting.

- Technology: LED display or LCD display, with or without backlight
- Mounting: flush mounting or wall mounting

The remote displays are connected to the LAN expansion bus which provides the power supply.

Туре	Description	Reference	Weight kg/ <i>lb</i>
Remote flush mounting displays With realtime clock	 LED display: 4 digits,7 segments Keyboard: 4 buttons Communication port: 1 for LAN expansion bus – with wired connector (1) or screw terminal blocks 	TM171DLED	0.042/ 0.090
	 LCD display (with segments) Keyboard: 7 buttons Flush mounting Communication port: 1 for LAN expansion bus – with screw terminal blocks 2 analog inputs: 1 NTC or digital input 1 NTC or 4-20 mA or digital input 	TM171DLCD2U	0.170/ 0.370
Remote wall mounting displays With realtime clock	■ Without backlight	TM171DWAL2U	0.143/ 0.320
	■ With backlight	TM171DWAL2L	0.143/ 0.320

with realtime clock					
		■ With backlight		TM171DWAL2L	0.143/ 0.320
Connection to be ordered		essories for M171 (parately	Optimi	zed logic contro	ollers
Туре	Item	Description	Cable length (m/ft.)	Unit reference	Weight kg/lb
Low voltage connector Sold in lots of 5	1	Screw terminal block and a cordset equipped with a 20-pin connector at one end	1/3.3	TM171ACB4OI1M	0.575/ 1.270
			2/6.6	TM171ACB4OI2M	1.120/ 2.470
Analog output connector (0-10 V outputs) Sold in lots of 5	2	Cordset equipped with a 4-pin connector at one end	1/3.3	TM171ACB4OAO1M	0.075/ 0.170
			2/6.6	TM171ACB4OAO2M	0.125/ 0.280
Modbus connector Sold in lots of 5	• 3	Cordset equipped with a 3-pin connector at one end	1/3.3	TM171ACB4ORS485 (3)	0.052/ 0.110
LAN expansion bus connector Sold in lots of 5	4	Cordset equipped with a 3-pin connector at each end	2/6.6	TM171ACB4OLAN	0.060/ 0.130
LAN Communication adaptor Supplied with removable terminal blocs for bus		LAN-RS485 converter (accessory which allows to connect Modbus devices through the LAN connector of the M171 Optimized		TM171ALAN	0.170/ 0.374

(1) Supplied with LAN expansion bus connector TM171ACB4OLAN.

controller)

- (2) Minimum set for operating controllers.
- (3) This product is only compatible for modbus version of M171 Optimized 22 I/Os.



TM171DLED (1)



TM171DLCD2U



TM171DWAL2U



TM171DWAL2L



Connection accessories (2)

for M171 Optimized logic controller (rail mounting): TM1710BM22R, TM1710D22R, TM1710DM22R and TM1710DM22S For M171 Optimized logic controller (flush mounting): TM1710F22R and TM1710FM22R







Connection accessories (2) for M171 Optimized logic controller (rail mounting): TM1710BM14R, TM1710D14R, TM1710DM14R

N.B.: terminal blocks are supplied with

TM1710BM14R, TM1710D14R, and TM1710DM14R



TM171ALAN

connections

Logic controllers for HVAC and Pumping applications

M171 Performance logic controllers

M171 Performance logic controllers

M171 Performance logic controllers comprise 4 models that can be used to control from 3 up to 27 embedded I/O (digital and analog).


- Power supply: 24 V \eqsim or 48 V ==
- Two types of housing:
 - with built-in display
 - without display

Each controller includes a connection (through the CAN expansion bus or through Modbus SL) for a remote display, available in the catalog.

- Two types of mounting:
 - On 35 mm/1.38 in \perp r rail mounting: controllers to be mounted inside a cabinet
 - Flush mounting: controllers to be mounted on a cabinet door or wall-mounted using the wall bracket accessory;
- Communication ports on M171 Performance logic controllers:
 - One Modbus SL client/server
 - Two USB
 - One CAN expansion bus

On flush mounting version:

- One Modbus SL client/server
- One Modbus TCP and BACnet IP (B-AAC profile) (WebVisu)
- One CAN expansion bus
- M171 Performance logic controllers can be connected to communication modules, adding another connection for the CAN expansion bus, Ethernet network, or Profibus, etc., see page 42.
- M171 Performance logic controllers are certified C€, cURus (UL Recognized), CSA, EAC, RCM, RoHS China.



TM171P●M27● Performance logic controllers (1)

- 1 Connector for removable terminal block for digital inputs
- 2 Connector for removable terminal block for analog inputs
- 3 Connector for removable terminal block for Modbus SL
- 4 Connector for removable terminal block for CAN expansion bus
- 5 4-position DIP switches for address selection
- Five control keys for setting controller parameters
- 7 Connector for removable terminal block for power supply (24 V ₹, 48 V ==)
- 8 Connector for removable terminal block for fast digital inputs (high speed counter)
- Connector for removable terminal block for digital outputs
- 10 Connector for removable terminal block for analog outputs
- 11 Mounting clips for 35 mm/1.38 in _ rail mounting
- 12 On TM171PDM27●: display

On TM171PBM27R: 6- and 10-position DIP switches, behind a front panel

Behind the removable protective cover: 13 and 14

- 13 USB-B port to connect a PC
- 14 USB-A port for USB stick
- 15 Connector for communication module
- 16 Three status LEDs




TM171PFE03R●●● Performance logic controllers (2)

- 1 Displa
- 2 Three status LEDs
- 3 Five control keys for setting controller parameters

On the rear side of the controller

- 4 Terminal block for power supply (24 V \(\sigma\) or 48 V \(\sigma\).
- 5 Terminal block for CAN expansion bus
- 6 Terminal block for Modbus SL
- 7 Terminal block for analog input
- 8 RJ45 connector for Ethernet
- 9 Built-in NTC sensor (analog)



(2) Terminal blocks supplied with flush mounting version of Performance controllers.





Logic controllers for HVAC and Pumping applications

M171 Performance logic controllers



35 I No. of I/O 27

No.

of I/O

TM171PBM27R



TM171PDM27R



TM171PDM27S

171 Performance logic controllers: Power supply: 24 V 元, 48 V							
mm/1.38 in ∟ rail mounting							
	Number and type of cha Inputs	nnels Outputs	Embedded communication port	Display	Reference	Weight kg/lb	
	9 digital inputs (8 + 1): ■ 2 groups of 4 digital inputs, 24 V ¬ or 48 V ¬ ■ 1 fast digital input, or high speed counter volt-free	7 digital outputs: ■ 2 SPDT (8 A, 230 V ~) with independent common ■ 5 SPST (5 A, 230 V ~) with independent common	■ 1 RS485 ■ 1 CAN expansion bus	Remote display (optional)	TM171PBM27R	0.385/ 0.850	
	6 configurable analog inputs: ■ 2 NTC or digital inputs, ■ 4 NTC, or PT1000, or 4-20 mA, or 0-5 V, or 0-10 V, or 0-30 kΩ/0-5 kΩ variable resistor, or digital inputs	5 analog outputs: ■ 3 x 0+10 V or 4-20 mA ■ 2 x 0+10 V, or 4-20 mA, or digital output open collector		Built-in display 128x64 LCD with backlight	TM171PDM27R	0.385/ 0.850	
		7 digital outputs: ■ 2 SPDT (8 A, 230 V ~) with independent common ■ 3 SPST (5 A, 230 V ~) with independent common ■ 2 SSR (1 A, 230 V ~) outputs 5 analog outputs: ■ 3 x 0+10 V or 4-20 mA ■ 2 x 0+10 V, or 4-20 mA, or digital output open collector	■ 1 RS485 ■ 1 CAN expansion bus	Built-in display	TM171PDM27S	0.385/ 0.850	



TM171PFE03



1

TM171ABKPB

■ 1 built-in NTC ■ 1 NTC or digital inp ■ 1 x 4-20 mA or 0-10			
Accessories for M171	Performance logic controllers to be ordered separately		
Designation	Use	Reference	Weight kg/lb
Screw terminal blocks	For TM171PBM27R, TM171PDM27R, and TM171PDM27S	TM171ASCTB27	0.100/

Embedded

■ 1 RS485

communication port

■ 1 CAN expansion bus

Display

Built-in

display

Reference

TM171PFE03

Weight

kg/lb

0.320/ 0.710

200.9.1			kg/ <i>lb</i>
Screw terminal blocks	For TM171PBM27R, TM171PDM27R, and TM171PDM27S	TM171ASCTB27	0.100/ <i>0.220</i>
Wall bracket for flush mounting Performance logic controllers	For TM171PFE03	TM171ABKPB	0.015/ 0.030

Flush mounting (to be used with the wall bracket accessory – see below)

Number and type of channels

3 configurable analog

inputs:

Logic controllers for HVAC and Pumping applications

I/O expansion modules

I/O expansion modules

Two I/O expansion modules are available to increase the number of I/O:

- up to 351 on M171 Performance logic controllers
- up to 366 on M172 logic controllers
- up to 78 on M173 Optimized logic controllers
- Expanded I/O types are digital and analog
- They are connected via the CAN expansion bus on M171 Performance, M172 and M173 Optimized logic controllers
- I/O expansion modules compatibility:

Logic controllers	Compatible I/O expansion module (reference)
M172 Optimized (TM172O••••)	TM171EP14R, TM171EP27R
M172 Performance (TM172P●●●●)	TM171EP14R, TM171EP27R
M171 Performance (TM171P●●●●)	TM171EP14R, TM171EP27R
M173 Optimized (TM173O••••)	TM171EP14R, TM171EP27R

■ They are certified C€, UL, CSA, EAC, RoHS China

35 mm/1.38 in _rail mounting I/O expansion modules

TM171EP27R expansion module (1)

- 1 Connector for removable terminal block for digital inputs
- 2 Connector for removable terminal block for analog inputs
- 3 Connector for removable terminal block for Modbus SL
- 4 Connector for removable terminal block for CAN expansion bus
- 5 4-position DIP switches for address selection
- 6 Connector for removable terminal block for power supply (24 V 元, 48 V =)
- 7 Connector for removable terminal block for fast digital inputs
- 8 Connector for removable terminal block for digital outputs
- 9 Connector for removable terminal block for analog outputs
- 10 Clip-on lock for 35 mm/1.38 in ⊥r rail mounting
- 11 6- and 10-position DIP switches for address selection
- 12 3 status LEDs

TM171EP14R expansion module (1)

- 1 4-position DIP switches
- 2 Connector for removable terminal block for CAN expansion bus
- 3 Removable terminal block for digital outputs
- 4 Behind the removable protective cover: Service port (TTL)
- 5 Connector for low voltage I/O
- 6 Clip-on lock for 35 mm/1.38 in ¬ rail mounting
- 7 Connector for removable terminal block for power supply (24 V ≂)

(1) Removable terminal blocks to be ordered separately, see page 39.





Logic controllers for HVAC and Pumping applications I/O expansion modules





TM171EP27R


I/O	expansion module	es				
	nm/1.38 in 🖵 rail moui	•				
No. of I/O	Number and type of cha Inputs	outputs	Compatibility with logic controller	Embedded communication port	Reference	Weight kg/ <i>lb</i>
14	4 digital inputs: $4 \times 24 \text{ V} \sim \text{or } 24 \text{ V} = (1)$ 4 analog inputs: (configurable in pairs) 4 NTC, or PT1000, or PTC, or 4-20 mA, or 0-5 V, or 0-10 V, or digital inputs	4 digital outputs: ■ 1 SPDT (5 A, 230 V ~) with independent common ■ 3 SPST (3 A, 230 V ~) with independent common 2 analog outputs: ■ 2 x 0-10 V (1)	TM171P•••• TM172•••• TM173O••••	■ 1 CAN expansion bus	TM171EP14R	0.190/ <i>0.420</i>
27	9 digital inputs (8 + 1): ■ 2 groups of 4 digital inputs, 24 V ≂ or 48 V ≕ ■ 1 fast digital input or high speed counter, volt-free	7 digital outputs: ■ 2 SPDT (8 A, 230 V ~) with independent common ■ 5 SPST (5 A, 230 V ~) with independent common	TM171P•••• TM172•••• TM173O••••	■ 1 CAN expansion bus	TM171EP27R	0.385/ 0.850
	6 analog inputs: ■ 2 NTC or digital inputs ■ 4 NTC, or 4-20 mA, or 0-10 V, or digital inputs	5 analog outputs: ■ 5 x 0-10 V, or 4-20 mA				



Accessories for I/O expans	sion modules to be ordered separately		
Designation	Description	Unit reference	Weight kg/lb
Screw terminal blocks (inputs, outputs, and communication bus)		TM171ASCTB14	0.050/ <i>0.110</i>
	27 I/O – For TM171EP27R	TM171ASCTB27	0.100/ 0.220


⁽¹⁾ On the same channel: 2 digital inputs or 2 analog outputs (depending on the configuration). (2) Minimum set for operating controllers.

Logic controllers for HVAC and Pumping applications Secure Interfaces




M173 Optimized logic controller and Plug-in Interface for secure Ethernet communication:

- Secure connection via HTTPs (TLS1.2) to the webserver
- Secure email SMTPs (TLS1.2) Secure file transport protocol FTPs (TLS1.2)



M172 Performance logic controller and Plug-in Interface for:

- Secure connection via HTTPs (TLS1.2) to the webserver
- Secure email SMTPs (TLS1.2)
- Secure file transport protocol FTPs (TLS1.2)



M171Optimized / M172 Performance logic controllers and Gateway Interface for cybersecure connection to the cloud for machine monitoring

Secure Interfaces

TM172SI Secure Interfaces are designed to establish a secure Internet connection, and to connect unsafe devices to a secure Ethernet network.

Two versions are available to perform different types of secured operations, and compatible with existing machines or installations.

- TM172SIP: Plug-in version for M173 Optimized and M172 logic controllers
 - to send files to an FTPs server (when related to Secure Interfaces only), to reply to an FTPs client (having an FTPs server)
 - to send e-mails to providers using secure encryption algorithms
 - to manage SNMP protocol, that allows to exchange Object ID information relating to SNMP protocol in an Ethernet network
 - to access the machine via a secure webserver.
- TM172SIG: Gateway version to ensure a cyberSecure connection on M173 Optimized and M172 logic controllers, and On M171 Optimized logic controllers via the Modbus communication module.
- It is possible to create programs within TM172SI Secure Interfaces that allow the PLC to be able to find variables or parameters in connected devices, and to save files through micro SD, USB memory key or in the NAND flash memory of TM172SI. Secure Interfaces.
- Secure Interface compatibilty:

Logic controller type	Reference	Compatible Secure Interface (reference)
M173 Optimized	TM173ODM22S, TM173ODM22R, TM173OBM22R	TM172SIG TM172SIP
M172	TM172OBM18R, TM172ODM18R, TM172OBM28R, TM172ODM28R, TM172ODM28R, TM172ODM42R, TM172PBG07R, TM172PBG18R, TM172PBG18R, TM172PDG18S, TM172PDG18S, TM172PDG28R, TM172PDG28RI, TM172PDG28RI, TM172PDG28RI, TM172PDG42R, TM172PDG42R, TM172PDG42R, TM172PDG42R, TM172PDG42R, TM172PDG42RI, TM172PDG42RI, TM172PDG42RI, TM172PDG42RI, TM172PDG42RI, TM172PDG42RI, TM172PDG42RI, TM172PDG42RI, TM172PDG42RI, TM172PDG42RI	TM172SIG TM172SIP
M171 Optimized	TM1710BM14R, TM1710DM14R, TM1710BM22R, TM1710DM22R, TM1710DM22S, TM1710FM22R	TM172SIG
M171 Optimized (when controller is associated to TM171AMB Modbus communication module)	TM1710D14R, TM1710D22R, TM1710F22R	TM172SIG

- EcoStruxure Machine Expert HVAC programming software is available to program and customize applications in association with M171, M172 and M173 logic controllers.
- The Secure Interfaces are certified C€, UL, CSA, EAC, RCM, UKCA.
- Secure Interface Security
 - The TM172SI

 Secure Interfaces are designed to meet cybersecurity requirements in accordance with the standard IEC 62443-4-1 (2020 edition).
 - Within the TM172SI interface, you can enhance cybersecurity by the following methods:
 - Configure user rights
 - Disable unused services (for example, FTP, HTTP).
 - Follow the Recommended Cybersecurity Best Practices | Schneider Electric

Logic controllers for HVAC and Pumping applications Secure Interfaces

Secure Interfaces

35 mm/1.38 in _rail mounting Secure Interfaces (1)

- Connector for removable terminal block for power supply (24 V ≂)
- TTL communication port to logic controller (Only on TM172SIP)
- Memory card slot (Micro SD)
- Programmable LEDs (red, yellow, green)
- Power LED (green)
- USB-B port
- USB A port
- Ethernet ports (2x RJ45)
- Serial line port (RS485) (Only on TM172SIG)



TM172SIP



Designation	Description	Reference	Weight kg/ <i>lb</i>
Secure Interface Plug-in (1)	Size: 4 DIN (2) Double Ethernet port with switch capabilities Equipped with a intergrated TTL communication port, to communicate with the controller	TM172SIP	0.165 <i>0.</i> 363
Secure Interface Gateway (1)	Size: 4 DIN (2) Double Ethernet port with switch capabilities Equipped with a RS485 serial port used to communicate with a controller via a Modbus RTU connection	TM172SIG	0.165 0.363

⁽¹⁾ Removable screw terminal blocks are included with TM172SI•. (2) 4 DIN: Interface width is 72 mm (2.83 in).

Logic controllers for HVAC and Pumping applications

Communication modules

Communication modules

The communication module offer is dedicated to M171 Performance, and M172 logic controllers (1).

The 8 optional modules provide specific connections:

- To fieldbuses, including:
 - CAN bus
 - Modbus TCP
 - Profibus
 - Modbus SL (RS 485)
 - BACnet MS/TP (B-AAC profile)
 - BACnet IP (B-AAC profile)
 - RS 232 serial link
 - LonWorks (FFT-10)
 - Konnex (KNX) via Schneider Electric' spaceLYnk gateway (1)
- To services, including:
 - Ethernet
 - WebVisu and remote download functions
- They are mounted by simply interlocking on the left-hand side of M171 Performance or M172 logic controllers (1). Only one communication module can be added to a logic controller.
- The communication module is powered by the controller.
- Each communication module has its own type of connector, adapted to the bus or communication network, see page 43.
- Communication modules compatibilty:

Logic controllers	Compatible Communication modules (reference)
M172 Optimized (TM172O••••)	TM171ACAN, TM171AMB, TM171ARS485, TM171ARS232, TM171ALON, TM171AETH, TM171AETHRS485
M172 Performance (TM172P••••)	TM171ACAN, TM171AMB, TM171ARS485, TM171ARS232, TM171ALON
M171 Optimized (TM171O••••)	-
M171 Performance (TM171P••••)	TM171ACAN, TM171AETH, TM171APBUS, TM171AMB, TM171ARS485, TM171ARS232, TM171AETHRS485, TM171ALON





TM171A • • • communication modules

- 1 Communication connector (2)
- 2 Locking device
- 3 Expansion connector to the controller
- Clip-on lock for 35 mm/1.38 in ∟r rail mounting

(1) spaceLYnk offer: please consult the offer on our website.

(2) The communication connector type depends on the communication modules, see page 43.

Logic controllers for HVAC and Pumping applications Communication modules

	35 mm/1.38 in ∟ rail mou	ntina				
	Fieldbus, services access	Compatibility with logic controller	Communication port	Reference	Weight kg/lb	
	■ CAN	M172 Optimized, M172 Performance, M171 Performance	■ 2 screw terminal blocks (1)	TM171ACAN	0.077 0.17	
	 Modbus TCP Ethernet BACnet IP (B-AAC profile) WebVisu and remote download functions 	M171 Performance M172 Optimized,	■ 1 RJ45	TM171AETH	0.077 <i>0.17</i>	
	■ Profibus	M171 Performance,	■ 1 SUB-D 9	TM171APBUS	0.077 <i>0.17</i>	
	■ Modbus SL (RS485)	M172 Optimized, M172 Performance, M171 Performance	■ 2 screw terminal blocks (1)	TM171AMB	0.077 0.17	
	■ Modbus SL or BACnet MS/TP (B-AAC profile)	M172 Optimized, M172 Performance, M171 Performance	■ 2 screw terminal blocks (1)	TM171ARS485	0.077 <i>0.17</i> 6	
	■ RS 232 serial link ■ Relay output	M172 Optimized, M172 Performance, M171 Performance	■ 1 SUB-D 9 for RS 232 ■ 1 screw terminal block for relay output (1)	TM171ARS232	0.077 0.17	
·	 Modbus TCP and BACnet/IP Modbus SL or BACnet MS/TP (B-AAC profile) WebVisu and remote download functions Ethernet 		■ 1 RJ45 for Ethernet ■ 2 screw terminal blocks for RS485 (1)	TM171AETHRS485	0.077 0.17	
3485	■ LonWorks (FFT-10)	M172 Optimized, M172 Performance, M171 Performance	■ 1 screw terminal block for LON bus	TM171ALON	0.077 <i>0.17</i>	

⁽¹⁾ Removable terminal blocks supplied with communication modules.

M172 EEVD

M171 EEVD

Modicon M171/M172/M173

Logic controllers for HVAC and Pumping applications

Electronic expansion valve drivers


Electronic expansion valve drivers

Electronic expansion valves drivers are specifically designed to control electronic expansion valves used in various types of refrigeration systems.

They regulate the superheat level by modulating the valve position and can be used with various type of refrigerants and for many applications, from small residential unit to large HVAC systems. The control system optimizes the superheat control and increase the energy savings of the unit.

Two versions of drivers:


- TM172EVEV1•: Electronic Expansion Valve Drivers that are used in combination with M172 logic controllers. The pressure and temperatures sensors are wired to the controller which manages the control algorithm. The user has the choice to use preprogrammed superheat functions or to create his own control algorithm. This provides a very optimized and flexible solution.
 - Several versions are available depending of the valve technology (unipolar or bipolar) and the number of valves to control (single or dual valves). Those drivers are compatible with the battery backup which provides energy to close the valve in case of power failure.
- TM171VEVM4: Superheat Electronic Expansion Valve Driver that can be used independently to any other controller. The temperature and pressure sensors are directly wired to the driver and the embedded control algorithm regulates the superheat. This driver is equipped with Modbus SL communication which allows to communicate with the M171 and M172 logic controllers or third party Modbus devices for remote monitoring and setting configuration.
- Electronic expansion valve drivers compatibilty:



■ They are certified C€, UL, CSA, EAC, RoHS China



TM172EVEV1U, TM172EVEV1B



10 2 3 3 5 6 7 7 8 8

TM171VEVM4

35 mm/1.38 in ∟ rail mounting

TM172EVEV1UTM172EVEV1B, TM172EVEV2B (1)

- 1 Valve Outputs terminal block CN2, CN3
- 2 Power supply terminal block CN4
- 3 Battery backup connector
- 4 CAN Expansion bus port terminal block CN1
- 5 Clip-on lock for 35 mm/1.38 in ∟ rail
- 6 Dip switch
- 7 TTL programming port
- 8 Status LEDs

TM171VEVM4 (1)

- 1 Output terminal block and power supply connector (24 V ≂)
- 2 Protective cover
- 3 Status LEDs

Behind the removable protective cover:

- 4 6-position DIP switches
- **5** Status LED (for operation with TM171AMFK programming stick)
- 6 LAN serial port for connecting TM171DLED remote display
- 7 Terminal block for analog/digital inputs
- 8 Clip-on lock for 35 mm/1.38 in ⊥r rail mounting
- 9 Modbus (RS 485) port
- 10 TTL programming port

⁽¹⁾ Screw terminal blocks are delivered with electronic expansion valve drivers.

Logic controllers for HVAC and Pumping applications

Electronic expansion valve drivers



TM172EVEV1U

Electronic expans	sion vaive drivers			
M172 EEVD				
Application	Communication port	Size (3)	Reference	Weight kg/ <i>lb</i>
EEVD for single valve unipolar (1) (2)	CAN expansion Bus	2 DIN	TM172EVEV1U	0.087/ 0.191



TM172EVEV1B

EEVD for single valve bipolar (1) (2)	CAN expansion Bus	2 DIN	TM172EVEV1B	0.089/ <i>0.196</i>



TM172EVEV2B

EEVD for dual valves bipolar	CAN expansion Bus	4 DIN	TM172EVEV2B	0.119/
(1) (2)				0.262



TM171VEVM4

M171 EEVD				
Application	Number and type of channels		Reference	Weight
	Inputs	Outputs		kg/ <i>lb</i>
Superheat EEVD RS485 for Modbus SL, for single valve Size: 4 DIN (2) (3)	2 digital inputs: ■ 2 volt-free 4 analog inputs: ■ 2 NTC ■ 2 PT1000, 4-20 mA, or 0-5 V, or 0-10 V	2 digital outputs: ■ 1 open collector (100 mA, 12 V····) ■ 1 SPST NO relay contact, 5 A, ~ 250 V	TM171VEVM4	0.190/ 0.420



Accessories for electronic expansion valve drivers: to be ordered separately						
Designation	Use	To use with	Reference	Weight kg/ <i>lb</i>		
Battery backup	To provide power when the primary source of power is unavailable.	TM172EVEV1U TM172EVEV1B TM172EVEV2B	TM172EVEVBAT	0.157/ 0.346		

⁽¹⁾ Compatible with Battery backup TM172EVEVBAT.
(2) Removable screw terminal blocks are included with M172 /M171 EEVD.
(3) in 2 DIN: controller width is 36 mm (1.41 in) in 4 DIN: controller width is 72 mm/2.83 in).

Logic controllers for HVAC and Pumping applications Measurement accessories: Temperature and Humidity control

Temperature and I	lumidity co						
Designation		Use	Description	Cable length	Unit reference	Sold in	Weight
		■ Applications	ID 00	m (ft)		lots of (1)	kg/lb
NTC probes			- IP 68 - Grey	1.5 <i>(4.92)</i>	TM1STNTCRN52015		0.144/0.32
		Temperature control.	- Equipped with 2 conductor		TM1STNTCRN5201P		0.144/0.32
		= 301110 G (=122230 T)	cables for controller side	3 (9.84)	TM1STNTCRN52030		0.180/0.40
					TM1STNTCRN5203P		0.180/0.40
				5 (16.40)	TM1STNTCRN52050	4	0.228/0.50
			- IP 67	1.5 <i>(4.92)</i>	TM1STNTCRN61515	8	0.104/0.23
		Temperature control:	BlackEquipped with 2 conductor		TM1STNTCRN6151P	100	0.104/0.23
		- 50+110 °C (-122230 °F)	cables for controller side	3 (9.84)	TM1STNTCRN61530	5	0.125/0.28
	_	•			TM1STNTCRN6153P	50	0.125/0.28
				5 (16.40)	TM1STNTCRN61550	4	0.164/0.36
					TM1STNTCRN6155P	25	0.164/0.36
		Multi-purpose	- FAST	1.5 (4.92)	TM1STNTCSF44015	8	0.144/0.32
		■ Temperature control:	- IP 67	3 (9.84)	TM1STNTCSF44030	5	0.175/0.39
		- 50+110 °C (-122230 °F)	 Grey Equipped with 2 conductor cables for controller side 		TM1STNTCSF4403P	50	0.175/0.39
		Multi-purpose	- IP 68	1.5 (4.92)	TM1STNTCSN62015	8	0.144/0.32
			- Grey	,/	TM1STNTCSN6201P		0.144/0.32
		-50+110 °C (-122230 °F)	- Equipped with 2 conductor	3 (9.84)	TM1STNTCSN62030		0.175/0.39
			cables for controller side	0 (3.04)	TM1STNTCSN6203P		0.175/0.39
				F (16 10)			
				5 (16.40)	TM1STNTCSN62050		0.232/0.51
					TM1STNTCSN6205P		0.232/0.51
NTC probes with a strap			- IP 68 - Grey	1.5 <i>(4.92)</i>	TM1STNTCTN62015		0.152/0.34
опар	8	Temperature control:	- Equipped with 2 conductor		TM1STNTCTN6201P		0.152/0.34
	000000	- 50+110 °C (-122230 °F)	cables for controller side	3 (9.84)	TM1STNTCTN62030	5	0.180/0.40
PT1000 probes		Multi-purpose	- IP 68	1.5 (4.92)	TM1STPTTSN62015	8	0.144/0.320
		■ Temperature control:	- Green	()	TM1STPTTSN6201P		0.144/0.32
		- 50+110 °C (-122230 °F)	- Equipped with 2 conductor	3 (9.84)	TM1STPTTSN62030		0.175/0.320
		≡	cables for controller side	3 (3.04)			
				- (10 10)	TM1STPTTSN6203P		0.175/0.39
				5 (16.40)		4	0.232/0.51
					TM1STPTTSN6205P		0.232/0.51
			- IP 68	1.5 <i>(4.92)</i>	TM1STPTTSN52015		0.136/0.30
		Temperature control.	GreenEquipped with 2 conductor		TM1STPTTSN5201P	100	0.136/0.30
		- 50+110 °C (-122230 °F)	cables for controller side	3 (9.84)	TM1STPTTSN52030	5	0.175/0.39
					TM1STPTTSN5203P	50	0.175/0.39
				5 (16.40)	TM1STPTTSN52050	4	0.232/0.51
					TM1STPTTSN5205P	25	0.232/0.51
NTC probe	9 9	Outside air ■ Temperature control: -50100 °C (-58212 °F)	- IP 65 - Wall mounting - NTC 10kOhm /25°C		TM1STNTCW69755		0.050/0.110
		Inside air (room)	- IP 30		TM1STNTCWN75750		0.050/0.110
	Đ	■ Temperature control: -2540 °C (-13104 °F)	 Indoor wall mounting NTC 10kOhm /25°C 				
lumidity probe		Multi-purpose	- IP 65		TM1SHC4		0.140/0.30
	Signature of the same of the s	■ Humidity control: 0100%	- Wall mounting - 4-20 mA				
lumidity & emperature probes		Multi-purpose	- IP 65 - Wall mounting		TM1SHTCN4		0.140/0.30
		■ Humidity control: 0100%■ Temperature control:	- 4-20 mA, NTC 10kOhm /25	5°C			
	Schypider	-4060 °C (-40140 °F)	- IP 65 - Wall mounting - 2x 4-20 mA		TM1SHTCC4		0.140/0.30
	₽	-	 IP 65 Wall mounting 2x Modbus ports embedde Modbus RTU) 	d (RS-485/	TM1SHTM4		0.140/0.30

Logic controllers for HVAC and Pumping applications Variable speed drives

Application	Type of machine controlled	Compressor				
	Number of phases	3				
	Type of motor	Asynchronous	Asynchronous and Synch	Asynchronous and Synchronous		
Compressor size	0.18 kW (0.25 HP)	Altivar 12 Consult catalog Ref. DIA2ED2130101EN				
	0.37 kW (0.5 HP)		Altivar 320 Consult catalog Ref.			
	0.75 kW (1 HP)		DIA2ED2160311EN	Altivar Process	Altivar 212 Consult catalog Ref DIA2ED2101102EN	
	2.2 kW (0.25 HP)			ATV600 Consult catalog Ref. DIA2ED2140502EN		
	4.0 kW (5 HP)				l	
	7.5 kW (10 HP)					
	15 kW (20 HP)					
	18.5 kW (25 HP)			_		
	22 kW (30 HP)					
	30 kW (40 HP)			_		
	37 kW (50 HP)					
	45 kW (60 HP)			_		
	55 kW (67 HP)			_		
	75 kW (100 HP)			_		
	90 kW (120 HP)			_		
	110 kW (150 HP)			-		
	315 kW (422 HP)			_		
	355 kW (480 HP)			_		
	400 kW (540 HP)			_		
	450 kW (603 HP)			_		
	500 kW (670 HP)			_		
	560 kW (750 HP)			_		
	630 kW (850 HP)			_		
	710 kW (950 HP)					
	800 kW (1100 HP)					
Application	Type of machine controlled	Fan				
	Number of phases	3				
an size	0.18 kW (0.25 HP)	Altivar 12 Consult catalog R	ef			
	0.37 kW (0.5 HP)	DIA2ED21301011	<u>EN</u>			
	0.75 kW (1 HP)			ar 212 Altiv	var Process Drive ATV60	
	2.2 kW (0.25 HP)		Ref. <u>DIA2EI</u>	D2101102EN	Consult catalog Ref. <u>DIA2ED2140502EN</u>	
	4.0 kW (5 HP)					
	7.5 kW (10 HP)					
	15 kW (20 HP)					
	75 kW (100 HP)					
	> 75 kW (> 100 HP)					
		Compatible range of varia	able enced drives			

Logic controllers for HVAC and pumping applications

EcoStruxure Machine Expert - HVAC programming software

Software solution



EcoStruxure Machine Expert - HVAC programming software

EcoStruxure Machine Expert - HVAC programming software is compliant with IEC 61131-3. It can be used to develop, configure, and commission HVAC solution systems.

It includes:

- Programming M171, M172 and M173 logic controllers, remote display units and Secure Interfaces
- Setting up expansion buses and networks
- Creating the screen of the displays (built-in and displays of M171, M172 and M173 logic controller offer)
- Configuring BMS communication modules on BACnet MS/TP (B-AAC profile), Modbus SL, Modbus TCP, BAcnet MS/TP, BACnet IP (B-AAC profile), and LonWorks (FFT-10)
- Dedicated libraries such as:
 - a library of application function blocks
 - a library of Tested, Validated, and Documented Applications (TVDA)
- Full simulation mode

General characteristics	
Programming languages	■ ST (Structured Text) ■ FBD (Function Block Diagram) ■ LD (Ladder) ■ IL (Instruction List) ■ SFC (Sequential Function Chart)
Applications	■ Graphical and text-based languages:
System solutions management	■ Multi-target project ■ Management of Modbus data ■ Data exchange between several M171, M172 Performance, and M173 logic controllers
Graphical user interface	■ Graphic display: - Multipage - Buttons - Edit box - Static text - Images - Animations - Bars - Lists of data (parameters/variables/alarms) ■ Configurable buttons ■ Multilanguage ■ Automatic documentation
Communication bus configurators	■ Control networks: Modbus TCP, Modbus SL, Profibus ■ Expansion bus fieldbus: CAN expansion bus ■ BMS connectivity: BACnet MS/TP (B-AAC profile), BACnet IP (B-AAC profile), LonWorks (FFT-10), MQTT, SNMP
Advanced simulation options	■ Full simulation - I/O emulation - HMI - IEC code - Live debug - Triggers - Oscilloscope
Advanced debugging and simulation options	■ Remote control/download: - Modbus SL & TCP - CAN - Modem ■ Parameter management ■ Status monitoring ■ Field test: - Oscilloscope - Debug window - Export to Excel

Logic controllers for HVAC and pumping applications

EcoStruxure Machine Expert - HVAC programming software



EcoStruxure Machine Expert - HVAC programming software

Programming software

 ${\bf EcoStruxure\ Machine\ Expert\ -\ HVAC\ software\ is\ supplied\ by\ downloading\ from\ our\ \underline{website}}$

The product version concerned offers the EcoStruxure Machine Expert - HVAC functions associated with logic controllers.

Operating system

- Windows 10, 64 bit, Windows 11, 64 bit
- Architecture x64
- RAM: 2 GB (4 GB preferred)
- CPU: Intel Core i3 1,6 GHz or later
- Hard Disk: 1 GB free space
- Peripherals: USB, Monitor (1563x864 min/ 1920x1080 recommended), Mouse and Keyboard

Designation	Application	Reference
EcoStruxure Machine Expert - HVAC programming software	Logic controllers, remote display units and Secure Interfaces	Only available as a download from our website

USB-A USB-B

Local programming, download via USB-B port on M171 Performance or M172 logic controllers: any USB-A/USB-B cable can be used



Local programming, download via USB-C port on M173 Optimized logic controllers: any smart-phone cable can be used

Programming accessories

The USB cable is recommended for local programming. An Ethernet port is recommended for remote download or remote programming.

Description	Characteristics and use	Length	Reference	Weight kg/lb
Ethernet connection cable (1)	on Shielded twisted pair straight cord Equipped with 1 RJ45 connector at each end From the PC RJ45 port to the RJ45 port on TM171AETH Communication module and M172 logic controller C\$\xi\$ compatible	2 m/6.56 ft	490NTW00002	_
		5 m/16.40 ft	490NTW00005	_
		12 m/39.37 ft	490NTW00012	_
		40 m/131.23 ft	490NTW00040	_
Programming cable (2)	Between a PC and the TTL pro of M171 Optimized logic control		TM171ADMI	0.157/ 0.350



Remote programming via USB port on TM171AETH Communication module + M172 Performance logic controller

Programming stick (3)	To transfer parameters from one M171 Optimized or M173 Optimized logic controller to another, or to download the program	TM171AMFK	0.010/ 0.020




Local programming, download via TTL port on M171 Optimized logic controllers

Logic controllers for HVAC and pumping applications
Product reference index

#	
490NTW00002	49
490NTW00005	49
490NTW00012	49
490NTW00040	49
T	
TM171ABKPB	37
TM171ABKPG	29
TM171ACAN	43
TM171ACB4OAO1M	31 34
	35
TM171ACB4OAO2M	31 34
	35
TM171ACB4OI1M	31
	34 35
TM171ACB4OI2M	31
	34
TM474ACD4CLAN	35
TM171ACB4OLAN	31 34
	35
TM171ACB4ORS485	31 35
TM171ADMI	49
TM171AETH	43
TM171AETHRS485	43
TM171ALAN	35
TM171ALON	43
TM171AMB	43
TM171AMFK	49
TM171APBUS	43
TM171ARS232 TM171ARS485	43 43
TM171ASCTB14	39
TM171ASCTB17	37
	39
TM171DLCD2U	31
TM171DLED	35 31
TIMTTTDEED	35
TM171DWAL2L	31
TM474DWALOU	35
TM171DWAL2U	31 35
TM171EO14R	31
	34
TM171EO15R	31 34
TM171EO22R	31
	34
TM171EP14R	39
TM171EP27R TM171OBM14R	39 31
TWT7TOBWT4R	33
TM171OBM22R	31
	33
TM1710D14R	31 33
TM171OD22R	31
	33
TM171ODM14R	31 33
TM171ODM22R	33
	33
TM171ODM22S	31
TM1710F22R	33 31
	33

TMATAOEMOOD	
TM171OFM22R	31 33
TM171PBM27R	37
TM171PDM27R	37
TM171PDM27S TM171PFE03	37
TM171VEVM4	45
TM172ABKPG	29
TM172ABKPW	29
TM172AP12PM	24 27
TM172ASCTB07	24
TM172ASCTB12E	27
TM172ASCTB18	24
TM172ASCTB28	24
TM172ASCTB28E TM172ASCTB42	27 24
TM172DCLFG	21
	29
TM172DCLFW	<u>31</u> 21
TIMITIZE CELL W	29
TM172DCLWT	31
TM172DGLWT	21 29
	31
TM172DCLWTH	21 29
	31
TM172DCLWTHP	21 29
	31
TM172DGRP	21
TM172E12R	29 27
TM172E28R	27
TM172EVEV1B	45
TM172EVEV1U	45
TM172EVEV2B	45
TM172EVEVBAT TM172OBM18R	<u>45</u> 21
TWITT ZODIWITOR	24
TM172OBM28R	21 24
TM172OBM42R	21
TM172ODM18R	24
TWIT720DWIT6R	24
TM172ODM28R	21 24
TM172ODM42R	21
TM172PBG07R	24
TWIT/2PBGU/R	25
TM172PBG18R	21 25
TM172PBG28R	21
TM172PBG28RI	25 21
	25
TM172PBG42R	21 25
TM172PBG42RI	21 25
TM172PDG07R	21 25
TM172PDG18R	21
TM172PDG18S	25 21
	25

FM172PDG28R	21
ΓM172PDG28RI	25 21
	25
ΓM172PDG28SI	21 25
TM172PDG42R	21 25
TM172PDG42RI	21 25
TM172PDG42S	21
ΓM172PDG42SI	25 21
FM172SIG	25 31
	41
ГМ172SIP ГМ173OBM22R	41 17
	19
ГМ173ODM22R	17 19
ΓM173ODM22S	17 19
ΓM1SHC4	46
TM1SHTCC4	46
FM1SHTCN4	46 46
FM1SHTM4 FM1STNTCRN52015	46
TM1STNTCRN5201P	46
TM1STNTCRN52030	46
FM1STNTCRN5203P	46
FM1STNTCRN52050 FM1STNTCRN61515	46 46
FM1STNTCRN6151P	46
FM1STNTCRN61530	46
TM1STNTCRN6153P	46
FM1STNTCRN61550 FM1STNTCRN6155P	46
FM1STNTCSF44015	46 46
TM1STNTCSF44030	46
TM1STNTCSF4403P	46
FM1STNTCSN62015	46
FM1STNTCSN6201P FM1STNTCSN62030	46 46
FM1STNTCSN6203P	46
FM1STNTCSN62050	46
FM1STNTCSN6205P	46
FM1STNTCTN62015 FM1STNTCTN6201P	46 46
FM1STNTCTN62030	46
TM1STNTCW69755	46
TM1STNTCWN75750	46
FM4STPTTSN52015	46
FM1STPTTSN5201P FM1STPTTSN52030	46 46
TM1STPTTSN5203P	46
TM1STPTTSN52050	46
TM1STPTTSN5205P	46
TM1STPTTSN62015 TM1STPTTSN6201P	46 46
TM1STPTTSN62030	46
TM1STPTTSN6203P	46
TM1STPTTSN62050	46
TM1STPTTSN6205P	46



Access an all-in-one customized online experience and benefit from tailored business services, resources, and tools to efficiently support your business operations.

- Efficiency: In just a few clicks, find all the information and support you need to get the job done.
- Simplicity: Use a single login to access all business services, in one place, available 24/7. You no longer need to log in to multiple platforms.
- Personalization: Benefit from content, tools, and business services tailored to your activity, and customize your landing page based on your preferences.

Watch the How-to Videos



Order management

- > Select Products and Add to Cart
- Check for Products' Price and Availability
- > Order Products with Generic Commercial References



Product information

- > Find a Product Data Sheet and Related Documents
- > Select Products and Add to Cart
- > Stay Up to Date on the Status of My Products



Support

> Get Quicker Answers
Thanks to Online Support



Training

Access Trainings Dedicated to My Activity

Create your account







Learn more about our products at www.se.com

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Design: Schneider Electric Photos: Schneider Electric

Schneider Electric Industries SAS

Head Office 35, rue Joseph Monier - CS 30323 F-92500 Rueil-Malmaison Cedex France

DIA3ED2151001EN January 2024 - V6.0