







D

C

B

A



GENERAL NOTES

- FLOOR MOUNTED ENCLOSURE.
TYPE 1 (C) CONSTRUCTED FROM CODE GAUGE STEEL.
FINISH TYPE: ANSI 61 GRAY POLYESTER SEMI GLOSS ELECTROSTATIC POWDER.
- DOOR EQUIPPED WITH A KEY LOCKING HANDLE
- DESIGNED FOR FRONT & REAR ACCESS.
- RECOMMENDED CLEARANCES: FRONT: 40" [1016.00mm] REAR: 30" [762mm]
- CENTER OF GRAVITY
- APPROXIMATE SHIPPING WEIGHT: 1700 LB [771 KG].
- ACCESSORY 40, OPTIONAL SOURCE LOCATIONS IS AVAILABLE ON SERIES 7000 ONLY.

TRANSFER SWITCH

- P FRAME ISOLATION-BYPASS TRANSFER SWITCH.
- TRANSFER SWITCH RATING: 600 AMPS, 800 AMPS, 1000 AMPS, 1200 AMPS
WITHSTAND AND CLOSING RATING WHEN PROTECTED BY A CIRCUIT BREAKER WITHOUT AN ADJUSTABLE SHORT TIME RESPONSE,
MAXIMUM 0.05 SECONDS: 50,000 RMS SYM @ 240V, 480V, 600V.
WITHSTAND AND CLOSING RATING WHEN PROTECTED BY A CIRCUIT BREAKER WITH AN ADJUSTABLE SHORT TIME RESPONSE,
MAXIMUM 0.30 SECONDS: 36,000 RMS SYM @ 240V, 480V, 600V.
MAXIMUM 0.50 SECONDS: 30,000 RMS SYM @ 240V, 480V.
- A FULL RATED NEUTRAL CONNECTION FOR EACH SOURCE AND THE LOAD IS OPTIONAL.
WHEN PROVIDED IT IS IN ONE OF THE FOLLOWING FORMATS.
A. SOLID NEUTRAL
B. SWITCHED NEUTRAL POLE
- UL 1008 OR CSA C22.2 No. 178.1

TERMINATIONS 600A

- MECHANICAL (SCREW TYPE) LUGS FOR CU/AL CABLE.
SOURCE 1 (NORMAL): (2) 1/0-600MCM [50-300mm²] PER PHASE & NEUTRAL
LOAD: (2) 1/0-600MCM [50-300mm²] PER PHASE & NEUTRAL
SOURCE 2 (EMERGENCY): (2) 1/0-600MCM [50-300mm²] PER PHASE & NEUTRAL
GROUND: (6) 1/0-600MCM [50-300mm²]
A. SUITABLE WIRE BENDING SPACE IS PROVIDED AS PER NEC.
- SWITCH MAY BE SUPPLIED WITHOUT LUGS.
- OPTIONAL LUGS MAY BE SUPPLIED (MAY AFFECT ENCLOSURE SIZE).

TERMINATIONS 800A-1200A

- MECHANICAL (SCREW TYPE) LUGS FOR CU/AL CABLE.
SOURCE 1 (NORMAL): (4) 1/0-600MCM [50-300mm²] PER PHASE & NEUTRAL
LOAD: (4) 1/0-600MCM [50-300mm²] PER PHASE & NEUTRAL
SOURCE 2 (EMERGENCY): (4) 1/0-600MCM [50-300mm²] PER PHASE & NEUTRAL
GROUND: (12) 1/0-600MCM [50-300mm²]
A. SUITABLE WIRE BENDING SPACE IS PROVIDED AS PER NEC.
- SWITCH MAY BE SUPPLIED WITHOUT LUGS.
- OPTIONAL LUGS MAY BE SUPPLIED (MAY AFFECT ENCLOSURE SIZE).

WIRING/CABLING

- USE 90°C MINIMUM CU/AL WIRE FOR POWER CABLES.
- WIRE SIZE TO BE BASED ON AMPACITY OF 75°C WIRE.
- USE 60°C MINIMUM CU WIRE FOR CONTROLS.

PROJECT NAME:		REV. TO SHEET	ECN NO.	BY	APP.	DATE
OUTLINE		MOUNTING				
PATB 600A - 1200A						
TYPE 1 91 X 38 X 48						
DRAWN BY	SV	DATE	05-12-23	MANUFACTURING TOLERANCES TO BE IN ACCORDANCE WITH ASCO PROCEDURE MP-I-003. FOR PLASTIC PARTS SEE MP-I-055	ASSEM. REF. NO.	COMPUTER GENERATED DRAWING
CHECKED				PROPERTY OF ASCO POWER TECHNOLOGIES. USE PERMITTED FOR OUR WORK ONLY. ALL RIGHTS OF DESIGN OR INVENTION ARE RESERVED.		SCALE 1/16" = 1" SIZE DS
PROJECT APPROVAL				ASCOTM ASCO POWER TECHNOLOGIES, L.P. FLORHAM PARK, NEW JERSEY 07932 U.S.A.		DWG. NO. 992762
FINAL APPROVAL						DRAWING REV. B ECN NO. 303563 SHEET 1 OF 1