

Industrial Automation

EcoStruxure™ Automation Expert

Software-defined Automation

Software version v26.0

www.se.com




Quick access to product information

Get technical information about your product

Each commercial reference presented in a catalog contains a hyperlink. Click on it to obtain the technical information of the product:


- Characteristics, Dimensions and drawings, Mounting and clearance, Connections and schemas, Performance curves
- Instruction sheets, User guides, Product certifications, End of life manuals, etc



View the Automation Catalog libraries


On [Digi-Cat Online](#) you can access the Industrial Automation and Control catalogs, in both English and French

- Up-to-date catalogs
- Optimized search by commercial references
- Integrated product selectors and configurators




Direct access to Configurators Home pages

- Configure your [motor control and protection solution](#)
- Configure your [control system with a PLC controller and I/O modules](#)
- Configure your [motion control and robotics system](#)



Select your training

- Find the right [Training](#) for your needs on our Global website
- Locate the [Training center](#) with the selector tool



General contents

EcoStruxure™ Automation Expert

■ General overview

- EcoStruxure Automation Expert..... [page 2](#)
- Open, software-defined automation..... [page 3](#)
- Feature overview [page 4](#)

■ Presentation

- Software
 - EcoStruxure Automation Expert Build Time [page 6](#)
 - EcoStruxure Automation Expert - HMI [page 8](#)
 - EcoStruxure Automation Expert - Archive [page 8](#)
 - EcoStruxure Automation Expert - AVEVA System Platform integration..... [page 9](#)
 - EcoStruxure Automation Expert - Libraries [page 10](#)
 - System requirements..... [page 14](#)
- Hardware
 - Software dPAC [page 15](#)
 - Edge Controller..... [page 15](#)
 - Modicon dPAC..... [page 16](#)
 - Altivar dPAC [page 17](#)
 - Selection Guide [page 18](#)
 - Architecture [page 21](#)
- Licenses
 - EcoStruxure Automation Expert – Perpetual licensing [page 27](#)
 - EcoStruxure Automation Expert – Subscription-based licensing [page 32](#)
 - EcoStruxure Automation Expert Licensing – Architecture [page 34](#)
- **Compatibility**
 - List of Modicon X80 hardware compatible with Modicon M580 dPAC, Modicon CRD for Simplex/High Availability Soft dPAC (Linux OS) [page 36](#)
 - List of Modicon Edge I/O NTS compatible with Modicon M262 dPAC and Simplex Soft dPAC (Linux OS) [page 38](#)
 - List of TM3 hardware compatible with ModiconM251 dPAC and M262 dPAC [page 39](#)
 - Altivar hardware and Altivar ATV dPAC compatibility [page 40](#)
- **Services**..... [page 41](#)
- **Product reference index**..... [page 44](#)


EcoStruxure™ Automation Expert platform

EcoStruxure Automation Expert platform is a unified software platform from Schneider Electric that brings together your industrial software applications into a single environment. This platform enhances user experience, bringing new and improved capabilities such as collaboration across project teams and data continuity.

In this version, the platform provides functionalities including user management, system management, multi-user collaboration, version control, and AI conversational help, all delivered through a unified modular environment for automation control.

EcoStruxure™ Automation Expert

EcoStruxure Automation Expert has been integrated into the Automation Expert platform, strengthen open, software-defined industrial automation solutions. This innovative approach allows industrial operators to achieve significant improvements over traditional process control systems. It enhances productivity, quality and flexibility throughout the entire life cycle of industrial assets.



(1) Depending on the target controller, Edge I/O NTS is supported over Ethernet IP or Modbus TCP. Please refer to the release note for more details.

- > EcoStruxure Automation Expert Build Time encompasses the design, engineering and monitoring of the application.
- > Distributed Programmable Automation Controller (dPAC) platforms with the UniversalAutomation.org Shared Source Runtime engine:
 - ATV dPAC for Altivar
 - Modicon M251 dPAC
 - Modicon M262 dPAC
 - Modicon M580 dPAC
- > Plus, innovative new software-based controllers:
 - Soft dPAC for Windows™, for standalone configurations
 - Soft dPAC for Linux™, for standalone and high availability configurations
- > EcoStruxure Automation Expert - HMI, a fully integrated, object-oriented industrial visualization solution
- > EcoStruxure Automation Expert - Archive, a centralized solution for the historization of process data, alarms, and trends
- > Schneider Electric Libraries, a comprehensive set of software-defined libraries, ranging from basic functions up to segment solutions
- > Asset Link for Bulk Engineering to extract data from engineering tools for automated application generation
- > Asset Link for AVEVA OMI to create application objects (AppObjects) in the AVEVA System Platform in an automated workflow
- > High Availability add-on to create applications that promote continuous operation and minimize downtime in critical applications by using a High Availability Soft dPAC.
- > Procedural Automation add-on to create, modify, and execute automated routines, recipes, tasks and complex sequences or procedures.

Note: UniversalAutomation.org is a non-profit organization dedicated to overseeing the implementation of an industrial shared-source runtime execution engine. For more information, please visit universalautomation.org website.

Open, software-defined automation

Open, software-defined automation is an innovative approach that unifies software-defined control with fully interoperable, vendor-agnostic architectures. By combining software-defined automation with the principles of open automation, it enables seamless integration of diverse devices and systems.

This model empowers industrial users to overcome the traditional hardware constraints and move beyond proprietary limitations, unlocking greater agility across their operations. It enhances flexibility, scalability, and collaboration throughout the entire lifecycle of industrial applications.



Hardware independence

Automation software operates independently from specific hardware platforms, allowing organizations to select devices based on performance, availability, and business requirements rather than proprietary constraints. This flexibility reduces lifecycle risk, mitigates obsolescence, and supports long-term scalability by enabling architectures that remain adaptable as technology evolves.



Distributed intelligence

Control functions can be deployed and redistributed across edge devices, servers, and compute resources in real time, enabling continuity and resilience. This distributed model enhances system availability, minimizes unplanned downtime, and supports scalable performance for continuous, batch, and discrete processes without requiring manual reconfiguration.



Application centric

Engineering shifts from hardware-driven design to modular, reusable application components that encapsulate logic, diagnostics, visuals, and metadata. This approach accelerates development, simplifies replication, and strengthens integration across engineering disciplines. It supports consistent lifecycle management from concept design through commissioning and operation.



Digital continuity

Digital continuity helps information flows consistently and accurately across engineering, operations, and maintenance. By connecting IT and OT systems and preserving contextual data throughout the automation lifecycle, organizations can enable advanced analytics, automated workflows, and model-based validation. This integrated approach strengthens decision-making, improves operational efficiency, and supports higher performance across industrial assets.

Feature overview

EcoStruxure Automation Expert represents a software-defined approach to designing, building, operating, and maintaining industrial automation systems that offers a unique technology mix.



Complexity mastered

Systems, devices, services, and assets are natively represented as ready-to-use software objects called composite automation types (CATs) that encapsulate internal behaviour and simplify functional interfaces. An object-oriented approach promotes code reuse enables standardization on best practice, and helps manage complexity while providing the fundamental building blocks for the creation of cyber-physical systems. CAT objects follow a type/instance relation and can be combined to create new objects that encapsulate:

- Control logic
- HMI/SCADA visualization
- I/O and device communications
- Simulation and test rigging
- Documentation



Decoupling the application from implementation

EcoStruxure Automation Expert allows the engineer to generate their automation control strategies without the need for the hardware architecture by decoupling the application from the runtime deployment. This allows professionals to focus independently on each task throughout the project lifecycle, combining the best capabilities of classic PLC with DCS control approaches. Applications are portable, reusable, and interoperable across runtime platforms, meaning deployment decisions are made just in time and on the fly, enabling exceptional system agility.



Efficient engineering


EcoStruxure Automation Expert Build Time provides a single, modular engineering environment for all tasks needed to engineer, monitor, and manage the complete automation system including hardware and software, control, and visualization. It automates low value engineering and integration tasks, reducing engineering effort and sources of error by leveraging Asset Link to perform digital engineering. Complex functions can be encapsulated into manageable objects, enabling non-technical users to understand and manage complex systems.

Cross communications are transparent and implicit regardless of physical location, requiring zero engineering consideration.




Common runtime environment

Through the implementation of the shared source Runtime engine provided by universalautomation.org across hardware and software platforms, exceptional re-usability, scalability, and architectural flexibility are now available. Application portability provides cost savings through the decoupling of the lifecycles of software and hardware systems.



Simple system integration

EcoStruxure Automation Expert was designed with the complete lifecycle of an automation system in mind, with functions to facilitate management and monitoring of multiple assets and devices at scale. With a single user environment covering the entire system scope including third-party devices, orchestration of complex, heterogeneous systems becomes simpler.



Native IT integration

Modern automation systems generate increased value when coupled with business information and hence wider IT ecosystems. EcoStruxure Automation Expert provides an expandable platform for Industry 4.0 solutions with support for high-level programming, modular systems design, and open standards. Thanks to event-driven execution and object-oriented design, EcoStruxure Automation Expert applies to IT programming language standards.



Feature overview (continued)

Cybersecurity

EcoStruxure Automation Expert offers improved cybersecurity support, including credential and privilege management. It utilizes secure protocols such as TLS, HTTPS, and OPC UA, along with encryption function blocks to help ensure secure communication between controllers, HMIs, SCADA, and third-party devices.

Since the v22.0 release, EcoStruxure Automation Expert conforms to CA SB327 California Connected Devices. Syslog functionality for Altivar ATVd, Modicon M262d, Modicon M580d, and Soft dPAC has been available in recent versions. This supports audit logging with events accessible in a read-only format by Syslog servers.

The following cybersecurity events are available in accordance with CTI-13:

- Creation/modification/deletion of ID/password
- Successful/unsuccessful device login, device deployment, firmware update, IP address change (device properties)
- Set/Reset security of a device from topology manager
- Modification of system time
- Connection to Syslog server

Access control is extended to support privilege management with Role-Based Access Control.

Preconfigured roles "Security Administrator", "Engineer", "Installer", "Operator" and "Viewer" are provided as well as the ability to define custom roles.

Granular permissions can be assigned to roles to manage escalation of privilege threats.

- Deploying security configuration
- Deploying Device configurations and applications
- Viewing diagnostics counters
- Starting or Stopping Devices/applications
- Firmware updates
- IP address setting
- EAE HMI read and write access
- OPC UA read and write access
- Watching values
- Forcing values
- Setting IP address

Since the v25.0 release, EcoStruxure Automation Expert has been certified against [IEC 62443-3-3 at SL2](#). The [Cybersecurity – User Guide](#) helps users configure a cybersecure system that is confident and meets IEC 62443-3-3 requirements.

EcoStruxure Automation Expert platform

EcoStruxure Automation Expert platform is a unified software platform from Schneider Electric that brings together your industrial software applications into a single environment. This platform enhances user experience, bringing new and improved capabilities such as collaboration across project teams and data continuity.

The platform enhances collaboration across project teams, minimizes merge conflicts during simultaneous multi-user application development, and provides functionality including user management, system management, version control, and an AI assistant - all delivered through a unified, modular environment for automated control.

EcoStruxure Automation Expert platform – multi-user

EcoStruxure Automation Expert platform enhances collaboration across project teams and minimizes merge conflicts when sharing application development with simultaneous multi-users.

The multi-user capability features a reservation mechanism that enables users to reserve specific zones within a project, making them read-only for other users. This can help minimize potential conflicts. Additionally, the system supports recursive zones, allowing zones to contain sub-zones with dependencies. When a user reserves a zone, all dependent zones are automatically reserved as well, to help prevent potential conflicts.

Each device also functions as a zone; when a user accesses a device – such as logging in, deploying, or monitoring – it becomes unavailable to others. Furthermore, the Automation Expert platform hosts the main repository, allowing users to work independently without interruptions from other users' deliveries.

The history of changes is tracked by enabling a commit message before any modifications are delivered. This practice enhances accountability and clarity, as each commit message should contain relevant details about the changes made, such as the purpose of the modification, the specific areas impacted, and any related detail. Teams can maintain a clear record of the project's evolution, fostering collaboration and simplifying future reviews or troubleshooting efforts.

EcoStruxure Automation Expert platform – AI Assistant

The AI Assistant is a Generative AI-powered feature that provides fast, intuitive access to EcoStruxure Automation Expert help content. Rather than navigating multiple chapters or knowing Automation Expert-specific terminology, users can ask questions in natural language. Within seconds, the AI Assistant returns concise summaries and direct links to the most relevant EcoStruxure Automation Expert HTML help topics.

The AI Assistant supports multilingual queries in five languages: English, French, German, Japanese, and Spanish. The underlying model is not trained using customer data.

Currently, the AI Assistant is included with the EcoStruxure Automation Expert Engineering license. However, an activation key is required and remains valid for one year. Please contact your Schneider Electric representative for further details.

EcoStruxure Automation Expert platform – system management

The System Management app enables comprehensive monitoring of control system devices, including their health, security status, and performance. It delivers an exceptional user experience with detailed contextual information, real-time access to system alarms, and event tracking capabilities. These features support efficient diagnostics and maintenance workflows.

EcoStruxure Automation Expert platform – advanced system management

The Advanced System Management app introduces advanced features designed to automate and optimize maintenance operations like self-healing mechanisms for high availability system.

High Availability Disruption Avoidance is the ability to maintain Edge Controller High Availability at all times by adding several spare controller units to enable self-healing after a controller detected failure.

When a failure is detected on the High-Availability pair, we minimize call-outs by dynamically selecting the appropriate spare part and then restoring High Availability immediately.

EcoStruxure Automation Expert Software


The EcoStruxure Automation Expert software offer includes:

- EcoStruxure Automation Expert Build Time is the main tool for designing, engineering, and monitoring the application.
 - Asset Link for Bulk Engineering to extract data from engineering tools for automated application generation.
 - Asset Link for AVEVA OMI to create application objects (AppObjects) in the AVEVA System Platform in an automated workflow
 - High Availability add-on to create applications that promote continuous operation and minimize downtime in critical applications by using a High Availability Soft dPAC.
 - Procedural Automation add-on to create, modify, and execute automated routines, recipes, tasks, and complex sequences or procedures.
- EcoStruxure Automation Expert HMI Configurator
- EcoStruxure Automation Expert Archive
- Asset-oriented application libraries

EcoStruxure Automation Expert Build Time

EcoStruxure Automation Expert Build Time is an asset-based, fully-integrated engineering environment that allows portable, automation systems to be managed within a single environment. EcoStruxure Automation Expert Build Time provides the capability to:

- Design and manage asset-based applications using object libraries based on multifaceted models such as asset logic, operating modes, HMI symbols and faceplates (including alarms and trends), I/O interface, and asset documentation
- Design the control strategy for process and machine based on asset-oriented objects with single line connections
- Create rich process displays to monitor and control the process from the control room or line terminal by dragging and dropping asset-based objects
- Manage a single solution independently of the number of controllers and HMI stations
- Design the application solution independently of the hardware configuration
- Test and simulate the control and HMI for the whole solution
- Create and modify procedural automation CATs based on S88 state model with graphical editor
- Support multi-user change management through SVN client integration
- Design, configure, and manage network and device topologies
- Flexibly deploy applications to multiple hardware or software platforms based on UniversalAutomation.Org a shared runtime execution engine
- Automatically discover and diagnose compatible runtime devices
- Asset Link for bulk generation of asset instances from AVEVA Engineering or DEXPI files
- Asset Link for bulk generation of asset instances for AVEVA System Platform
- Embedded AVEVA industrial graphic editor in EcoStruxure Automation Expert Build Time to create new AVEVA industrial graphics or to reuse graphics from existing applications
- Secure the automation system by managing authentication with encrypted communication and security certificates at solution and devices level



EcoStruxure Automation Expert V26.0 Build Time

EcoStruxure Automation Expert Software

EcoStruxure Automation Expert – HMI

EcoStruxure Automation Expert HMI is a tightly integrated human-machine interface designed for EcoStruxure Automation Expert applications. Its features include:


- Compatibility with Windows™ OS/Linux™ OS panel PCs
- Seamless management of controller and HMI communication
- Support for single/multi operator stations with cloning
- User management for access control
- Multi-language application
- Monitoring of runtime connections

EcoStruxure Automation Expert HMI Client for Window™/Linux™ operating system can be installed on various hardware such as Workstations, Industrial PCs, and Edge Boxes, provided they meet the minimum system requirements. It facilitates effective management of communication between the controller and HMI.

Furthermore, the EcoStruxure Automation Expert HMI Client for Harmony ST6 is compatible with HMIST6200, HMIST6400, HMIST6500, HMIST6600, HMIST6700, HMISTM6400, and HMISTM6200 touch panel screens. It offers seamless management of controller and automatic HMI communication, particularly ideal for a small number of assets.

EcoStruxure Automation Expert – Archive

EcoStruxure Automation Expert Archive enables the connection between the Distributed Programmable Automation Controller (dPAC) platforms configured in your solution and the Archive database, operating as a highly integrated local data historian. It provides minimal engineering effort for historization and retrieval of live process data, alarms, and events to be displayed within Automation Expert HMI and the capability to integrate with larger enterprise data storage systems by Structured Query Language (SQL). It is compatible with Server 2019 and Server 2022 in addition to Windows10, windows11 and Linux operating system.




EcoStruxure Automation Expert Software (continued)

EcoStruxure Automation Expert – AVEVA System Platform integration

EcoStruxure Automation Expert includes native support for System Platform - AVEVA's real-time operations control platform for supervisory, HMI, SCADA, and IIoT applications. EcoStruxure Automation Expert is capable of auto-generating OPC UA-based secure communications between platforms and generate AVEVA System Platform-compatible graphics for clean integration. Furthermore, it now embeds the AVEVA Industrial Graphics editor so that users no longer need to move from EcoStruxure Automation Expert Build Time to AVEVA Build Time, providing unpreceded integration.

Automation Expert version	Library compatible version	Platform version for Asset Link	Version for Asset Link and AVEVA Industrial Graphics
V23.0	AVEVA System Platform 2020 R2 SP1	AVEVA System Platform 2020 R2 SP1 or later	No AVEVA Industrial Graphics support
V23.1	AVEVA System Platform 2023	AVEVA System Platform 2020 R2 SP1 or later (New Galaxy creation is possible only with Library compatible version) ⁽¹⁾	AVEVA System Platform 2023 or later
V24.1	AVEVA System Platform 2023 or R2 SP1	AVEVA System Platform 2020 R2 SP1 or later (New Galaxy creation is possible only with AVEVA System Platform 2023 R2 SP1) ⁽¹⁾	AVEVA System Platform 2023 or later (New Galaxy creation is possible only with AVEVA System Platform 2023 R2 SP1) ⁽¹⁾
V25.0	AVEVA System Platform 2023 R2 SP1 P01	AVEVA System Platform 2023 or later (New Galaxy creation is possible only with AVEVA System Platform R2 SP1 P01) ⁽¹⁾	AVEVA System Platform 2023 or later (New Galaxy creation is possible only with AVEVA System Platform R2 SP1 P01) ⁽¹⁾
V 26.0	AVEVA System Platform 2023 R2 SP1 P01 ⁽²⁾	AVEVA System Platform 2023 R2 SP1 P01 ⁽²⁾	AVEVA System Platform 2023 R2 SP1 P01 ⁽²⁾


(1) Only Select Existing Galaxy from the configurator is possible if Library compatible version is not available with the user.
 (2) AVEVA provides hotfixes directly. For optimal stability and compatibility, use the officially tested versions listed in this table.




Embedded AVEVA industrial graphic editor in EcoStruxure Automation Expert Build Time

EcoStruxure Automation Expert Software (continued)

EcoStruxure Automation Expert – Libraries



Example of field devices symbol and faceplate on EcoStruxure Automation Expert HMI



Example of Application CAT symbol and faceplate on AVEVA OMI

EcoStruxure Automation Expert includes a set of application libraries with generic process and control models such as motors / valves and segment-based libraries with equipment models that include multiple facets – logic, Automation Expert HMI, AVEVA System Platform template, and documentation within a single package to minimize the engineering time.

EcoStruxure Automation Expert offers a comprehensive set of general application libraries with diverse functionalities for process and control models like motors and valves. This accelerates development cycles, helps reduce errors, and enhances overall software quality with logic, Automation Expert HMI object, AVEVA System Platform template, and documentation, all within a single package.

Additionally, specialized application segment-based libraries are provided, enabling developers to streamline their development process with standard functionality. This allows them to focus on adding value to their specific industry or application domain with optimized functions and algorithms tailored to their unique requirements.

EcoStruxure Automation Expert also incorporates a field devices library to facilitate the seamless integration of commonly used Schneider Electric and Technical Partner's field devices via Modbus / Ethernet IP. This library provides the necessary communication mapping, Automation Expert HMI objects for control and diagnostic, and documentation required for their smooth utilization within the application.


On version 26.0, these libraries are included at no extra cost:

- Field Device
- Base and common process
- Sequence management and Phase Management
- Liquid food
- Water and Wastewater (including desalination)
- Mining, Minerals, and Metals
- Single line power monitoring
- Conveying
- Building Management System

EcoStruxure Automation Expert Software (continued)

EcoStruxure Automation Expert – Libraries (continued)

These libraries include HMI objects that are compatible with Windows and Linux Ubuntu native HMI runtime. Moreover, "plug and produce" software and hardware components from UniversalAutomation.org vendors are fully compatible with EcoStruxure Automation Expert applications, irrespective of the vendor.



EcoStruxure Automation Expert Software (continued)

EcoStruxure Automation Expert – Libraries (continued)

EcoStruxure Automation Expert libraries

Library name	Short description	Extended description
Runtime.Base	Standard blocks	This library contains the basic function blocks to be used for: <ul style="list-style-type: none"> ■ Runtime management ■ Arithmetic functions ■ Logic functions ■ Format conversion ■ Event management ■ etc.
App2BMS library	-	-
NTS EdgelO library	-	-
SE.App2Base	Elementary blocks of the application	Library with application CATs covering basic application functions like alarms, conditions, owners, and signal conditioning that are used by other application CATs like the ones from SE.App2CommonProcess.
SE.App2CommonProcess	Common process application	Library with application CATs to address common process assets or functions like digital I/O, analog I/O, motors, valves, flow control, etc. These types of object can be used in any industrial application as well as in process control in manufacturing applications.
SE.App2Conveying	Conveying application	Library with application CATs to address common equipment such as conveyors, sorters, transfer tables, and turntables, typically used in logistic hubs and distribution centers.
SE.App2LiquidFood	Liquid and food (CPG)	Library with application CATs to address Liquid and Food applications with mix proof valves; transfer of materials and liquids from a source to a destination; and equipment status function is a crucial component within a system that monitors and reports the operational condition of various equipment.
SE.App2MMM	Mining, Mineral and Metals application	Library with the Group Control application CAT to manage and control multiple devices as a group, simplifying the process of coordinating and supervising various elements within a system.
SE.App2BMS	Building management system application	Library with objects targeting HVAC system and air handling unit to suit building management system applications.
SE.App2SingleLinePowerMonitoring	Low and medium power monitoring application	Library with application CATs with common functions for electrical objects such as busbars, sources, infeeds, and loads that can be connected to energy management hardware CATs.
SE.App2WWW	State management	Library with application CATs used to monitor and manage control sequences like aeration and dual media filter for Water and Wastewater applications.
SE.App2StateManagement	State management	Library with application CATs to provide state management functionality for generic application (State Manager) as well as ISA-88 based application (Phase Manager). Phase Manager also includes a phase logical interface that accepts commands from external batching interfaces such as AVEVA Batch Management and returns the Phase Manager status.
SE.AppSequence	Sequence Control	Library with a set of application CATs that allows you to create sequential control algorithms with steps and transitions to command control modules. This library works with both SE.AppCommonProcess and t.App2CommonProcess.
SE.DPAC	dPAC hardware controllers	Library containing the dPAC device types
AVEVA.IndustrialGraphicsLibrary	Industrial graphics library	Industrial Graphics are vector-based graphics that can be scaled, animated, embedded into application objects, and deployed. The library contains common industrial equipment. You can modify graphics or add graphics to the library by creating new graphics using the Industrial Graphic Editor.
SE.EAEPortal	AVEVA System Platform Device type	The AVEVA System Platform device type is required by Asset Link for establishing communication and creating the application objects automatically in AVEVA System Platform
SE.FieldDevice	Field device hardware CATs	This library has ready-to-use hardware CATs for motor control, energy management, machine safety, and weighing from Schneider Electric, allowing dPAC communication with these devices by Modbus TCP, Modbus RTU, or EtherNet/IP depending on the device.
SE.HwCommon	Common hardware CAT functions	Library of functions used by the various hardware CAT libraries
SE.IoATV	Variable speed drive I/O services for ATV dPAC	Library of hardware CATs for Altivar I/O (local and modules) used for the Altivar dPAC module hardware configuration

EcoStruxure Automation Expert Software (continued)

EcoStruxure Automation Expert – Libraries (continued)

EcoStruxure Automation Expert libraries (continued)

Library name	Short description	Extended description
SE.ioNet	UDP gateway	Library of hardware CATs to enable UDP communication
SE.ioTMx	TM I/O services for M251d/M262d	Library of hardware CATs for TM3 I/O modules used for M251d and M262d hardware configuration
SE.ioX80	X80 I/O services for M580d/CRd	Library of hardware CATs for X80 I/O modules used for M580d/CRd hardware configuration
SE.ModEdgeIOnTS	Edge I/O NTS services for Simplex Linux Soft dPAC	Library of hardware CATs for Modicon Edge I/O NTS
SE.ModbusGateway	Standard Modbus gateway	Library of hardware CATs to enable Modbus TCP communication with import of data description file
SE.Standard	EcoStruxure Automation Expert HMI device type	Library with EcoStruxure Automation Expert HMI device type
Standard.ioEtherNetIP	Standard Ethernet IP scanner functions	Library of hardware CATs used for EIP scanner configuration (Implicit use by the EcoStruxure Automation Expert system when using the EIP scanner and also to add custom EIP connections)
Standard.ioModbus	Standard Modbus functions	Library of hardware CATs to enable Modbus client communication
Standard.ioModbusSlave	Standard Modbus server functions	Library of hardware CATs to enable Modbus server communication
Standard.OPCUAClient	Standard OPC UA client functions	Functions to enable OPC UA client connection, monitor, read, and write data
Standard.EtherCAT	Standard EtherCAT functions	Library for configuring hardware CATs on EtherCAT main device and subdevices to enable communication.
Standard.ioPROFINET	Standard PROFINET functions for I/O Controller and I/O device	Library of hardware CATs and function blocks used to enable PROFINET I/O controller and I/O device roles.

Definitions:

- CAT object: A composite automation type (CAT) function block includes objects with multiple facets:
 - Logic to define its operating modes
 - I/O interfaces to exchange data/events with its environment
 - Symbols/faceplates for control and monitoring in the HMI
 - Documentation that is implicitly part of the project online help
- Application CAT: representing application assets or functions
- Hardware CAT: representing hardware devices that can be added to the hardware configuration, for device monitoring and control

EcoStruxure Automation Expert Software (continued)

System requirements

Windows – Engineering, HMI, and Archive

System requirements	Minimum			Recommended		
	Engineering	HMI	Archive	Engineering	HMI	Archive
Processor	1 GHz			2 GHz or higher		
RAM ⁽¹⁾	2 GB	2 GB	2 GB	4 GB	4 GB	4 GB
Hard disk free space ⁽¹⁾	1 GB	1 GB	1 GB	10 GB	10 GB	10 GB
Display resolution	1280x1024			1920x1080 or higher		
Pointing device	Mouse or compatible					
Network access	One Ethernet interface					
Operating system	Microsoft Windows 10 Professional (64-bit) Version 1903 and later, Microsoft Windows 11 Professional Version 21H2 and later, and Microsoft Server Version 2019 (1809 and later)					
.NET framework	.NET 4.8			.NET 4.8 or higher		

⁽¹⁾ Requirement is indicated for each software package. More than one software package can be installed on the same device. In this case, you need to add the respective RAM and hard disk free space requirements together. For example, if you install the HMI and Archive software packages on the same device, the minimum RAM required is 4 GB (2 GB + 2 GB).

Distributed Programmable Automation Controller (dPAC) Platforms

Soft dPAC

Soft dPAC represents an open, software-based controller built on a containerized version of the shared-source UAO runtime engine, designed to execute control and compute applications and interact with field devices. The hardware-agnostic nature of Soft dPAC enables deployment across a wide range of hardware platforms, such as edge controllers, servers, workstations, industrial PCs, and microcomputers that meet the required system specifications.

Soft dPAC supports both Linux™ and Windows™ operating systems:

- The Linux Soft dPAC is ideal for real-time control when installed in conjunction with a Linux real-time patch. In a Linux environment, multiple instances of Soft dPAC can be seamlessly installed on a single host machine, allowing tasks like line expansions to be completed without disrupting ongoing processes. This capability minimizes downtime, thereby enhancing productivity and profitability.
- The Windows Soft dPAC is best suited for non-critical applications that do not demand real-time control. For Windows, one Soft dPAC instance can be installed per host machine.

Soft dPAC is compatible with Modicon Edge I/O NTS, TM3 I/O, X80 I/O modules, and third-party IO modules. For Modicon X80 I/O, a dedicated module is required, which provides comprehensive compatibility and functionality within industrial automation setups.

Part numbers for Modicon X80 IO head unit:

- **BMECRD0100**: Remote IO head for EcoStruxure Automation Expert
- **BMECRD0100C**: Remote IO head unit for EcoStruxure Automation Expert in a coated version

High Availability Soft dPAC

High Availability Soft dPAC (HA Soft dPAC) represents an open, software-based high availability solution engineered to maintain uptime upon a failure, offering resilience against hardware, software, or network failures. This capability effectively minimizes process downtime, making it ideal for demanding applications where uninterrupted process flows are critical. The integration of the high-availability solution with EcoStruxure Automation Expert software plays a pivotal role in enhancing productivity by significantly reducing process downtime.

High Availability Soft dPAC is a versatile edge controller compatible with a variety of hardware options, such as the Schneider Electric Harmony Performance Edge Controller, Automation Processor AP310 and third-party edge controllers such as ASRock™ industrial IoT controller. For compatibility with other hardware options, please contact your Schneider Electric representative for further details.

Moreover, High Availability Soft dPAC seamlessly integrates with Modicon X80 IOs using the BMECRD0100 Remote I/O module, which provides comprehensive compatibility and functionality within industrial automation setups.

Essential Edge Controller

Essential Edge Controller, a part of the Harmony iPC range with pre-installed Soft dPAC. This versatile controller is tailored to meet a diverse set of control and compute application needs. Its design aims to significantly reduce commissioning time, thereby enhancing the overall customer experience.

Product reference: **HMIBX1A0NDA**

The Essential Edge Controller is an open-to-application edge terminal that runs on Linux operating system. This edge device delivers substantial value for diverse industrial use cases with:

- Pre-installed Soft dPAC Simplex, HMI for immediate deployment
- Capability to run third-party applications on the same hardware

The Essential Edge controller has no embedded I/O; it supports Remote I/O on Modicon Edge I/O NTS, TM3 I/O, and X80 I/O expansion modules.

NOTE: Please contact your Schneider Electric representative for additional information.



HMIBX1A0NDA

Distributed Programmable Automation Controller (dPAC) Platforms (continued)

Performance Edge Controller



HMIP6-BCTO

The Performance Edge Controller, a part of the Harmony iPC range with pre-installed Soft dPAC. This Edge controller delivers enhanced performance compared to Essential Edge Controller. It comes with pre-installed Soft dPAC Simplex, HMI, and Archive, to provide smooth integration and remarkable flexibility. Moreover, its capability to host third-party applications on the same hardware empowers users to customize and extend functionality to align with their unique requirements.

The Performance Edge Controller operates on the Linux operating system, offering an efficient platform for industrial automation. It seamlessly integrates with a diverse array of industrial applications, providing effortless integration for the industry.

Product Reference: **HMIP6-BCTO**

It is a configure-to-order product, where the user can choose the processor type (Celeron / i3), Memory size, and accessories.

The Performance Edge controller has no embedded I/O; it supports Remote I/O on Modicon Edge I/O NTS, TM3 I/O, and X80 I/O expansion modules.

This innovative Performance Edge controller is an all-in-one solution, streamlining operations and maximizing efficiency.

Modicon M580 dPAC



BMED581020

A distributed field controller with up to 64 MB ECC RAM for programs and data. The Modicon M580 dPAC supports the robust, high-performance Modicon X80 I/O catalog⁽¹⁾ and is available in standard and conformal coated versions.

Product references:

- **BMED581020: Modicon M580 dPAC (standard)**
- **BMED581020C: Modicon M580 dPAC (conformal coated)**

BMED581020 and **BMED581020C** controllers support:

- Up to 1,408 discrete I/O channels⁽²⁾
- Up to 352 analog I/O channels⁽²⁾
- Up to 4 racks of local I/O

Modicon M251 dPAC



TM251MDESE

A cost-optimized, low-footprint distributed controller based on the machine-specialized Modicon M251 Logic Controller platform. The Modicon M251 dPAC provides a single Ethernet port for fieldbus, switched dual Ethernet ports for peer communications, and supports the field-proven TM3 I/O system⁽¹⁾.

Product reference:

- **TM251MDESE: Modicon M251 dPAC**

The **TM251MDESE** controller has no embedded I/O; it supports Modicon TM3 I/O expansion modules:

- Up to 112 discrete I/O channels⁽²⁾
- Up to 112 analog I/O channels⁽²⁾
- Up to 14 Modicon TM3 expansion modules (7 local modules + 7 remote modules) with Modicon TM3 bus expansion modules (transmitter module and receiver module)

It is possible to control up to 4 TeSys U and TeSys D motor starters by connecting a **TM3XTYS4** TM3 module to the Modicon M251 dPAC.

Modicon M262 dPAC



TM262L01MDESE8T

This is the controller for performance machines. It is powered with a non-isolated 24 V DC power supply, has a built-in overload protection, embeds a dual-core processor and a 256 MB memory capacity and supports RSTP protocol.

Product reference:

- **TM262L01MDESE8T: Modicon M262 dPAC**

The **TM262L01MDESE8T** controller has no embedded I/O; it supports Modicon TM3 I/O and Modicon Edge I/O NTS expansion modules:

- Up to 3,000 discrete I/O channels
- Up to 875 analog I/O channels
- Up to 16 Islands with a maximum of 32 modules each.

It is possible to control up to 4 TeSys U and TeSys D motor starters by connecting a **TM3XTYS4** TM3 module to the Modicon M262 dPAC.

(1) Expert/specialist modules are not supported in this release. Please refer to the compatibility list on [page 36](#).

(2) These values are theoretical limits; the device limits are highly dependent on the event load of the user application.

Distributed Programmable Automation Controller (dPAC) Platforms (continued)

Altivar ATV dPAC module



Altivar Process drives slots



VW3A3530D

The ATV dPAC module is distributed controller solution platform, with 12 MB memory for programs and data. It is intended to be used as a slide-in option for ATV600, ATV900, and ATV340 variable speed drive (VSD) families(1). The Altivar ATV dPAC module is powered by the drive and provides dual Ethernet sockets for connection to peer controllers, distributed I/O, or remote secondary devices.

Product references:

- **VW3A3530D**: Altivar ATV dPAC module
- **VW3A1111**: Graphic display terminal

The **VW3A3530D** dedicated controller has no embedded I/O. However, all standard I/O on the respective Altivar Process and Altivar Machine drives can be used and extended with I/O modules:

- Up to 23 discrete I/O
- Up to 7 analog I/O
- Encoder interfaces (ATV900 and ATV340)
- Safety modules (ATV900 and ATV340)

It is possible to control up to 8 Modbus TCP devices, such as Altivar drives and soft starters, TeSys motor starters, remote I/O using a TM3BCEIP bus coupler, PowerLogic meters, or Harmony Hub wireless sensors.

For more information about the input/output capability, refer to [Altivar dPAC Module VW3A3530D user guide](#).

(1) For details, please refer to the compatibility table on [page 38](#).

Information Technology (IT)/Operational Technology (OT) Communication Protocols		Soft dPAC High Availability (Linux)	Simplex Soft dPAC (Linux)	Simplex Soft dPAC (Windows OS)	M580 dPAC	M262 dPAC	M251 dPAC	ATV dPAC
OPC UA	Client	-	✓	✓	-	✓	-	✓
	Server	✓	✓	✓	✓	✓	✓	✓
MQTT	Client (Pub/Sub)	-	✓	✓	✓	✓	-	✓
Modbus TCP	Client	✓	✓	✓	✓	✓	✓	✓
	Server	✓	✓	✓	✓	✓	✓	✓
Modbus RTU	Client	-	-	-	-	✓	✓	-
	Server	-	-	-	-	✓	✓	-
EtherNet/IP	Scanner (Client)	-	✓	-	✓	✓	✓	-
PROFIBUS DP	Client	Through Modbus TCP third party gateway (1)	Through Modbus TCP third party gateway (1)	Through Modbus TCP third party gateway (1)	Through Modbus TCP third party gateway (1)	Through Modbus TCP third party gateway (1)	Through Modbus TCP third party gateway (1)	Through Modbus TCP third party gateway (1)
Asi-5 / Asi-3		Through Modbus TCP third party gateway (1)	Through Modbus TCP third party gateway (1)	Through Modbus TCP third party gateway (1)	Through Modbus TCP third party gateway (1)	Through Modbus TCP third party gateway (1)	Through Modbus TCP third party gateway (1)	Through Modbus TCP third party gateway (1)
HART		✓	✓	-	✓	-	-	-
Open TCP/IP		-	✓	✓	✓	✓	✓	✓
EtherCAT	Main Device (Client)	-	✓	-	-	-	-	-
PROFINET	Client (IO-Controller)	-	✓	-	-	-	-	-
	Server (IO-Device)	-	✓	-	-	-	-	-
IEC 61850 MMS	Client	-	✓	-	-	-	-	-

(1) Refer to the documentation for the compatibility of gateways.

Distributed Programmable Automation Controller (dPAC) Platforms (continued)

Selection guide

		High Availability Soft dPAC	Simplex Soft dPAC (Linux OS)	Simplex Soft dPAC (Windows OS)	Modicon M580 dPAC	Modicon M262 dPAC	Modicon M251 dPAC	Altivar dPAC	
									
Applications	Type Specification	Containerized device For critical real time applications	Containerized device For real time applications	Virtualized device For non-real time applications	Embedded device For robust process application	Embedded device For performance modular machines	Embedded device For small modular machines	Embedded device For distributed or Variable Speed Drive centric applications, including mini modular machines	
Max Application size (Mbytes)		Scalable ⁽¹⁰⁾	Scalable ⁽¹⁰⁾	Scalable ⁽¹⁰⁾	100MB	100MB	20MB	16MB	
Communication fieldbus and network performance	Embedded	OPC UA Server (40,000 variables) Modbus TCP Client (64 devices) ⁽¹⁾ Modbus TCP Server	OPCUA Server (40,000 variables) OPCUA Client EtherNet/IP (128 devices @20ms RPI) ⁽¹⁾ Modbus TCP Client (64 devices) ⁽¹⁾ Modbus TCP Server (2300 variables) ⁽¹⁾ Profinet Client (IO-Controller) Profinet Server (IO-Device) EtherCAT Main Device IEC 61850 MMS Client	OPCUA Server (40,000 variables) Modbus TCP Client (64 devices) ⁽¹⁾ Modbus TCP Server (2300 variables) ⁽¹⁾	OPCUA Server (5000 variables) EtherNet/IP (16 devices @20ms RPI) ⁽¹⁾ Modbus TCP Client (24 devices) ⁽¹⁾ Modbus TCP Server (1200 variables) ⁽¹⁾	OPCUA Server (5000 variables) EtherNet/IP (32 devices @20ms RPI) ⁽¹⁾ Modbus TCP Client (32 devices) ⁽¹⁾ Modbus TCP Server (1600 variables) ⁽¹⁾ Modbus RTU 115 kbps	OPCUA Server (1000 variables) EtherNet/IP (8 devices @20ms RPI) ⁽¹⁾ Modbus TCP Client (16 devices) ⁽¹⁾ Modbus TCP Server (800 variables) ⁽¹⁾ Modbus RTU 115 kbps	OPCUA Server (2000 variables) OPCUA Client Modbus TCP Client (8 devices) ⁽¹⁾ Modbus TCP Server (800 variables) ⁽¹⁾	
	Optional	Profibus DP through Modbus TCP third party gateway	Asi-5/Asi-3 through Modbus TCP third party gateway Profibus DP through Modbus TCP third party gateway	Asi-5/Asi-3 through Modbus TCP third party gateway Profibus DP through Modbus TCP third party gateway	Asi-5/Asi-3 through Modbus TCP third party gateway Profibus DP through Modbus TCP third party gateway	Asi-5/Asi-3 through Modbus TCP third party gateway Profibus DP through Modbus TCP third party gateway	Asi-5/Asi-3 through Modbus TCP third party gateway Profibus DP through Modbus TCP third party gateway	Asi-5/Asi-3 through Modbus TCP third party gateway Profibus DP through Modbus TCP third party gateway	–
	Connectivity services	–	MQTT Client (Pub/Sub)	MQTT Client (Pub/Sub)	Open TCP/IP MQTT Client (Pub/Sub)	Open TCP/IP	Open TCP/IP	Open TCP/IP	Open TCP/IP MQTT Client (Pub/Sub)
I/O⁽²⁾	Discrete I/O channels	1750	13750	–	1408	3448	112	23	
	Analog I/O channels	1750	5250	–	352	987	112	7	
Type of I/Os	Local/Extension I/O	–	–	–	Up to 1408 discrete I/O channels Up to 352 analog I/O channels Up to 4 Modicon X80 backplane	Up to 448 discrete I/O channels Up to 112 analog I/O channels Up to 14 Modicon TM3	Up to 112 discrete I/O channels Up to 112 analog I/O channels Up to 14 Modicon TM3	Up to 23 discrete I/O channels (depending on drive reference) Up to 7 analog I/O channels (depending on drive reference)	
	Remote I/O	Up to 1750 discrete I/O channels ⁽³⁾ Up to 1750 analog I/O channels ⁽³⁾ Up to 16 Modicon X80 backplane	Up to 1750 discrete I/O channels ⁽³⁾ Up to 1750 analog I/O channels ⁽³⁾ Up to 16 Modicon X80 backplane	–	–	–	–	–	
	Distributed I/O	–	Up to 12,000 discrete I/O channels Up to 3,500 analog I/O channels Up to 64 islands with a maximum of 32 modules	–	–	Up to 3,000 discrete I/O channels Up to 875 analog I/O channels Up to 16 islands with a maximum of 32 modules	–	–	
Compatible expansion I/O module ranges⁽⁵⁾	Local/Extension I/O	–	–	–	4 Modicon X80 backplane	14 Modicon TM3	14 Modicon TM3	Altivar Safety option modules	
	Remote I/O	16 Modicon X80 backplane ⁽⁴⁾	Modicon CRD, Modicon X80	–	–	–	–	–	
	Distributed I/O	Modicon Edge I/O NTS	Modicon Edge I/O NTS	–	Modicon Edge I/O NTS	Modicon Edge I/O NTS	Modicon Edge I/O NTS	Modicon TM3 (Modbus TCP) Modicon Edge I/O NTS (Modbus TCP)	
References		Hardware agnostic⁽⁸⁾	Hardware agnostic⁽⁸⁾	Hardware agnostic⁽⁹⁾	BMED581020 / BMED581020C	TM262L01MDESE8T	TM251MDESE	VW3A3530D⁽⁶⁾ / VW3A1111⁽⁷⁾	

(1) Recommended limit

(2) These values are theoretical limits; the device limits are highly dependent on the event load of the user application.

(3) I/O count can increase or decrease depending on the CPU version used on the host iPC, I/O scan rate or change rate, and the auxiliary application load with connected devices, such as Modbus. The host iPC processor speed greatly affects the performance capabilities of the controller. The performance limits can be increased when using more powerful iPC processors, such as the Intel i5/i7 offerings.

(4) BMECRD0100: Ethernet Remote I/O drop adapter for Edge Controller powered by Soft dPAC

(5) Consult the [DIA3ED2140109EN](#) and [DIA6ED2131203EN](#) catalog for additional information on the I/O compatibility.

(6) Altivar ATV dPAC module

(7) Graphic display terminal for Altivar ATV340

(8) Reference value based on the Harmony P6 Celeron (2 cores)

(9) Minimum requirements available in the section Windows – Software dPAC (page 13).

(10) Maximum application size can increase or decrease depending on the CPU version on the host iPC. Refer to user guide for minimum hardware specification.

Distributed Programmable Automation Controller (dPAC) Platforms (continued)

System requirements

Linux – Software dPAC

System requirements	Minimum	Recommended	Required for RT control
OS	Debian 10.3, Ubuntu 18.04 and 20.04, or Raspbian 32- or 64-bit		Ubuntu 20.04 with low-latency patch or other distribution with PREEMPT-RT patch
Docker	Docker 19.03.8 and above		
CPU	X86/ARM 1 GHz or higher	Multi-core X86/ARM 1 GHz or higher	Dedicated cores
RAM	256 MB	1 GB	
HDD/SSD	16 GB	32 GB	
Network interface	At least one Network Interface Card (NIC)	Two NICs to isolate control and device networks	One NIC per container for RT fieldbuses
Time synchronization	NTPv4 client	NTPv4 client support with monotonic and drift compensation	

Linux – Software dPAC, High Availability⁽¹⁾

System requirements	Description	Note
Processor	PC Celeron 4305UE, 2 Core, 2 Threads	Need Multi-core X86 processor. ARM is not supported for v24.1
RAM	SO-DIMM RAM 4 GB	Minimum 4GB. ECC support is optional.
Memory	M.2 SSD Standard Endurance 128 GB	128 GB is not required. However, it is the lowest that was tested.
Network interface	RJ45 GbE Ethernet NIC	Three NICs are needed for redundant network configuration. <ul style="list-style-type: none"> • One 1 GB speed NIC for interlink connection • Two 100MB for device network
Operating system	Linux	Ubuntu 20.04 (Harmony P6)/22.04 (ASRock) tested

⁽¹⁾ A set of 2 manageable switches compatible with RSTP and having at least 6 physical ports is also needed.

Windows – Software dPAC

System requirements	Minimum	Performance
Processor	1 GHz	2 GHz or higher
RAM ⁽¹⁾	2 GB	4 GB
Hard disk free space ⁽¹⁾	1 GB	10 GB
Display resolution	1280x1024	1920x1080 or higher
Pointing device	Mouse or compatible	
Network interface	One Ethernet interface	
Operating system	Microsoft Windows 10 Professional (64-bit) Version 1903 and later, Microsoft Windows 11 Professional Version 21H2 and later, and Microsoft Server Version 2019 (1809 and later)	
.NET framework	.NET 4.8	.NET 4.8 or higher


⁽¹⁾ Requirement is indicated for each software package. More than one software package can be installed on the same device. In this case, you need to add the respective RAM and hard disk free space requirements together. For example, if you install the HMI and Archive software packages on the same device, the minimum RAM required is 4 GB (2 GB + 2 GB).

Types of standard architectures

EcoStruxure Automation Expert breaks the dependency between the application software and the hardware platform it runs. Together with its distribution capabilities, EcoStruxure Automation Expert is a unique automation tool to be used in any kind of architecture, from small machines up to complex process architecture.


Example of Soft dPAC standard architecture

The architecture for small machines increases engineering efficiency by using the Automatically generated network transparent communications between controller and HMI objects with many-to-many connectivity and communication protocol for field devices.





Distributed architectures

The openness and scalability makes it ready for IT/OT with connectivity AI model by HTTP and apps and analytics in an architecture with distributed controllers.



Examples of distributed architectures

The distributed architectures below illustrates the extensive possibilities of distributed control applications among the different dPACs. These examples are focused on a combination of Modicon M262d, Modicon M580d, Simplex Soft dPAC, and Altivar ATV dPACs.



Types of Soft dPAC architectures

The Soft dPAC HA solution is used for more demanding applications in terms of the availability of the control/command system where no interruption of the process can be tolerated. The Soft dPAC HA solution helps increase productivity by minimizing process downtime.

As a new step in the adoption of software-defined automation principles, EcoStruxure Automation Expert V25.0 introduces High Availability Disruption Avoidance (HADA), an innovative new type of Soft dPAC architecture enabling new ways of increasing plant availability, reducing mean time to repair (MTTR), and enabling system self-healing capabilities, in our path towards autonomous operation.

Simplex			
All Running	1 st Failure	2 nd Failure	Comments
		—	<ul style="list-style-type: none"> • Single point of failure • Control application/controller failure disrupts plant operation
High Availability			
All Running	1 st Failure	2 nd Failure	Comments
			<ul style="list-style-type: none"> • Primary and secondary are constantly in sync • Avoids single point of failure • Control application continues to run on secondary after 1st failure, help ensuring plant operation • HA state not maintained after 1st failure • 2nd failure disrupts the plant operation
High Availability Disruption Avoidance			
All Running	1 st Failure	2 nd Failure	Comments
			<ul style="list-style-type: none"> • Primary and secondary are constantly in sync with one or more connected spares available • Control application continues to run on secondary after 1st failure and on spare after subsequent failures, creating new HA pairs • HA state maintained as long as spares are available • No plant disruption as long as spares are available

Types of high-availability architectures


High-Availability Soft dPAC based on Ethernet RIO architecture

The high-availability configuration comprises two identical iPCs (industrial computers), each hosting a High-Availability Soft dPAC, and configured to run in a Pair where one instance (a Partner) is driving the process while the other Partner is ready to take over control, if the first one stops working.

The two Partners check each other's availability by communicating over two links:

- A dedicated cable (the HA Interlink), and
- The device network, which also carries commands and diagnostics.

In a high-availability Soft dPAC topology based on an Ethernet RIO architecture, devices are hardwired on remote I/O over Ethernet by BMECRD1020 (RIO drop adapter for Modicon X80 I/Os modules). This high-availability system is used for sensitive processes that require a bumpless I/O control takeover time.



1. Linux-based iPC pair, each hosting an instance of High Availability Soft dPAC
2. HA Interlink: 1GB/s Network Interface Card (NIC)/connection
3. Redundant network: 100MB/s with NIC bonding
4. Linux-based standalone iPC, hosting an instance of non-redundant Soft dPAC
5. Non-redundant Modicon X80 I/O drop with BMECRD0100 RIO drop adapter and redundant power supplies
6. Non-redundant Modicon X80 I/O drop with BMECRD0100 RIO drop adapter and redundant power supplies
7. Remote I/O RSTP - enabled ring network
8. Workstation running EcoStruxure Automation Expert Build Time
9. Workstation running AVEVA System Platform (ASP), AVEVA Operation Management Interface (OMI), and AVEVA historian. Communication is over OPC UA
10. Workstation running EcoStruxure Automation Expert Runtime HMI
11. Managed switches, for example, Modicon switch

Components of a high-availability system


High-Availability Soft dPAC pair

At the heart of a high-availability architecture are two *i*PCS - Preferred Primary and Non-Preferred Primary, with identical hardware configurations, based on Linux software connected via a high-speed (1 Gbps) communication link. The Preferred Primary device executes the application program and controls the I/Os located in Modicon X80 drops. The Non-Preferred Primary remains in the background. In the event of a detected error affecting the Primary device, the Standby system switches over automatically, changing over the execution of the application program and control of the I/O to the Standby device with an up-to-date data context. Once the changeover is complete, the Standby device becomes the Primary device while the former Primary device is being cleared from the detected error: when clearance is done, the device reconnects to the standby system and acts as the Standby device. The changeover from Primary to Standby is performed smoothly at the outputs and is completely transparent to the process.

Modicon X80 Redundant power supplies and compatible backplanes

For high-availability applications, two BMXCPS●●02 redundant power supplies can be used on the same rack to increase the availability of power supply. They are supported by 6-slot BMEXBP0602 backplane and 10-slot BMEXBP1002 backplane equipped with dual slots marked CPS1 and CPS2. On CPS1 slot, the power supply is initially set as Primary and on CPS2 slot, as Standby. When power stops being supplied in accordance with expected rate, they switch roles so that power can be continuously delivered. See Modicon X80 modules catalog for more details.

Example of complex high-availability architecture




The complex architecture illustrates the extensive possibilities of the High-Availability Soft dPAC in terms of cross-communication, RIO and DIO networks:

1. Linux-based *i*PC pair, each hosting an instance of High Availability Soft dPAC
2. HA Interlink: 1GB/s NIC/connection
3. Redundant network: 100MB/s with NIC bonding
4. Remote I/O RSTP enabled ring network
5. Non-redundant X80 I/O drop with:
 - BMECRD0100 RIO drop adapter
 - Redundant power supplies on the main backplane
6. Non-redundant Modicon X80 I/O drop with BMECRD0100 RIO drop adapter
7. Cross-communication with Altivar ATVdPAC for motor control
8. Modbus TCP devices such as in an Intelligent power (PM5500), motor control center (MasterPact MTZ) or motor controllers (TeSysT)
9. Managed switches
10. Workstation running AVEVA System Platform (ASP), AVEVA Operation Management Interface (OMI), and AVEVA historian
Communication is over OPC UA
11. Workstation running EcoStruxure Automation Expert Runtime HMI.

Types of high-availability architectures (continued)


High-Availability Disruption Avoidance architecture



1. Linux-based iPC pair, each hosting an instance of High Availability Soft dPAC
2. Linux-based iPC spare
3. HADA Interlink network: 1GB/s Network Interface Card (NIC)/connection
4. Managed switch, for example, Modicon switch
5. Redundant network: 100MB/s with NIC bonding
6. Non-redundant Modicon X80 I/O drop with BMECRD0100 RIO drop adapter and redundant power supplies
7. Remote I/O RSTP - enabled ring network
8. Workstation running EcoStruxure Automation Expert Build Time
9. Workstation running AVEVA System Platform (ASP), AVEVA Operation Management Interface (OMI), and AVEVA historian. Communication is over OPC UA
10. Workstation running EcoStruxure Automation Expert Runtime HMI
11. Orchestrator for High Availability Soft dPAC

EcoStruxure Automation Expert – Perpetual licensing

The EcoStruxure Automation Expert offer provides a simplified approach to the software licensing model. The offer has two categories of licenses – **Engineering** and **Application**.



EcoStruxure Automation Expert – Engineering license

The **Engineering** software requires a license per seat to create Automation Expert based applications. The **Engineering** license provides the capability to create, configure, and manage UAO runtime control applications, HMI, archive, and network/device topologies.

When the user downloads and installs Automation Expert, they benefit from a free Trial version. The Trial version includes a full function demo mode for 42 days unlicensed, capable of deploying a solution in a local simulation. During the trial period, all the software features except the application deployment and features protected by engineering add-on licenses can be used.

The **Engineering** licenses can be perpetual or subscription-based⁽¹⁾ and are available in two types:

Standard: The Standard engineering license includes an essential set of features, supports custom library creation and offers the ability to extend features by including add-on licenses to address any type of applications.

The add-ons that are available with EcoStruxure Automation Expert Standard licenses are:


- Asset Link for AVEVA OMI, optional add-on to create applications objects in the AVEVA System Platform in an automated workflow.
- High Availability Engineering, optional add-on to create applications that promote continuous operation and minimize downtime in critical applications by using high availability soft dPAC.
- Procedural Automation, optional add-on to create automated routines, task and complex sequences or procedures.
- Asset Link for Bulk Engineering, to extract data from engineering tools for automated application generation and is already included in the Standard engineering license.

Professional: The Professional engineering license includes all currently available features. Any new features released within the first year following the activation date will be included in software updates.

Each commercial license provides:

- The capability to design, develop, simulate with HMI, and commission a complete system
- Collaborative engineering (SVN client) plugin
- Physical topology editor
- Free software updates, within the first 12 months from the activation date
- Support desk from 9 am to 5pm
- Access to private communities on exchange.se.com for p2p support, libraries, project samples, training material, TVDAs, and so on.

(1) For more information, refer to [EcoStruxure Automation Expert – Subscription-based licensing](#).



Modular, now available in **multi-seat** to adapt to Design Team size: 1, 3, 10, and 100 seats, and their upgrades.

Engineering license references

The engineering licenses are available in Standard or Professional versions. Standard and Professional licenses can be perpetual or subscription-based⁽¹⁾ and are available in single seat and multi-seats.

Reference	Description
EALBTC	EcoStruxure Automation Expert - Standard Engineering license
EALBTC3	EcoStruxure Automation Expert - Standard Engineering license 3 seats
EALBTCT	EcoStruxure Automation Expert - Standard Engineering license 10 seats
EALBTCH	EcoStruxure Automation Expert - Standard Engineering license 100 seats
EALBFC	EcoStruxure Automation Expert - Professional Engineering license
EALBFC3	EcoStruxure Automation Expert - Professional Engineering license 3 seats
EALBFCT	EcoStruxure Automation Expert - Professional Engineering license 10 seats
EALBFCH	EcoStruxure Automation Expert - Professional Engineering license 100 seats
EALUAOC	EcoStruxure Automation Expert - Engineering license for UAO vendor

The standard engineering license includes the "Asset Link for Bulk Engineering" add-on and allows for the addition of the following add-ons:

Reference	Description
EALBATC	Add-on for Asset Link for AVEVA OMI
EALBAHC	Add-on for High Availability
EALBAPC	Add-on for Procedural/Automation

The engineering licenses can be upgraded from Standard to Professional, and from single-seat to multi-seat versions. These upgrades are handled using upgrade credit units and are managed through MySchneider software experience⁽²⁾.

Reference	Description
EALBUC	EcoStruxure Automation Expert – Engineering license upgrade credit unit

(1) For more information, refer to [EcoStruxure Automation Expert – Subscription-based licensing](#).

(2) For further details on how to upgrade your current license, contact your local Schneider Electric representative.


EcoStruxure Automation Expert – Perpetual licensing (continued)

EcoStruxure Automation Expert – Application licenses

In addition to the engineering license required to create EcoStruxure Automation Expert applications, an **Application** license is required for the operation and maintenance of the application.

The **Application** licenses are available for Control and Orchestration use cases. These **Application** licenses are available in perpetual and subscription-based models⁽¹⁾.

The optional licenses are required depending on the type of HMI platform or additional communication protocol used in the application.



For exact calculation of the number of Application licenses, a software license configurator for EcoStruxure Automation Expert is available on our [website](#).

(1) For more information, refer to [EcoStruxure Automation Expert – Subscription-based licensing](#).

EcoStruxure Automation Expert – Perpetual licensing (continued)

EcoStruxure Automation Expert – Application Licenses

The **Application** licenses are stackable and independent of the number and type of controllers used in the solution, and are available in two different types:

■ **Control Application Licenses:**

- Based on IO Points (IOPs) and independent of the number and type of controllers.
- Available in control packs of 10, 100, 1000, and 5000 IOPs, users can stack several packages together in the same solution for flexibility and scalability.
- Available for Simplex and High-Availability configurations.
- Available in perpetual and subscription-based models⁽¹⁾.

An IO Point is the physical or hardwired I/Os used for control purposes, regardless of:

- Type of signal: Digital or Analog
- Source: Local, Distributed, or Remote

Reference	Description
EALPTXP	EcoStruxure Automation Expert - Control pack 10 IO Points
EALPTCP	EcoStruxure Automation Expert - Control pack 100 IO Points
EALPTMP	EcoStruxure Automation Expert - Control pack 1000 IO Points
EALPTVMP	EcoStruxure Automation Expert - Control pack 5000 IO Points
EALPTHACP	EcoStruxure Automation Expert - Control pack High Availability 100 IO Points
EALPTHAMP	EcoStruxure Automation Expert - Control pack High Availability 1000 IO Points
EALPTHAVMP	EcoStruxure Automation Expert - Control pack High Availability 5000 IO Points

■ **Orchestration Application Licenses:** for competitiveness in small projects for machine, discrete and hybrid process, where:

- Based on orchestrated nodes and independent of the number and type of controllers.
- Available in node packs of 1, 10, 100, and 500, users can stack several packages together in the same solution for flexibility and scalability.
- Available in perpetual and subscription-based models⁽¹⁾.

An Orchestrated node is any smart or intelligent device, based on ISA-95 hierarchy levels 0 and 1, that exchanges communication, control or process parameters with EcoStruxure Automation Expert application over a network.

Examples include variable speed drives, smart flow meters, power meters, packaged units, skids, and other smart devices.

When orchestrated nodes are connected through a gateway, the gateway is not considered as single node. Each smart device connected to the gateway must be counted individually.

Reference	Description
EALRIP	EcoStruxure Automation Expert - Orchestration pack 1 node
EALRXP	EcoStruxure Automation Expert - Orchestration pack 10 nodes
EALRCP	EcoStruxure Automation Expert - Orchestration pack 100 nodes
EALRVCP	EcoStruxure Automation Expert - Orchestration pack 500 nodes

(1) For more information, refer to [EcoStruxure Automation Expert – Subscription-based licensing](#).

EcoStruxure Automation Expert – Perpetual Licensing (continued)

EcoStruxure Automation Expert – HMI license

The Automation Expert HMI license includes rights to both HMI and Archive runtimes. All runtime licenses are perpetual. Different license types are required depending on the platform on which the runtime is installed, as per the following table:

Automation Expert Runtime	Platform	License type
HMI ⁽¹⁾	Harmony ST6 HMI range	1 license per HMI runtime instance
HMI ⁽¹⁾	PC-type HMI (Windows 10/Linux)	1 license per HMI runtime instance

(1) Each license includes both Automation Expert HMI and Automation Expert Archive runtime rights.

Download the HMIBMI, HMIBMO,
and HMIP6 ranges catalog



The Automation Expert HMI Runtime licenses are:

Reference	Description
EALH1P	Automation Expert HMI Runtime - Panel (ST6)
EALH2P	Automation Expert HMI Runtime - Operator (iPC)

For exact calculation of the number of devices and controller type for the application license, a software license configurator for Automation Expert is available on se.com.

EcoStruxure Automation Expert – Communication Protocol License

The communication protocol licenses are optional licenses required to connect to any device using the specified protocol.

The communication protocol OPC UA client provides service function blocks that allow to connect over OPC UA to multiple servers and exchange data with them, including read, write, and monitor data rights.

The communication protocol OPC UA client is available on the following platforms:

- Soft dPAC Linux, includes encrypted communication between client and server.
- Soft dPAC Windows.
- ATV dPAC, includes encrypted communication between client and server.

Reference	Description
EALCUP	Automation Expert – Communication Protocol OPC UA Client

The communication protocol PROFINET RT IO-Controller (Client) provides service function blocks that enable the controller to operate as a PROFINET IO-Controller, allowing to exchange real time process data with multiple PROFINET IO-Devices.

Reference	Description
EALCPP	Automation Expert – Communication Protocol PROFINET RT IO-Controller Client

The communication protocol EtherCAT MainDevice (Client) provides service function blocks that allow the controller to function as an EtherCAT main device, managing and communicating with multiple EtherCAT sub devices, allowing to exchange data and precise synchronization with field devices.


Reference	Description
EALCEP	Automation Expert – Communication Protocol EtherCAT Main Device Client

The Communication Protocol IEC 61850 provides services function blocks that allow to enable IEC 61850 MMS Client to the controller and exchange data with multiple intelligent electronic devices (IED). The Communication Protocol IEC 61850 is available on Simplex Soft dPAC Linux.

Reference	Description
EALCGP	EcoStruxure Automation Expert – Communication Protocol IEC 61850

EcoStruxure Automation Expert – Subscription-based licensing

To provide customers with more business and economic model flexibility and reduced obsolescence risk, both **Engineering** and **Application** licenses are available under a subscription-based model consisting of 1-year termed subscriptions. The subscription-based licenses model is available for project business with end-users.



Each commercial license provides:

- The capability to design, develop, simulate with HMI, and commission a complete system
- Collaborative engineering (SVN client) plugin
- Physical topology editor
- Free software updates
- Support desk from 9 am to 5 pm
- Access to private communities on exchange.se.com for p2p support, libraries, project samples, training material, TVDAs, and so on.

Engineering subscription-based licenses

The Engineering subscription-based licenses are available in two different types:

Standard: A basic set of features equivalent to Standard perpetual-based license.

Professional: This version includes all available features, including:

- Asset Link for AVEVA OMI
- High Availability Engineering
- Procedural Automation

The **Engineering** subscription-based licenses are offered for single-seat and multi-seats.

Reference	Description
EALBTS1	EcoStruxure Automation Expert - Build - Standard Engineering Yearly
EALBTS13	EcoStruxure Automation Expert - Standard Engineering license 3 seats Yearly
EALBTS1T	EcoStruxure Automation Expert - Standard Engineering license 10 seats Yearly
EALBTS1H	EcoStruxure Automation Expert - Standard Engineering license 100 seats Yearly
EALBTS2	EcoStruxure Automation Expert - Build - Professional Engineering Yearly
EALBTS23	EcoStruxure Automation Expert - Professional Engineering license 3 seats Yearly
EALBTS2T	EcoStruxure Automation Expert - Professional Engineering license 10 seats Yearly
EALBTS2H	EcoStruxure Automation Expert - Professional Engineering license 100 seats Yearly

EcoStruxure Automation Expert – Subscription-based licensing (continued)

Application subscription-based licenses

The **Application** subscription-based licenses are stackable and independent on the number and type of controllers used in the solution and are available in two different types

Control:

- Based on IO points and available in different control packs of 10, 100, 1000 and 5000 IOPs. The user can stack several packages together in the same solution for flexibility and scalability
- Available for using Simplex and High-Availability configurations

Orchestration:

- Based on orchestrated nodes and available in different orchestration packs of 1, 10, 100, 500 nodes. The user can stack several packages together in the same solution for flexibility and scalability

The optional licenses are required depending on the type of additional communication protocol used in the application.

Reference	Description
EALPTCY	EcoStruxure Automation Expert - Control pack 100 IO Points Yearly
EALPTMY	EcoStruxure Automation Expert - Control pack 1000 IO Points Yearly
EALPTVMY	EcoStruxure Automation Expert - Control pack 5000 IO Points Yearly
EALPTHACY	EcoStruxure Automation Expert - Control pack High Availability 100 IO Points Yearly
EALPTHAMY	EcoStruxure Automation Expert - Control pack High Availability 1000 IO Points Yearly
EALPTHAVMY	EcoStruxure Automation Expert - Control pack High Availability 5000 IO Points Yearly
EALRXY	EcoStruxure Automation Expert - Orchestration pack 10 nodes Yearly
EALRCY	EcoStruxure Automation Expert - Orchestration pack 100 nodes Yearly
EALRVCY	EcoStruxure Automation Expert - Orchestration pack 500 nodes Yearly
EALCUY	EcoStruxure Automation Expert - Communication Protocol OPC UA Client Yearly
EALCPY	EcoStruxure Automation Expert – Communication Protocol PROFINET RT IO-Controller Client Yearly
EALCEY	EcoStruxure Automation Expert – Communication Protocol EtherCAT Main Device Client Yearly
EALCGY	EcoStruxure Automation Expert – Communication Protocol IEC 61850 Yearly


Please contact your Schneider Electric representative for additional information.

In addition to the advantages included in perpetual licenses, subscription-based licenses include:

- Access to upcoming software releases and features in the scope of your license
- Customer adoption support plan, with a Trusted Advisor that will support you to reduce your time to value with each new release and its features, recommend the appropriate evolutions, and support you on license lifecycle and renewal process.

EcoStruxure Automation Expert Licensing – Architecture

Example of distributed controller architecture



Engineering Licenses

Considering a total of 3 engineering seats

Reference	Description	No. of Seats
EALBTC3	EcoStruxure Automation Expert - Standard Engineering license 3 seats	1


Application Licenses

Considering the full application, Unit 1, Unit 2, and Unit 3.
Total of 450 IO Points and 40 orchestrated nodes.

Reference	Description	No. of Licenses
EALPTCP	EcoStruxure Automation Expert - Control pack 100 IO Points	5
EALRXP	EcoStruxure Automation Expert - Orchestration pack 10 nodes	4

For exact calculation of the number of Application licenses, a software license configurator for EcoStruxure Automation Expert is available on our [website](#).

EcoStruxure Automation Expert Licensing – Architecture (continued)
High-Availability Disruption Avoidance architecture



Engineering licenses

Considering a total of 10 engineering seats

Reference	Description	No. of Seats
EALBFCT	EcoStruxure Automation Expert - Professional Engineering license 10 seats	1

Application licenses

Considering the full high-availability application.
Total of 600 IO Points and 100 orchestrated nodes.

Reference	Description	No. of Licenses
EALPTHACP	EcoStruxure Automation Expert - Control pack High Availability	6
EALRCP	EcoStruxure Automation Expert - Orchestration pack 100 nodes	1

For exact calculation of the number of Application licenses, a software license configurator for EcoStruxure Automation Expert is available on our [website](#).

List of Modicon X80 hardware compatible with Modicon M580 dPAC, Modicon CRD for Simplex/High Availability Soft dPAC (Linux OS)

Type	Reference	Description	Compatibility with Modicon M580 dPAC	Compatibility with Modicon CRD for Simplex/High Availability Soft dPAC (Linux OS)
Backplane	BMEXBP0400	4-slot Ethernet backplane	Yes	Yes
Backplane	BMEXBP0400H	Ruggedized 4-slot Ethernet backplane	Yes	Yes
Backplane	BMEXBP0602	6-slot Ethernet backplane redundant PS	Yes	Yes
Backplane	BMEXBP0602H	Ruggedized 6-slot Ethernet backplane redundant PS	Yes	Yes
Backplane	BMEXBP0800	8-slot Ethernet backplane redundant PS	Yes	Yes
Backplane	BMEXBP0800H	Ruggedized 8-slot Ethernet backplane redundant PS	Yes	Yes
Backplane	BMEXBP1002	10-slot Ethernet backplane redundant PS	Yes	Yes
Backplane	BMEXBP1002H	Ruggedized 10-slot Ethernet backplane redundant PS	Yes	Yes
Backplane	BMEXBP1200	12-slot Ethernet backplane redundant PS	Yes	Yes
Backplane	BMEXBP1200H	Ruggedized 12-slot Ethernet backplane redundant PS	Yes	Yes
Backplane	BMXXBP0400	4-slot backplane	Yes	Yes
Backplane	BMXXBP0400H	Ruggedized 4-slot backplane	Yes	Yes
Backplane	BMXXBP0600	6-slot backplane	Yes	Yes
Backplane	BMXXBP0600H	Ruggedized 6-slot backplane	Yes	Yes
Backplane	BMXXBP0800	8-slot backplane	Yes	Yes
Backplane	BMXXBP0800H	Ruggedized 8-slot backplane	Yes	Yes
Backplane	BMXXBP1200	12-slot backplane	Yes	Yes
Backplane	BMXXBP1200H	Ruggedized 12-slot backplane	Yes	Yes
Backplane	BMXXBE1000	Standard backplane extender	Yes	Yes
Backplane	BMXXBE1000H	Ruggedized Standard backplane extender	Yes	Yes
Backplane	BMXXBE2005	Backplane extender kit	Yes	Yes
Extension cable	BMXXBC008K	Backplane extension cable 0.8 m/2.6 ft	Yes	Yes
Extension cable	BMXXBC015K	Backplane extension cable 1.5 m/4.9 ft	Yes	Yes
Extension cable	BMXXBC030K	Backplane extension cable 3 m/9.8 ft	Yes	Yes
Extension cable	BMXXBC050K	Backplane extension cable 5 m/16.4 ft	Yes	Yes
Extension cable	BMXXBC120K	Backplane extension cable 12 m/39 ft	Yes	Yes
Power Supply	BMXCPS2000	Standard AC power supply	Yes	Yes
Power Supply	BMXCPS2000H	Ruggedized standard AC power supply	Yes	Yes
Power Supply	BMXCPS2010	Standard isolated DC power supply	Yes	Yes
Power Supply	BMXCPS3020	High-power isolated 24 to 48 V DC power supply	Yes	Yes
Power Supply	BMXCPS3020H	Ruggedized high-power isolated 24 to 48 V DC power supply	Yes	Yes
Power Supply	BMXCPS3500	High-power AC power supply	Yes	Yes
Power Supply	BMXCPS3500H	Ruggedized high-power AC power supply	Yes	Yes
Power Supply	BMXCPS3522	Redundant 125 V DC power supply	Yes	Yes
Power Supply	BMXCPS3522H	Ruggedized redundant 125 V DC power supply	Yes	Yes
Power Supply	BMXCPS3540T	High-power 125 V DC power supply	Yes	Yes
Power Supply	BMXCPS4002	Redundant AC power supply	Yes	Yes
Power Supply	BMXCPS4002H	Ruggedized redundant AC power supply	Yes	Yes
Power Supply	BMXCPS4022	Redundant 24 to 48 V DC power supply	Yes	Yes
Power Supply	BMXCPS4022H	Ruggedized redundant 24 to 48 V DC power supply	Yes	Yes
SD card	BMXRMS004GPF	Optional M580 SD card 4 GB	Yes	No
Analog I/O Input	BMEAH10812H	Ruggedized 8x current isolated analog inputs, HART	Yes	Yes
Analog I/O Input	BMXAMI0410	4x voltage/current isolated high-speed analog inputs	Yes	Yes
Analog I/O Input	BMXAMI0410H	Ruggedized 4x voltage/current isolated high-level analog inputs	Yes	Yes
Analog I/O Input	BMXAMI0800	8x voltage/current non-isolated fast analog inputs	Yes	Yes
Analog I/O Input	BMXAMI0800H	Ruggedized 8x voltage/current non-isolated fast analog inputs	Yes	Yes
Analog I/O Input	BMXAMI0810	8x voltage/current isolated fast analog inputs	Yes	Yes
Analog I/O Input	BMXAMI0810H	Ruggedized 8x voltage/current isolated fast analog inputs	Yes	Yes
Analog I/O Input	BMXART0414	4x isolated TC/RTD inputs	Yes	Yes
Analog I/O Input	BMXART0414H	Ruggedized 4x isolated TC/RTD inputs	Yes	Yes
Analog I/O Input	BMXART0814	8x isolated TC/RTD inputs	Yes	Yes
Analog I/O Input	BMXART0814H	Ruggedized 8x isolated TC/RTD inputs	Yes	Yes
Analog I/O Input	BMEAH10812	8x current isolated analog inputs, HART	Yes	Yes
Analog I/O Output	BMXAMO0210	2x isolated analog outputs	Yes	Yes
Analog I/O Output	BMXAMO0210H	Ruggedized 2x voltage/current isolated analog outputs	Yes	Yes
Analog I/O Output	BMXAMO0410	4x voltage/current isolated analog outputs	Yes	Yes
Analog I/O Output	BMXAMO0410H	Ruggedized 4x voltage/current isolated analog outputs	Yes	Yes
Analog I/O Output	BMXAMO0802	8x current non-isolated analog outputs	Yes	Yes
Analog I/O Output	BMXAMO0802H	Ruggedized 8x current non-isolated analog outputs	Yes	Yes
Analog I/O Output	BMEAHO0412	4x current isolated high-level analog outputs, HART	Yes	Yes
Analog I/O Output	BMEAHO0412C	Coated 4x current isolated high-level analog outputs, HART	Yes	Yes

List of Modicon X80 hardware compatible with Modicon M580 dPAC, Modicon CRD for Simplex/High Availability Soft dPAC (Linux OS) (continued)

Type	Reference	Description	Compatibility with Modicon M580 dPAC	Compatibility with Modicon CRD for Simplex/High Availability Soft dPAC (Linux OS)
Analog I/O Mixed	BMXAMM0600	4x analog inputs - 2x analog outputs	Yes	Yes
Analog I/O Mixed	BMXAMM0600H	Ruggedized 4x analog inputs - 2x analog outputs	Yes	Yes
Discrete I/O Input	BMXDDI1602	16x 24 V DC sink discrete inputs	Yes	Yes
Discrete I/O Input	BMXDDI1602H	Ruggedized 16x 24 V DC sink discrete inputs	Yes	Yes
Discrete I/O Input	BMXDDI1603	16x 48 V DC sink discrete inputs	Yes	Yes
Discrete I/O Input	BMXDDI1603H	Ruggedized 16x 48 V DC sink discrete inputs	Yes	Yes
Discrete I/O Input	BMXDDI3202K	32x 24 V DC sink discrete inputs	Yes	Yes
Discrete I/O Input	BMXDDI3202KH	Ruggedized 32x 24 V DC sink discrete inputs	Yes	Yes
Discrete I/O Input	BMXDDI6402K	64x 24 V DC sink discrete inputs	Yes	Yes
Discrete I/O Input	BMXDDI6402KH	Ruggedized 64x 24 V DC sink discrete inputs	Yes	Yes
Discrete I/O Input	BMXDAI0805	8x 200...240 V AC non-isolated discrete inputs	Yes	Yes
Discrete I/O Input	BMXDAI0814	8x 100...120 V AC isolated discrete inputs	Yes	Yes
Discrete I/O Input	BMXDAI1602	16x 24 V non-isolated discrete inputs	Yes	Yes
Discrete I/O Input	BMXDAI1602H	Ruggedized 16x 24 V non-isolated discrete inputs	Yes	Yes
Discrete I/O Input	BMXDAI1604	16x 100...120 V AC capacitive inputs	Yes	Yes
Discrete I/O Input	BMXDAI1604H	Ruggedized 16x 100...120 V AC capacitive inputs	Yes	Yes
Discrete I/O Input	BMXDAI1614	16x 100...120 V AC isolated discrete inputs	Yes	Yes
Discrete I/O Input	BMXDAI1614H	Ruggedized 16x 100...120 V AC isolated discrete inputs	Yes	Yes
Discrete I/O Input	BMXDAI16142	16x 100...120 V AC isolated discrete inputs	Yes	Yes
Discrete I/O Input	BMXDAI1615	16x 200...240 V AC isolated discrete inputs	Yes	Yes
Discrete I/O Input	BMXDAI1615H	Ruggedized 16x 200...240 V AC isolated discrete inputs	Yes	Yes
Discrete I/O Output	BMXDDO1602	16x transistor source 0.5 A discrete outputs	Yes	Yes
Discrete I/O Output	BMXDDO1602H	Ruggedized 16x transistor source 0.5 A discrete outputs	Yes	Yes
Discrete I/O Output	BMXDDO1612	16x transistor sink 0.5 A discrete outputs	Yes	Yes
Discrete I/O Output	BMXDDO1612H	Ruggedized 16x transistor sink 0.5 A discrete outputs	Yes	Yes
Discrete I/O Output	BMXDDO3202	32x transistor source 0.5 A discrete outputs	Yes	Yes
Discrete I/O Output	BMXDDO3202H	Ruggedized 32x transistor source 0.5 A discrete outputs	Yes	Yes
Discrete I/O Output	BMXDDO3202K	32x transistor source 0.1 A positive discrete outputs	Yes	Yes
Discrete I/O Output	BMXDDO3202KH	Ruggedized 32x transistor source 0.1 A positive discrete outputs	Yes	Yes
Discrete I/O Output	BMXDDO6402K	64x transistor source 0.1 A discrete outputs	Yes	Yes
Discrete I/O Output	BMXDDO6402KC	Ruggedized 64x transistor source 0.1 A discrete outputs	Yes	Yes
Discrete I/O Output	BMXDAO1605	16x 100...240 V AC triac outputs	Yes	Yes
Discrete I/O Output	BMXDAO1605H	Ruggedized 16x 100...240 V AC triac outputs	Yes	Yes
Discrete I/O Output	BMXDAO1615	16x 24...240 V AC triac outputs	Yes	Yes
Discrete I/O Output	BMXDAO1615H	Ruggedized 16x 24...240 V AC triac outputs	Yes	Yes
Discrete I/O Output	BMXDRA0804T	8 NO relay outputs, 100...150 V DC discrete outputs, extended temperature	Yes	Yes
Discrete I/O Output	BMXDRA0805	8x non-isolated relay outputs	Yes	Yes
Discrete I/O Output	BMXDRA0815	8x isolated relay outputs	Yes	Yes
Discrete I/O Output	BMXDRA0815H	Ruggedized 8x isolated relay outputs	Yes	Yes
Discrete I/O Output	BMXDRA1605	16x discrete relay outputs	Yes	Yes
Discrete I/O Output	BMXDRA1605H	Ruggedized 16x discrete relay outputs	Yes	Yes
Discrete I/O Output	BMXDRC0805	8 NO or NC relay outputs, 24...240 V AC, 24...125V DC discrete outputs	Yes	Yes
Discrete I/O Output	BMXDRC0805H	8 NO or NC relay outputs, 24...240 V AC, 24...125 V DC discrete outputs, for severe environments	Yes	Yes
Discrete I/O Mixed	BMXDDM16022	8x 24 V DC discrete inputs, 8x discrete solid state outputs	Yes	Yes
Discrete I/O Mixed	BMXDDM16022H	Ruggedized 8x 24 V DC discrete inputs, 8x discrete solid state outputs	Yes	Yes
Discrete I/O Mixed	BMXDDM16025	8x 24 V DC discrete inputs, 8x discrete relay outputs	Yes	Yes
Discrete I/O Mixed	BMXDDM16025H	Ruggedized 8x 24 V DC discrete inputs, 8x discrete relay outputs	Yes	Yes
Discrete I/O Mixed	BMXDDM3202K	16x 24 V DC discrete inputs, 16x discrete solid state outputs	Yes	Yes
Expert	BMXEHC0800	8 high-speed counter channels	Yes	Yes
Expert	BMXEHC0800H	Ruggedized 8 high-speed counter channels	Yes	Yes

List of Modicon Edge I/O NTS compatible with Modicon M262 dPAC and Simplex Soft dPAC (Linux OS)

Type Reference	Reference	Description
NIM & Bus Extender	NTSNEC1200H	Network interface module, EtherNet/IP, Modbus TCP, 100 Mbps, 2 RJ45, Hardened
NIM & Bus Extender	NTSNEC1200K	Network interface module + Base + Termination, EtherNet/IP, Modbus TCP, 100 Mbps, 2 RJ46
Power Supply	NTSPFD1002HK	Power supply module + Base, 24 V DC, Field, Hardened
Power Supply	NTSPFB1002HK	Power supply module + Base, 24 V DC, Bus and Field, Hardened
Discrete I/O	NTSDDI1602XK	Discrete input module + Base, 16 In, 24 V DC, Sink, 1/2/3 Wires
Discrete I/O	NTSDDI1602XHK	Discrete input module + Base, 16 In, 24 V DC, Sink, 1/2/3 Wires, Hardened
Discrete I/O	NTSDDO0802K	Discrete output module + Base, 8 Out, 24 V DC, 2 A, Source, Protected, External Supply, 1 Wire
Discrete I/O	NTSDDI1602K	Discrete input module + Base, 16 In, 24 V DC, Sink, 1 Wire
Discrete I/O	NTSDDI1642K	Discrete input module + Base, 16 In, 24 V DC, Source, 1 Wire
Discrete I/O	NTSDDI0402K	Discrete input module + Base, 4 In, 24 V DC, Sink, Diagnostics, 1/2/3 Wires
Discrete I/O	NTSDAI0215HK	Discrete input module + Base, 2 Isolated In, 100...240 V AC, Sink, 1/2/3 Wires, Hardened
Discrete I/O	NTSDAI0404HK	Discrete input module + Base, 4 In, 100...240 V AC, Sink, 1/2 Wires, Hardened
Discrete I/O	NTSDAI0804K	Discrete input module + Base, 8 In, 100...240 V AC, Sink, 1 Wire
Discrete I/O	NTSDDI0602K	Discrete input module + Base, 6 In, 24 V DC, Sink, 1/2/3 Wires
Discrete I/O	NTSDDI0802XK	Discrete input module + Base, 8 In, 24 V DC, Sink, 1/2 Wires
Discrete I/O	NTSDAI0403H	Discrete input module, 4 In, 24 V AC, 48 V UC, Sink, 1/2/3 Wires, Hardened
Discrete I/O	NTSDDO0212HK	Discrete output module + Base, 2 Isolated Out, 24 V DC, 2 A, Source, Protected, 1/2/3 Wires, Hardened
Discrete I/O	NTSDDO0602K	Discrete output module + Base, 6 Out, 24 V DC, 500 mA, Source, Protected, 1/2/3 Wires
Discrete I/O	NTSDDO1602XK	Discrete output module + Base, 16 Out, 24 V DC, 500 mA, Source, Protected, 1/2 Wires
Discrete I/O	NTSDAO0205K	Discrete output module + Base, 2 Out, 1 A, 100...240 V AC, 1/2/3 Wires
Discrete I/O	NTSDAO0415	Discrete output module, 4 Isolated Out, 2 A, 100...240 V AC, 1/2/3 Wires
Discrete I/O	NTSDAO0415H	Discrete output module, 4 Isolated Out, 2 A, 100...240V AC, 1/2/3 Wires, Hardened
Discrete I/O	NTSDDO0402	Discrete output module, Edge I/O NTS, 4 Out, 24 V DC, 500 mA, Source, Diagnostics, Protected, 1/2/3 Wires,
Discrete I/O	NTSDDO0402H	Discrete output module, Edge I/O NTS, 4 Out, 24 V DC, 500 mA, Source, Diagnostics, Protected, 1/2/3 Wires, Hardened
Discrete I/O	NTSDDO1602X	Discrete output module, 16 Out, 24 V DC, 500 mA, Source, Protected, 1/2 Wires
Discrete I/O	NTSDRA0615K	Relay output module + Base, 6 Isolated Out, NO, 2 A, 5 V to 125 V DC, 24 V to 240 V AC
Discrete I/O	NTSDRC0215K	Relay output module + Base, 2 Isolated Out, NO/NC, 2 A, 5 V to 125 V DC, 24 V to 240 V AC
Discrete I/O	NTSDRC0415	Relay output module, 4 Isolated Out, NO/NC, 5 A, 5...125 V DC, 24 V...240V AC
Discrete I/O	NTSDRC0415H	Relay output module, 4 Isolated Out, NO/NC, 5 A, 5...125 V DC, 24 V...240V AC, Hardened
Analog I/O	NTSACI0802XK	Analog input module + Base, 8 In, Current, 1/2 wires, Loop Power
Analog I/O	NTSAHI0412XH	Analog input module, 4 Isolated In, Current, HART, 2 wires, Loop Power, Hardened
Analog I/O	NTSAHO0212H	Analog output module, 2 Isolated Out, Current, HART, Hardened
Analog I/O	NTSAMI0210K	Analog input module + Base, 2 Isolated In, Current, Voltage, 2/3/4 Wires, Loop Power
Analog I/O	NTSAMI0400K	Analog input module + Base, 4 In, Current, Voltage, 2 Wires
Analog I/O	NTSAMI0420K	Analog input module + Base, 4 Differential In, Current, Voltage, 2 Wires
Analog I/O	NTSAMI0800K	Analog input module + Base, 8 In, Current, Voltage, 2 Wires
Analog I/O	NTSAMM0600	Analog input/output module, 4 In, 2 Out, Group Isolated, Current, Voltage, 2 Wires
Analog I/O	NTSAMO0210K	Analog output module + Base, 2 Isolated Out, Current, Voltage
Analog I/O	NTSAMO0400HK	Analog output module + Base, 4 Out, Current, Voltage, Hardened
Analog I/O	NTSAMO0400K	Analog output module + Base, 4 Out, Current, Voltage
Analog I/O	NTSART0214	Temperature input module, 2 Isolated In, RTD, ThC, mV, 2/3/4 Wires
Analog I/O	NTSART0214H	Temperature input module, 2 Isolated In, RTD, ThC, mV, 2/3/4 wires, Hardened
Analog I/O	NTSART0404	Temperature input module, 4 Differential In, RTD, ThC, mV, 2/3 Wires
Analog I/O	NTSART0404XH	Temperature input module, 4 Differential In, RTD, ThC, mV, 2/3/4 wires, Hardened
Analog I/O	NTSART0603K	Temperature input module + Base, 6 Differential In, RTD, Thermistor, 2/3 Wires
Counting I/O	NTSEHC0100	High speed counter module, 1 Incremental In, 24 V DC, 250 kHz, 2 In
Counting I/O	NTSEHC0120H	High speed counter module, 1 Incremental In, 24 V DC, 250 kHz, 2 In, 4 Out, Hardened
Counting I/O	NTSEHC0220	High Speed Counter Module, 2 Incremental In, 24V DC, 250 kHz, 4 In, 8 Out

List of TM3 hardware compatible with Modicon M251 dPAC and M262 dPAC

Type	Reference	Description
Discrete I/O	TM3DI16/TM3DI16G	16 discrete inputs
Discrete I/O	TM3DI32K	32 discrete inputs, HE10 connection
Discrete I/O	TM3DI8/TM3DI8A/TM3DI8G	8 discrete inputs
Discrete I/O	TM3DQ8T/TM3DQ8TG	8x 0.5 A transistor source discrete outputs
Discrete I/O	TM3DQ16T/TM3DQ16TG	16x 0.5 A transistor source discrete outputs
Discrete I/O	TM3DQ16R/TM3DQ16RG	16x 2 A discrete relay outputs
Discrete I/O	TM3DQ32TK	32x 0.1 A transistor source discrete outputs, HE10 connection
Discrete I/O	TM3DQ8U/TM3DQ8UG	8x 0.3 A transistor sink discrete outputs
Discrete I/O	TM3DQ16U/TM3DQ16UG	16x 0.3 A transistor sink discrete outputs
Discrete I/O	TM3DQ32UK	32x 0.4 A transistor sink discrete outputs, HE10 connection
Analog I/O	TM3AI2H/TM3AI2HG	2 high-resolution analog inputs, +10 V, 0-10 V, 0-20 mA, 4-20 mA, 16-bit, 1 ms
Analog I/O	TM3AI4/TM3AI4G	4 analog inputs, +10 V, 0-10 V, 0-20 mA, 4-20 mA, 12-bit, 1 ms
Analog I/O	TM3AI8/TM3AI8G	8 analog inputs, +10 V, 0-10 V, 0-20 mA, 4-20 mA, 12-bit, 1 ms
Analog I/O	TM3AQ2/TM3AQ2G	2 analog outputs, +10 V, 0-10 V, 0-20 mA, 4-20 mA, 12-bit, 1 ms
Analog I/O	TM3AQ4/TM3AQ4G	4 analog outputs, +10 V, 0-10 V, 0-20 mA, 4-20 mA, 12-bit, 1 ms
Safety I/O	TM3SAC5R/TM3SAC5RG	CAT3 Safety, 1 function, max. PL d/SIL3, 3 outputs 6 A relays
Safety I/O	TM3SAF5R/TM3SAF5RG	CAT4 Safety, 1 function, max. PL e/SIL3, 3 outputs 6 A relays
Safety I/O	TM3SAFL5R/TM3SAFL5RG	CAT3 Safety, 2 functions, max. PL d/SIL3, 3 outputs 6 A relays
Safety I/O	TM3SAK6R/TM3SAK6RG	CAT4 Safety, 3 functions, max. PL e/SIL3, 3 outputs 6 A relays
Mixed analog I/O	TM3AM6/TM3AM6G	4 analog outputs, 2 analog inputs, +10 V, 0-10 V, 0-20 mA, 4-20 mA, 12-bit, 1 ms
Thermocouple mixed	TM3TM3/TM3TM3G	2 temperature inputs + 1 analog output TC (J, K, R, S, B, T, N, E, C, L), RTD (NI100, NI1000, PT100, PT1000) (+10 V, 0-10 V) (0-20 mA, 4-20 mA) 16-bit, 100 ms
Thermocouple input	TM3TI4/TM3TI4G	4 temperature inputs TC (J, K, R, S, B, T, N, E, C, L) RTD (NI100, NI1000, PT100, PT1000), (+10 V, 0-10 V) (0-20 mA, 4-20 mA) 16-bit, 100 ms
Thermocouple input	TM3TI8T/TM3TI8TG	8 temperature inputs, NTC, PTC, and TC (J, K, R, S, B, T, N, E, C, L), 16-bit 100 ms
Relay I/O	TM3DM8R/TM3DM8RG	8x 2 A relay outputs
Relay I/O	TM3DM24R/TM3DM24RG	24x 2 A relay outputs
Relay I/O	TM3DQ8R/TM3DQ8RG	8x 2 A relays outputs
Other	TM3XREC1	TM3 remote receiver module
Other	TM3XTRA1	TM3 remote transmitter module
Other	TM3XTYS4	TM3 parallel interface for 4 Tesys motor starters
Expert	TM3XHSC202/TM3XHSC202G	High-speed counting, 2 HSC channels, 10 inputs, 8 outputs

List of Altivar hardware compatible with Altivar ATV dPAC			
Type	Reference	Description	Compatible
Drive	ATV340●●●N4	Altivar Machine drives	Yes
Drive	ATV340●●●N4E ≤ D22	Altivar Machine drives	No
Drive	ATV340●●●N4E ≥ D30	Altivar Machine drives	Yes
Drive	ATV630●●●●● ATV630●●●●●F	Altivar Process drives	Yes
Drive	ATV650●●●●● ATV650●●●●●E ATV650●●●●●F	Altivar Process drives	Yes
Drive	ATV930●●●●● ATV930●●●●●C ATV930●●●●●F	Altivar Process drives	Yes
Drive	ATV950●●●●● ATV950●●●●●E ATV950●●●●●F	Altivar Process drives	Yes
Drive	ATV660●●●●● ATV680●●●●●	Altivar Process drive systems	Yes
Drive	ATV960●●●●● ATV980●●●●●	Altivar Process drive systems	Yes
Drive	ATV99●●●●●	Altivar Process drive systems	Yes
Drive	ATV6A0●●●●● ATV6B0●●●●●	Altivar Process Modular drives	Yes
Drive	ATV9A0●●●●● ATV9B0●●●●●	Altivar Process Modular drives	Yes
Drive	ATV6L0●●●●● ATV9L0●●●●●	Altivar Process liquid-cooled drives	Yes
Mixed I/O	VW3A3203	Extended I/O module - 6 digital inputs/ 2 digital outputs/2 analog inputs	Yes
Mixed I/O	VW3A3204	Extended relay module - 3 relay outputs	Yes
Encoder	VW3A3420	Digital encoder interface module for Altivar 340 and Altivar 9●● variable speed drives	Yes
Encoder	VW3A3422	Analog encoder interface module for Altivar 340 and Altivar 9●● variable speed drives	Yes
Encoder	VW3A3423	Resolver interface module for Altivar 340 and Altivar 9●● variable speed drives	Yes
Encoder	VW3A3424	HTL encoder interface module for Altivar 340 and Altivar 9●● variable speed drives	Yes
Safety	VW3A3802	Hardwired safety module for Altivar 340 and Altivar 9●● variable speed drives	Yes
Safety	VW3A3809	CIP safety module for Altivar 340 and Altivar 9●● variable speed drives	Yes
Safety	VW3A3800	Safety module support extension for Altivar 340 and Altivar 9●● variable speed drives	Yes
Other	VW3A1111	Graphic display terminal	Yes
Other	VW3A1112	Door mounting kit	Yes
Other	VW3A1104R10	Remote mounting cordset	Yes
Other	TCSXCNAMUM3P	USB/Mini B USB cable for graphic display terminal	Yes



Schneider Electric offers lifecycle services for your industrial automation systems based on EcoStruxure Automation Expert. Our lifecycle services include field and digital services. We believe, with our advanced processes and tools, we are your trusted expert in field and digital services to help you achieve greater functional safety, efficiency, sustainability, and resilience in your plant operations.

We offer services that are designed to address your needs as you plan, install, operate, and optimize your industrial automation systems based on EcoStruxure Automation Expert. These include:

- Consulting services
- Maintenance and support services
- Training Services
- Migration Services

For more information, visit our [Industrial Automation Services page](#).

Consulting services

Consulting services are about bringing our expertise to help find solutions to some of your key operational challenges. Be it about maximizing the business value from your digital transformation initiatives, identifying improvement opportunities in your industrial automation system lifecycle management plans, or improving your cybersecurity posture and compliance, we can help. Take a look at some of our consulting offerings:

Security consulting

Our cybersecurity consultants will help you assess and review your EcoStruxure Automation Expert systems to detect gaps, identify risks, uncover any security malpractices, assess your staff's security competencies, provide emergency response services, and more. For more information, visit our [Cybersecurity Services page](#).

IA lifecycle consulting

Audits performed by our service team provide insights and recommendations to help improve the maintenance plans of industrial automation assets. This service helps identify potential risks to the reliability and maintainability of these assets and plan mitigation actions. Watch the video to learn more about our [IA Lifecycle Consulting Service](#).

Maintenance and support services

Our maintenance and support offerings help you quickly restore your operations in the event of an unplanned downtime incident. They can also help reduce the risk of occurrence and the associated costs. Take a look at some of our maintenance and support offerings:

Extended warranty

The extended warranty offer gives you the option to extend the warranty of selected Schneider Electric hardware by up to three years.

Note: Please contact your Customer Care Center for offer availability.

Spare parts, exchanges, and repairs

These solutions help you to respond, in the most optimal manner, to requests for spare parts for your EcoStruxure Automation Expert system based on Schneider Electric hardware. Services include:

- Parts management service:
 - Onsite or shared spares inventory, managed by us, to help ensure parts availability, while optimizing costs.
- Repair:
 - Product repairs performed onsite when possible, or at our repair centers.
- Exchange:
 - A refurbished product is provided in exchange for a product returned with a detected fault.

Note: Availability of these services may vary depending on the applicable Schneider Electric hardware. Please contact your Customer Care Center for offer availability.

Maintenance and support services (continued)

Maintenance and support contracts

Our Support and Maintenance Service Offers, are a simplified and modular annual support services agreements, designed to provide you with the right level of flexibility and confidence to meet your support and maintenance needs for your industrial automation systems based on EcoStruxure Automation Expert.

Available as Advantage Service Plan (ASP) for Automation Control or as Customer FIRST (CF) Program for Automation Control, they offer a pre-packaged set of services relevant to operating and maintaining an EcoStruxure Automation Expert Systems. For further customization, a set of optional services are available.

The following table provides a snapshot of the plan:

Included Services	Support Levels	
	ASP	CF
	Essential	Primary
Core Support and Services		
Priority Technical Support Access – NBH ^(a)	SLA ^(b)	SLA ^(b)
mySchneider Portal Access – <i>Premium support</i>	Yes	Yes
Software Version Update ^(c)	Yes	Yes
Optional services^(d)		
24/7 Priority Technical Support – Phone		
Block of Support Hours		

- (a) Normal Business Hours
- (b) Service Level Agreement
- (c) Excludes labor and hardware
- (d) Subject to local availability

With the enhancements to EcoStruxure Automation Expert V25.0 licensing system, we will progressively offer a more digital experience for customers seeking to maintain the currency of their EcoStruxure Automation Expert software. With this experience, customers with our support and maintenance service offers, will be able to update, in a self-service mode, their EcoStruxure Automation Expert software installation, as and when installations are ready. Please contact your Customer Care Center for offer availability.

Application design services

Our Application Design Service leverages our extensive expertise in implementing systems based on EcoStruxure Automation Expert. This service helps you maximize the benefits of software-defined automation while reducing the risks and costs associated with application development.

Included services:

- Remote Application Engineering and implementation assistance by Schneider Electric's experts
- Service delivered by certified engineers with experience in Automation Expert projects and library development.

Typical deliverables:

- Functional design specification
- Custom library and/or CATs
- Tested Automation Expert application

Training services

Our training services are designed for users to take maximum advantage of our industrial automation systems based on EcoStruxure Automation Expert. Our training catalog includes courses on:

- Automation fundamentals
- IEC 61499 concepts
- EcoStruxure Automation Expert Build Time and configuration

For more information, please visit our [Learning Services Home Page](#) or send us an [email](#).

Modernization and migration services

Over the years, we have been involved in migrating many major automation systems to Schneider Electric. Our migration services, based on this expertise and complemented by a set of dedicated tools, helps to minimize the risks and costs involved in such upgrades to an open EcoStruxure Automation Expert-based system. The available set of tools and services are outlined below:

Tools and services

Source platforms		Tools and services		
		Reverse engineering	Application conversion service	Wiring systems for Modicon X80
Schneider Electric	Modicon Premium	Yes	2023	Yes
Rockwell Automation	SLC 500	Yes	Yes	Yes
	PLC-5	Yes	Yes	Yes
	ControlLogix	Yes	2023	—

In addition to the above, we can also offer project-specific solutions. Please contact your local service teams for more information.

ATV6B0C25Q4	40	ATV6L0C20Q4	40	ATV6L0M16Q6	40	ATV950D22N4E	40
ATV6B0C25Q6	40	ATV6L0C20Q6	40	ATV6L0M16T6	40	ATV950D30N4	40
ATV6B0C25R4	40	ATV6L0C20R4	40	ATV6L0M18N6	40	ATV950D30N4E	40
ATV6B0C25T4	40	ATV6L0C20T4	40	ATV6L0M18Q4	40	ATV950D37N4	40
ATV6B0C25T6	40	ATV6L0C20T6	40	ATV6L0M18Q6	40	ATV950D37N4E	40
ATV6B0C31N6	40	ATV6L0C25Q4	40	ATV6L0M18R4	40	ATV950D45N4	40
ATV6B0C31Q4	40	ATV6L0C25R4	40	ATV6L0M18T4	40	ATV950D45N4E	40
ATV6B0C31Q6	40	ATV6L0C25T4	40	ATV6L0M18T6	40	ATV950D55N4	40
ATV6B0C31R4	40	ATV6L0C28N6	40	ATV6L0M22N6	40	ATV950D55N4E	40
ATV6B0C31T4	40	ATV6L0C28Q6	40	ATV6L0M22Q6	40	ATV950D75N4	40
ATV6B0C31T6	40	ATV6L0C28T6	40	ATV6L0M22T6	40	ATV950D75N4E	40
ATV6B0C35Q4	40	ATV6L0C31N6	40	ATV6L0M26N6	40	ATV950D90N4	40
ATV6B0C35R4	40	ATV6L0C31Q4	40	ATV6L0M26Q6	40	ATV950D90N4E	40
ATV6B0C35T4	40	ATV6L0C31Q6	40	ATV6L0M26T6	40	ATV950U07N4	40
ATV6B0C40N6	40	ATV6L0C31R4	40	ATV930C11N4	40	ATV950U07N4E	40
ATV6B0C40Q4	40	ATV6L0C31T4	40	ATV930C11N4C	40	ATV950U15N4	40
ATV6B0C40Q6	40	ATV6L0C31T6	40	ATV930C11N4F	40	ATV950U15N4E	40
ATV6B0C40R4	40	ATV6L0C40N6	40	ATV930C13N4	40	ATV950U22N4	40
ATV6B0C40T4	40	ATV6L0C40Q4	40	ATV930C13N4C	40	ATV950U22N4E	40
ATV6B0C40T6	40	ATV6L0C40Q6	40	ATV930C13N4F	40	ATV950U30N4	40
ATV6B0C45Q4	40	ATV6L0C40R4	40	ATV930C16N4	40	ATV950U30N4E	40
ATV6B0C45R4	40	ATV6L0C40T4	40	ATV930C16N4C	40	ATV950U40N4	40
ATV6B0C45T4	40	ATV6L0C40T6	40	ATV930C16N4F	40	ATV950U40N4E	40
ATV6B0C50N6	40	ATV6L0C45N6	40	ATV930C20N4F	40	ATV950U55N4	40
ATV6B0C50Q4	40	ATV6L0C45Q6	40	ATV930C22N4	40	ATV950U55N4E	40
ATV6B0C50Q6	40	ATV6L0C45T6	40	ATV930C22N4C	40	ATV950U75N4	40
ATV6B0C50R4	40	ATV6L0C50Q4	40	ATV930C25N4C	40	ATV950U75N4E	40
ATV6B0C50T4	40	ATV6L0C50R4	40	ATV930C25N4F	40	ATV960C11Q4X1	40
ATV6B0C50T6	40	ATV6L0C50T4	40	ATV930C31N4C	40	ATV960C11T4X1	40
ATV6B0C56Q4	40	ATV6L0C56N6	40	ATV930C31N4F	40	ATV960C13Q4X1	40
ATV6B0C56R4	40	ATV6L0C56Q6	40	ATV930D11N4	40	ATV960C13T4X1	40
ATV6B0C56T4	40	ATV6L0C56T6	40	ATV930D15N4	40	ATV960C16Q4X1	40
ATV6B0C63N6	40	ATV6L0C63Q4	40	ATV930D18N4	40	ATV960C16T4X1	40
ATV6B0C63Q4	40	ATV6L0C63R4	40	ATV930D22N4	40	ATV960C20Q4X1	40
ATV6B0C63Q6	40	ATV6L0C63T4	40	ATV930D30N4	40	ATV960C20T4X1	40
ATV6B0C63R4	40	ATV6L0C71N6	40	ATV930D37N4	40	ATV960C25Q4X1	40
ATV6B0C63T4	40	ATV6L0C71Q6	40	ATV930D45N4	40	ATV960C25T4X1	40
ATV6B0C63T6	40	ATV6L0C71T6	40	ATV930D55N4	40	ATV960C31Q4X1	40
ATV6B0C71Q4	40	ATV6L0C80Q4	40	ATV930D55N4C	40	ATV960C31T4X1	40
ATV6B0C71R4	40	ATV6L0C80R4	40	ATV930D75N4	40	ATV960C35Q4X1	40
ATV6B0C71T4	40	ATV6L0C80T4	40	ATV930D75N4C	40	ATV960C35T4X1	40
ATV6B0C80N6	40	ATV6L0C90N6	40	ATV930D90N4	40	ATV960C40Q4X1	40
ATV6B0C80Q4	40	ATV6L0C90Q4	40	ATV930D90N4C	40	ATV960C40T4X1	40
ATV6B0C80Q6	40	ATV6L0C90Q6	40	ATV930U07N4	40	ATV960C45Q4X1	40
ATV6B0C80R4	40	ATV6L0C90R4	40	ATV930U15N4	40	ATV960C45T4X1	40
ATV6B0C80T4	40	ATV6L0C90T4	40	ATV930U22N4	40	ATV960C50Q4X1	40
ATV6B0C80T6	40	ATV6L0C90T6	40	ATV930U30N4	40	ATV960C50T4X1	40
ATV6B0M10N6	40	ATV6L0M10Q4	40	ATV930U40N4	40	ATV960C56Q4X1	40
ATV6B0M10Q4	40	ATV6L0M10R4	40	ATV930U55N4	40	ATV960C56T4X1	40
ATV6B0M10Q6	40	ATV6L0M10T4	40	ATV930U75N4	40	ATV960C63Q4X1	40
ATV6B0M10R4	40	ATV6L0M12N6	40	ATV950C11N4F	40	ATV960C63T4X1	40
ATV6B0M10T4	40	ATV6L0M12Q4	40	ATV950C13N4F	40	ATV960C71Q4X1	40
ATV6B0M10T6	40	ATV6L0M12Q6	40	ATV950C16N4F	40	ATV960C71T4X1	40
ATV6B0M12N6	40	ATV6L0M12R4	40	ATV950C20N4F	40	ATV960C80Q4X1	40
ATV6B0M12Q6	40	ATV6L0M12T4	40	ATV950C25N4F	40	ATV960C80T4X1	40
ATV6B0M12T6	40	ATV6L0M12T6	40	ATV950C31N4F	40	ATV980C11Q4X1	40
ATV6L0C13Q4	40	ATV6L0M14N6	40	ATV950D11N4	40	ATV980C11T4X1	40
ATV6L0C13R4	40	ATV6L0M14Q6	40	ATV950D11N4E	40	ATV980C13Q4X1	40
ATV6L0C13T4	40	ATV6L0M14T6	40	ATV950D15N4	40	ATV980C13T4X1	40
ATV6L0C16Q4	40	ATV6L0M15Q4	40	ATV950D15N4E	40	ATV980C16Q4X1	40
ATV6L0C16R4	40	ATV6L0M15R4	40	ATV950D18N4	40	ATV980C16T4X1	40
ATV6L0C16T4	40	ATV6L0M15T4	40	ATV950D18N4E	40	ATV980C20Q4X1	40
ATV6L0C20N6	40	ATV6L0M16N6	40	ATV950D22N4	40	ATV980C20T4X1	40

ATV980C25Q4X1	40	ATV9A0C40N6	40	ATV9B0C20R4	40	ATV9L0C16Q4	40
ATV980C25T4X1	40	ATV9A0C40Q4	40	ATV9B0C20T4	40	ATV9L0C16R4	40
ATV980C31Q4X1	40	ATV9A0C40Q6	40	ATV9B0C20T6	40	ATV9L0C16T4	40
ATV980C31T4X1	40	ATV9A0C40R4	40	ATV9B0C25N6	40	ATV9L0C20N6	40
ATV980C35Q4X1	40	ATV9A0C40T4	40	ATV9B0C25Q4	40	ATV9L0C20Q4	40
ATV980C35T4X1	40	ATV9A0C40T6	40	ATV9B0C25Q6	40	ATV9L0C20Q6	40
ATV980C40Q4X1	40	ATV9A0C45Q4	40	ATV9B0C25R4	40	ATV9L0C20R4	40
ATV980C40T4X1	40	ATV9A0C45R4	40	ATV9B0C25T4	40	ATV9L0C20T4	40
ATV980C45Q4X1	40	ATV9A0C45T4	40	ATV9B0C25T6	40	ATV9L0C20T6	40
ATV980C45T4X1	40	ATV9A0C50N6	40	ATV9B0C31N6	40	ATV9L0C25Q4	40
ATV980C50Q4X1	40	ATV9A0C50Q4	40	ATV9B0C31Q4	40	ATV9L0C25R4	40
ATV980C50T4X1	40	ATV9A0C50Q6	40	ATV9B0C31Q6	40	ATV9L0C25T4	40
ATV980C56Q4X1	40	ATV9A0C50R4	40	ATV9B0C31R4	40	ATV9L0C28N6	40
ATV980C56T4X1	40	ATV9A0C50T4	40	ATV9B0C31T4	40	ATV9L0C28Q6	40
ATV980C63Q4X1	40	ATV9A0C50T6	40	ATV9B0C31T6	40	ATV9L0C28T6	40
ATV980C63T4X1	40	ATV9A0C56Q4	40	ATV9B0C35Q4	40	ATV9L0C31N6	40
ATV980C71Q4X1	40	ATV9A0C56R4	40	ATV9B0C35R4	40	ATV9L0C31Q4	40
ATV980C71T4X1	40	ATV9A0C56T4	40	ATV9B0C35T4	40	ATV9L0C31Q6	40
ATV980C80Q4X1	40	ATV9A0C63N6	40	ATV9B0C40N6	40	ATV9L0C31R4	40
ATV980C80T4X1	40	ATV9A0C63Q4	40	ATV9B0C40Q4	40	ATV9L0C31T4	40
ATV9A0C11N6	40	ATV9A0C63Q6	40	ATV9B0C40Q6	40	ATV9L0C31T6	40
ATV9A0C11Q4	40	ATV9A0C63R4	40	ATV9B0C40R4	40	ATV9L0C40N6	40
ATV9A0C11Q6	40	ATV9A0C63T4	40	ATV9B0C40T4	40	ATV9L0C40Q4	40
ATV9A0C11R4	40	ATV9A0C63T6	40	ATV9B0C40T6	40	ATV9L0C40Q6	40
ATV9A0C11S6	40	ATV9A0C71Q4	40	ATV9B0C45Q4	40	ATV9L0C40R4	40
ATV9A0C11T4	40	ATV9A0C71R4	40	ATV9B0C45R4	40	ATV9L0C40T4	40
ATV9A0C11T6	40	ATV9A0C71T4	40	ATV9B0C45T4	40	ATV9L0C40T6	40
ATV9A0C13N6	40	ATV9A0C80N6	40	ATV9B0C50N6	40	ATV9L0C45N6	40
ATV9A0C13Q4	40	ATV9A0C80Q4	40	ATV9B0C50Q4	40	ATV9L0C45Q6	40
ATV9A0C13Q6	40	ATV9A0C80Q6	40	ATV9B0C50Q6	40	ATV9L0C45T6	40
ATV9A0C13R4	40	ATV9A0C80R4	40	ATV9B0C50R4	40	ATV9L0C50Q4	40
ATV9A0C13S6	40	ATV9A0C80T4	40	ATV9B0C50T4	40	ATV9L0C50R4	40
ATV9A0C13T4	40	ATV9A0C80T6	40	ATV9B0C50T6	40	ATV9L0C50T4	40
ATV9A0C13T6	40	ATV9A0M10N6	40	ATV9B0C56Q4	40	ATV9L0C56N6	40
ATV9A0C16N6	40	ATV9A0M10Q4	40	ATV9B0C56R4	40	ATV9L0C56Q6	40
ATV9A0C16Q4	40	ATV9A0M10Q6	40	ATV9B0C56T4	40	ATV9L0C56T6	40
ATV9A0C16Q6	40	ATV9A0M10R4	40	ATV9B0C63N6	40	ATV9L0C63Q4	40
ATV9A0C16R4	40	ATV9A0M10T4	40	ATV9B0C63Q4	40	ATV9L0C63R4	40
ATV9A0C16S6	40	ATV9A0M10T6	40	ATV9B0C63Q6	40	ATV9L0C63T4	40
ATV9A0C16T4	40	ATV9A0M12N6	40	ATV9B0C63R4	40	ATV9L0C71N6	40
ATV9A0C16T6	40	ATV9A0M12Q6	40	ATV9B0C63T4	40	ATV9L0C71Q6	40
ATV9A0C20N6	40	ATV9A0M12T6	40	ATV9B0C63T6	40	ATV9L0C71T6	40
ATV9A0C20Q4	40	ATV9B0C11N6	40	ATV9B0C71Q4	40	ATV9L0C80Q4	40
ATV9A0C20Q6	40	ATV9B0C11Q4	40	ATV9B0C71R4	40	ATV9L0C80R4	40
ATV9A0C20R4	40	ATV9B0C11Q6	40	ATV9B0C71T4	40	ATV9L0C80T4	40
ATV9A0C20S6	40	ATV9B0C11R4	40	ATV9B0C80N6	40	ATV9L0C90N6	40
ATV9A0C20T4	40	ATV9B0C11T4	40	ATV9B0C80Q4	40	ATV9L0C90Q4	40
ATV9A0C20T6	40	ATV9B0C11T6	40	ATV9B0C80Q6	40	ATV9L0C90Q6	40
ATV9A0C25N6	40	ATV9B0C13N6	40	ATV9B0C80R4	40	ATV9L0C90R4	40
ATV9A0C25Q4	40	ATV9B0C13Q4	40	ATV9B0C80T4	40	ATV9L0C90T4	40
ATV9A0C25Q6	40	ATV9B0C13Q6	40	ATV9B0C80T6	40	ATV9L0C90T6	40
ATV9A0C25R4	40	ATV9B0C13R4	40	ATV9B0M10N6	40	ATV9L0M10Q4	40
ATV9A0C25T4	40	ATV9B0C13T4	40	ATV9B0M10Q4	40	ATV9L0M10R4	40
ATV9A0C25T6	40	ATV9B0C13T6	40	ATV9B0M10Q6	40	ATV9L0M10T4	40
ATV9A0C31N6	40	ATV9B0C16N6	40	ATV9B0M10R4	40	ATV9L0M12N6	40
ATV9A0C31Q4	40	ATV9B0C16Q4	40	ATV9B0M10T4	40	ATV9L0M12Q4	40
ATV9A0C31Q6	40	ATV9B0C16Q6	40	ATV9B0M10T6	40	ATV9L0M12Q6	40
ATV9A0C31R4	40	ATV9B0C16R4	40	ATV9B0M12N6	40	ATV9L0M12R4	40
ATV9A0C31T4	40	ATV9B0C16T4	40	ATV9B0M12Q6	40	ATV9L0M12T4	40
ATV9A0C31T6	40	ATV9B0C16T6	40	ATV9B0M12T6	40	ATV9L0M12T6	40
ATV9A0C35Q4	40	ATV9B0C20N6	40	ATV9L0C13Q4	40	ATV9L0M14N6	40
ATV9A0C35R4	40	ATV9B0C20Q4	40	ATV9L0C13R4	40	ATV9L0M14Q6	40
ATV9A0C35T4	40	ATV9B0C20Q6	40	ATV9L0C13T4	40	ATV9L0M14T6	40

ATV9L0M15Q4	40	BMXCPS4022	36	BMXBP0800	36	NTSAMI0400K	38
ATV9L0M15R4	40	BMXCPS4022H	36	BMXBP0800H	36	NTSAMI0420K	38
ATV9L0M15T4	40	BMXDAI0805	37	BMXBP1200	36	NTSAMI0800K	38
ATV9L0M16N6	40	BMXDAI0814	37	BMXBP1200H	36	NTSAMM0600	38
ATV9L0M16Q6	40	BMXDAI1602	37	E		NTSAMO0210K	38
ATV9L0M16T6	40	BMXDAI1602H	37	EALBAHC	28	NTSAMO0400HK	38
ATV9L0M18N6	40	BMXDAI1604	37	EALBAPC	28	NTSAMO0400K	38
ATV9L0M18Q4	40	BMXDAI1604H	37	EALBATC	28	NTSART0214	38
ATV9L0M18Q6	40	BMXDAI1614	37	EALBFC	28	NTSART0214H	38
ATV9L0M18R4	40	BMXDAI16142	37	EALBFC3	28	NTSART0404	38
ATV9L0M18T4	40	BMXDAI1614H	37	EALBFCH	28	NTSART0404XH	38
ATV9L0M18T6	40	BMXDAI1615	37	EALBFCT	28	NTSART0603K	38
ATV9L0M22N6	40	BMXDAI1615H	37	EALBTC	28	NTSDAI0215HK	38
ATV9L0M22Q6	40	BMXDAO1605	37	EALBTC3	28	NTSDAI0403H	38
ATV9L0M22T6	40	BMXDAO1605H	37	EALBTCH	28	NTSDAI0404HK	38
ATV9L0M26N6	40	BMXDAO1615	37	EALBTCT	28	NTSDAI0804K	38
ATV9L0M26Q6	40	BMXDAO1615H	37	EALBTS1	32	NTSDAO0205K	38
ATV9L0M26T6	40	BMXDDI1602	37	EALBTS13	32	NTSDAO0415	38
B		BMXDDI1602H	37	EALBTS1H	32	NTSDAO0415H	38
BMEAHI0812	36	BMXDDI1603	37	EALBTS1T	32	NTSDDI0402K	38
BMEAHI0812H	36	BMXDDI1603H	37	EALBTS2	32	NTSDDI0602K	38
BMEAHO0412	36	BMXDDI3202K	37	EALBTS23	32	NTSDDI0802XK	38
BMEAHO0412C	36	BMXDDI3202KH	37	EALBTS2H	32	NTSDDI1602K	38
BMEXBP0400	36	BMXDDI6402K	37	EALBTS2T	32	NTSDDI1602XHK	38
BMEXBP0400H	36	BMXDDI6402KH	37	EALBUC	28	NTSDDI1602XK	38
BMEXBP0602	36	BMXDDM16022	37	EALCEP	31	NTSDDI1642K	38
BMEXBP0602H	36	BMXDDM16022H	37	EALCEY	33	NTSDDO0212HK	38
BMEXBP0800	36	BMXDDM16025	37	EALCGP	31	NTSDDO0402	38
BMEXBP0800H	36	BMXDDM16025H	37	EALCGY	33	NTSDDO0402H	38
BMEXBP1002	36	BMXDDM3202K	37	EALCPP	31	NTSDDO0602K	38
BMEXBP1002H	36	BMXDDO1602	37	EALCPY	33	NTSDDO0802K	38
BMEXBP1200	36	BMXDDO1602H	37	EALCUP	31	NTSDDO1602X	38
BMEXBP1200H	36	BMXDDO1612	37	EALCUY	33	NTSDDO1602XK	38
BMXAMI0410	36	BMXDDO1612H	37	EALH1P	31	NTSDRA0615K	38
BMXAMI0410H	36	BMXDDO3202	37	EALH2P	31	NTSDRC0215K	38
BMXAMI0800	36	BMXDDO3202H	37	EALPTCP	30	NTSDRC0415	38
BMXAMI0800H	36	BMXDDO3202K	37		34	NTSDRC0415H	38
BMXAMI0810	36	BMXDDO3202KH	37	EALPTCY	33	NTSEHC0100	38
BMXAMI0810H	36	BMXDDO6402K	37	EALPTHACP	30	NTSEHC0120H	38
BMXAMI0810H	36	BMXDDO6402KC	37		35	NTSEHC0220	38
BMXAMM0600	37	BMXDRA0804T	37	EALPTHACY	33	NTSEHC0220	38
BMXAMM0600H	37	BMXDRA0805	37	EALPTHAMP	30	NTSNEC1200H	38
BMXAMO0210	36	BMXDRA0815	37	EALPTHAMY	33	NTSNEC1200K	38
BMXAMO0210H	36	BMXDRA0815H	37	EALPTHAVMP	30	NTSPFB1002HK	38
BMXAMO0410	36	BMXDRA1605	37	EALPTHAVMY	33	NTSPFD1002HK	38
BMXAMO0410H	36	BMXDRA1605H	37	EALPTMP	30	T	
BMXAMO0802	36	BMXDRA1605H	37	EALPTMY	33	TCSXCNAMUM3P	40
BMXAMO0802H	36	BMXDRC0805	37	EALPTVMP	30	TM3AI2H	39
BMXART0414	36	BMXDRC0805H	37	EALPTVMY	33	TM3AI2HG	39
BMXART0414H	36	BMXEHC0800	37	EALPTXP	30	TM3AI4	39
BMXART0814	36	BMXEHC0800H	37	EALRCP	30	TM3AI4G	39
BMXART0814H	36	BMXRMS004GPF	36		35	TM3AI8	39
BMXCPS2000	36	BMXXBC008K	36	EALRCY	33	TM3AI8G	39
BMXCPS2000H	36	BMXXBC015K	36	EALRIP	30	TM3AM6	39
BMXCPS2010	36	BMXXBC030K	36	EALRVCP	30	TM3AM6G	39
BMXCPS3020	36	BMXXBC050K	36	EALRVCY	33	TM3AQ2	39
BMXCPS3020H	36	BMXXBC120K	36	EALRXP	30	TM3AG2G	39
BMXCPS3500	36	BMXXBE1000	36		34	TM3AQ4	39
BMXCPS3500H	36	BMXXBE1000H	36	EALRXY	33	TM3AQ4G	39
BMXCPS3522	36	BMXXBE2005	36	EALUAOC	28	TM3DI16	39
BMXCPS3522H	36	BMXXBP0400	36	N		TM3DI16G	39
BMXCPS3540T	36	BMXXBP0400H	36	NTSACI0802XK	38	TM3DI32K	39
BMXCPS4002	36	BMXXBP0600	36	NTSAHI0412XH	38	TM3DI8	39
BMXCPS4002H	36	BMXXBP0600H	36	NTSAHO0212H	38	TM3DI8G	39
				NTSAMI0210K	38		

TM3DI8A	39
TM3DM24R	39
TM3DM24RG	39
TM3DM8R	39
TM3DM8RG	39
TM3DQ16R	39
TM3DQ16RG	39
TM3DQ16T	39
TM3DQ16TG	39
TM3DQ16U	39
TM3DQ16UG	39
TM3DQ32TK	39
TM3DQ32UK	39
TM3DQ8R	39
TM3DQ8RG	39
TM3DQ8T	39
TM3DQ8TG	39
TM3DQ8U	39
TM3DQ8UG	39
TM3SAC5R	39
TM3SAC5RG	39
TM3SAF5R	39
TM3SAF5RG	39
TM3SAFL5R	39
TM3SAFL5RG	39
TM3SAK6R	39
TM3SAK6RG	39
TM3TI4	39
TM3TI4G	39
TM3TI8T	39
TM3TI8TG	39
TM3TM3	39
TM3TM3G	39
TM3XHSC202	39
TM3XHSC202G	39
TM3XREC1	39
TM3XTRA1	39
TM3XTYS4	39
V	
VW3A1104R10	40
VW3A1111	40
VW3A1112	40
VW3A3203	40
VW3A3204	40
VW3A3420	40
VW3A3422	40
VW3A3423	40
VW3A3424	40
VW3A3800	40
VW3A3802	40
VW3A3809	40

mySchneider, your personalized digital experience

Access an all-in-one customized online experience and benefit from tailored business services, resources, and tools to efficiently support your business operations.

- **Efficiency:** In just a few clicks, find all the information and support you need to get the job done.
- **Simplicity:** Use a single login to access all business services, in one place, available 24/7. You no longer need to log in to multiple platforms.
- **Personalization:** Benefit from content, tools, and business services tailored to your activity, and customize your landing page based on your preferences.

Watch the How-to Videos



Order management

- > [Select Products and Add to Cart](#)
- > [Check for Products' Price and Availability](#)
- > [Order Products with Generic Commercial References](#)




Product information

- > [Find a Product Data Sheet and Related Documents](#)
- > [Select Products and Add to Cart](#)
- > [Stay Up to Date on the Status of My Products](#)



Support

- > [Get Quicker Answers Thanks to Online Support](#)



Training

- > [Access Trainings Dedicated to My Activity](#)

[Create your account](#)

Life Is 

Schneider
Electric

Legal information

The information provided in this Catalog contains description of Schneider Electric products, solutions and services ("Offer") with technical specifications and technical characteristics of the performance of the corresponding Offer.

The content of this document is subject to revision at any time without notice due to continued progress in methodology, design and manufacturing.


To the extent permitted by applicable law, no responsibility or liability is assumed by Schneider Electric and its subsidiaries for any type of damages arising out of or in connection with (i) informational content of this Catalog not conforming with or exceeding the technical specifications, or (ii) any error contained in this Catalog, or (iii) any use, decision, act or omission made or taken on basis of or in reliance on any information contained or referred to in this Catalog.

SCHNEIDER ELECTRIC MAKES NO WARRANTY OR REPRESENTATION OF ANY KIND, WHETHER EXPRESS OR IMPLIED, AS TO WHETHER THIS CATALOG OR ANY INFORMATION CONTAINED THEREIN SUCH AS PRODUCTS AND SERVICES WILL MEET REQUIREMENTS, EXPECTATIONS OR PURPOSE OF ANY PERSON MAKING USE THEREOF.

Schneider Electric brand and any trademarks of Schneider Electric and its subsidiaries referred to in this Catalog are property of Schneider Electric or its subsidiaries. All other brands are trademarks of their respective owners.

This Catalog and its content are protected under applicable copyright laws and provided for informative use only. No part of this Catalog may be reproduced or transmitted in any form or by any means (electronic, mechanical, photocopying, recording, or otherwise), for any purpose, without the prior written permission of Schneider Electric.

Copyright, intellectual, and all other proprietary rights in the content of this Catalog (including but not limited to software, audio, video, text, and photographs) rests with Schneider Electric or its licensors. All rights in such content not expressly granted herein are reserved. No rights of any kind are licensed or assigned or shall otherwise pass to persons accessing this information.



Learn more about our products at
www.se.com

Design: Schneider Electric
Photos: Schneider Electric

Schneider Electric Industries SAS

Head Office
35, rue Joseph Monier - CS 30323
F-92500 Rueil-Malmaison Cedex
France

DIA3ED2201101EN
May 2026 - V11.0