

# Lexium™ MC12 multi carrier

The multi carrier transport system



# Lexium

## Discover [Lexium](#)

Advanced motion control and robotics

**Lexium** servo drives, motors, and robotics series are designed for a broad range of motion-centric machines. From single-axis to high-performance multi-axis machines, the **Lexium** range enables high-speed movements and precise positioning in packaging, material handling, material working, electronics, and food and beverage applications.

## Explore our offer

- [Lexium](#) Servo Drives and Motors
- [Lexium](#) Integrated Servo Drives
- [Lexium](#) Robotics
- [Lexium](#) Stepper Drives




# Quick access to product information

## Get technical information about your product

Each commercial reference presented in a catalog contains a hyperlink. Click on it to obtain the technical information of the product:


- Characteristics, Dimensions and drawings, Mounting and clearance, Connections and schemas, Performance curves
- Instruction sheets, User guides, Product certifications, End of life manuals, etc



## View the Automation Catalog libraries


On [Digi-Cat Online](#) you can access the Industrial Automation and Control catalogs, in both English and French

- Up-to-date catalogs
- Optimized search by commercial references
- Integrated product selectors and configurators




## Direct access to Configurators Home pages

- Configure your [motor control and protection solution](#)
- Configure your [control system with a PLC controller and I/O modules](#)
- Configure your [motion control and robotics system](#)



## Select your training

- Find the right [Training](#) for your needs on our Global website
- Locate the [Training center](#) with the selector tool



# Lexium MC12 multi carrier

## The multi carrier transport system



# General content

## Lexium™ MC12 multi carrier The multi carrier transport system

■ Introduction to EcoStruxure Machine .....	page 2
■ Specifications of Lexium MC12 multi carrier .....	page 4
■ Examples of applications	
- Filling,	
- Grouping,	
- Stacking,	
- Pick and Place,	
- Free movements .....	page 5
■ System components to create a track .....	page 6
■ Setting up	
- Designing a track	
- Connecting a track .....	page 7
■ Complementary of offers .....	page 8
■ Communication .....	page 9
■ Embedded safety function SFO .....	page 9
■ Main characteristics .....	page 9
■ System component references	
- Longstator motor segment,	
- Braking resistor,	
- Connection module,	
- Communication interconnects,	
- Power interconnects,	
- Carrier,	
- Accessories .....	page 10
- Guide rail,	
- Cables,	
- Power supply .....	page 11
- Related offers .....	page 11
■ Configuration .....	page 12
■ Type code	
- Segment, Carrier .....	page 13
- Rail, Bridge (Communication interconnect) .....	page 14
- Accessories .....	page 15
■ Product references index .....	page 16

To be competitive in today's digital era, machine builders must be innovative. Smart machines, those that are better connected, more flexible, more efficient, and safe, are enabling machine builders to innovate in ways never before possible.

EcoStruxure, Schneider Electric's open, IoT-enabled architecture and platform, offers powerful solutions for the digital era. As part of this, EcoStruxure Machine brings powerful opportunities for machine builders and OEMs, empowering them to offer smart machines and compete in the new, digital era.

EcoStruxure Machine brings together key technologies for product connectivity and edge control on premises, and cloud technologies to provide analytics and digital services.

EcoStruxure Machine helps you bring more innovation and added value to your customers throughout the entire machine life cycle.

**Innovation at Every Level for Machines is full systems across three layers:**

- Connected products  
Our connected products for measuring, actuating, device level monitoring, and control adhere to open standards to provide unmatched integration opportunities and flexibility
- Edge Control  
We are IIoT-ready with a proven set of tested and validated reference architectures that enable the design of end-to-end open, connected, and interoperable systems based on industry standards. Ethernet and OPC UA facilitates IT/OT convergence meaning machine builders reap benefits from web interfaces and cloud.
- Apps, Analytics & Services  
Seamless integration of machines to the IT layer allows the collection and aggregation of data ready for analysis – for machine builders and end users alike this means increased uptime and the ability to find information faster for more efficient operations and maintenance.

**These levels are completely integrated from shop floor to top floor. And we have cloud offers and end-to-end cybersecurity wrapped around.**


EcoStruxure Machine makes it easier for OEMs/machine builders to offer their customers smarter machines. The advent of smart machines is driven by the changing needs of end users:

- Evolving workforce
- Reducing costs
- Dynamic markets
- Shorter life cycles
- Prioritizing functional safety and cybersecurity

EcoStruxure Machine provides one solution for the whole machine life cycle:

- With Smart Design & Engineering the time to market is reduced by up to 30% using our automated engineering and the simulation capabilities
- During Commissioning & Operation of the machine, resources such as energy, material and loss can be improved, and with seamless integration to the IT world efficiency can be improved by up to 40%
- Smart Maintenance & Services reduces the time for corrective actions up to 50%

# EcoStruxure™ Machine



# Lexium MC12 multi carrier

## The multi carrier transport system

### Specifications

#### Specifications of Lexium MC12 multi carrier



Lexium MC12 multi carrier transport system

Lexium MC12 multi carrier is an innovative transport system to be used in machines. It uses latest linear motion technology to move products individually through the machine. These individual movements allow for new machine designs making machines faster, more flexible and space efficient.

#### New level of performance & flexibility for more sustainability

- Less format specific parts needed, a big step ahead in direction of toolless change over at a push of a button
- Leap in flexibility, larger variety of products can be run on the same machine

#### Simplified operation and maintenance

- Integral part of PacDrive 3 system diagnostic mechanisms
- Automatic configuration after replacement of segments or carriers
- Enhanced diagnostics and commissioning with EcoStruxure Machine Expert software
- Mobile app for diagnostics (Industrial Device)
- Integral part of Schneider Electric's solution for remote monitoring/health monitoring and predictive maintenance (Machine Advisor)
- Modular mechanical design for quick replacements
- Automated lubrication: Two components of the multicarrier offering are designed to support automated lubrication of the transport system: their use reduces manual maintenance and improves system longevity

#### Differentiation & saving time in machine design for less time to market

- Game changer for machine design  
Next generation of multi carrier system, providing new leeway for even better machine designs
- The evolution – mechanical camming – electronic camming – no camming – is providing new unknown potential for more flexible machines with less footprint!
- Efficient engineering and life cycle management with a single and well-known engineering tool
- Shorter time to market though easy and time saving mechanical/electrical/program implementation
- Virtual commissioning to verify machine behavior in an early implementation phase
- Transportation, grouping and positioning of products is completely decoupled from the machine cycle

#### Increasing the Overall Equipment Effectiveness (OEE) of machine

- Flexibility: more formats per machine and simplified change over procedures with less format specific part
- Optimized maintenance by high-service-parts
- Higher machine uptime
- Better use of production space through machines with less footprint
- Smart Carrier ensures unique carrier identification at startup — no identification run required, even after complete power loss.

#### Main fields of application


- Packaging
  - Cartoning
  - Stacking (grouping)
  - Product flow adjustments (gap correction, position correction)
  - Filling, folding (tubes, bottles, pouches, ...)
  - Labelling
- Food processing
  - Applying
  - Cutting
- Assembly
  - Mechatronical products
  - Pharmaceutical products
- Material handling



Packaging application



Food processing application




Assembly application

#### Examples of applications

The Lexium MC12 multi carrier system is a transport system for moving, positioning or grouping objects in machines for discrete processes.

#### Filling



Filling

- Multi carrier replaces transportation chain
- Individual bottle movements
- Bottles move twice as fast through capping station
- Smaller gaps between products outside processing stations reduces footprint
- Clamping for different bottle diameters increases flexibility
- Less stations (cost savings)
- More compact
- Faster and simplified format change


#### Grouping



Grouping

- Products can be loaded on the fly
- Pocket size can be adjusted to adapt to formats or to simplify loading
- Products move individually, high performance, increasing group size does not impact performance
- Buffer between loading and unloading station can compensate jitter in product flow
- Flexible grouping patterns


#### Stacking



Stacking and Grouping

- Pocket "grows" with products put into pocket
- Different products from different infeed stations can be stacked into same pocket
- Grouping of stacked products
- Products can be pushed together

#### Pick and Place



Pick and Place with variable speed of carrier

- More picks per min, products can be picked more often in robot sweet spot by slower speeds in working envelope and higher speeds during transfer (to next robot)
- Better accuracy, no belt slipping

#### Free movements



Free movements

- A carrier can be moved freely throughout the track. It can brake, accelerate, position or exert a constant force when stationary or also in motion. Like any linear motor, the carrier can synchronize on other movements. When arranged in a circle, the carriers move endlessly following the flow of product.
- Several carriers can all be moved independently of each other. They can be positioned at absolute positions over the entire distance traveled. In addition, they can be moved relative to each other and avoid collisions with their neighbour.

# Lexium MC12 multi carrier


## The multi carrier transport system

### System components to create a track

#### System components

Lexium MC12 multi carrier is a modular system for machine applications and consists of long stator motors, on which multiple carrier units can be moved independently from each other.

- > The system components are designed for compact, modular, flexible and efficient machine designs. Lexium MC12 multi carrier can reduce engineering efforts, mechanical variants, and changeover time.
- > The components of Lexium MC12 multi carrier are mounted at the machine frame.



#### Guide rails 1

- > Same curve and straight guide rails are installed at top and bottom of the straight and curved long stator motor segments, used to handle the carriers.
- > The Guide rails are available in different length and can be combined freely.

#### Carriers/Smart Carriers 2

- > The carrier contains magnetic plates which, with the coil of the long stator motor segment can generate propulsive force. The encoder integrated in long stator motor segment measures the position of each carrier.
- > The smart carrier enables each carrier of a track to be uniquely identified immediately at startup, without requiring a mechanical or manual identification run. The identification can be triggered during Sercos phase-up, requires no movement, and remains available even after a complete power loss.
- > Up to 200 removable carriers can move on a same track. The motion of each carrier is independent from each other allowing different spacings, different cycle times, and different speeds (up to 4 m/s). The minimal gap between two carriers is null.

#### Straight 3 and curve 4 long stator motor segments

- > These are linear motors with integrated power electronics and multi carrier position measurement.
- > The longstator motor segments can be combined freely into open and closed tracks, and can be mounted from top on a base plate.
- > Integrated mechanical alignments simplify the mounting process.
- > No cabinet space is required for the drive electronics as it is integrated in the track segments.
- > Straight long stators are designed for automatic rail lubrication. A minimum spacing of 6 meters (19.7 ft) between lubrication points is recommended.
- > The maximum length of a track is 40 m (131.2 ft) (1)
- > Each segment is equipped with electronic type plates which enables the controller to identify the segments and the resulting track geometry automatically.

#### Communication interconnect 5

- > Communication interconnects are used to interconnect the straight or curve longstator motor segments and to support the transmission of the communication (Sercos III), and of the SFO safety function (Safe Force Off).



#### Connection modules 6

- > The Connection modules ensure the overvoltage protection, and the supply voltage monitoring.


#### Power interconnects 7

- > Power interconnects are used to interconnect the straight or curve longstator motor segments, and to support the transmission of the DC power, ensuring a quick wiring.
- > When mounting two longstators, supply voltage is automatically connected through.

(1) For track length of more than 20 m (65,61 ft), Please contact your SE representative.




Available Open or closed track geometries



Vertical orientation



Horizontal orientation



Communication interconnects associated to Sercos as provided by LMCPro2 motion controller (1) and safe outputs: TM5SDO4TFS, TM5SDO4TAFS safety modules, and XPSMCMRO0004G, XPSMCMDO0004G modular safety modules (2) combined with Harmony XB5 Emergency stop pushbuttons (3).  
 ABLU3A48200 (4): 3-phase power supply is dedicated to Lexium MC12 multi carrier system.

## Setting up the system components

### Designing a track

#### Shapes

- > Open tracks or closed tracks that can be realized with 300 mm (11.81 in) straight long stator motor segments and 200 mm (7.87 in) 45° outside curve long stator motor segments.
- > The Maximum track length is 40 m (131.23 ft) (1).
- > The free space left inside a track allows the integration of additional equipment such as Delta robots, reduces the space of an installation, and ease the access for service or maintenance.
- > **Track's orientation**
  - Track can be mounted in Vertical or Horizontal orientations.

### Connecting a track

#### Communication interconnects

- > There are different interconnects available, e.g. to connect Sercos cables or to connect Safe Force Off signal.
- > The communication interconnects ensure the Sercos communication and Safety function:
  - Once connected, the interconnects eliminate further wiring
  - Multiple safety zones are allowed with one connection per zone

#### Connection modules

- > Connection module are installed close to power supply, between power supply and power connector at track. They provide the internal DC Bus and power supply on tracks, they ensure the overvoltage protection, and the supply voltage monitoring.
- > The Internal DC Bus and the power supply (48 V DC) are automatically connected through when mounting two segments.
  - No wiring is required between the segments
  - Up to three 48 V power supplies can be installed in parallel according to the needs of application
  - The Power infeed is applied in parallel at straight and/or curves long stator segments

#### Power interconnects

- > There are different versions available, e.g. with a power connector to connect power to the track or a disconnector which allows to split a track into different power zones.
- > The power interconnects ensure the power distribution in the track. They are mounted at the bottom side and provide an alignment aid helping to mount the long stator motor segments properly.

(1) For track length of more than 20 m (65,61 ft), Please contact your SE representative.


# Lexium MC12 multi carrier

## The multi carrier transport system

### Complementary of offers

#### Complementary of offers

- Control** > Lexium MC12 multi carrier is integrated into PacDrive 3 system, using PacDrive 3 motion controllers (LMC Pro2). Lexium MC12 becomes part of PacDrive 3 architecture.
- Configuration** > Lexium MC12 multi carrier applications can be developed and commissioned with dedicated application libraries (CAD, Eplan, Application function block, ...) embedded in **EcoStruxure Machine Expert**, Schneider Electric's single engineering environment for developing, configuring and commissioning complete automation solutions, with less time to market.  
The multi dimensional software architecture allows visualization and simulation during the conception of a motion centric machine.
- > Lexium MC12 multi carrier is part of the EcoStruxure Machine Expert Twin software, **Builder** and **Visu** license (integrated in EcoStruxure Machine Expert):
- EcoStruxure Machine Expert **Visu** together with the Multi Carrier Configurator of Machine Expert is allowing users to automatically create Digital twin models of 1 multi carrier, allowing to visualize 3D models for testing purposes.
  - EcoStruxure Machine Expert Twin **Builder** is allowing users to automatically generate digital twin models from tracks pre-defined in Machine Expert and deployed to a PacDrive LMC. Multiple models can be generated.
- Related products** > Schneider Electric offers several ranges of robots and products (actuators, control systems) to complete a PacDrive 3 automation solution.
- > The compact design of the Lexium MC12 multi carrier leaves space to mount additional equipment like Delta robots within closed tracks.



- |   |   |
|---|---|
| 1 <a href="#">AVEVA™ Insight</a>  | 8 <a href="#">Modicon TM5CSLC Safety logic controller</a>   |
| 2 <a href="#">AVEVA XR for Operations and Maintenance</a>                               | 9 <a href="#">Modicon TM5: Sercos interface module. Safety IO expansion module. IO expansion module (IP 20)</a> |
| 3 <a href="#">Harmony iPC panel, Harmony Edge box</a>                                   | 10 <a href="#">Lexium 62 ILD detached servo drives</a>  |
| 4 <a href="#">Lexium Cobot: Collaborative robot and Cobot compact controller</a>        | 11 <a href="#">Lexium SCARA Scara robot</a>   |
| 5 <a href="#">PacDrive LMC Pro2 Motion controller, Lexium 62 Multi axis servo drive</a> | 12 <a href="#">Harmony XALD Harmony XB5 Emergency stop pushbuttons</a>  |
| 6 <a href="#">EcoStruxure Machine Expert software</a>                                   | 13 <a href="#">Contactless RFID safety switch</a>   |
| 7 <a href="#">EcoStruxure Machine Expert Twin software</a>                              | 14 <a href="#">Lexium PAS: Linear axes with movable carriage and fixed axis</a>                                 |
|   | 15 <a href="#">Lexium MC12 multi carrier</a>  |
|   | 16 <a href="#">Lexium P Delta 3 robot</a>   |


# Lexium MC12 multi carrier

## The multi carrier transport system

Communication, Embedded safety function SFO, Main characteristics

**sercos**  
the automation bus

- Cat 5e
- Baudrate: 100 Mbps
- Cycle time: 1...4 ms



### Communication

Lexium MC12 multi carrier is communicating via Sercos III automation bus, and controlled by the PacDrive 3 LMC Pro2 motion controller.

- Each carrier is handled as Sercos device by the system with a Sercos ID and a reserved area for communication, similar to a servo drive in configuration and application.

### Embedded safety function SFO

Lexium MC12 multi carrier is an integral part of the Machine safety system with its drive embedded Safe Force Off (SFO) function.

- This function meets the requirements of SIL 3 according IEC 61800-5-2, IEC 62061 and IEC 61508 as well as up to category 3 and PLe according to EN ISO 13849-1.
- It simplifies the setup of installations requiring complex safety equipment and improves performance during maintenance operations.

### Main characteristics (1)

Lexium MC12 multi carrier		
Peak Force (2)		120 N (26.97 lbf)
Total mass (3)		≤ 3 kg (6.61 lb)
Nominal mass of a carrier		0.73 kg (1.6 lb)
Max. payload per carrier		2.27 kg (5.0 lb)
Max. acceleration for 1 kg (2.204 lb)		120 m/s <sup>2</sup> (393.70 ft/s <sup>2</sup> )
Max. speed		4 m/s (13.12 ft/s)
Length	Straight longstator segment	300 mm (11.81 in)
	Curve longstator segment	200 mm (7.87 in) – Radius: 255 mm (10.04 in)
Repetitive accuracy (4)	Straight longstator segment	0.03 mm (0.001 in)
	Curve longstator segment	0.05 mm (0.002 in)
Absolute accuracy	Straight longstator segment	0.25 mm (0.009 in)
	Curve longstator motor	0.35 mm (0.013 in)
IP Class		IP65
Cleanroom Class (ISO / GMP)		ISO class 6 / GMP class B
Max. number of carriers	per track	Equals max. number of servo axis controller can handle (currently up to 200)
	per segment	6 carriers on Straight longstator segment 4 carriers on Curve longstator segment
Carrier/Smart carrier	Width x Height	50 x 143 mm (1.96 x 5.63 in)
	Weight without load	0.73 kg (1.6 lb)
Max. track length		40 m (131.23 ft) (5)

(1) More characteristics on [Product datasheet](#).

(2) Max. force generated in moving direction of carrier, Peak force can be increased by use of multiple carriers together.

(3) Mass of the carrier plus payload.


(4) Single carrier to single point accuracy.

(5) For track length of more than 20 m (65,61 ft), Please contact your SE representative.

# Lexium MC12 multi carrier

## The multi carrier transport system


### System components



LXMMC12MS06S100  
LXMMC12MS06S10L



LXMMC12MA02S100



LXMMCABR120S100



LXMMCACMD02S100



LXMMBCBA001S100



LXMMBCBAS01S100



LXMMBCBAF01S100



LXMMBCDASF1S100



LXMMBCDAS01S100




LXMMCBPA001S100  
LXMMCBPA00XS100




LXMMCBPAP01S100




LXMMCBPAB01S100



LXMMC12CA51S100



LXMMCACT0A1S100




LXMMC12CA51U100



LXMMCAMGEALS100



LXMMCARS0AXS100



LXMMCAMGMALS100



VW33MAP22

Designation	Description	Reference	Weight kg lb
<b>System components</b>			
<b>Longstator motor segments (to build the tracks)</b>			
<b>Longstator motor segment</b>	Straight segment Length: 300 mm (11.81 in)	LXMMC12MS06S100	7.900 17.41
with an integrated drive, IP65	Straight segment with automated lubrication Length: 300 mm (11.81 in) Works in tandem with guide rail type of LXMMCRS0A06S10L	LXMMC12MS06S10L (1)	7.900 17.41
	Curve segment 45° arc	LXMMC12MA02S100	4.500 9.92
<b>Braking resistor (to increase the amount of energy that can be absorbed during deceleration phases of demanding applications)</b>			
<b>Braking resistor</b>	Degree of protection: IP65 To connect to a Connection module Ohmic value: 3 Ω Continuous power: 100 W Connection cable length: 2 m (78.74 in)	LXMMCABR120S100	0.600 1.32
<b>Connection modules (to provide the internal DC Bus and power supply on the tracks)</b>			
<b>Connection module</b>	20 A continuous power to connect track to power supply Installed between two segments	LXMMCACMD02S100	0.045 0.09
	Connection module connector kit (Spare part)	LXMMCACMCS1S100	0.045 0.09
<b>Communication interconnects (to support the transmission of communication over Sercos III, and/or SFO safety function (Safe Force Off))</b>			
<b>Communication interconnects</b>	Communication interconnect between segments	Sold by 1 piece LXMMBCBA001S100 Sold by 10 pieces LXMMBCBA00XS100 With two additional Sercos connectors (infeed port/outfeed port) LXMMBCBAS01S100 With one additional SFO connector LXMMBCBAF01S100 To use at the beginning of an open track With one additional Sercos connector (infeed port) and one additional SFO connector LXMMBCDASF1S100 To use at the end of an open track With one additional Sercos connector (outfeed port) LXMMBCDAS01S100	0.050 0.11 0.100 0.22
<b>Power interconnects (to support the transmission of the DC power)</b>			
<b>Power interconnects</b>	To use between segments	1 piece LXMMCBPA001S100 Sold by 10 pieces LXMMCBPA00XS100 With M23 power infeed connector LXMMCBPAP01S100	0.400 0.88 3.500 7.71 0.600 1.32
<b>Power disconnecter</b>	Used to separate the DC bus between segments	LXMMCBPAB01S100	0.400 0.88
<b>Carriers (to handle the products on the track)</b>			
<b>Carrier</b>	Linear motors independently controlled for speed, position, and timing.	Sold by 1 piece LXMMC12CA51S100 Sold by 10 pieces LXMMC12CA5XS100	0.730 1.60 8.000 17.6
<b>Smart carrier</b>	Carrier with embedded, motion-free identification available at startup providing carrier identification and traceability	Sold by 1 piece LXMMC12CA51U100	0.765 1.68
<b>Carrier handling tool</b>	Handling tool to put carrier on track or to remove carrier from track	LXMMCACT0A1S100	0.520 1.15
<b>Carrier roller replacement set</b>	10 sets of 4 rollers and required screws 10x 2 lubrication pads	LXMMCARSOAXS100	0.500 1.1
<b>Encoder magnet for carrier</b>		Sold by 50 pieces LXMMCAMGEALS100	0.200 0.44
<b>Motion magnet set for carrier</b>		Sold by 50 pieces LXMMCAMGMALS100	1.850 4.08
<b>Accessories</b>			
<b>Material test kit 1</b>	Material probes for resistance tests	LXMMCAMK001S100	1.250 2.76
<b>Set of hard stops</b>	Set of 2 (one hard stop for each end of the track) To stop carriers at the end of an open track	LXMMCCHS001S00	6.300 13.89
<b>Single-hand lubrication gun</b>	To refill the lubrication reservoirs of the carriers Oil capacity: 120 cc Delivery volume: 0.5 cc/stroke	VW33MAP22	0.563 1.241

(1) The lubrication pump and tubes required for the system are sold by third-party suppliers.



LXMMCRS0A06S100  
LXMMCRS0A06S10L



LXMMCRSEA03S100



LXMMCRABA62S100



LXMMCRABA64S100



LXMMCRABA66S100



LXMMCRABA68S100

LXMMCAPC●●●S100



XZCP1141L●

XZCP1241L●



VW3E3065R0



ABLU3A48200

### System components

Designation	Description	Reference	Weight			
			kg	lb		
<b>Guide rail ( to hold the segments)</b>						
Guide rail sets for straight segment	Set of top and bottom guide rails for straight segment	1 unit of length	LXMMCRS0A06S100	1.300	2.86	
		1 unit of length	LXMMCRS0A06S10L	1.300	2.86	
		For automated lubrication (It works in tandem with Longstator motor straight segment type of LXMMC12MS06S10L)		(1)		
		2 units of length	LXMMCRS0A12S100	2.500	5.51	
		3 units of length	LXMMCRS0A18S100	3.800	8.37	
		4 units of length	LXMMCRS0A24S100	5.000	11.00	
Guide rail sets for curve segment	Set of top and bottom guide rails for curve segment	5 units of length	LXMMCRS0A30S100	6.200	13.66	
		Open track with curves				
		0.5 units of length	LXMMCRSEA03S100	0.700	1.54	
		45° arc, 1 unit of length	LXMMCRABA62S100	2.200	4.85	
		90° arc, 1 unit of length	LXMMCRABA64S100	3.000	6.61	
		135° arc, 1 unit of length	LXMMCRABA66S100	3.800	8.37	
	180° arc, 1 unit of length	LXMMCRABA68S100	4.600	10.14		
	360° arc	LXMMCRA0A00S100	6.600	14.55		

### Cables

Description	For use	Length of cable		Reference	Weight		
		m	ft		kg	lb	
Power cables M23 connector (Power interconnect side), free wires (connection module side)	Between Connection module LXMMCACMD02S100 and Power interconnect LXMMCBPAP01S100	2	6.56	LXMMCAPC020S100	0.500	1.10	
		4	13.12	LXMMCAPC040S100	0.900	2.00	
		6	6.56	LXMMCAPC060S100	1.300	2.86	
		8	26.24	LXMMCAPC080S100	1.700	3.74	
		10	32.80	LXMMCAPC100S100	2.100	4.62	
		12	39.37	LXMMCAPC120S100	2.500	5.51	
		14	45.93	LXMMCAPC140S100	2.900	6.39	
		16	52.49	LXMMCAPC160S100	3.300	7.27	
		18	59.05	LXMMCAPC180S100	3.700	8.15	
		20	65.61	LXMMCAPC200S100	4.100	9.04	
Pre-wired connectors for SFO safety function M12, 4-pin connectors Metal clamping ring PUR cable	Between Modicon TM5 safety IO module and Communication interconnects (SFO)	Straight	2	6.56	XZCP1141L2SE	0.090	0.198
			5	16.40	XZCP1141L5SE	0.190	0.418
			10	32.80	XZCP1141L10SE	0.370	0.815
			20	65.61	XZCP1141L20SE	0.750	1.65
		Elbowed	2	6.56	XZCP1241L2SE	0.090	0.198
			5	16.40	XZCP1241L5SE	0.190	0.418
			10	32.80	XZCP1241L10SE	0.370	0.815
			15	49.21	XZCP1241L15SE	0.500	1.10
Sercos cables RJ45 / M12 angled, 4-pin connector	Between LMC Pro2 motion controller or Modicon TM5 safety controller and Communication interconnects (with Sercos connector)	3	9.84	VW3E3065R030	1.367	3.01	
		5	16.40	VW3E3065R050	0.557	1.23	
		10	32.81	VW3E3065R100	1.075	2.37	


### Dedicated offer

Designation	Description	Reference (1)
3-phase Power supply for industrial use, rail mounting	Input voltage: 380...500 Vac Output voltage: 48 Vdc Nominal power: 960 W Nominal current: 20 A	ABLU3A48200


### Related offers

Title	Consult catalog
EcoStruxure Machine Expert configuration software	<a href="#">DIA3ED2180701EN</a>
PacDrive3, A complete automation solution for motor centric machines	<a href="#">DIA3ED2160301EN</a>
PacDrive LMC Pro2, Motion controller for automating machines/lines with 0 – 130 servo or robot axes	<a href="#">DIA7ED2160303EN</a>
Lexium 62, Multi axis servo drive and servo motors	<a href="#">DIA7ED2160305EN</a>
Lexium 62 ILM, Multiaxis integrated servo drives	<a href="#">DIA7ED2160306EN</a>
Lexium 62 ILD, Detached servo drives	<a href="#">DIA3ED2161202EN</a>
Lexium T & P, Delta 2 and Delta 3 robots for pick & place solutions	<a href="#">DIA3ED2160307EN</a>
Lexium SCARA robot	<a href="#">DIA7ED2240302EN</a>
Lexium Cobot, Collaborative robot	<a href="#">DIA7ED2220801EN</a>
Modicon TM5, High-Performance and Safe IP20 Modular I/O system	<a href="#">DIA3ED2131204EN</a>


(1) The lubrication pump and tubes required for the system are sold by third-party suppliers.



Track configuration



Carrier configuration



Catalog ref. [DIA3ED2180701EN](#)

## Configuration

### Toolset covering the machine life cycle

- Design & Engineering
  - Physical configuration of the track or generated from scan
  - Definition of coordinate system and direction
  - Handling physical dimensions of carriers and products
  - Visualization and virtual commissioning of multi carrier system
- Implement
  - Library
  - Mechanical bricks mounted by the OEM
  - Configurator
- Operating, Maintenance & services
  - Monitoring with Ecostruxure Machine Advisor
  - Visualization

## Software

- As Lexium MC12 multi carrier becomes part of PacDrive architecture, its configuration is managed with Ecostruxure Machine Expert software (1) :
  - Deep integration into engineering environment
  - Different usability levels
  - Motion synchronization capabilities
  - Simulation
  - Visualization
  - Virtual commissioning

## Libraries

- For the efficient
  - Predefined functions for common needs, like carrier queuing, two carrier clamping, multi carrier positioning and release, automatic gap control between moving carriers, ...
- For the experienced
  - Functions working on track level, like scanning a track, management of carriers on the track, monitoring and emergency reactions on track level
- For the experts
  - Carriers are represented like servo axis in the system
  - Existing functionality, e.g. camming can be applied to move carriers
  - Full freedom with full responsibility to manage all movements

(1) Consult catalog ref. [DIA3ED2180701EN](#)

# Lexium MC12 multi carrier

## The multi carrier transport system

### Segment, Carrier

Type code													
To order a Segment, make up the reference as follows:													
	Family			Group		Model	Segment type	Segment geo	Length	Variant	Revision	Reserved	Function
<b>Example</b>	L	X	M	M	C	12	M	S	06	S	1	0	0
Product family	L	X	M										
Product group	MC: Multicarrier			M	C								
Model	12 = 120N Peakforce					12							
Segment	M = Standard segment						M						
Segment geometry	S= Straight							S					
	A= Arc outside							A					
Length	for straight segments length given in n50 mm (n1.96 in), e.g 06 = 300 mm (11.81 in)								06				
	for curved segments angle is given in n22,5°, e.g 02 = 45°								02				
Variant	Standard (Anodized Aluminum, IP65)									S			
Revision	1 = Initial version										•		
Reserved	0											0	
Function	0: Standard												0
	L: With automated lubrication												L

To order a Carrier, make up the reference as follows:													
	Family			Group		Model	Product group	Type	Length	Quantity	Variant	Revision	Reserved
<b>Example</b>	L	X	M	M	C	12	C	A	5	1	S	1	00
Product family	L	X	M										
Product group	MC: Multicarrier			M	C								
Model	120 N Peakforce					12							
Carrier	Always C for carrier						C						
Type (equals to model of rail)	A							A					
Size	50 mm (1.96 in)								5				
Quantity	1 piece									1			
	10 pieces									X			
Variant	Standard (Anodized Aluminum, IP65)										S		
	Smart carrier										U		
Revision	1 = Initial Version											•	
Reserved	00												00

# Lexium MC12 multi carrier

## The multi carrier transport system

### Rail, Bridge (Communication interconnect)

Type code													
To order a Rail (1), make up the reference as follows:													
	Family			Group		Rail	Geo. 1	Geo. 2	Model	Size	Variant	Revision	Reserved
<b>Example</b>	L	X	M	M	C	R	A	0	A	02	S	1	00
Product family	L	X	M										
Product group	MC: Multicarrier			M	C								
Product detail	R: Rail					R							
Geometry 1	S= Straight						S						
	A= Arc outside						A						
Geometry 2	0= no straight at end(s)							0					
	E= End of open track with curve							E					
	B= Straight at both sides							B					
Model	A								A				
Size	nn / (ul/6) ul equals length of straight segment + air gap between segments. ul/6 equals approx. 50 mm (1.96 in) 30 equals a length of 5 segments + air gaps => approx. 1.5 m (4.92 ft) rail max. rail length is 1,5 m									••			
Variant	S = Standard (Anodized Aluminum, IP65)										S		
Revision	1 = Initial Version											•	
Reserved	00												00

(1) Rails are always sold as a set of two rails (bottom and top rail).

(2) Max. rail length is 1,5 m (4.92 ft).

To order a Communication interconnect, make up the reference as follows:														
	Family			Group		Bridge	Bridge type	Model	Supplies	Quantity	Variant	Revision	Reserved	
<b>Example</b>	L	X	M	M	C	B	C	A	0	0	1	S	1	00
Product family	L	X	M											
Product group	MC= Multicarrier			M	C									
Product detail	B= Communication interconnect					B								
Bridge type	C= Communication closed track						C							
	D = Communication open end of track						D							
	P = Power closed track						P							
	Q = Power open end of track						Q							
Model	A= stands for current Bridge design							A						
Supplies up to 2 different inputs/outputs can be specified	0 = no supply, plain interconnect								0	0				
	D = disconnecter, interrupts connection between segment, no supply								D	D				
	P = Power supply								P	P				
	S = Bus supply (Sercos III)								S	S				
	F = Safe Force Off								F	F				
Quantity	1 = 1, X = 10										•			
Variant	S = Standard (Anodized Aluminum, IP65)										S			
Revision	1 = Initial version											•		
Reserved	00												00	

Type code													
To order an Accessory, make up the reference as follows:													
			Family			Group		Accessory	Type	Specifics	Variant	Revision	Reserved
<b>Example</b>			L	X	M	M	C	A	RS	0AX	S	1	00
Product family			L	X	M								
Product group			MC: Multicarrier			M	C						
Accessory			A: Accessory					A					
Accessory type	Type	Specifics	Variant										
	FC= Safe Force Off cable	xxx: length / 10 cm (3.93 in)	S					FC	●●●	S			
	RS= Roller set	0xy: 0 Roller Type, x: type of rail see rails-model for coding, y qty: 1= 1, X= 10, L= 50						RS	0●●				
	MG= Magnet	xAy: x: Type of Magnet: E= Encoder, M= Motion, Variant = A, y qty: 1= 1, X= 10, L= 50						MG	●A●				
	CT= Carrier drop tool	0A1: 0 is not used, A variant of drop tool, 1 quantity						CT	0A●				
	CM= Connection module 20A	D02	S					CM	D02	S			
	CM= Connection module connector kit	CS1	S					CM	CS1	S			
	MK= Material kit	001						MK	001				
Revision	1 = Initial version											●	
Reserved	00												00

A		V	
<a href="#">ABLU3A48200</a>	11	<a href="#">VW33MAP22</a>	10
LXM		<a href="#">VW3E3065R030</a>	11
<a href="#">LXMMC12CA51S100</a>	10	<a href="#">VW3E3065R050</a>	11
<a href="#">LXMMC12CA51U100</a>	10	<a href="#">VW3E3065R100</a>	11
<a href="#">LXMMC12CA5XS100</a>	10	X	
<a href="#">LXMMC12MA02S100</a>	10	<a href="#">XZCP1141L10SE</a>	11
<a href="#">LXMMC12MS06S100</a>	10	<a href="#">XZCP1141L2SE</a>	11
<a href="#">LXMMC12MS06S10L</a>	10	<a href="#">XZCP1141L5SE</a>	11
<a href="#">LXMMCABR120S100</a>	10	<a href="#">XZCP1241L10SE</a>	11
<a href="#">LXMMCACMCS1S100</a>	10	<a href="#">XZCP1241L15SE</a>	11
<a href="#">LXMMCACMD02S100</a>	10	<a href="#">XZCP1241L20SE</a>	11
<a href="#">LXMMCACT0A1S100</a>	10	<a href="#">XZCP1241L2SE</a>	11
<a href="#">LXMMCAHS001S00</a>	10	<a href="#">XZCP1241L5SE</a>	11
<a href="#">LXMMCAMGEALS100</a>	10		
<a href="#">LXMMCAMGMALS100</a>	10		
<a href="#">LXMMCAMK001S100</a>	10		
<a href="#">LXMMCAPC020S100</a>	11		
<a href="#">LXMMCAPC040S100</a>	11		
<a href="#">LXMMCAPC060S100</a>	11		
<a href="#">LXMMCAPC080S100</a>	11		
<a href="#">LXMMCAPC100S100</a>	11		
<a href="#">LXMMCAPC120S100</a>	11		
<a href="#">LXMMCAPC140S100</a>	11		
<a href="#">LXMMCAPC160S100</a>	11		
<a href="#">LXMMCAPC180S100</a>	11		
<a href="#">LXMMCAPC200S100</a>	11		
<a href="#">LXMMCARSA0XS100</a>	10		
<a href="#">LXMMBCA001S100</a>	10		
<a href="#">LXMMBCA00XS100</a>	10		
<a href="#">LXMMBCAF01S100</a>	10		
<a href="#">LXMMBCAS01S100</a>	10		
<a href="#">LXMMCBDAS01S100</a>	10		
<a href="#">LXMMCBDASF1S100</a>	10		
<a href="#">LXMMCBPA001S100</a>	10		
<a href="#">LXMMCBPA00XS100</a>	10		
<a href="#">LXMMCBPAB01S100</a>	10		
<a href="#">LXMMCBPAP01S100</a>	10		
<a href="#">LXMMCRA0A00S100</a>	11		
<a href="#">LXMMCRABA62S100</a>	11		
<a href="#">LXMMCRABA64S100</a>	11		
<a href="#">LXMMCRABA66S100</a>	11		
<a href="#">LXMMCRABA68S100</a>	11		
<a href="#">LXMMCRS0A06S100</a>	11		
<a href="#">LXMMCRS0A06S10L</a>	11		
<a href="#">LXMMCRS0A12S100</a>	11		
<a href="#">LXMMCRS0A18S100</a>	11		
<a href="#">LXMMCRS0A24S100</a>	11		
<a href="#">LXMMCRS0A30S100</a>	11		
<a href="#">LXMMCRSEA03S100</a>	11		



# Connect to other users and experts

## Welcome to Schneider Electric community

Schneider Electric support forum for Motion Control solutions from design, implementation to troubleshooting and more, including:

- Multicarrier systems
- Robotics
- Integrated Drives
- Servo Drives and Motors
- Stepper Drives and Motors
- Motion Controllers
- Programmable Logic Controllers
- Safety PLC Controllers
- Input/Output (I/O) modules
- Engineering software

[Access the community forum](#)

**Schneider**  
Electric



# Advantage Service Plan for Robotics

## Keep the movement on

Keep your Lexium Robots, Cobots, MC12 Multi Carrier, SCARA, Cartesian, and associated controllers running smoothly and efficiently with a service contract. Maintain productivity by reducing unexpected downtime. Get peace of mind from knowing that you have access to experienced service technicians and spare parts when and where you need them.



### Key benefits

- Reduce costs by identifying and correcting potential issues before they cause unplanned downtime.
- Access to experts helps you maintain production, reduce downtime and get the most out of your robotic systems.
- Minimize unplanned downtime with ready access to wear and spare parts.
- Extend asset life with properly maintained robotics.

[se.com/services](https://se.com/services)

**Schneider**  
Electric



# Advantage Service Plan for Robotics

## Key features

### Preventive maintenance visit

Periodic maintenance, based on the operations performed by the robot, is essential to prevent unplanned downtime and extend asset life. During the included preventive maintenance visit, our service representatives perform a routine check-up, and all the maintenance activities needed, based on the number of operations or operating time performed.

### Remote technical support

Your Advantage Service Plan provides you with access to our advanced technical support team, who can answer your robotics questions and troubleshoot a problem via phone or email during normal business hours.

### On site corrective maintenance service

In the event of an incident that results in unplanned downtime for your robot that cannot be resolved remotely, our service representatives can respond on site for diagnostic and corrective maintenance activities. Programming and commissioning are not included in this service.

### Preferred rate for parts

For simplified ordering, we offer parts needed for the upkeep of your robots. These parts are offered at preferential rates for our contract customers.

### Extended warranty (optional service)

When ordered with the contract, you can extend the warranty for one year beyond the standard warranty.

### Support coverage

Support is available for the following ranges of Schneider Electric™ robots:

- Lexium Delta P
- Lexium Delta T
- Lexium Cobots
- Lexium MC12 Multi Carrier
- Lexium SCARA
- Lexium Cartesian

### Service Plans (Available with TWO tiers)

Advantage Service Plan for Robotics	Duration	Essential	Advanced
Remote technical support (8X5) - Premium	1 year	Yes	Yes
Access to MySchneider portal - Premium	1 year	Yes	Yes
Preventive Maintenance visit	1 year		Yes
Preferred rate for parts	1 year		Yes
Onsite corrective Maintenance	1 year		Yes
<b>Optional Service</b>			
Extended warranty - 1 year	1 year		

For more information, please contact your Schneider Electric Representative.

[se.com/services](https://se.com/services)



# mySchneider, your personalized digital experience

Access an all-in-one customized online experience and benefit from tailored business services, resources, and tools to efficiently support your business operations.

- **Efficiency:** In just a few clicks, find all the information and support you need to get the job done.
- **Simplicity:** Use a single login to access all business services, in one place, available 24/7. You no longer need to log in to multiple platforms.
- **Personalization:** Benefit from content, tools, and business services tailored to your activity, and customize your landing page based on your preferences.

## Watch the How-to Videos



### Order management

- > [Select Products and Add to Cart](#)
- > [Check for Products' Price and Availability](#)
- > [Order Products with Generic Commercial References](#)




### Product information

- > [Find a Product Data Sheet and Related Documents](#)
- > [Select Products and Add to Cart](#)
- > [Stay Up to Date on the Status of My Products](#)



### Support

- > [Get Quicker Answers Thanks to Online Support](#)



### Training

- > [Access Trainings Dedicated to My Activity](#)

[Create your account](#)

**Schneider**  
Electric

# Legal information

The information provided in this Catalog contains description of Schneider Electric products, solutions and services ("Offer") with technical specifications and technical characteristics of the performance of the corresponding Offer.

The content of this document is subject to revision at any time without notice due to continued progress in methodology, design and manufacturing.


To the extent permitted by applicable law, no responsibility or liability is assumed by Schneider Electric and its subsidiaries for any type of damages arising out of or in connection with (i) informational content of this Catalog not conforming with or exceeding the technical specifications, or (ii) any error contained in this Catalog, or (iii) any use, decision, act or omission made or taken on basis of or in reliance on any information contained or referred to in this Catalog.

SCHNEIDER ELECTRIC MAKES NO WARRANTY OR REPRESENTATION OF ANY KIND, WHETHER EXPRESS OR IMPLIED, AS TO WHETHER THIS CATALOG OR ANY INFORMATION CONTAINED THEREIN SUCH AS PRODUCTS AND SERVICES WILL MEET REQUIREMENTS, EXPECTATIONS OR PURPOSE OF ANY PERSON MAKING USE THEREOF.

Schneider Electric brand and any trademarks of Schneider Electric and its subsidiaries referred to in this Catalog are property of Schneider Electric or its subsidiaries. All other brands are trademarks of their respective owners.

This Catalog and its content are protected under applicable copyright laws and provided for informative use only. No part of this Catalog may be reproduced or transmitted in any form or by any means (electronic, mechanical, photocopying, recording, or otherwise), for any purpose, without the prior written permission of Schneider Electric.

Copyright, intellectual, and all other proprietary rights in the content of this Catalog (including but not limited to software, audio, video, text, and photographs) rests with Schneider Electric or its licensors. All rights in such content not expressly granted herein are reserved. No rights of any kind are licensed or assigned or shall otherwise pass to persons accessing this information.



Learn more about our products at  
[www.se.com](http://www.se.com)

Design: Schneider Electric  
Photos: Schneider Electric

**Schneider Electric Industries SAS**

Head Office  
35, rue Joseph Monier - CS 30323  
F-92500 Rueil-Malmaison Cedex  
France

DIA7ED2210701EN  
April 2026 - V4.0