



EMC COMPLIANCE TEST REPORT

The product

Equipment Under Test	: UPS
Model Number	: BX1100CI
Product Series	: Please refer to page 9
Report Number	: HA210892-CE
Issue Date	: 09-May-2022

is produced by

American Power Conversion Holdings Inc., Taiwan Branch
5F, No. 189, Sec 2, Jiuzong Rd., Neihu Dist., Taipei, Taiwan



HongAn TECHNOLOGY CO., LTD.
HongAn TECHNOLOGY EMC Laboratory

NO.15-1, CWEISHUH KENG, CWEIPIN VILLAGE, LINKOU DIST, NEW TAIPEI CITY, TAIWAN, R. O. C.

TEL: +886-2-26030362 **FAX:** +886-2-26019259 **E-mail:** hatlab@ms19.hinet.net

Caution :

The results in this report apply to the test sample(s) mentioned above at the time of the testing period only and are not to be used to indicate applicability to other similar products. This report does not imply that the production product(s) has met the criteria for certification. The report must not be used by the client to claim product certification, approval, or endorsement by TAF or any government agencies.

HongAn shall have no liability for any deductions, inferences or generalizations drawn by the client or others from the reports issued by us. Opinions or interpretations expressed in this report, if any, are outside the scope of HongAn accreditations. Any opinions expressed do not necessarily reflect the opinion of HongAn, unless otherwise stated.

The test report shall not be reproduced except in full, without written approval of HongAn.



Contents

1	General Description	9
1.1	Description of EUT	9
1.2	Test Facility	10
1.3	Test Instruments	10
1.4	Test Methodolgy	13
1.5	Auxiliary Equipments	13
1.6	Block Diagram	13
1.7	Identifying the Final Test Mode	14
1.8	Final Test Mode	14
1.9	Condition of Power Supply	14
1.10	EUT Configuration	14
1.11	Performance criteria for immunity tests	14
2	Conducted Emission Test	15
2.1	Test Instruments	15
2.2	Test Arrangement and Procedure	15
2.3	Conducted Limit	16
2.4	Test Result	16
3	Radiated Emission Test	21
3.1	Test Instruments	21
3.2	Test Arrangement and Procedure	21
3.3	Radiated Limit	22
3.4	Test Result	22
4	Harmonic Current Emission Measurement	27
4.1	Test Instruments	27
4.2	Test Configuration and Procedure	27
4.3	EUT Operation Condition	28
4.4	Test Limit	28
4.5	Test Result	28
5	Electrostatic Discharge Immunity Test	31
5.1	Test Instruments	31
5.2	Test Configuration and Procedure	31
5.3	Test Result	32
6	Radio-frequency, Electromagnetic Field Immunity Test	33
6.1	Test Instruments	33
6.2	Test Configuration and Procedure	33



6.3	Test Result	34
7	Electrical Fast Transient Test	35
7.1	Test Instrument	35
7.2	Test Configuration and Procedure	35
7.3	Test Result	36
8	Surge Immunity Test	37
8.1	Test Instrument	37
8.2	Test Configuration and Procedure	37
8.3	Test Result	38
9	Radio-frequency, Conducted Disturbances Immunity Test	39
9.1	Test Instruments	39
9.2	Test Configuration and Procedure	39
9.3	Test Result	40
10	Power Frequency Magnetic Field Immunity Test	41
10.1	Test Instruments	41
10.2	Test Configuration and Procedure	41
10.3	Test Result	42
11	Low Frequency Signals Immunity Test	43
11.1	Test Instrument	43
11.2	Test Configuration and Procedure	43
11.3	Test Result	43
12	Photographs of Test	44
12.1	Power Line Conducted Test	44
12.2	Radiated Emission Test	45
12.3	Harmonic Current Measurement	46
12.4	Electrostatic Discharge Immunity Test	46
12.5	Radio-frequency, Electromagnetic Field Immunity Test	47
12.6	Electrical Fast Transient / Burst Immunity Test	47
12.7	Surge Immunity Test	48
12.8	Radio-frequency, Conducted Disturbances Immunity Test	48
12.9	Power Frequency Magnetic Field Immunity Test	49
13	Photographs of EUT	50
14	Photographs of ESD Test Points	57
15	Appendix	58
15.1	Conducted Emission Test	58
15.2	Radiated Emission Test	62



Release control Record

Report Version	Description	Issued Date
V00	Original release.	09-May-2022



Verification

Applicant : American Power Conversion Holdings Inc., Taiwan Branch
Manufacturer : American Power Conversion Holdings Inc., Taiwan Branch
Equipment Under Test : UPS
Model Number : BX1100CI
Product Series : Please refer to page 9
Sample Received Date : 25-Mar-2022
Test Result : Complied
Test Standard :

Emission:	Immunity:
☒ EN IEC 62040-2:2018 Environment : First Classification of EUT : Category C1 ☒ EN IEC 61000-3-2:2019+A1:2021	☒ EN IEC 62040-2:2018 Environment : First Classification of EUT : Category C1 ☒ IEC 61000-4-2:2008 ☒ IEC 61000-4-3:2020 ☒ IEC 61000-4-4:2012 ☒ IEC 61000-4-5:2017 ☒ IEC 61000-4-6:2013 ☒ IEC 61000-4-8:2009 ☒ IEC 61000-2-2:2002+A1:2017+A2:2018

Remark:

This report details the results of the test carried out on one sample. This report shows the EUT is technically compliant with the EN IEC 62040-2 official requirements. This report applies to the above sample only and shall not be reproduced in part without written approval of HongAn Technology Co., Ltd.

Documented by: Cherry Chi Date: 09-May-2022
Cherry Chi

Tested by: M.S. Shi Date: 05-May-2022
M.S. Shi

Approved by: Adam Yang Date: 09-May-2022
Adam Yang



Summary of Test Result - Emission

Emission			
Test Standard	Test Item	Test Result	Remark
EN IEC 62040-2 Category C1	Conducted emission at mains terminal	Pass	Highest Emission-(LINE mode) L: 1.043MHz, A.V. 37.71dBuV, Margin -8.29dB N: 1.043MHz, A.V. 39.38dBuV, Margin -6.62dB
			L: 0.404MHz, Q.P. 41.01dBuV, Margin -16.76dB N: 0.329MHz, Q.P. 50.64dBuV, Margin -8.85dB
EN IEC 62040-2 Category C1	Conducted emission at network port	N/A	Without telecommunication port of the EUT.
EN IEC 62040-2 Category C1	Radiated Emission	Pass	Highest Emission-(LINE mode) H: 30.560MHz, 20.57dBuV, Margin -9.43dB Antenna Height 400cm, Turntable Angle 99° V: 30.531MHz, 22.28dBuV, Margin -7.72dB Antenna Height 100cm, Turntable Angle 96°
			Highest Emission-(Battery mode) H: 129.015MHz, 22.16dBuV, Margin -7.84dB Antenna Height 399cm, Turntable Angle 50° V: 43.202MHz, 21.23dBuV, Margin -8.77dB Antenna Height 100cm, Turntable Angle 45°
EN IEC 61000-3-2	Harmonic	Pass	Refer to Page 28~29
Remark: Since U_{Lab} of our lab is less than U_{CISPR}, no matter if determining compliance with the limits in this standard shall be based on the results of the compliance measurements taking into account the considerations on measurement instrumentation uncertainty or not, any adjustment of the test result is not necessary, which means, - compliance is deemed to occur if no measured disturbance level exceeds the disturbance limit; - non-compliance is deemed to occur if measured disturbance level exceeds the disturbance limit. N/A: Not Applicable. Note : 1. Without telecommunication port of the EUT			



Summary of Test Result – Immunity

Immunity (Environment : First / Classification of EUT : Category C1)				
Test Standard	Test Item	Performance Criteria	Observed Result Class	Test Result
IEC 61000-4-2	Electrostatic Discharge	B	A	Pass
IEC 61000-4-3	Radiated Susceptibility	A	A	Pass
IEC 61000-4-4	Electrical Fast Transient	B	A	Pass
IEC 61000-4-5	Surge	B	A	Pass
IEC 61000-4-6	Conducted Susceptibility	A	A	Pass
IEC 61000-4-8	Magnetic Field	B	A	Pass
IEC 61000-2-2	Low Frequency Signals Immunity Test	A	A	Pass
Remark : According to the test standard, the uncertainty related to EMS test instrument calibration and test levels need not be recorded in the test report and shall not be taken into account. N/A: Not Applicable.				



Measurement Uncertainty

Where relevant, the following measurement uncertainty levels has been estimated for tests performed on the EUT as specified in CISPR 16-4-2:

The listed uncertainties are the worst case uncertainty for the entire range of measurement. Please note that the uncertainty values are provided for informational purposes only and are not used in determining the PASS/FAIL results.

Test Item	Expanded Uncertainty (U_{lab})	Expanded Uncertainty (U_{cisp})
Conducted emission at AC mains power using a V-AMN, 9kHz – 150kHz	$\pm 2.94\text{dB}$	$\pm 3.8\text{dB}$
Conducted emission at AC mains power using a V-AMN, 150kHz – 30MHz	$\pm 3.05\text{dB}$	$\pm 3.4\text{dB}$
Conducted emission at telecommunication port using AAN, 150kHz – 30MHz	$\pm 4.71\text{dB}$	$\pm 5.0\text{dB}$
Conducted emission at telecommunication port using CVP and CP, 150kHz – 30MHz	$\pm 3.92\text{dB}$	$\pm 4.0\text{dB}$
	$\pm 3.10\text{dB}$	
Radiated emission, 30MHz – 1GHz (Horizontal)	$\pm 4.92\text{dB}$	$\pm 6.3\text{dB}$
Radiated emission, 30MHz – 1GHz (Vertical)	$\pm 5.05\text{dB}$	$\pm 6.3\text{dB}$
Radiated emission, 1GHz – 6GHz	$\pm 4.35\text{dB}$	$\pm 5.2\text{dB}$
Radiated emission, 6GHz – 18GHz	$\pm 4.77\text{dB}$	$\pm 5.5\text{dB}$
Radiated electromagnetic disturbances using a LLAS, 9kHz – 30MHz	$\pm 3.27\text{dB}$	$\pm 3.3\text{dB}$
Disturbance Power, 30MHz – 300MHz	$\pm 4.04\text{dB}$	$\pm 4.5\text{dB}$

This reported expanded uncertainty is based on a standard uncertainty multiplied by a coverage factor of $k = 2$, providing a level of confidence of approximately 95%.



1 General Description

1.1 Description of EUT

Equipment Under Test	:	UPS
Model Number	:	BX1100CI
Product Series	:	SX31K1CI, BX1100CI-yyyyyyyy, BX1100CI, BX1100CI-AR, BX1100CI-CN, BX1100CI-GR, BX1100CI-RS, BX800CI-yyyyyyyy, BX800CI, BX800CI-AR, BX800CI-GR, BX800CI-RS, SX31K1CI-yyyyyyyy, SX31K1CI, SX31K1CI-GR, SX31K1CI-FR, SX3800CI-yyyyyyyy, SX3800CI, SX3800CI-GR, SX3800CI-FR
Applicant	:	American Power Conversion Holdings Inc., Taiwan Branch
Address of Applicant	:	5F, No. 189, Sec 2, Jiuzong Rd., Neihu Dist., Taipei, Taiwan
Manufacturer	:	American Power Conversion Holdings Inc., Taiwan Branch
Address of Manufacturer	:	5F, No. 189, Sec 2, Jiuzong Rd., Neihu Dist., Taipei, Taiwan
Power Supply	:	Input : AC 220-240V~, 4.8A, 50/60Hz, 1Ø, Icc : 1Ka Output : AC 220-240V~, 4.8A, 50/60Hz, 1100VA, 660W, 1Ø Output Cable*3 : ☐ Shielded ☒ Non-Shielded ☒ Detachable, 1m ☐ Un-Detachable ☐ with Ferrite Core ☒ without Ferrite Core
I/O Port	:	BATTERY BACKUP SURGE PROTECTION*6, INPUT Port*1
Data Cable	:	N/A
Description of EUT	:	Dimensions : 330 mm (L) X 210 mm (W) X 130 mm (H) Position : ☒ Table-top / ☐ Floor-standing Environment : ☒ First environment / ☐ Second environment Category of Equipment : ☒ C1 ☐ C2 ☐ C3 ☐ C4 Intended Function : The EUT is a UPS. Product Variance : The applicant declares that the difference between the EUT and its product series is as follow: Internal components : Main transformer, battery and fan are different. Function : Different output wattage. The EUT is the most advanced model within the series. HongAn is only responsible for the test result of the main test sample.



1.2 Test Facility

All the Conducted and Radiated Emission Tests and Immunity Tests are performed at No. 15-1, Cweishuh Keng, Cweipin Village, Linkou, New Taipei City, Taiwan, R.O.C.

1.3 Test Instruments

Conducted Emission					
Instrument Name	Manufacture	Model Number	Serial Number	Last Cal. Date	Next Cal. Date
EMI Test Receiver	R&S	ESC17	100931	04-Aug-2021	03-Aug-2022
LISN	EMCO	3810/2NM	9702-1821	25-Jul-2021	24-Jul-2022
LISN	SCHWARZBEC K	NSLK 8127	01021	15-Sep-2021	14-Sep-2022
ISN	TESEQ	ISN T800	49426	15-Sep-2021	14-Sep-2022
ISN	TESEQ	ISN T8-Cat6	50581	16-Sep-2021	15-Sep-2022
RF Current Probe	FCC	F-33-4	53	25-May-2021	24-May-2022
Capacitive Voltage Probe	SCHWARZBEC K	CVP 9222 B	01019	14-Jan-2022	13-Jan-2023
Cable	HongAn	RG 223/U	HA2-CE	20-Aug-2021	19-Aug-2022
Signal Generator	R&S	SMB100A	110549	06-Sep-2021	05-Sep-2022
Software	Audix	e3 (ver 6.101006a)	N/A	N/A	N/A
Software	R&S	Click Rate Analyzer (V2.5.2)	N/A	N/A	N/A
Radiated Emission Test					
Instrument Name	Manufacture	Model Number	Serial Number	Last Cal. Date	Next Cal. Date
EMI Test Receiver	R&S	ESC17	100931	04-Aug-2021	03-Aug-2022
Spectrum Analyzer	R&S	FSV 40	101296	06-Apr-2022	05-Apr-2023
Preamplifier	SCHAFFNER	CPA 9231A	0405	17-Dec-2021	16-Dec-2022
Preamplifier (1-18GHz)	EMCI	EMC051845SE	980692	06-Dec-2021	05-Dec-2022
Preamplifier (18~40GHz)	EMCI	EMC184045SE	980699	05-May-2021	04-May-2022
Loop Antenna	EMCO	6502	9202-2717	06-Sep-2021	05-Sep-2022
Bilog Antenna(3m)	TESEQ	CBL6111D	47016	19-Jul-2021	18-Jul-2022
Bilog Antenna(10m)	TESEQ	CBL6111D	47016	19-Jul-2021	18-Jul-2022
Horn Antenna	EMCO	3115	9912-5992	24-Feb-2022	23-Feb-2023
Horn Antenna	Com-Power	AH-840	101042	21-May-2021	20-May-2022
Cable	HongAn	8D-FB	HA2-10MSite	20-Aug-2021	19-Aug-2022



RF Cable (1~18GHz)	EMCI	EMC104-SM-NM -1000	191104	05-Dec-2021	04-Dec-2022
RF Cable (1~18GHz)	EMCI	EMC104-SM-NM -8000	191103	09-Dec-2021	08-Dec-2022
RF Cable (18~40GHz)	EMCI	EMC102-KM-KM -1000	200301	28-Apr-2021	27-Apr-2022
RF Cable (18~40GHz)	EMCI	EMC102-KM-KM -8000	200213	28-Apr-2021	27-Apr-2022
Signal Generator	R&S	SMB100A	110549	06-Sep-2021	05-Sep-2022
Software	Audix	e3 (ver 6.101006a)	N/A	N/A	N/A

Harmonic Current Emission

Instrument Name	Manufacture	Model Number	Serial Number	Last Cal. Date	Next Cal. Date
Signal conditioning unit	TESEQ	CCN 1000-1	1918A03073	02-Jul-2021	01-Jul-2022
AC Power Source	TESEQ	NSG 1007	1919A00280	02-Jul-2021	01-Jul-2022
Software	TESEQ	CTS4 (Version 4.29.0)	N/A	N/A	N/A

Electrostatic Discharge immunity test

Instrument Name	Manufacture	Model Number	Serial Number	Last Cal. Date	Next Cal. Date
Electrostatic Discharge Simulator	Noiseken	ESS-B3011	ESS1632985	25-Aug-2021	24-Aug-2022
Discharge Gun	Noiseken	GT-30RA	ESS2153540	25-Aug-2021	24-Aug-2022

Radiated, radio-frequency, electromagnetic field immunity test

Instrument Name	Manufacture	Model Number	Serial Number	Last Cal. Date	Next Cal. Date
Signal Generator	R&S	SMB100A	110549	06-Sep-2021	05-Sep-2022
RF Power Amplifier	ar	150W1000	0343919	N/A	N/A
RF Amplifier	ar	15S1G3	306578	N/A	N/A
Dual Directional Coupler	WERLATONE	C6021-10	108038	N/A	N/A
Directional Coupler	ATM	CHPsc22L-40	Q308504-01	N/A	N/A
Power Sensor	TESEQ	PM6003	074395	03-Aug-2021	02-Aug-2022
Power Sensor	TESEQ	PM6003	074396	03-Aug-2021	02-Aug-2022
Bilog Antenna	TESEQ	CBL6111D	58161	12-Jan-2022	11-Jan-2023
Horn Antenna	EMCO	3115	9912-5992	24-Feb-2022	24-Feb-2022
Broadband Field Meter	Narda	NBM-520	D-0519	16-Oct-2021	15-Oct-2022
Probe	Narda	EF-0691	D-0102	16-Oct-2021	15-Oct-2022
Software	Audix	i2 (Ver:20151112c)	N/A	N/A	N/A



Electrical fast transient/burst immunity test					
Instrument Name	Manufacture	Model Number	Serial Number	Last Cal. Date	Next Cal. Date
EMCPro Plus EMC Test System	ThermoFisher	EMC Pro PLUS	1507189	21-May-2021	20-May-2022
Capacitor Clamp	ThermoFisher	CCL	1507182	21-May-2021	20-May-2022
Software	KeyTek	CEWare32 (ver 4.1)	N/A	N/A	N/A
Surge immunity test					
Instrument Name	Manufacture	Model Number	Serial Number	Last Cal. Date	Next Cal. Date
EMCPro Plus EMC Test System	ThermoFisher	EMC Pro PLUS	1507189	22-May-2021	21-May-2022
Software	KeyTek	CEWare32 (ver 4.1)	N/A	N/A	N/A
Immunity to conducted disturbances, induced by radio-frequency fields					
Instrument Name	Manufacture	Model Number	Serial Number	Last Cal. Date	Next Cal. Date
Signal Generator	R&S	SMB100A	110549	06-Sep-2021	05-Sep-2022
Wide Band Amplifier	ifi	CMX50	D019-0200	N/A	N/A
6dB Attenuator	BIRD	50-A-MFN-06	0048	N/A	N/A
Dual Directional Coupler	WERLATONE	C6021-10	108038	N/A	N/A
Power Sensor	TESEQ	PM6003	074395	03-Aug-2021	02-Aug-2022
Power Sensor	TESEQ	PM6003	074396	03-Aug-2021	03-Aug-2022
CDN	FCC	FCC-801-M3-32 A	2019	27-Jan-2022	26-Jan-2023
CDN	FCC	FCC-801-M3-32 A	20116	27-Jan-2022	26-Jan-2023
Software	Audix	i2 (ver 20151112c)	N/A	N/A	N/A
Power frequency magnetic field immunity test					
Instrument Name	Manufacture	Model Number	Serial Number	Last Cal. Date	Next Cal. Date
EMCPro Plus EMC Test System	ThermoFisher	EMC Pro PLUS	1507189	22-May-2021	21-May-2022
Magnetic Field Immunity Loop	ThermoFisher	F-1000-4-8/9/10-L-1M	9953	22-May-2021	21-May-2022
Software	KeyTek	CEWare32 (ver 4.1)	N/A	N/A	N/A

※ The test equipments used are calibrated and can be traced to National ITRI and International Standards.



1.4 Test Methodolgy

All Emission Tests were performed according to the procedures specified in EN IEC 62040-2.

All Immunity Tests were performed according to the procedures specified in EN IEC 62040-2.

Deviations from the test standards as below description : N/A

1.5 Auxiliary Equipments


Provided by HongAn Technology Co., Ltd.

No.	Equipment	Model No.	Serial No.	EMC Approved	Brand	Description	
						Data Cable	Power Cable
1	LAMP*2	200W	N/A	N/A	N/A	N/A	N/A
2	LAMP	100W	N/A	N/A	N/A	N/A	N/A
3	LAMP*2	60W	N/A	N/A	N/A	N/A	N/A
4	LAMP	40W	N/A	N/A	N/A	N/A	N/A
5	Output Cable*3	N/A	N/A	N/A	N/A	N/A	Non-shielded, Detachable, 1.5m, Without Core
6	Power Cable	N/A	N/A	N/A	N/A	N/A	Non-shielded, Detachable, 1.5m, Without Core

Provided by the Manufacturer

No.	Equipment	Model No.	Serial No.	EMC Approved	Brand	Description	
						Data Cable	Power Cable
5	Output Cable*3	N/A	N/A	N/A	N/A	N/A	Non-shielded, Detachable, 1.5m, Without Core

1.6 Block Diagram





1.7 Identifying the Final Test Mode

1. LINE mode (Full load).660W
2. Battery mode (Full load).660W

Note 1: The additional power cords do not increase the disturbance level by 2dB. Therefore the final EMC assessment was performed for the Line mode and Battery mode.

Note 2: The Product Series (BX800CI) test data of please refer to appendix.

1.8 Final Test Mode

1. For Conducted Emission: choosing LINE Mode (Full load) and Battery Mode (Full load).
2. For Radiated Emission: choosing LINE Mode (Full load) and Battery Mode (Full load).
3. For Immunity test: choosing LINE Mode.

1.9 Condition of Power Supply

AC 230V, 50Hz

1.10 EUT Configuration

1. Setup the EUT as shown in Sec.1.6 Block Diagram.
2. Turn on the power of all equipments.
3. Activate the selected Final Test Mode.

1.11 Performance criteria for immunity tests

	Criterion A	Criterion B
External and internal indications and metering	Change only during test	Change only during test
Control signals to external devices	No change	Change only temporarily in consistence with the actual UPS mode of operation
Mode of operation ^a	No change	Change only temporarily
^a At all times, the UPS shall remain within the performance classification as declared by the UPS manufacturer (see EN IEC 62040-2:2018).		

1.11.1 Test Methodology

All Emission Tests were performed according to the procedures specified in EN IEC 62040-2. Radiated Emission Test was performed at 10 m distance from antenna to EUT. All Immunity Tests were performed according to the procedures specified in EN IEC 62040-2.

2 Conducted Emission Test

2.1 Test Instruments

Refer to Sec. 1.2 Test Instruments.

2.2 Test Arrangement and Procedure




Table-top Equipment

- The EUT was placed on a non-conductive table which was 80 cm above the horizontal coupling plane. The rear of the EUT was 40 cm from the vertical coupling plane.
- The excess interface cables were folded at the cable center into a bundle no longer than 40 cm, so that the bundles were on the table.
- The EUT was connected to the main power through a L.I.S.N. This set up provided 50 ohm / 50 μ H coupling impedance for the measuring equipment.
- All auxiliary equipment received power from a second L.I.S.N.
- The conducted emissions were measured between the Line Phase and the PE ground and between the Neutral Phase and the PE ground using an EMI Receiver.
- The values were recorded.



2.3 Conducted Limit

EN IEC 62040-2

Limits of mains terminal and network port disturbance voltage for category C1 and category C2 UPS in the range 0.15 MHz to 30 MHz

Frequency Range (MHz)	Limits dB(μ V)							
	☒ Category C1 UPS				☐ Category C2 UPS			
	Mains terminal		Network port		Mains terminal		Network port	
	Quasi-Peak	Average	Quasi-Peak	Average	Quasi-Peak	Average	Quasi-Peak	Average
0.15 to 0.50 ^b	66 to 56 ^a	56 to 46 ^a	84 to 74 ^a	74 to 64 ^a	79	66	97 to 87 ^a	84 to 74 ^a
0.50 to 5 ^b	56	46	74	64	73	60	87	74
5 to 30	60	50			73	60		
a The limit decreases linearly with the logarithm of the frequency.								
b The lower limit shall apply at the transition frequency.								

Limits of mains terminal and network port disturbance voltage for category C3 UPS in the frequency range 0.15 MHz to 30 MHz

UPS rated output current A	Frequency range (MHz)	Limits dB(μ V)			
		Mains terminal		Network port	
		Quasi-Peak	Average	Quasi-Peak	Average
>16 - 100	0.15 to 0.50 ^b	100	90	110 to 100 ^a	94 to 84 ^a
	0.50 to 5.0 ^b	86	76	100	84
	5.0 to 30.0	90 to 73 ^a	80 to 60 ^a		
>100	0.15 to 0.50 ^b	130	120	110 to 100 ^a	94 to 84 ^a
	0.50 to 5.0 ^b	125	115	100	84
	5.0 to 30.0	115	105		
a The limit decreases linearly with the logarithm of the frequency.					
b The lower limit shall apply at the transition frequency.					

2.4 Test Result


PASS

The final test data are shown on the following page(s).

**Conducted Emission Test Data (at Mains Terminal)**

Test Site : HA2
Model Number : BX1100CI
Power phase : LINE
Test Voltage : 230V/50Hz
Description : LINE mode

Test Date : 03-May-2022
Temperature : 26°C
Humidity : 57%RH
Test by : M.S. Shi




Remark : 1. All readings are Quasi-Peak and Average values.
2. Result = Reading + C.F..
3. Margin = Result – Limit.

**Conducted Emission Test Data (at Mains Terminal)**

Test Site : HA2
Model Number : BX1100CI
Power phase : NEUTRAL
Test Voltage : 230V/50Hz
Description : LINE mode

Test Date : 03-May-2022
Temperature : 26°C
Humidity : 57%RH
Test by : M.S. Shi




No.	Freq MHz	Reading dBuV	C.F dB	Result dBuV	Limit dBuV	Margin dB	Power Line	Remark
1	0.159	34.46	0.08	34.54	55.52	-20.98	NEUTRAL	Average
2	0.159	39.12	0.08	39.20	65.52	-26.32	NEUTRAL	QP
3	0.239	32.41	0.08	32.49	52.13	-19.64	NEUTRAL	Average
4	0.239	36.86	0.08	36.94	62.13	-25.19	NEUTRAL	QP
5	1.043	39.23	0.15	39.38	46.00	-6.62	NEUTRAL	Average
6	1.043	42.92	0.15	43.07	56.00	-12.93	NEUTRAL	QP
7	1.577	28.03	0.18	28.21	46.00	-17.79	NEUTRAL	Average
8	1.577	31.90	0.18	32.08	56.00	-23.92	NEUTRAL	QP
9	2.001	17.95	0.19	18.14	46.00	-27.86	NEUTRAL	Average
10	2.001	27.52	0.19	27.71	56.00	-28.29	NEUTRAL	QP
11	9.603	11.60	0.63	12.23	50.00	-37.77	NEUTRAL	Average
12	9.603	25.50	0.63	26.13	60.00	-33.87	NEUTRAL	QP

Remark : 1. All readings are Quasi-Peak and Average values.
2. Result = Reading + C.F..
3. Margin = Result – Limit.

**Conducted Emission Test Data (at Mains Terminal)**

Test Site : HA2
 Model Number : BX1100CI
 Power phase : LINE
 Test Voltage : 0V
 Description : Battery mode

Test Date : 03-May-2022
 Temperature : 26°C
 Humidity : 57%RH
 Test by : M.S. Shi



No.	Freq MHz	Reading dBμV	C.F dB	Result dBμV	Limit dBμV	Margin dB	Power Line	Remark
1	0.327	15.28	0.09	15.37	49.53	-34.16	LINE	Average
2	0.327	42.34	0.09	42.43	59.53	-17.10	LINE	QP
3	0.404	14.93	0.09	15.02	47.77	-32.75	LINE	Average
4	0.404	40.92	0.09	41.01	57.77	-16.76	LINE	QP
5	0.675	15.34	0.11	15.45	46.00	-30.55	LINE	Average
6	0.675	34.21	0.11	34.32	56.00	-21.68	LINE	QP
7	2.225	13.22	0.19	13.41	46.00	-32.59	LINE	Average
8	2.225	32.75	0.19	32.94	56.00	-23.06	LINE	QP
9	5.166	12.26	0.38	12.64	50.00	-37.36	LINE	Average
10	5.166	33.86	0.38	34.24	60.00	-25.76	LINE	QP
11	19.740	11.94	0.89	12.83	50.00	-37.17	LINE	Average
12	19.740	41.02	0.89	41.91	60.00	-18.09	LINE	QP

Remark : 1. All readings are Quasi-Peak and Average values.


2. Result = Reading + C.F..

3. Margin = Result – Limit.

**Conducted Emission Test Data (at Mains Terminal)**

Test Site : HA2
Model Number : BX1100CI
Power phase : NEUTRAL
Test Voltage : 0V
Description : Battery mode

Test Date : 03-May-2022
Temperature : 26°C
Humidity : 57%RH
Test by : M.S. Shi



No.	Freq MHz	Reading dBuV	C.F dB	Result dBuV	Limit dBuV	Margin dB	Power Line	Remark
1	0.280	18.05	0.09	18.14	50.81	-32.67	NEUTRAL	Average
2	0.280	49.20	0.09	49.29	60.81	-11.52	NEUTRAL	QP
3	0.329	16.53	0.09	16.62	49.49	-32.87	NEUTRAL	Average
4	0.329	50.55	0.09	50.64	59.49	-8.85	NEUTRAL	QP
5	0.375	17.74	0.09	17.83	48.39	-30.56	NEUTRAL	Average
6	0.375	48.67	0.09	48.76	58.39	-9.63	NEUTRAL	QP
7	0.683	14.76	0.12	14.88	46.00	-31.12	NEUTRAL	Average
8	0.683	42.17	0.12	42.29	56.00	-13.71	NEUTRAL	QP
9	2.346	14.09	0.20	14.29	46.00	-31.71	NEUTRAL	Average
10	2.346	42.51	0.20	42.71	56.00	-13.29	NEUTRAL	QP
11	17.383	14.92	0.82	15.74	50.00	-34.26	NEUTRAL	Average
12	17.383	42.69	0.82	43.51	60.00	-16.49	NEUTRAL	QP

Remark : 1. All readings are Quasi-Peak and Average values.
2. Result = Reading + C.F..
3. Margin = Result – Limit.



3 Radiated Emission Test

3.1 Test Instruments

Refer to Sec. 1.2 Test Instruments.

3.2 Test Arrangement and Procedure




Table-top Equipment

- The EUT was placed on a non-conductive turntable which was 80 cm above the horizontal ground plane. The EUT was set 10 m away from the receiving antenna that was mounted on a non-conductive mast.
- Main cables draped to the ground plane and were routed to the mains power outlet. The mains power outlet was bonded to and did not protrude above the ground plane.
- The antenna was adjusted between 1 m and 4 m in height above the ground plane and the Antenna-to-EUT azimuth was also varied during the measurements to find the top 6 maximum meter readings within the frequency range limit as indicated in Sec 3.3.
- The radiated emissions were measured when the Antenna-to-EUT polarization was set horizontally and vertically.
- The values were recorded.



3.3 Radiated Limit

☒ EN IEC 62040-2

Frequency Range (MHz)	Quasi-Peak dB(μ V/m)		
	☒ Category C1 UPS	☐ Category C2 UPS	☐ Category C3 UPS
30 to 230 ^a	30	40	50
230 to 1000	37	47	60
^a The lower limit shall apply at the transition frequency.			

3.4 Test Result


PASS

The final test data are shown on the following page(s).

**Radiated Emission Test Data**

Test Site : HA2 10m
Model Number : BX1100CI
Polarization : Horizontal
Test Voltage : 230V/50Hz
Description : LINE mode

Test Date : 04-May-2022
Temperature : 24°C
Humidity : 56%RH
Test by : M.S. Shi




No.	Freq MHz	Reading dBuV	C.F dB/m	Result dBuV/m	Limit dBuV/m	Margin dB	Height cm	Angle deg	Antenna Pol.	Remark
1	30.560	25.81	-5.24	20.57	30.00	-9.43	400	99	HORIZONTAL	QP
2	40.988	28.68	-10.56	18.12	30.00	-11.88	400	151	HORIZONTAL	QP
3	75.446	34.98	-16.71	18.27	30.00	-11.73	400	42	HORIZONTAL	QP
4	113.316	30.63	-12.30	18.33	30.00	-11.67	398	37	HORIZONTAL	QP
5	139.361	32.64	-12.17	20.47	30.00	-9.53	395	180	HORIZONTAL	QP
6	224.519	32.19	-13.49	18.70	30.00	-11.30	391	220	HORIZONTAL	QP

- Remark : 1. All readings are Quasi-Peak values.
2. Result = Reading + C.F..
3. Margin = Result – Limit.

**Radiated Emission Test Data**

Test Site : HA2 10m
Model Number : BX1100CI
Polarization : Vertical
Test Voltage : 230V/50Hz
Description : LINE mode

Test Date : 04-May-2022
Temperature : 24°C
Humidity : 56%RH
Test by : M.S. Shi




No.	Freq MHz	Reading dBuV	C.F dB/m	Result dBuV/m	Limit dBuV/m	Margin dB	Height cm	Angle deg	Antenna Pol.	Remark
1	30.531	27.51	-5.23	22.28	30.00	-7.72	100	96	VERTICAL	QP
2	50.232	35.19	-15.36	19.83	30.00	-10.17	100	150	VERTICAL	QP
3	67.202	38.18	-17.55	20.63	30.00	-9.37	100	120	VERTICAL	QP
4	116.540	30.93	-12.19	18.74	30.00	-11.26	102	34	VERTICAL	QP
5	139.361	34.24	-12.17	22.07	30.00	-7.93	105	78	VERTICAL	QP
6	227.691	32.85	-13.18	19.67	30.00	-10.33	108	210	VERTICAL	QP

Remark : 1. All readings are Quasi-Peak values.
2. Result = Reading + C.F..
3. Margin = Result – Limit.

**Radiated Emission Test Data**

Test Site : HA2 10m
Model Number : BX1100CI
Polarization : Horizontal
Test Voltage : 0V
Description : Battery mode

Test Date : 04-May-2022
Temperature : 24°C
Humidity : 56%RH
Test by : M.S. Shi




Remark : 1. All readings are Quasi-Peak values.
2. Result = Reading + C.F..
3. Margin = Result – Limit.

**Radiated Emission Test Data**

Test Site : HA2 10m
Model Number : BX1100CI
Polarization : Vertical
Test Voltage : 0V
Description : Battery mode

Test Date : 04-May-2022
Temperature : 24°C
Humidity : 56%RH
Test by : M.S. Shi



No.	Freq MHz	Reading dBuV	C.F dB/m	Result dBuV/m	Limit dBuV/m	Margin dB	Height cm	Angle deg	Antenna Pol.	Remark
1	31.955	26.16	-5.83	20.33	30.00	-9.67	100	96	VERTICAL	QP
2	43.202	32.75	-11.52	21.23	30.00	-8.77	100	45	VERTICAL	QP
3	61.995	38.12	-18.14	19.98	30.00	-10.02	100	120	VERTICAL	QP
4	171.995	32.96	-13.96	19.00	30.00	-11.00	103	135	VERTICAL	QP
5	266.609	32.62	-9.13	23.49	37.00	-13.51	105	71	VERTICAL	QP
6	446.414	27.26	-5.94	21.32	37.00	-15.68	135	166	VERTICAL	QP

Remark : 1. All readings are Quasi-Peak values.
2. Result = Reading + C.F..
3. Margin = Result – Limit.




4 Harmonic Current Emission Measurement

4.1 Test Instruments

Refer to Sec. 1.2 Test Instruments.

4.2 Test Configuration and Procedure



- The EUT was set in series with the Power Analyzer through an Impedance Network for the measurement of harmonic currents.
- The supply voltage and frequency setting on the Programmable AC Source was programmed as the rated voltage and frequency of the EUT.
- Classify the EUT class in accordance with the EN IEC 61000-3-2 for the purpose of harmonic current limitation. The measurement was automatically performed by test software. The test result was collected and analyzed by the computer.



4.3 EUT Operation Condition

Environment Condition

Test Site	Test Date	Temperature	Humidity	Atmospheric Pressure
HA3	04-May-2022	26°C	55%RH	1009mbar

4.4 Test Limit

Class A Equipment

Harmonic Order (n)	Maximum permissible harmonic current (A)
Odd harmonics	
3	2.30
5	1.14
7	0.77
9	0.40
11	0.33
13	0.21
$15 \leq n \leq 39$	$0.15 * 15 / n$
Even harmonics	
2	1.08
4	0.43
6	0.30
$8 \leq n \leq 40$	$0.23 * 8 / n$

4.5 Test Result


PASS

The measured result is shown on the following page(s)




Test Result: Pass Source qualification: Normal

Current & voltage waveforms



Harmonics and Class A limit line

European Limits



Test result: Pass Worst harmonics H9-5.8% of 150% limit, H9-8.7% of 100% limit



Test Result: Pass Source qualification: Normal
 THCA: 0.173 I-THD(%): 5.6 POHC(A): 0.007 POHC Limit(A): 0.251

Highest parameter values during test:

V_RMS (Volts): 230.01 Frequency(Hz): 50.00
 I_Peak (Amps): 4.656 I_RMS (Amps): 3.113
 I_Fund (Amps): 3.108 Crest Factor: 1.496
 Power (Watts): 714.8 Power Factor: 0.998

Harm#	Harms(avg)	100%Limit	%of Limit	Harms(max)	150%Limit	%of Limit	Status
2	0.016	1.080	N/A	0.016	1.620	N/A	Pass
3	0.139	2.300	6.1	0.140	3.450	4.1	Pass
4	0.005	0.430	N/A	0.005	0.645	N/A	Pass
5	0.068	1.140	6.0	0.068	1.710	4.0	Pass
6	0.002	0.300	N/A	0.002	0.450	N/A	Pass
7	0.056	0.770	7.3	0.056	1.155	4.9	Pass
8	0.001	0.230	N/A	0.001	0.345	N/A	Pass
9	0.035	0.400	8.7	0.035	0.600	5.8	Pass
10	0.001	0.184	N/A	0.001	0.276	N/A	Pass
11	0.022	0.330	6.6	0.022	0.495	4.4	Pass
12	0.001	0.153	N/A	0.001	0.230	N/A	Pass
13	0.017	0.210	N/A	0.017	0.315	N/A	Pass
14	0.001	0.131	N/A	0.001	0.197	N/A	Pass
15	0.013	0.150	N/A	0.013	0.225	N/A	Pass
16	0.000	0.115	N/A	0.000	0.173	N/A	Pass
17	0.008	0.132	N/A	0.008	0.198	N/A	Pass
18	0.000	0.102	N/A	0.000	0.153	N/A	Pass
19	0.005	0.118	N/A	0.005	0.178	N/A	Pass
20	0.000	0.092	N/A	0.000	0.138	N/A	Pass
21	0.004	0.107	N/A	0.004	0.161	N/A	Pass
22	0.000	0.084	N/A	0.000	0.125	N/A	Pass
23	0.003	0.098	N/A	0.004	0.147	N/A	Pass
24	0.000	0.077	N/A	0.000	0.115	N/A	Pass
25	0.002	0.090	N/A	0.002	0.135	N/A	Pass
26	0.001	0.071	N/A	0.001	0.107	N/A	Pass
27	0.002	0.083	N/A	0.002	0.125	N/A	Pass
28	0.002	0.066	N/A	0.002	0.099	N/A	Pass
29	0.002	0.078	N/A	0.002	0.116	N/A	Pass
30	0.001	0.061	N/A	0.001	0.092	N/A	Pass
31	0.002	0.073	N/A	0.002	0.109	N/A	Pass
32	0.002	0.058	N/A	0.002	0.086	N/A	Pass
33	0.001	0.068	N/A	0.001	0.102	N/A	Pass
34	0.001	0.054	N/A	0.001	0.081	N/A	Pass
35	0.001	0.064	N/A	0.001	0.096	N/A	Pass
36	0.000	0.051	N/A	0.000	0.077	N/A	Pass
37	0.001	0.061	N/A	0.001	0.091	N/A	Pass
38	0.000	0.048	N/A	0.000	0.073	N/A	Pass
39	0.001	0.058	N/A	0.001	0.087	N/A	Pass
40	0.000	0.046	N/A	0.000	0.069	N/A	Pass

※Harmonic currents less than 0,6 % of the input current measured under the test conditions, or less than 5 mA, whichever is greater, are disregarded.

5 Electrostatic Discharge Immunity Test

5.1 Test Instruments

Refer to Sec. 1.2 Test Instruments.

5.2 Test Configuration and Procedure




Table-top Equipment

- The EUT was located on a 0.8 m high wooden table standing on the ground reference plane with a 1.6 * 0.8 m horizontal coupling plane on the top. The EUT and cables was isolated from the coupling plane by an insulating support 0.5 mm thick.
- In Contact Discharge, the EUT was exposed to minimum 200 discharges, 100 each at negative and positive polarity on the selected test points (the selected test points were marked with red labels on the EUT)
- In Air Discharge, the EUT exposed to minimum of 10 single discharges on the selected test points.
- The result was observed and analyzed.



5.3 Test Result

5.3.1 Environment Condition

Test Site	Test Date	Temperature	Humidity	Atmospheric Pressure
HA3	04-May-2022	26°C	55%RH	1009mbar

5.3.2 Observation of Direct Discharge

Test Points: 1. Surface of Case. 2. Junction of Case. 3. Screw.

Type of Discharge	Test Specifications				Performance Required by EN IEC 62040-2	Observed Result	Verdict
	Test Level	Polarity	Test Point	Number of Discharge			
Air Discharge	2,4,8 (kV)	±	1~2	10/ per point	B	A	Pass ¹
Contact Discharge	4 (kV)	±	3	10/ per point	B	A	Pass ²
Remarks	1. No temporary degradation or loss of function has been observed throughout the entire time interval of air discharge. 2. No temporary degradation or loss of function has been observed throughout the entire time interval of contact discharge.						
Note	The selected points were marked with red labels on the EUT.						

The Performance Requirement Class Criterion is defined in Sec. 1.11.

5.3.3 Observation of Indirect Discharge

Test Points: 1. Front Side. 2. Rear Side. 3. Left Side. 4. Right Side.

Type of Discharge	Test Specifications				Performance Required by EN IEC 62040-2	Observed Result	Verdict
	Test Level	Polarity	Test Point	Number of Discharge			
HCP Application	4 (kV)	±	1~4	10/ per point	B	A	Pass ¹
VCP Application	4 (kV)	±	1~4	10/ per point	B	A	Pass ²
Remarks	1. No temporary degradation or loss of function has been observed throughout the entire time interval of HCP application. 2. No temporary degradation or loss of function has been observed throughout the entire time interval of VCP application.						
Note	The selected points were marked with red labels on the EUT.						

The Performance Requirement Class Criterion is defined in Sec. 1.11.

PASS

The test result shows that the EUT is in compliance with the test performance criteria specified in EN IEC 62040-2.



6 Radio-frequency, Electromagnetic Field Immunity Test

6.1 Test Instruments

Refer to Sec. 1.2 Test Instruments.

6.2 Test Configuration and Procedure




Table-top Equipment

- The field calibration was executed to create a uniform field area (UFA), 3 m away from the antenna, to ensure the validity of the test results.
- The EUT was placed on a non-conductive table 0.8 m high in the UFA.
- The EUT was then connected to power and signal wires according to relevant installation instruction.
- The EUT was positioned so that the four sides of the EUT were exposed to the electromagnetic field in sequence. In each position, the performance of the EUT was investigated and monitored by a CCD camera.



6.3 Test Result

6.3.1 Environment Condition

Test Site	Test Date	Temperature	Humidity	Atmospheric Pressure
HA3	04-May-2022	26°C	55%RH	1009mbar

6.3.2 Observation of Test

Type of Modulation	Test Specifications				Performance Required by EN IEC 62040-2	Observed Result	Verdict
	Field Strength	Frequency Range	Modulated	Polarity			
Amplitude Modulation	3 V/m	80 to 1000MHz	1kHz, 80% AM, Sine wave	V&H	A	A	Pass ¹
Remark	1. No temporary degradation or loss of function has been observed throughout the entire test.						
Note	The applied 0°, 90°, 180°, 270° relative to the position to the equipment under test.						

The Performance Requirement Class Criterion is defined in Sec. 1.11.

PASS

The test result shows that the EUT is in compliance with the test performance criteria specified in EN IEC 62040-2.



7 Electrical Fast Transient Test

7.1 Test Instrument

Refer to Sec. 1.2 Test Instruments.

7.2 Test Configuration and Procedure




Table-top Equipment

- The EUT was placed on a table of 0.8 m height above the 1 * 1 m metallic ground reference plane, which projected beyond the EUT by at least 0.1 m on all sides.
- The ground plane was connected to the protective earth.
- The distance between the EUT and all other conductive structures, except the ground plane beneath the EUT was more than 0.5 m.
- The length of the signal and power lines between the coupling device and the EUT was 0.5 m.
- All cables to the EUT were placed on the insulation support 0.1 m above the ground reference plane.
- The EUT was connected to the power mains through a coupling device that directly coupled the EFT interference signal. Each of the Line, Neutral and Protective Earth conductors was injected with burst for 1 minute. The test time was broken down into six 10 s bursts separated by a 10 s pause for avoiding synchronization. Both voltage polarities were applied for each test level.
- Operating condition was shown on the monitor and observed.



7.3 Test Result

7.3.1 Environment Condition

Test Site	Test Date	Temperature	Humidity	Atmospheric Pressure
HA3	04-May-2022	26°C	55%RH	1009mbar

7.3.2 Observation of Power Supply Port

Coupling Selection	Test Specifications				Performance Required by EN IEC 62040-2	Observed Result	Verdict
	Voltage (kV)	Test Duration (Sec)	Repetition Frequency (kHz)	Tr/ Th (nS)			
L	±1	60	5	5/50	B	A	Pass ¹
N	±1	60	5	5/50	B	A	Pass ¹
PE	±1	60	5	5/50	B	A	Pass ¹
L + N	±1	60	5	5/50	B	A	Pass ¹
L + PE	±1	60	5	5/50	B	A	Pass ¹
N + PE	±1	60	5	5/50	B	A	Pass ¹
L + N +PE	±1	60	5	5/50	B	A	Pass ¹
Remark	1. No temporary degradation or loss of function has been observed throughout the entire test.						

The Performance Requirement Class Criterion is defined in Sec. 1.11.

PASS

The test result shows that the EUT is in compliance with the test performance criteria specified in EN IEC 62040-2.



8 Surge Immunity Test

8.1 Test Instrument

Refer to Sec. 1.2 Test Instruments.

8.2 Test Configuration and Procedure




Table-top Equipment

- The EUT was placed on a table of 0.8 m height above the 1 * 1 m metallic ground reference plane, which projected beyond the EUT by at least 0.1 m on all sides.
- The ground plane was connected to the protective earth.
- The length of power cord between the coupling device and the EUT is less than 2 m (provided by the manufacturer).
- The EUT was connected to the power mains through a coupling device that directly couples the Surge interference signal. The surge noise was applied synchronized to the voltage phase at the zero crossing and the peak value of the AC voltage wave (positive and negative).
- The surges were applied line to line and line(s) to earth. When testing line to earth the test voltage was applied successively between each of the lines and earth. Steps up to the test level specified increased the test voltage. All lower levels including the selected test level were tested. The polarity of each surge level included positive and negative test pulses.
- Operating condition was shown on the monitor and observed.



8.3 Test Result

8.3.1 Environment Condition

Test Site	Test Date	Temperature	Humidity	Atmospheric Pressure
HA3	04-May-2022	26°C	55%RH	1009mbar

8.3.2 Observation of Power Supply Port

Coupling Selection	Test Specifications			Performance Required by EN IEC 62040-2	Observed Result	Verdict
	Voltage (kV)	Min. of Surge at Each Polarity	Repetition Rate (per min)			
L ► N	±0.5, 1	5	1	B	A	Pass ¹
L ► PE	±0.5, 1, 2	5	1	B	A	Pass ¹
N ► PE	±0.5, 1, 2	5	1	B	A	Pass ¹
Remark	1. No temporary degradation or loss of function has been observed throughout the entire test.					

The Performance Requirement Class Criterion is defined in Sec. 1.11.

8.3.3 Observation of other supply/ signal lines: (Applicable only to ports which according to the manufacturer's specification may connect directly to outdoor cables)

N/A

PASS


The test result shows that the EUT is in compliance with the test performance criteria specified in EN IEC 62040-2.

9 Radio-frequency, Conducted Disturbances Immunity Test

9.1 Test Instruments

Refer to Sec. 1.2 Test Instruments.

9.2 Test Configuration and Procedure



- The EUT was placed on an insulating support of 0.1 m height above a ground reference plane. All cables exiting the EUT was supported at a height of 30 mm above the ground reference plane.
- The EUT was connected to the power mains through a Coupling and Decoupling Networks (CDN).
- The CDN was located 0.3 m from the EUT as indicated in the diagram above.
- The test was performed with the test generator connected to each of the CDN in turn while the other non-excited RF input ports of the coupling devices were terminated by a 50Ω terminator.
- The conducted disturbance was applied on the EUT from 150 kHz to 80 MHz using the signal levels established during the setting process. .
- Operating condition was shown on the monitor and observed.



9.3 Test Result

9.3.1 Environment Condition

Test Site	Test Date	Temperature	Humidity	Atmospheric Pressure
HA3	04-May-2022	26°C	55%RH	1009mbar

9.3.2 Observation of Test

Type of Modulation	Test Specifications			Performance Required by EN IEC 62040-2	Observed Result	Verdict
	Voltage Level (emf) U_0	Frequency Range	Modulation			
Amplitude Modulation	3V / 130dB μ V	0.15 to 80MHz	80%, 1kHz, sinusoidal	A	A	Pass ¹
Remark	1. No temporary degradation or loss of function has been observed throughout the entire test.					

The Performance Requirement Class Criterion is defined in Sec. 1.11.

PASS

The test result shows that the EUT is in compliance with the test performance criteria specified in EN IEC 62040-2.



10 Power Frequency Magnetic Field Immunity Test

10.1 Test Instruments

Refer to Sec. 1.2 Test Instruments.

10.2 Test Configuration and Procedure




Table-top Equipment

- The EUT was placed on a non-magnetic metal ground plane of 0.25 mm thickness with the interposition of a 0.1 m thickness insulating support. The ground plane was connected to the protected earth.
- The EUT was placed at the center of the 1 * 1 m induction coil with the test generator placed within 3 m distance.
- The test was operated by moving and shifting the induction coil to expose to the test field.
- The operation condition was observed and analyzed.
- The induction coil was then rotated by 90° to expose the EUT to the test field with different orientations and the same procedure.



10.3 Test Result

10.3.1 Environment Condition

Test Site	Test Date	Temperature	Humidity	Atmospheric Pressure
HA3	04-May-2022	26°C	55%RH	1009mbar

10.3.2 Observation of Test

Level (A/m)	Frequency (Hz)	Performance Required by EN IEC 62040-2	Observed Result	Verdict
3	50	B	A	Pass ¹
Remark:	1. No temporary degradation or loss of function has been observed throughout the entire test.			

The Performance Requirement Class Criterion is defined in Sec. 1.11.

PASS

The test result shows that the EUT is in compliance with the test performance criteria specified in EN IEC 62040-2.




11 Low Frequency Signals Immunity Test

11.1 Test Instrument

Refer to Sec. 1.2 Test Instruments.

11.2 Test Configuration and Procedure



- Let U.P.S. to be under charging and line status
- Adjust programmable AC source to output a 10Vrms (sine wave from 140 to 360Hz) that can be induced 10Vrms to link between AC source and UPS (through the isolation transformer).
- The induced signals shall mixed in normal AC source and U.P.S. shall withstand it and no performances shall be reduced

11.3 Test Result

11.3.1 Environment Condition

Test Site	Test Date	Temperature	Humidity	Atmospheric Pressure
HA3	04-May-2022	26°C	55%RH	1009mbar

11.3.2 Observation

Frequency Range (Hz)	Strength	Required by EN IEC 62040-2	Observed Result	Verdict
140 to 360	10V (rms) Sinusoidal	A	A	Pass ¹
Remark: 1. No temporary degradation or loss of function has been observed throughout the entire test.				

The Performance Requirement Class Criterion is defined in Sec. 1.11.


PASS

The test result shows that the EUT is in compliance with the test performance criteria specified in EN IEC 62040-2.




12 Photographs of Test

12.1 Power Line Conducted Test



Front View



Rear View



12.2 Radiated Emission Test



Front View




Rear View



12.3 Harmonic Current Measurement



12.4 Electrostatic Discharge Immunity Test





12.5 Radio-frequency, Electromagnetic Field Immunity Test



12.6 Electrical Fast Transient / Burst Immunity Test





12.7 Surge Immunity Test



12.8 Radio-frequency, Conducted Disturbances Immunity Test





12.9 Power Frequency Magnetic Field Immunity Test





13 Photographs of EUT



Front View of the EUT



Rear View of the EUT




View of the I/O Port



Inside View of the EUT




Front View of the PCB 1



Rear View of the PCB 1



Front View of the PCB 2



Rear View of the PCB 2



View of the Transformer



View of the Battery



View of the Output Cable*3



Front View of the EUT (Product Series : BX800CI)



Rear View of the EUT (Product Series : BX800CI)



View of the I/O Port (Product Series : BX800CI)



14 Photographs of ESD Test Points



View of ESD Test Points



View of ESD Test Points




15 Appendix

15.1 Conducted Emission Test

Conducted Emission Test Data (at Mains Terminal)

Test Site : HA2
Model Number : BX800CI
Power phase : LINE
Test Voltage : 230V/50Hz
Description : LINE mode
Test Date : 03-May-2022
Temperature : 26°C
Humidity : 57%RH
Test by : M.S. Shi



Remark : 1. All readings are Quasi-Peak and Average values.


2. Result = Reading + C.F..

3. Margin = Result – Limit.

**Conducted Emission Test Data (at Mains Terminal)**

Test Site : HA2
Model Number : BX800CI
Power phase : NEUTRAL
Test Voltage : 230V/50Hz
Description : LINE mode

Test Date : 03-May-2022
Temperature : 26°C
Humidity : 57%RH
Test by : M.S. Shi




No.	Freq MHz	Reading dBuV	C.F dB	Result dBuV	Limit dBuV	Margin dB	Power Line	Remark
1	0.159	23.90	0.08	23.98	55.52	-31.54	NEUTRAL	Average
2	0.159	28.05	0.08	28.13	65.52	-37.39	NEUTRAL	QP
3	0.201	24.97	0.08	25.05	53.58	-28.53	NEUTRAL	Average
4	0.201	29.30	0.08	29.38	63.58	-34.20	NEUTRAL	QP
5	0.844	19.70	0.13	19.83	46.00	-26.17	NEUTRAL	Average
6	0.844	27.07	0.13	27.20	56.00	-28.80	NEUTRAL	QP
7	1.544	23.82	0.18	24.00	46.00	-22.00	NEUTRAL	Average
8	1.544	26.46	0.18	26.64	56.00	-29.36	NEUTRAL	QP
9	1.939	19.08	0.19	19.27	46.00	-26.73	NEUTRAL	Average
10	1.939	27.34	0.19	27.53	56.00	-28.47	NEUTRAL	QP
11	14.517	10.81	0.74	11.55	50.00	-38.45	NEUTRAL	Average
12	14.517	21.86	0.74	22.60	60.00	-37.40	NEUTRAL	QP

Remark : 1. All readings are Quasi-Peak and Average values.
2. Result = Reading + C.F..
3. Margin = Result – Limit.

**Conducted Emission Test Data (at Mains Terminal)**

Test Site : HA2
Model Number : BX800CI
Power phase : LINE
Test Voltage : 0V
Description : Battery mode

Test Date : 03-May-2022
Temperature : 26°C
Humidity : 57%RH
Test by : M.S. Shi




No.	Freq MHz	Reading dBuV	C.F dB	Result dBuV	Limit dBuV	Margin dB	Power Line	Remark
1	0.259	18.33	0.09	18.42	51.47	-33.05	LINE	Average
2	0.259	47.16	0.09	47.25	61.47	-14.22	LINE	QP
3	0.419	17.45	0.09	17.54	47.46	-29.92	LINE	Average
4	0.419	50.10	0.09	50.19	57.46	-7.27	LINE	QP
5	0.513	15.56	0.10	15.66	46.00	-30.34	LINE	Average
6	0.513	47.15	0.10	47.25	56.00	-8.75	LINE	QP
7	1.249	9.36	0.15	9.51	46.00	-36.49	LINE	Average
8	1.249	37.03	0.15	37.18	56.00	-18.82	LINE	QP
9	2.213	12.65	0.19	12.84	46.00	-33.16	LINE	Average
10	2.213	29.96	0.19	30.15	56.00	-25.85	LINE	QP
11	23.636	10.57	0.93	11.50	50.00	-38.50	LINE	Average
12	23.636	28.30	0.93	29.23	60.00	-30.77	LINE	QP

Remark : 1. All readings are Quasi-Peak and Average values.
2. Result = Reading + C.F..
3. Margin = Result – Limit.

**Conducted Emission Test Data (at Mains Terminal)**

Test Site : HA2
Model Number : BX800CI
Power phase : NEUTRAL
Test Voltage : 0V
Description : Battery mode

Test Date : 03-May-2022
Temperature : 26°C
Humidity : 57%RH
Test by : M.S. Shi



No.	Freq MHz	Reading dBμV	C.F dB	Result dBμV	Limit dBμV	Margin dB	Power Line	Remark
1	0.282	18.24	0.09	18.33	50.76	-32.43	NEUTRAL	Average
2	0.282	46.88	0.09	46.97	60.76	-13.79	NEUTRAL	QP
3	0.383	19.44	0.09	19.53	48.21	-28.68	NEUTRAL	Average
4	0.383	50.90	0.09	50.99	58.21	-7.22	NEUTRAL	QP
5	0.435	18.50	0.09	18.59	47.15	-28.56	NEUTRAL	Average
6	0.435	50.15	0.09	50.24	57.15	-6.91	NEUTRAL	QP
7	1.077	9.16	0.15	9.31	46.00	-36.69	NEUTRAL	Average
8	1.077	36.94	0.15	37.09	56.00	-18.91	NEUTRAL	QP
9	7.252	10.66	0.52	11.18	50.00	-38.82	NEUTRAL	Average
10	7.252	24.53	0.52	25.05	60.00	-34.95	NEUTRAL	QP
11	22.655	8.45	0.92	9.37	50.00	-40.63	NEUTRAL	Average
12	22.655	22.59	0.92	23.51	60.00	-36.49	NEUTRAL	QP


Remark : 1. All readings are Quasi-Peak and Average values.
2. Result = Reading + C.F..
3. Margin = Result – Limit.



15.2 Radiated Emission Test

Radiated Emission Test Data

Test Site : HA2 10m
Model Number : BX800CI
Polarization : Horizontal
Test Voltage : 230V/50Hz
Description : LINE mode
Test Date : 04-May-2022
Temperature : 24°C
Humidity : 56%RH
Test by : M.S. Shi



Remark : 1. All readings are Quasi-Peak values.


2. Result = Reading + C.F..

3. Margin = Result – Limit.

**Radiated Emission Test Data**

Test Site : HA2 10m
Model Number : BX800CI
Polarization : Vertical
Test Voltage : 230V/50Hz
Description : LINE mode

Test Date : 04-May-2022
Temperature : 24°C
Humidity : 56%RH
Test by : M.S. Shi




No.	Freq MHz	Reading dBuV	C.F dB/m	Result dBuV/m	Limit dBuV/m	Margin dB	Height cm	Angle deg	Antenna Pol.	Remark
1	30.853	26.28	-5.39	20.89	30.00	-9.11	100	198	VERTICAL	QP
2	53.693	35.15	-16.84	18.31	30.00	-11.69	100	74	VERTICAL	QP
3	78.413	32.30	-16.36	15.94	30.00	-14.06	100	65	VERTICAL	QP
4	119.436	31.38	-12.11	19.27	30.00	-10.73	103	38	VERTICAL	QP
5	180.649	29.94	-14.51	15.43	30.00	-14.57	105	150	VERTICAL	QP
6	203.523	32.55	-14.03	18.52	30.00	-11.48	108	162	VERTICAL	QP

Remark : 1. All readings are Quasi-Peak values.
2. Result = Reading + C.F..
3. Margin = Result – Limit.

**Radiated Emission Test Data**

Test Site : HA2 10m
Model Number : BX800CI
Polarization : Horizontal
Test Voltage : 0V
Description : Battery mode

Test Date : 04-May-2022
Temperature : 24°C
Humidity : 56%RH
Test by : M.S. Shi




No.	Freq MHz	Reading dBuV	C.F dB/m	Result dBuV/m	Limit dBuV/m	Margin dB	Height cm	Angle deg	Antenna Pol.	Remark
1	30.853	24.62	-5.39	19.23	30.00	-10.77	400	47	HORIZONTAL	QP
2	75.977	36.23	-16.65	19.58	30.00	-10.42	400	63	HORIZONTAL	QP
3	127.665	28.16	-11.98	16.18	30.00	-13.82	398	158	HORIZONTAL	QP
4	175.037	29.86	-14.16	15.70	30.00	-14.30	395	190	HORIZONTAL	QP
5	229.293	30.17	-13.02	17.15	30.00	-12.85	391	22	HORIZONTAL	QP
6	301.422	28.74	-9.89	18.85	37.00	-18.15	384	100	HORIZONTAL	QP

Remark : 1. All readings are Quasi-Peak values.
2. Result = Reading + C.F..
3. Margin = Result – Limit.

**Radiated Emission Test Data**

Test Site : HA2 10m
Model Number : BX800CI
Polarization : Vertical
Test Voltage : 0V
Description : Battery mode

Test Date : 04-May-2022
Temperature : 24°C
Humidity : 56%RH
Test by : M.S. Shi



No.	Freq MHz	Reading dBμV	C.F dB/m	Result dBμV/m	Limit dBμV/m	Margin dB	Height cm	Angle deg	Antenna Pol.	Remark
1	30.531	24.79	-5.23	19.56	30.00	-10.44	100	85	VERTICAL	QP
2	46.995	31.99	-13.69	18.30	30.00	-11.70	100	99	VERTICAL	QP
3	74.919	35.53	-16.78	18.75	30.00	-11.25	100	210	VERTICAL	QP
4	144.335	29.06	-12.35	16.71	30.00	-13.29	103	173	VERTICAL	QP
5	182.559	33.36	-14.54	18.82	30.00	-11.18	105	65	VERTICAL	QP
6	329.039	27.29	-9.38	17.91	37.00	-19.09	114	51	VERTICAL	QP

Remark : 1. All readings are Quasi-Peak values.
2. Result = Reading + C.F..
3. Margin = Result – Limit.