

Modicon TM3

Digital I/O Modules

Hardware Guide

EIO0000003125.05
06/2024



Legal Information

The information provided in this document contains general descriptions, technical characteristics and/or recommendations related to products/solutions.

This document is not intended as a substitute for a detailed study or operational and site-specific development or schematic plan. It is not to be used for determining suitability or reliability of the products/solutions for specific user applications. It is the duty of any such user to perform or have any professional expert of its choice (integrator, specifier or the like) perform the appropriate and comprehensive risk analysis, evaluation and testing of the products/solutions with respect to the relevant specific application or use thereof.

The Schneider Electric brand and any trademarks of Schneider Electric SE and its subsidiaries referred to in this document are the property of Schneider Electric SE or its subsidiaries. All other brands may be trademarks of their respective owner.

This document and its content are protected under applicable copyright laws and provided for informative use only. No part of this document may be reproduced or transmitted in any form or by any means (electronic, mechanical, photocopying, recording, or otherwise), for any purpose, without the prior written permission of Schneider Electric.

Schneider Electric does not grant any right or license for commercial use of the document or its content, except for a non-exclusive and personal license to consult it on an "as is" basis.

Schneider Electric reserves the right to make changes or updates with respect to or in the content of this document or the format thereof, at any time without notice.

To the extent permitted by applicable law, no responsibility or liability is assumed by Schneider Electric and its subsidiaries for any errors or omissions in the informational content of this document, as well as any non-intended use or misuse of the content thereof.

Table of Contents

Safety Information	7
Qualification of Personnel	7
Intended Use	8
About the Book	9
TM3 Digital I/O Modules General Overview	15
TM3 Digital I/O Modules Description	16
General Description	16
Physical Description	20
Accessories	22
TM3 Digital I/O Modules Installation	25
TM3 Digital I/O Modules General Rules for Implementing	25
Environmental Characteristics	25
Certifications and Standards	27
TM3 Digital I/O Modules Installation	28
Installation and Maintenance Requirements	28
Installation Guidelines	29
Top Hat Section Rail (DIN rail)	31
Assembling a Module to a Controller or Receiver Module	33
Disassembling a Module from a Controller or Receiver Module	34
Direct Mounting on a Panel Surface	35
TM3 Digital I/O Modules Electrical Requirements	36
Wiring Best Practices	36
DC Power Supply Characteristics	41
Grounding the TM3 Digital I/O Modules	42
TM3 Digital Input Modules	44
TM3DI8A Module 8 Inputs 120 Vac	45
TM3DI8A Presentation	45
TM3DI8A Characteristics	46
TM3DI8A Wiring Diagram	48
TM3DI8 / TM3DI8G Module 8 Regular Inputs 24 Vdc	49
TM3DI8 / TM3DI8G Presentation	49
TM3DI8 / TM3DI8G Characteristics	51
TM3DI8 / TM3DI8G Wiring Diagram	53
TM3DI16 / TM3DI16G Module 16 Regular Inputs 24 Vdc	54
TM3DI16 / TM3DI16G Presentation	54
TM3DI16 / TM3DI16G Characteristics	56
TM3DI16 / TM3DI16G Wiring Diagram	59
TM3DI16K Module 16 Regular Inputs 24 Vdc	60
TM3DI16K Presentation	60
TM3DI16K Characteristics	62
TM3DI16K Wiring Diagram	65
TM3DI32K Module 32 Regular Inputs 24 Vdc	66
TM3DI32K Presentation	66
TM3DI32K Characteristics	68
TM3DI32K Wiring Diagram	71
TM3 Digital Output Modules	72

TM3DQ8R / TM3DQ8RG Module 8 Relay Outputs 2A 24 Vdc/240 Vac.....	73
TM3DQ8R / TM3DQ8RG Presentation	73
TM3DQ8R / TM3DQ8RG Characteristics.....	75
TM3DQ8R / TM3DQ8RG Wiring Diagram.....	78
TM3DQ8T / TM3DQ8TG Module 8 Regular Transistor Source Outputs 0.5A 24 Vdc	79
TM3DQ8T / TM3DQ8TG Presentation.....	79
TM3DQ8T / TM3DQ8TG Characteristics	81
TM3DQ8T / TM3DQ8TG Wiring Diagram.....	83
TM3DQ8U / TM3DQ8UG Module 8 Regular Transistor Sink Outputs 0.5A 24 Vdc.....	84
TM3DQ8U / TM3DQ8UG Presentation	84
TM3DQ8U / TM3DQ8UG Characteristics.....	86
TM3DQ8U / TM3DQ8UG Wiring Diagram.....	88
TM3DQ16R / TM3DQ16RG Module 16 Relay Outputs 2A 24 Vdc/240 Vac.....	89
TM3DQ16R / TM3DQ16RG Presentation	89
TM3DQ16R / TM3DQ16RG Characteristics.....	91
TM3DQ16R / TM3DQ16RG Wiring Diagram	94
TM3DQ16T / TM3DQ16TG Module 16 Regular Transistor Source Outputs 0.5A 24 Vdc.....	95
TM3DQ16T / TM3DQ16TG Presentation	95
TM3DQ16T / TM3DQ16TG Characteristics.....	97
TM3DQ16T / TM3DQ16TG Wiring Diagram.....	99
TM3DQ16TK Module 16 Regular Transistor Source Outputs 0.1A 24 Vdc.....	100
TM3DQ16TK Presentation	100
TM3DQ16TK Characteristics	102
TM3DQ16TK Wiring Diagram	104
TM3DQ16U / TM3DQ16UG Module 16 Regular Transistor Sink Outputs 0.5A 24 Vdc	105
TM3DQ16U / TM3DQ16UG Presentation	105
TM3DQ16U / TM3DQ16UG Characteristics.....	107
TM3DQ16U / TM3DQ16UG Wiring Diagram	109
TM3DQ16UK Module 16 Regular Transistor Sink Outputs 0.1A 24 Vdc.....	110
TM3DQ16UK Presentation	110
TM3DQ16UK Characteristics.....	112
TM3DQ16UK Wiring Diagram.....	114
TM3DQ32TK Module 32 Regular Transistor Outputs 0.1A 24 Vdc.....	115
TM3DQ32TK Presentation	115
TM3DQ32TK Characteristics	117
TM3DQ32TK Wiring Diagram	119
TM3DQ32UK Module 32 Regular Transistor Outputs 0.1A 24 Vdc.....	120
TM3DQ32UK Presentation	120
TM3DQ32UK Characteristics.....	122
TM3DQ32UK Wiring Diagram.....	123
TM3 Digital Mixed Input/Output Modules	125
TM3DM8R / TM3DM8RG Mixed I/O Module 4 Inputs/4 Outputs	126
TM3DM8R / TM3DM8RG Presentation.....	126

TM3DM8R / TM3DM8RG Characteristics	128
TM3DM8R / TM3DM8RG Wiring Diagram	133
TM3DM16R Mixed I/O Module 8 Inputs/8 Outputs.....	134
TM3DM16R Presentation	134
TM3DM16R Characteristics.....	135
TM3DM16R Wiring Diagram	139
TM3DM24R / TM3DM24RG Mixed I/O Module 16 Inputs/8 Outputs.....	141
TM3DM24R / TM3DM24RG Presentation	141
TM3DM24R / TM3DM24RG Characteristics.....	143
TM3DM24R / TM3DM24RG Wiring Diagram.....	147
TM3DM32R Mixed I/O Module 16 Inputs/16 Outputs	149
TM3DM32R Presentation	149
TM3DM32R Characteristics.....	151
TM3DM32R Wiring Diagram	156
Glossary	159
Index	161

Safety Information

Important Information

Read these instructions carefully, and look at the equipment to become familiar with the device before trying to install, operate, service, or maintain it. The following special messages may appear throughout this documentation or on the equipment to warn of potential hazards or to call attention to information that clarifies or simplifies a procedure.



The addition of this symbol to a "Danger" or "Warning" safety label indicates that an electrical hazard exists which will result in personal injury if the instructions are not followed.



This is the safety alert symbol. It is used to alert you to potential personal injury hazards. Obey all safety messages that follow this symbol to avoid possible injury or death.

⚠ DANGER
DANGER indicates a hazardous situation which, if not avoided, will result in death or serious injury.

⚠ WARNING
WARNING indicates a hazardous situation which, if not avoided, could result in death or serious injury.

⚠ CAUTION
CAUTION indicates a hazardous situation which, if not avoided, could result in minor or moderate injury.

NOTICE
NOTICE is used to address practices not related to physical injury.

Please Note

Electrical equipment should be installed, operated, serviced, and maintained only by qualified personnel. No responsibility is assumed by Schneider Electric for any consequences arising out of the use of this material.

A qualified person is one who has skills and knowledge related to the construction and operation of electrical equipment and its installation, and has received safety training to recognize and avoid the hazards involved.

Qualification of Personnel

Only appropriately trained persons who are familiar with and understand the contents of this manual and all other pertinent product documentation are authorized to work on and with this product.

The qualified person must be able to detect possible hazards that may arise from parameterization, modifying parameter values and generally from mechanical, electrical, or electronic equipment. The qualified person must be familiar with the standards, provisions, and regulations for the prevention of industrial accidents, which they must observe when designing and implementing the system.

Intended Use

The products described or affected by this document, together with software, accessories, and options, are expansion modules, intended for industrial use according to the instructions, directions, examples, and safety information contained in the present document and other supporting documentation.

The product may only be used in compliance with all applicable safety regulations and directives, the specified requirements, and the technical data.

Prior to using the product, you must perform a risk assessment in view of the planned application. Based on the results, the appropriate safety-related measures must be implemented.

Since the product is used as a component in an overall machine or process, you must ensure the safety of persons by means of the design of this overall system.

Operate the product only with the specified cables and accessories. Use only genuine accessories and spare parts.

Any use other than the use explicitly permitted is prohibited and can result in unanticipated hazards.

About the Book

Document Scope

This guide describes the hardware implementation of TM3 digital I/O expansion modules. It provides the parts description, characteristics, wiring diagrams, and installation details for TM3 digital I/O expansion modules.

Validity Note

This document has been updated for the release of EcoStruxure™ Machine Expert V2.2.

This document has been updated for the release of EcoStruxure™ Machine Expert - Basic V1.3.

For product compliance and environmental information (RoHS, REACH, PEP, EOL, etc.), go to www.se.com/ww/en/work/support/green-premium/.

The characteristics of the products described in this document are intended to match the characteristics that are available on www.se.com. As part of our corporate strategy for constant improvement, we may revise the content over time to enhance clarity and accuracy. If you see a difference between the characteristics in this document and the characteristics on www.se.com, consider www.se.com to contain the latest information.

Available Languages of this Document

This document is available in these languages:

- English (EIO0000003125)
- French (EIO0000003126)
- German (EIO0000003127)
- Spanish (EIO0000003128)
- Italian (EIO0000003129)
- Chinese (EIO0000003130)
- Portuguese (EIO0000003424)
- Turkish (EIO0000003425)


Related Documents

Title of Documentation	Reference Number
Modicon TM3 Expansion Modules - Programming Guide (EcoStruxure Machine Expert - Basic)	EIO0000003345 (ENG) EIO0000003346 (FRE) EIO0000003347 (GER) EIO0000003348 (SPA) EIO0000003349 (ITA) EIO0000003350 (CHS) EIO0000003351 (POR) EIO0000003352 (TUR)
Modicon TM3 Expansion Modules - Programming Guide (EcoStruxure Machine Expert)	EIO0000003119 (ENG) EIO0000003120 (FRE) EIO0000003121 (GER) EIO0000003122 (SPA) EIO0000003123 (ITA) EIO0000003124 (CHS)
Modicon M221 Logic Controller - Hardware Guide	EIO0000003313 (ENG) EIO0000003314 (FRE) EIO0000003315 (GER) EIO0000003316 (SPA) EIO0000003317 (ITA) EIO0000003318 (CHS) EIO0000003319 (POR) EIO0000003320 (TUR)
Modicon M241 Logic Controller - Hardware Guide	EIO0000003083 (ENG) EIO0000003084 (FRE) EIO0000003085 (GER) EIO0000003086 (SPA) EIO0000003087 (ITA) EIO0000003088 (CHS)
Modicon M251 Logic Controller - Hardware Guide	EIO0000003101 (ENG) EIO0000003102 (FRE) EIO0000003103 (GER) EIO0000003104 (SPA) EIO0000003105 (ITA) EIO0000003106 (CHS)

Title of Documentation	Reference Number
Modicon M262 Logic/Motion Controller - Hardware Guide	EIO0000003659 (ENG)
	EIO0000003660 (FRA)
	EIO0000003661 (GER)
	EIO0000003662 (SPA)
	EIO0000003663 (ITA)
	EIO0000003664 (CHS)
	EIO0000003665 (POR)
EIO0000003666 (TUR)	
TM3 Digital I/O Modules - Instruction Sheet	HRB59605

To find documents online, visit the Schneider Electric download center (www.se.com/ww/en/download/).


Product Related Information

 **DANGER**

HAZARD OF ELECTRIC SHOCK, EXPLOSION OR ARC FLASH

- Disconnect all power from all equipment including connected devices prior to removing any covers or doors, or installing or removing any accessories, hardware, cables, or wires except under the specific conditions specified in the appropriate hardware guide for this equipment.
- Always use a properly rated voltage sensing device to confirm the power is off where and when indicated.
- Replace and secure all covers, accessories, hardware, cables, and wires and confirm that a proper ground connection exists before applying power to the unit.
- Use only the specified voltage when operating this equipment and any associated products.

Failure to follow these instructions will result in death or serious injury.

 **DANGER**

POTENTIAL FOR EXPLOSION

- Only use this equipment in non-hazardous locations, or in locations that comply with Class I, Division 2, Groups A, B, C and D.
- Do not substitute components which would impair compliance to Class I, Division 2.
- Do not connect or disconnect equipment unless power has been removed or the location is known to be non-hazardous.
- Do not use the USB port(s), if so equipped, unless the location is known to be non-hazardous.

Failure to follow these instructions will result in death or serious injury.

▲ WARNING**LOSS OF CONTROL**

- Perform a Failure Mode and Effects Analysis (FMEA), or equivalent risk analysis, of your application, and apply preventive and detective controls before implementation.
- Provide a fallback state for undesired control events or sequences.
- Provide separate or redundant control paths wherever required.
- Supply appropriate parameters, particularly for limits.
- Review the implications of transmission delays and take actions to mitigate them.
- Review the implications of communication link interruptions and take actions to mitigate them.
- Provide independent paths for control functions (for example, emergency stop, over-limit conditions, and error conditions) according to your risk assessment, and applicable codes and regulations.
- Apply local accident prevention and safety regulations and guidelines.¹
- Test each implementation of a system for proper operation before placing it into service.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

¹ For additional information, refer to NEMA ICS 1.1 (latest edition), *Safety Guidelines for the Application, Installation, and Maintenance of Solid State Control* and to NEMA ICS 7.1 (latest edition), *Safety Standards for Construction and Guide for Selection, Installation and Operation of Adjustable-Speed Drive Systems* or their equivalent governing your particular location.

▲ WARNING**UNINTENDED EQUIPMENT OPERATION**

- Only use software approved by Schneider Electric for use with this equipment.
- Update your application program every time you change the physical hardware configuration.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

Information on Non-Inclusive or Insensitive Terminology

As a responsible, inclusive company, Schneider Electric is constantly updating its communications and products that contain non-inclusive or insensitive terminology. However, despite these efforts, our content may still contain terms that are deemed inappropriate by some customers.

Terminology Derived from Standards

The technical terms, terminology, symbols and the corresponding descriptions in the information contained herein, or that appear in or on the products themselves, are generally derived from the terms or definitions of international standards.

In the area of functional safety systems, drives and general automation, this may include, but is not limited to, terms such as *safety*, *safety function*, *safe state*, *fault*, *fault reset*, *malfunxion*, *failure*, *error*, *error message*, *dangerous*, etc.

Among others, these standards include:

Standard	Description
IEC 61131-2:2007	Programmable controllers, part 2: Equipment requirements and tests.
ISO 13849-1:2023	Safety of machinery: Safety related parts of control systems. General principles for design.
EN 61496-1:2020	Safety of machinery: Electro-sensitive protective equipment. Part 1: General requirements and tests.
ISO 12100:2010	Safety of machinery - General principles for design - Risk assessment and risk reduction
EN 60204-1:2006	Safety of machinery - Electrical equipment of machines - Part 1: General requirements
ISO 14119:2013	Safety of machinery - Interlocking devices associated with guards - Principles for design and selection
ISO 13850:2015	Safety of machinery - Emergency stop - Principles for design
IEC 62061:2021	Safety of machinery - Functional safety of safety-related electrical, electronic, and electronic programmable control systems
IEC 61508-1:2010	Functional safety of electrical/electronic/programmable electronic safety-related systems: General requirements.
IEC 61508-2:2010	Functional safety of electrical/electronic/programmable electronic safety-related systems: Requirements for electrical/electronic/programmable electronic safety-related systems.
IEC 61508-3:2010	Functional safety of electrical/electronic/programmable electronic safety-related systems: Software requirements.
IEC 61784-3:2021	Industrial communication networks - Profiles - Part 3: Functional safety fieldbuses - General rules and profile definitions.
2006/42/EC	Machinery Directive
2014/30/EU	Electromagnetic Compatibility Directive
2014/35/EU	Low Voltage Directive

In addition, terms used in the present document may tangentially be used as they are derived from other standards such as:

Standard	Description
IEC 60034 series	Rotating electrical machines
IEC 61800 series	Adjustable speed electrical power drive systems
IEC 61158 series	Digital data communications for measurement and control – Fieldbus for use in industrial control systems

Finally, the term *zone of operation* may be used in conjunction with the description of specific hazards, and is defined as it is for a *hazard zone* or *danger zone* in the *Machinery Directive (2006/42/EC)* and *ISO 12100:2010*.

NOTE: The aforementioned standards may or may not apply to the specific products cited in the present documentation. For more information concerning the individual standards applicable to the products described herein, see the characteristics tables for those product references.

TM3 Digital I/O Modules General Overview

What's in This Part

TM3 Digital I/O Modules Description	16
TM3 Digital I/O Modules Installation.....	25

TM3 Digital I/O Modules Description

What's in This Chapter

General Description.....	16
Physical Description	20
Accessories	22

General Description

Introduction

The range of TM3 digital I/O expansion modules includes:

- Input modules
- Output modules
- Mixed input/output modules

TM3 digital I/O expansion modules are equipped with (depending on the reference):

- Removable screw terminal blocks
- Removable spring terminal blocks
- HE10 (MIL 20) connectors

For modules with HE10 (MIL 20) connectors, a group of products known as Telefast 2 are available that enable these modules to be connected to sensors and actuators.

TM3 Digital Input Modules

The following table shows the TM3 digital input expansion modules, page 44, with corresponding channel type, nominal voltage/current, and terminal type:

Reference	Channels	Channel Type	Voltage Current	Terminal Type / Pitch
TM3DI8A, page 45	8	Regular inputs	120 Vac 7.5 mA	Removable screw terminal block / 5.08 mm
TM3DI8, page 49	8	Regular inputs	24 Vdc 7 mA	Removable screw terminal block / 5.08 mm
TM3DI8G, page 49	8	Regular inputs	24 Vdc 7 mA	Removable spring terminal block / 5.08 mm
TM3DI16, page 54	16	Regular inputs	24 Vdc 7 mA	Removable screw terminal blocks / 3.81 mm
TM3DI16G, page 54	16	Regular inputs	24 Vdc 7 mA	Removable spring terminal blocks / 3.81 mm
TM3DI16K, page 60	16	Regular inputs	24 Vdc 5 mA	HE10 (MIL 20) connector
TM3DI32K, page 66	32	Regular inputs	24 Vdc 5 mA	HE10 (MIL 20) connector

TM3 Digital Output Modules

The following table shows the TM3 digital output expansion modules, page 72, with corresponding channel type, nominal voltage/current, and terminal type:

Reference	Channels	Channel Type	Voltage Current	Terminal Type / Pitch
TM3DQ8R, page 73	8	Relay outputs	24 Vdc / 240 Vac 7 A maximum per common line / 2 A maximum per output	Removable screw terminal block / 5.08 mm
TM3DQ8RG, page 73	8	Relay outputs	24 Vdc / 240 Vac 7 A maximum per common line / 2 A maximum per output	Removable spring terminal block / 5.08 mm
TM3DQ8T, page 79	8	Regular transistor outputs (source)	24 Vdc 4 A maximum per common line/0.5 A maximum per output	Removable screw terminal block / 5.08 mm
TM3DQ8TG, page 79	8	Regular transistor outputs (source)	24 Vdc 4 A maximum per common line/0.5 A maximum per output	Removable spring terminal block / 5.08 mm
TM3DQ8U, page 84	8	Regular transistor outputs (sink)	24 Vdc 4 A maximum per common line/0.5 A maximum per output	Removable screw terminal block / 5.08 mm
TM3DQ8UG, page 84	8	Regular transistor outputs (sink)	24 Vdc 4 A maximum per common line/0.5 A maximum per output	Removable spring terminal block / 5.08 mm
TM3DQ16R, page 89	16	Relay outputs	24 Vdc / 240 Vac 8 A maximum per common line / 2 A maximum per output	Removable screw terminal blocks / 3.81 mm
TM3DQ16RG, page 89	16	Relay outputs	24 Vdc / 240 Vac 8 A maximum per common line / 2 A maximum per output	Removable spring terminal blocks / 3.81 mm
TM3DQ16T, page 95	16	Regular transistor outputs (source)	24 Vdc 8 A maximum per common line / 0.5 A maximum per output	Removable screw terminal blocks / 3.81 mm
TM3DQ16TG, page 95	16	Regular transistor outputs (source)	24 Vdc 8 A maximum per common line / 0.5 A maximum per output	Removable spring terminal blocks / 3.81 mm
TM3DQ16U, page 105	16	Regular transistor outputs (sink)	24 Vdc 8 A maximum per common line / 0.5 A maximum per output	Removable screw terminal blocks / 3.81 mm
TM3DQ16UG, page 105	16	Regular transistor outputs (sink)	24 Vdc 8 A maximum per common line / 0.5 A maximum per output	Removable spring terminal blocks / 3.81 mm

Reference	Channels	Channel Type	Voltage Current	Terminal Type / Pitch
TM3DQ16TK, page 100	16	Regular transistor outputs (source)	24 Vdc 2 A maximum per common line / 0.1 A maximum per output	HE10 (MIL 20) connector
TM3DQ16UK, page 110	16	Regular transistor outputs (sink)	24 Vdc 2 A maximum per common line / 0.1 A maximum per output	HE10 (MIL 20) connector
TM3DQ32TK, page 115	32	Regular transistor outputs (source)	24 Vdc 2 A maximum per common line / 0.1 A maximum per output	HE10 (MIL 20) connectors
TM3DQ32UK, page 120	32	Regular transistor outputs (sink)	24 Vdc 2 A maximum per common line / 0.1 A maximum per output	HE10 (MIL 20) connectors

TM3 Digital Mixed Input/Output Modules

This following table shows the TM3 mixed I/O modules, page 125, with corresponding channel type, nominal voltage/current, and terminal type:

Reference	Channels	Channel Type	Voltage Current	Terminal Type / Pitch
TM3DM8R, page 126	4	Regular inputs	24 Vdc 7 mA	Removable screw terminal block / 5.08 mm
	4	Relay outputs	24 Vdc / 240 Vac 7 A maximum per common line / 2 A maximum per output	
TM3DM8RG, page 126	4	Regular inputs	24 Vdc 7 mA	Removable spring terminal block / 5.08 mm
	4	Relay outputs	24 Vdc / 240 Vac 7 A maximum per common line / 2 A maximum per output	
TM3DM16R, page 134 ⁽¹⁾	8	Regular inputs	24 Vdc 5 mA	Removable screw terminal block / 3.81 mm
	8	Relay outputs	24 Vdc / 240 Vac 4 A maximum per common line / 2 A maximum per output	
TM3DM24R, page 141	16	Regular inputs	24 Vdc 7 mA	Removable screw terminal blocks / 3.81 mm
	8	Relay outputs	24 Vdc / 240 Vac 7 A maximum per common line / 2 A maximum per output	
TM3DM24RG, page 141	16	Regular inputs	24 Vdc 7 mA	Removable spring terminal blocks / 3.81 mm
	8	Relay outputs	24 Vdc / 240 Vac 7 A maximum per common line / 2 A maximum per output	
TM3DM32R, page 149 ⁽¹⁾	16	Regular inputs	24 Vdc 5 mA	Removable screw terminal block / 3.81 mm
	16	Relay outputs	24 Vdc / 240 Vac 4 A maximum per common line / 2 A maximum per output	

(1) This expansion module is available only in selected countries.

Physical Description


Introduction

This section describes the physical characteristics of the TM3 digital expansion modules. The modules, depending on the reference, support one of two different types of connectors:

- Removable screw or spring terminal block
- HE10 (MIL 20) connector

TM3 Digital I/O Modules with Removable Screw or Spring Terminal Block

The following figure shows the main elements of TM3 digital expansion modules with removable screw or spring terminal block:




This table describes the main elements of the TM3 digital expansion modules shown above:

N°	Description	Refer to
1	LEDs for displaying the state of the I/O channels	–
2	Clip-on lock for 35 mm (1.38 in.) top hat section rail (DIN rail)	Top Hat Section Rail (DIN rail), page 31
3	Removable terminal block (screw)	Rules for Removable Screw Terminal Block, page 38
4	Expansion connector for TM3 I/O bus (one on each side)	–
5	Locking device for attachment to the previous module	–
6	Removable terminal block (spring)	Rules for Removable Spring Terminal Block, page 38

TM3 Digital I/O Modules with HE10 (MIL 20) Connector

The following figure shows the main elements of a TM3 digital expansion module with HE10 (MIL 20) connector:



This table describes the main elements of the TM3 digital expansion module shown above:

N°	Description	Refer to
1	LEDs for displaying the state of the I/O channels	—
2	Clip-on lock for 35 mm (1.38 in.) top hat section rail (DIN-rail)	Top Hat Section Rail (DIN rail), page 31
3	HE10 (MIL 20) connector socket	Cables, page 22
4	Expansion connector for TM3 I/O bus (one on each side)	—
5	Locking device for attachment to the previous module	—

Accessories

Overview

This section describes the accessories, cables, and Telefast.

Accessories

Reference	Description	Use	Quantity	
TMAT2MSET	Set of 8 removable screw terminal blocks: <ul style="list-style-type: none"> 4 x Removable screw terminal blocks (pitch 3.81 mm) with 11 terminals for inputs/outputs 4 x Removable screw terminal blocks (pitch 3.81 mm) with 10 terminals for inputs/outputs 	Connects the module I/Os.	1	
TMAT2MSETG	Set of 8 removable spring terminal blocks: <ul style="list-style-type: none"> 4 x Removable spring terminal blocks (pitch 3.81 mm) with 11 terminals for inputs/outputs 4 x Removable spring terminal blocks (pitch 3.81 mm) with 10 terminals for inputs/outputs 			
NSYTRAAB35	End brackets			Helps secure the controller or receiver module and their expansion modules on a top hat section rail (DIN rail).
TMAM2	Mounting kit			Mounts the controller and I/O modules directly to a flat, vertical panel.
TM200RSRCEMC	Shielding take-up clip			Mounts and connects the ground to the cable shielding.


For top hat section rails (DIN rails), refer to Top Hat Section Rail (DIN rail), page 31.

Cables

Reference	Description	Details	Length
TWDFCW••K	Digital I/O cables with free wires for 20-pin connectors	Cable equipped at one end with an HE 10/MIL20 connector (AWG 22 / 0.34 mm ²).	3 or 5 m (9.84 or 16.4 ft)


TWDFCW••K Cable Description

The following table provides specifications for the TWDFCW••K cable with free wires for 20-pin connectors (HE10/MIL20):

Cable illustration	Pin Connector	Wire Color
	1	White
	2	Brown
	3	Green
	4	Yellow
	5	Grey
	6	Pink
	7	Blue
	8	Red
	9	Black
	10	Violet
	11	Grey and pink
	12	Red and blue
	13	White and green
	14	Brown and green
	15	White and yellow
	16	Yellow and brown
	17	White and grey
	18	Grey and brown
	19	White and pink
	20	Pink and brown

Telefast Pre-Wiring Sub-Bases

The following illustration shows the Telefast system:



1 TM3DI16K / TM3DI32K

2 TM3DQ16TK / TM3DQ32TK

3 Cable equipped with a 20-way HE10/MIL20 connector at each end.

4 16 channel sub-base for input extension modules.

5-6 16 channel sub-base for output extension modules.

Refer to TM3 Digital I/O Modules Instruction Sheet.

TM3 Digital I/O Modules Installation

What's in This Chapter

TM3 Digital I/O Modules General Rules for Implementing 25
 TM3 Digital I/O Modules Installation 28
 TM3 Digital I/O Modules Electrical Requirements 36

TM3 Digital I/O Modules General Rules for Implementing

Environmental Characteristics

Enclosure Requirements

TM3 expansion module components are designed as Zone B, Class A industrial equipment according to IEC/CISPR Publication 11. If they are used in environments other than those described in these standards, or in environments that do not meet the specifications in this manual the ability to meet electromagnetic compatibility requirements in the presence of conducted and/or radiated interference may be reduced.

All TM3 expansion module components meet European Community (CE) requirements for open equipment as defined by IEC/EN 61131-2. You must install them in an enclosure designed for the specific environmental conditions and to minimize the possibility of unintended contact with hazardous voltages. Use metal enclosures to improve the electromagnetic immunity of your TM3 expansion module components. Use enclosures with a keyed locking mechanism to minimize unauthorized access.

Environmental Characteristics

All the TM3 expansion module components are electrically isolated between the internal electronic circuit and the input/output channels. This equipment meets CE requirements as indicated in the table below. This equipment is intended for use in a Pollution Degree 2 industrial environment.

▲ WARNING
UNINTENDED EQUIPMENT OPERATION
Do not exceed any of the rated values specified in the environmental and electrical characteristics tables.
Failure to follow these instructions can result in death, serious injury, or equipment damage.

The following table shows the general environmental characteristics:

Characteristic	Minimum Specification	Tested Range	
Standard compliance	IEC/EN 61131-2	–	
Ambient operating temperature	–	Horizontal installation	-10...55 °C (14...131 °F)
	–	Vertical installation	-10...35 °C (14...95 °F)
Storage temperature	–	-25...70 °C (-13...158 °F)	
Relative humidity	–	Transport and storage	10...95 % (non-condensing)
		Operation	10...95 % (non-condensing)
Degree of pollution	IEC/EN 60664-1	2	
Degree of protection	IEC/EN 61131-2	IP20	
Corrosion immunity	–	Atmosphere free from corrosive gases	
Operating altitude	–	0...2000 m (0...6560 ft)	
Storage altitude	–	0...3000 m (0...9843 ft)	
Vibration resistance	IEC/EN 61131-2	Panel mounting or mounted on a top hat section rail (DIN rail)	10 mm (0.39 in) fixed amplitude from 5...8.7 Hz 29.4 m/s ² (96.45 ft/s ²) (3 g _n) fixed acceleration from 8.7...150 Hz
Mechanical shock resistance	–	147 m/s ² or 482.28 ft/s ² (15 g _n) for a duration of 11 ms	
<p>NOTE: The tested ranges may indicate values beyond that of the IEC Standard. However, our internal standards define what is necessary for industrial environments. In all cases, we uphold the minimum specification if indicated.</p>			

Electromagnetic Susceptibility

The TM3 expansion module components meets electromagnetic susceptibility specifications as indicated in the following table:

Characteristic	Minimum Specification	Tested Range		
Electrostatic discharge	IEC/EN 61000-4-2	8 kV (air discharge) 4 kV (contact discharge)		
Radiated electromagnetic field	IEC/EN 61000-4-3	10 V/m (80...1000 MHz) 3 V/m (1.4...2 GHz) 1 V/m (2...3 GHz)		
Magnetic field	IEC/EN 61000-4-8	30 A/m 50 Hz, 60 Hz		
Fast transients burst	IEC/EN 61000-4-4	–	CM ¹ and DM ²	
		AC/DC Power lines	–	
		Relay Outputs	2 kV	
		24 Vdc I/Os	1 kV	
		Analog I/Os	–	
		Communication line	–	
Surge immunity	IEC/EN 61000-4-5 IEC/EN 61131-2	–	CM ¹	DM ²
		DC Power lines	1 kV	0.5 kV
		AC Power lines	2 kV	1 kV
		Relay Outputs	2 kV	1 kV
		24 Vdc I/Os	1 kV	–
		Shielded cable (between shield and ground)	1 kV	–
Induced electromagnetic field	IEC/EN 61000-4-6	10 Vrms (0.15...80 MHz)		
Conducted emission	IEC 61000-6-4	AC power line: • 0.15...0.5 MHz: 79 dBµV/m QP / 66 dBµV/m AV • 0.5...300 MHz: 73 dBµV/m QP / 60 dBµV/m AV		
		AC/DC power line: • 10...150 kHz: 120...69 dBµV/m QP • 150...1500 kHz: 79...63 dBµV/m QP • 1.5...30 MHz: 63 dBµV/m QP		
Radiated emission	IEC 61000-6-4	30...230 MHz: 40 dBµV/m QP 230...1000 MHz: 47 dBµV/m QP		
<p>1 Common Mode</p> <p>2 Differential Mode</p> <p>NOTE: The tested ranges may indicate values beyond that of the IEC Standard. However, our internal standards define what is necessary for industrial environments. In all cases, we uphold the minimum specification if indicated.</p>				

Certifications and Standards

Introduction

For information on certifications and conformance to standards, go to www.se.com.

For product compliance and environmental information (RoHS, REACH, PEP, EOLI, etc.), go to www.se.com/green-premium.

TM3 Digital I/O Modules Installation

Installation and Maintenance Requirements

Before Starting

Read and understand this chapter before beginning the installation of your system.

The use and application of the information contained herein require expertise in the design and programming of automated control systems. Only you, the user, machine builder or integrator, can be aware of all the conditions and factors present during installation and setup, operation, and maintenance of the machine or process, and can therefore determine the automation and associated equipment and the related safeties and interlocks which can be effectively and properly used. When selecting automation and control equipment, and any other related equipment or software, for a particular application, you must also consider any applicable local, regional or national standards and/or regulations.

Pay particular attention in conforming to any safety information, different electrical requirements, and normative standards that would apply to your machine or process in the use of this equipment.

Disconnecting Power

All options and modules should be assembled and installed before installing the control system on a mounting rail, onto a mounting plate or in a panel. Remove the control system from its mounting rail, mounting plate or panel before disassembling the equipment.

DANGER

HAZARD OF ELECTRIC SHOCK, EXPLOSION OR ARC FLASH

- Disconnect all power from all equipment including connected devices prior to removing any covers or doors, or installing or removing any accessories, hardware, cables, or wires except under the specific conditions specified in the appropriate hardware guide for this equipment.
- Always use a properly rated voltage sensing device to confirm the power is off where and when indicated.
- Replace and secure all covers, accessories, hardware, cables, and wires and confirm that a proper ground connection exists before applying power to the unit.
- Use only the specified voltage when operating this equipment and any associated products.

Failure to follow these instructions will result in death or serious injury.

Programming Considerations

WARNING

UNINTENDED EQUIPMENT OPERATION

- Only use software approved by Schneider Electric for use with this equipment.
- Update your application program every time you change the physical hardware configuration.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

Operating Environment

In addition to the **Environmental Characteristics**, refer to **Product Related Information** in the beginning of the present document for important information regarding installation in hazardous locations for this specific equipment.

⚠ WARNING
UNINTENDED EQUIPMENT OPERATION
Install and operate this equipment according to the conditions described in the Environmental Characteristics.
Failure to follow these instructions can result in death, serious injury, or equipment damage.

Installation Considerations

⚠ WARNING
UNINTENDED EQUIPMENT OPERATION
<ul style="list-style-type: none"> • Use appropriate safety interlocks where personnel and/or equipment hazards exist. • Install and operate this equipment in an enclosure appropriately rated for its intended environment and secured by a keyed or tooled locking mechanism. • Use the sensor and actuator power supplies only for supplying power to the sensors or actuators connected to the module. • Power line and output circuits must be wired and fused in compliance with local and national regulatory requirements for the rated current and voltage of the particular equipment. • Do not use this equipment in safety-critical machine functions unless the equipment is otherwise designated as functional safety equipment and conforming to applicable regulations and standards. • Do not disassemble, repair, or modify this equipment. • Do not connect any wiring to reserved, unused connections, or to connections designated as No Connection (N.C.).
Failure to follow these instructions can result in death, serious injury, or equipment damage.

NOTE: JDYX2 or JDYX8 fuse types are cULus-recognized.

Installation Guidelines

Introduction

TM3 expansion modules are assembled by connecting them to a logic controller or receiver module.

The logic controller or receiver module and their expansion modules can be installed on a top hat section rail (DIN rail).

Mounting Position and Minimum Clearances

The mounting position and minimum clearances of the expansion modules must conform with the rules defined for the appropriate hardware system. Refer to the *Installation chapter* in the *Controller Hardware* documentation for your specific controller.

⚠ WARNING


UNINTENDED EQUIPMENT OPERATION

- Place devices dissipating the most heat at the top of the cabinet and ensure adequate ventilation.
- Avoid placing this equipment next to or above devices that might cause overheating.
- Install the equipment in a location providing the minimum clearances from all adjacent structures and equipment as directed in this document.
- Install all equipment in accordance with the specifications in the related documentation.

Failure to follow these instructions can result in death, serious injury, or equipment damage.


Correct Mounting Position

To obtain optimal operating characteristics, the TM3 Digital I/O Modules should be mounted horizontally on a vertical plane as shown in the figure below:




Acceptable Mounting Position

The TM3 Digital I/O Modules can also be mounted vertically on a vertical plane as shown below:



Incorrect Mounting Positions

The TM3 Digital I/O Modules should only be positioned as shown in the Correct Mounting Position, page 30 figure. The figures below show the incorrect mounting positions:




Top Hat Section Rail (DIN rail)

Dimensions of Top Hat Section Rail DIN Rail

You can mount the controller or receiver and their expansions on a 35 mm (1.38 in.) top hat section rail (DIN rail). The DIN rail can be attached to a smooth mounting surface or suspended from an EIA rack or mounted in a NEMA cabinet.


Symmetric Top Hat Section Rails (DIN Rail)

The following illustration and table indicate the references of the top hat section rails (DIN rail) for the wall-mounting range:



Reference	Type	Perforated	Rail Length (B)
NSYS DR50A	A	At each end	450 mm (17.71 in.)
NSYS DR60A	A	At each end	550 mm (21.65 in.)
NSYS DR80A	A	At each end	750 mm (29.52 in.)
NSYS DR100A	A	At each end	950 mm (37.40 in.)


The following illustration and table indicate the references of the symmetric top hat section rails (DIN rail) of 2000 mm (78.74 in.):



Reference	Type	Perforated	Rail Length
NSYSDR200	A	No	2000 mm (78.74 in.)
NSYSDR200D	A	Yes	

Double-Profile Top Hat Section Rails (DIN rail)

The following illustration and table indicate the references of the double-profile top hat section rails (DIN rail) of 2000 mm (78.74 in.):



Reference	Type	Perforated	Rail Length
NSYDPR200	-	No	2000 mm (78.74 in.)
NSYDPR200D	-	Yes	

Assembling a Module to a Controller or Receiver Module

Introduction

This section describes how to assemble an expansion module to a controller, receiver module or other modules.

⚠️ DANGER

HAZARD OF ELECTRIC SHOCK, EXPLOSION OR ARC FLASH

- Disconnect all power from all equipment including connected devices prior to removing any covers or doors, or installing or removing any accessories, hardware, cables, or wires except under the specific conditions specified in the appropriate hardware guide for this equipment.
- Always use a properly rated voltage sensing device to confirm the power is off where and when indicated.
- Replace and secure all covers, accessories, hardware, cables, and wires and confirm that a proper ground connection exists before applying power to the unit.
- Use only the specified voltage when operating this equipment and any associated products.

Failure to follow these instructions will result in death or serious injury.

After connecting new modules to the controller, either directly or through a transmitter/receiver, update and redownload your application program before placing the system back in service. If you do not revise your application program to reflect the addition of new modules, I/O located on the expansion bus may no longer operate normally.

⚠️ WARNING

UNINTENDED EQUIPMENT OPERATION

- Only use software approved by Schneider Electric for use with this equipment.
- Update your application program every time you change the physical hardware configuration.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

Assembling a Module to a Controller or Receiver Module

The following procedure shows how to assemble a controller or receiver module and a module together:

Step	Action
1	Remove all power and dismount any existing controller I/O assembly from its DIN mounting.
2	Remove the expansion connector sticker from the controller or the outermost installed expansion module.
3	Verify that the locking device, page 20 on the new module is in the upper position.
4	Align the internal bus connector on the left side of the module with the internal bus connector on the right side of the controller, receiver module or expansion module.
5	Press the new module towards the controller, receiver module or expansion module until it is securely in place.
6	Push down the locking device, page 20 on the top of the new module to lock it to the controller, receiver module or previously installed expansion module.

Disassembling a Module from a Controller or Receiver Module

Introduction

This section describes how to disassemble a module from a controller or receiver module.

⚡⚠ DANGER

HAZARD OF ELECTRIC SHOCK, EXPLOSION OR ARC FLASH

- Disconnect all power from all equipment including connected devices prior to removing any covers or doors, or installing or removing any accessories, hardware, cables, or wires except under the specific conditions specified in the appropriate hardware guide for this equipment.
- Always use a properly rated voltage sensing device to confirm the power is off where and when indicated.
- Replace and secure all covers, accessories, hardware, cables, and wires and confirm that a proper ground connection exists before applying power to the unit.
- Use only the specified voltage when operating this equipment and any associated products.

Failure to follow these instructions will result in death or serious injury.

Disassembling a Module from a Controller or Receiver Module

The following procedure describes how to disassemble a module from a controller or receiver module:

Step	Action
1	Remove all power from the control system.
2	Dismount the assembled controller and modules from the mounting rail.
3	Push up the locking device, page 20 from the bottom of the module to disengage it from the controller or the receiver module.
4	Pull apart the module from the controller or the receiver module.


Direct Mounting on a Panel Surface

Overview

This section shows how to install TM3 expansion module using the Panel Mounting Kit. This section also provides mounting hole layout for all modules.


Installing the Panel Mounting Kit

The following procedure shows how to install a mounting strip:


Step	Action
1	Insert the mounting strip TMAM2 into the slot at the top of the module. 

Mounting Hole Layout


The following diagram shows the mounting hole layout for TM3 with 8 and 16 screw or spring I/O channels:




The following diagram shows the mounting hole layout for TM3 with 24 screw or spring I/O channels:



The following diagram shows the mounting hole layout for TM3 with 32 HE10 (MIL 20) I/O channels:



The following diagram shows the mounting hole layout for the TM3DM32R expansion module:



TM3 Digital I/O Modules Electrical Requirements

Wiring Best Practices

Overview

This section describes the wiring guidelines and associated best practices to be respected when using the TM3 system.

⚡⚠ DANGER

HAZARD OF ELECTRIC SHOCK, EXPLOSION OR ARC FLASH

- Disconnect all power from all equipment including connected devices prior to removing any covers or doors, or installing or removing any accessories, hardware, cables, or wires except under the specific conditions specified in the appropriate hardware guide for this equipment.
- Always use a properly rated voltage sensing device to confirm the power is off where and when indicated.
- Replace and secure all covers, accessories, hardware, cables, and wires and confirm that a proper ground connection exists before applying power to the unit.
- Use only the specified voltage when operating this equipment and any associated products.

Failure to follow these instructions will result in death or serious injury.

▲ WARNING

LOSS OF CONTROL

- Perform a Failure Mode and Effects Analysis (FMEA), or equivalent risk analysis, of your application, and apply preventive and detective controls before implementation.
- Provide a fallback state for undesired control events or sequences.
- Provide separate or redundant control paths wherever required.
- Supply appropriate parameters, particularly for limits.
- Review the implications of transmission delays and take actions to mitigate them.
- Review the implications of communication link interruptions and take actions to mitigate them.
- Provide independent paths for control functions (for example, emergency stop, over-limit conditions, and error conditions) according to your risk assessment, and applicable codes and regulations.
- Apply local accident prevention and safety regulations and guidelines.¹
- Test each implementation of a system for proper operation before placing it into service.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

¹ For additional information, refer to NEMA ICS 1.1 (latest edition), *Safety Guidelines for the Application, Installation, and Maintenance of Solid State Control* and to NEMA ICS 7.1 (latest edition), *Safety Standards for Construction and Guide for Selection, Installation and Operation of Adjustable-Speed Drive Systems* or their equivalent governing your particular location.

Wiring Guidelines

The following rules must be applied when wiring a TM3 system:

- I/O and communication wiring must be kept separate from the power wiring. Route these 2 types of wiring in separate cable ducting.
- Verify that the operating conditions and environment are within the specification values.
- Use proper wire sizes to meet voltage and current requirements.
- Use copper conductors.
- Use twisted-pair, shielded cables for analog, and/or fast I/O.
- Use twisted-pair, shielded cables for networks, and field bus.

▲ WARNING

UNINTENDED EQUIPMENT OPERATION

- Use shielded cables for all fast I/O, analog I/O, and communication signals.
- Ground cable shields for all fast I/O, analog I/O, and communication signals at a single point¹.
- Route communications and I/O cables separately from power cables.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

¹Multipoint grounding is permissible if connections are made to an equipotential ground plane dimensioned to help avoid cable shield damage in the event of power system short-circuit currents.

NOTE: Surface temperatures may exceed 60 °C (140 °F).

To conform to IEC 61010 standards, route primary wiring (wires connected to power mains) separately and apart from secondary wiring (extra low voltage wiring coming from intervening power sources). If that is not possible, double insulation is required such as conduit or cable gains.

Rules for Removable Screw Terminal Block

The following tables show the cable types and wire sizes for a **3.81 pitch** removable screw terminal block (I/Os and power supply):

mm ²	0.14...1.5	0.14...1.5	0.25...1.5	0.25...0.5	2 x 0.14...0.5	2 x 0.14...0.75	2 x 0.25...0.34	2 x 0.5
AWG	26...16	26...16	22...16	22...20	2 x 26...20	2 x 26...20	2 x 24...22	2 x 20

		N•m	0.28
Ø 2,5 mm (0.1 in.)		lb-in	2.48

The following tables show the cable types and wire sizes for a **5.08 pitch** removable screw terminal block (I/Os and power supply):

mm ²	0.2...2.5	0.2...2.5	0.25...2.5	0.25...2.5	2 x 0.2...1	2 x 0.2...1.5	2 x 0.25...1	2 x 0.5...1.5
AWG	24...14	24...14	23...14	23...14	2 x 24...17	2 x 24...16	2 x 23...17	2 x 20...16

		N•m	0.49
Ø 3,5 mm (0.14 in.)		lb-in	4.34

The use of copper conductors is required.

⚠ DANGER

FIRE HAZARD

- Use only the correct wire sizes for the maximum current capacity of the I/O channels and power supplies.
- For relay output (2 A) wiring, use conductors of at least 0.5 mm² (AWG 20) with a temperature rating of at least 80 °C (176 °F).
- For common conductors of relay output wiring (7 A), or relay output wiring greater than 2 A, use conductors of at least 1.0 mm² (AWG 16) with a temperature rating of at least 80 °C (176 °F).

Failure to follow these instructions will result in death or serious injury.

Rules for Removable Spring Terminal Block

The following tables show the cable types and wire sizes for a **3.81 pitch** removable spring terminal block (I/Os and power supply):

mm ²	0.5...1.5	0.5...1.5	0.25...1.0	0.25...0.5
AWG	21...16	21...16	23...18	23...21

The following tables show the cable types and wire sizes for a **5.08 pitch** removable spring terminal block (I/Os and power supply):

	mm ²	0.2...2.5	0.2...2.5	0.25...2.5	0.25...2.5	2 x 0.5...1
	AWG	24...14	24...14	23...14	23...14	2 x 20...17

The use of copper conductors is required.

⚠ DANGER

FIRE HAZARD

- Use only the correct wire sizes for the maximum current capacity of the I/O channels and power supplies.
- For relay output (2 A) wiring, use conductors of at least 0.5 mm² (AWG 20) with a temperature rating of at least 80 °C (176 °F).
- For common conductors of relay output wiring (7 A), or relay output wiring greater than 2 A, use conductors of at least 1.0 mm² (AWG 16) with a temperature rating of at least 80 °C (176 °F).

Failure to follow these instructions will result in death or serious injury.

The spring clamp connectors of the terminal block are designed for only one wire or one cable end. Two wires to the same connector must be installed with a double wire cable end to help prevent loosening.

⚠⚠ DANGER

LOOSE WIRING CAUSES ELECTRIC SHOCK

Do not insert more than one wire per connector of the spring terminal blocks unless using a double wire cable end (ferrule).

Failure to follow these instructions will result in death or serious injury.

Protecting Outputs from Inductive Load Damage

Depending on the load, a protection circuit may be needed for the outputs on the controllers and certain modules. Inductive loads using DC voltages may create voltage reflections resulting in overshoot that will damage or shorten the life of output devices.

⚠ CAUTION

OUTPUT CIRCUIT DAMAGE DUE TO INDUCTIVE LOADS

Use an appropriate external protective circuit or device to reduce the risk of inductive direct current load damage.

Failure to follow these instructions can result in injury or equipment damage.

If your controller or module contains relay outputs, these types of outputs can support up to 240 Vac. Inductive damage to these types of outputs can result in welded contacts and loss of control. Each inductive load must include a protection device such as a peak limiter, RC circuit or flyback diode. Capacitive loads are not supported by these relays.

⚠ WARNING

RELAY OUTPUTS WELDED CLOSED

- Always protect relay outputs from inductive alternating current load damage using an appropriate external protective circuit or device.
- Do not connect relay outputs to capacitive loads.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

AC-driven contactor coils are, under certain circumstances, inductive loads that generate pronounced high-frequency interference and electrical transients when the contactor coil is de-energized. This interference may cause the logic controller to detect an I/O bus error.


⚠ WARNING

CONSEQUENTIAL LOSS OF CONTROL

Install an RC surge suppressor or similar means, such as an interposing relay, on each TM3 expansion module relay output when connecting to AC-driven contactors or other forms of inductive loads.

Failure to follow these instructions can result in death, serious injury, or equipment damage.


Protective circuit A: this protection circuit can be used for both AC and DC load power circuits.



C Value from 0.1 to 1 μ F

R Resistor of approximately the same resistance value as the load


Protective circuit B: this protection circuit can be used for DC load power circuits.



Use a diode with the following ratings:

- Reverse withstand voltage: power voltage of the load circuit x 10.
- Forward current: more than the load current.

Protective circuit C: this protection circuit can be used for both AC and DC load power circuits.



In applications where the inductive load is switched on and off frequently and/or rapidly, ensure that the continuous energy rating (J) of the varistor exceeds the peak load energy by 20 % or more.

DC Power Supply Characteristics

Overview

This section provides the characteristics of the DC power supply.

Power Supply Voltage Range

If the specified voltage range is not maintained, outputs may not switch as expected. Use appropriate safety interlocks and voltage monitoring circuits.

⚠ DANGER
<p>FIRE HAZARD</p> <p>Use only the correct wire sizes for the maximum current capacity of the I/O channels and power supplies.</p> <p>Failure to follow these instructions will result in death or serious injury.</p>
⚠ WARNING
<p>UNINTENDED EQUIPMENT OPERATION</p> <p>Do not exceed any of the rated values specified in the environmental and electrical characteristics tables.</p> <p>Failure to follow these instructions can result in death, serious injury, or equipment damage.</p>

DC Power Supply Characteristics

The 24 Vdc power supplies must be rated Protective Extra Low Voltage (PELV) according to IEC 61140. These power supplies are isolated between the electrical input and output circuits of the power supply.

⚠ WARNING
<p>POTENTIAL OF OVERHEATING AND FIRE</p> <ul style="list-style-type: none"> Do not connect the equipment directly to line voltage. Use only isolating PELV power supplies to supply power to the equipment¹. <p>Failure to follow these instructions can result in death, serious injury, or equipment damage.</p>

¹For compliance to UL (Underwriters Laboratories) requirements, the power supply must also conform to the various criteria of NEC Class 2, and be inherently current limited to a maximum power output availability of less than 100 VA (approximately 4 A at nominal voltage), or not inherently limited but with an additional protection device such as a circuit breaker or fuse meeting the requirements of clause 9.4 Limited-energy circuit of UL 61010-1. In all cases, the current limit should never exceed that of the electric characteristics and wiring diagrams for the equipment described in the present documentation. In all cases, the power supply must be grounded, and you must separate Class 2 circuits from other circuits. If the indicated rating of the electrical characteristics or wiring diagrams are greater than the specified current limit, multiple Class 2 power supplies may be used.

Grounding the TM3 Digital I/O Modules

Overview

Due to the effects of electromagnetic interference, cables carrying fast I/O, analog I/O, and the fieldbus communication signals must be shielded.

⚠ WARNING

UNINTENDED EQUIPMENT OPERATION

- Use shielded cables for all fast I/O, analog I/O, and communication signals.
- Ground cable shields for all fast I/O, analog I/O, and communication signals at a single point¹.
- Route communications and I/O cables separately from power cables.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

¹Multipoint grounding is permissible if connections are made to an equipotential ground plane dimensioned to help avoid cable shield damage in the event of power system short-circuit currents.

The use of shielded cables requires compliance with the following wiring rules:

- For protective earth ground connections (PE), metal conduit or ducting can be used for part of the shielding length, provided there is no break in the continuity of the ground connections. For functional earth ground (FE), the shielding is intended to attenuate electromagnetic interference and the shielding must be continuous for the length of the cable. If the purpose is both functional and protective, as is often the case for communication cables, the cable must have continuous shielding.
- Wherever possible, keep cables carrying one type of signal separate from the cables carrying other types of signals or power.

Shielded Cables Connections

Cables carrying fast I/O, analog I/O, and the fieldbus communication signals must be shielded. The shielding must be securely connected to ground. Fast I/O and analog I/O shields may be connected either to the functional earth ground (FE) or to the protective earth ground (PE) of your TM3 expansion module. The fieldbus communication cable shields must be connected to the protective earth ground (PE) with a connecting clamp secured to the conductive backplane of your installation.

Protective Earth Ground (PE) on the Backplane

The protective earth ground (PE) is connected to the conductive backplane by a heavy-duty wire, usually a braided copper cable with the maximum allowable cable section.


Functional Earth Ground (FE) on the DIN Rail

The DIN Rail for your TM3 system is common with the functional earth ground (FE) plane and must be mounted on a conductive backplane.

⚠ WARNING
UNINTENDED EQUIPMENT OPERATION
Connect the DIN rail to the functional earth ground (FE) of your installation.
Failure to follow these instructions can result in death, serious injury, or equipment damage.

Functional Earth Ground (FE) Connections

To connect the functional earth ground (FE):



Label	Signification	Description
1	Grounding of the module	Connect the module to the functional earth ground (FE) terminal.
2	Grounding of the sensor	Attach and ground the shielding of cables as close as possible to the controller: <ol style="list-style-type: none"> Strip the shielding Attach the cable to the metal support by attaching the clamp to the stripped part of the shielding. The shielding must be clamped tightly enough to the metal support to achieve good contact.

TM3 Digital Input Modules

What's in This Part

TM3DI8A Module 8 Inputs 120 Vac.....	45
TM3DI8 / TM3DI8G Module 8 Regular Inputs 24 Vdc	49
TM3DI16 / TM3DI16G Module 16 Regular Inputs 24 Vdc	54
TM3DI16K Module 16 Regular Inputs 24 Vdc	60
TM3DI32K Module 32 Regular Inputs 24 Vdc	66

TM3DI8A Module 8 Inputs 120 Vac

What's in This Chapter

TM3DI8A Presentation45
 TM3DI8A Characteristics46
 TM3DI8A Wiring Diagram48

Overview

This chapter describes the TM3DI8A expansion modules, its characteristics, and its connection to the different sensors.

TM3DI8A Presentation

Overview

TM3DI8A (screw) digital expansion module:

- 8 channels
- 120 Vac digital input
- 2 common lines
- Removable screw terminal block

Main Characteristics

Characteristic		Value
Number of input channels		8
Input type		Type 1 (IEC/EN 61131-2)
Logic type		N/A
Rated input voltage		120 Vac
Connection type		Removable screw terminal block
Cable type and length	Type	Stranded wire 2,5 mm ²
	Length	-

Status LEDs

The following figure shows the status LEDs:



This table describes the status LEDs:

LED	Color	Status	Description
0...7	Green	On	The input channel is activated.
		Off	The input channel is deactivated.

TM3DI8A Characteristics

Introduction


This section provides a general description of the characteristics of the TM3DI8A expansion module.

See also Environmental Characteristics, page 25.

⚠ WARNING
UNINTENDED EQUIPMENT OPERATION
Do not exceed any of the rated values specified in the environmental and electrical characteristics tables.
Failure to follow these instructions can result in death, serious injury, or equipment damage.

Dimensions

The following diagrams show the external dimensions for the TM3DI8A module:



* 8.5 mm (0.33 in.) when the clamp is pulled out.

Input Characteristics

The table below describes the inputs characteristics of the TM3DI8A expansion module:

Characteristic		Value
Number of input channels		8 inputs
Number of channels groups		2 common lines of 4 channels each
Input type		Type 1 (IEC/EN 61131-2)
Logic type		N/A
Rated input voltage		120 Vac
Input voltage range		0...132 Vac
Rated input current		7.5 mA at 100 Vac
Input impedance		11 k Ω
Turn on time		25 ms
De-rating	-10...55 °C (14...131 °F)	No de-rating
Input limit values	Voltage at state 1	> 79 Vac (79...132 Vac)
	Voltage at state 0	< 20 Vac (0...20 Vac)
	Current at state 1	2 mA < I < 15 mA
Isolation	Between input and internal logic	1500 Vac
	Between input groups	1500 Vac
Connector type		Removable screw terminal block
Connector insertion/removal durability		Over 100 times
Current draw on 5 Vdc internal bus		60 mA (all inputs on)
		25 mA (all inputs off)
Current draw on 24 Vdc internal bus		0 mA (all inputs on)
		0 mA (all inputs off)

TM3DI8A Wiring Diagram

Introduction


This expansion module has a built-in removable screw terminal block for the connection of inputs and power supply.

Wiring Rules

See Wiring Best Practices, page 36.

Wiring Diagram

The following figure illustrates the connection between the inputs, the sensors, and their commons:



The COM0 and COM1 terminals are **not** connected internally.

⚠ WARNING
<p>UNINTENDED EQUIPMENT OPERATION</p> <p>Do not connect wires to unused terminals and/or terminals indicated as “No Connection (N.C.)”.</p> <p>Failure to follow these instructions can result in death, serious injury, or equipment damage.</p>

TM3DI8 / TM3DI8G Module 8 Regular Inputs 24 Vdc

What's in This Chapter

TM3DI8 / TM3DI8G Presentation.....49
 TM3DI8 / TM3DI8G Characteristics 51
 TM3DI8 / TM3DI8G Wiring Diagram 53

Overview

This chapter describes the TM3DI8 / TM3DI8G expansion modules, its characteristics and its connection to the different sensors.

TM3DI8 / TM3DI8G Presentation

Overview

TM3DI8 (screw) and TM3DI8G (spring) digital expansion module:


- 8 channels
- 24 Vdc digital input
- 1 common line
- Sink/source
- Removable screw or spring terminal block

Main Characteristics

Characteristic		Value
Number of input channels		8 inputs
Input type		Type 1 (IEC/EN 61131-2)
Logic type		Sink/Source
Rated input voltage		24 Vdc
Connection type	TM3DI8	Removable screw terminal block
	TM3DI8G	Removable spring terminal block
Cable type and length	Type	Unshielded
	Length	Maximum 30 m (98 ft)
Weight		85 g (3 oz)

Status LEDs

The following figure shows the status LEDs:



This table describes the status LEDs:

LED	Color	Status	Description
0...7	Green	On	The input channel is activated
		Off	The input channel is deactivated

TM3DI8 / TM3DI8G Characteristics

Introduction


This section provides a description of the input characteristics of TM3DI8 / TM3DI8G expansion modules.

See also Environmental Characteristics, page 25.

⚠ WARNING
UNINTENDED EQUIPMENT OPERATION
Do not exceed any of the rated values specified in the environmental and electrical characteristics tables.
Failure to follow these instructions can result in death, serious injury, or equipment damage.

Dimensions

The following diagrams show the external dimensions for the TM3DI8 / TM3DI8G expansion modules:



* 8.5 mm (0.33 in.) when the clamp is pulled out.

Input Characteristics

The table below describes the inputs characteristics of the TM3DI8 / TM3DI8G:

Characteristic		Value
Number of input channels		8 inputs
Number of channels groups		1 common line on three terminals for 8 channels
Input type		Type 1 (IEC/EN 61131-2)
Logic type		Sink/Source
Rated input voltage		24 Vdc
Input voltage range		19.2...28.8 Vdc
Rated input current		7 mA
Input impedance		3.4 kΩ
Turn on time		SV ⁽¹⁾ < 2.0: 4 ms
Turn off time		SV ⁽¹⁾ ≥ 2.0: 100 μs ⁽²⁾
Input limit values	Voltage at state 1	> 15 Vdc (15...28.8 Vdc)
	Voltage at state 0	< 5 Vdc (0...5 Vdc)
	Current at state 1	> 2.5 mA
	Current at state 0	< 1.0 mA
Isolation	Between input and internal logic	500 Vac
	Between input groups	N/A
Connection type	TM3DI8	Removable screw terminal block
	TM3DI8G	Removable spring terminal block
Connector insertion/removal durability		Over 100 times
Current draw on 5 Vdc internal bus	22 mA (all inputs on)	
	5 mA (all inputs off)	
Current draw on 24 Vdc internal bus	0 mA (all inputs on)	
	0 mA (all inputs off)	
<p>(1) SV refers to the version and is printed on the product label. (2) The range depends on the configured filter value. If you use EcoStruxure Machine Expert - Basic, refer to the Modicon TM3 (EcoStruxure Machine Expert - Basic) Expansion Modules Configuration - Programming Guide. If you use EcoStruxure Machine Expert, refer to the Modicon TM3 Expansion Modules - Programming Guide.</p>		

TM3DI8 / TM3DI8G Wiring Diagram

Introduction


These expansion modules have a built-in removable screw or spring terminal block for the connection of inputs and power supply.

Wiring Rules

See Wiring Best Practices, page 36.

Wiring Diagram

The following figure illustrates the connection between the inputs, the sensors, and their commons:



The 3 COM terminals are connected internally.

A Sink wiring (positive logic)

B Source wiring (negative logic)

For information about 24 Vdc power supply, refer to DC Power Supply Characteristics, page 41.

TM3DI16 / TM3DI16G Module 16 Regular Inputs 24 Vdc

What's in This Chapter

TM3DI16 / TM3DI16G Presentation	54
TM3DI16 / TM3DI16G Characteristics.....	56
TM3DI16 / TM3DI16G Wiring Diagram.....	59

Overview

This chapter describes the TM3DI16 / TM3DI16G expansion modules, its characteristics and its connection to the different sensors.

TM3DI16 / TM3DI16G Presentation

Overview

TM3DI16 (screw) and TM3DI16G (spring) digital expansion module:

- 16 channels
- 24 Vdc digital input
- 1 common line
- Sink/source
- Removable screw or spring terminal block

Main Characteristics

Characteristic		Value
Number of input channels		16
Input type		Type 1 (IEC/EN 61131-2)
Logic type		Sink/Source
Rated input voltage		24 Vdc
Connection type	TM3DI16	Removable screw terminal blocks
	TM3DI16G	Removable spring terminal blocks
Cable type and length	Type	Unshielded
	Length	Maximum 30 m (98 ft)
Weight		100 g (3.52 oz)

Status LEDs

The following figure show the status LEDs:



This table describes the status LEDs:

LED	Color	Status	Description
0...15	Green	On	The input channel is activated
		Off	The input channel is deactivated

TM3DI16 / TM3DI16G Characteristics

Introduction


This section provides a description of the input characteristics of TM3DI16 / TM3DI16G expansion modules.

See also Environmental Characteristics, page 25.

▲ WARNING
UNINTENDED EQUIPMENT OPERATION
Do not exceed any of the rated values specified in the environmental and electrical characteristics tables.
Failure to follow these instructions can result in death, serious injury, or equipment damage.

Dimensions

The following diagrams show the external dimensions for the TM3DI16 / TM3DI16G expansion modules:



* 8.5 mm (0.33 in.) when the clamp is pulled out.


Input Characteristics

The table below describes the inputs characteristics of the TM3DI16 / TM3DI16G:

Characteristic		Value
Number of input channels		16 inputs
Number of channels groups		1 common line on 4 terminals (2 per connector) for 16 channels
Input type		Type 1 (IEC/EN 61131-2)
Logic type		Sink/Source
Rated input voltage		24 Vdc
Input voltage range		19.2...28.8 Vdc
Rated input current		7 mA
Input impedance		3.4 kΩ
Input limit values	Voltage at state 1	> 15 Vdc (15...28.8 Vdc)
	Voltage at state 0	< 5 Vdc (0...5 Vdc)
	Current at state 1	> 2.5 mA
	Current at state 0	< 1.0 mA
Turn on time		SV ⁽¹⁾ < 2.0: 4 ms
Turn off time		SV ⁽¹⁾ ≥ 2.0: 100 μs ⁽²⁾
Isolation	Between input and internal logic	500 Vac
	Between input groups	N/A
Connection type	TM3DI16	Removable screw terminal blocks
	TM3DI16G	Removable spring terminal blocks
Connector insertion/removal durability		Over 100 times
Current draw on 5 Vdc internal bus		34 mA (all inputs on) 5 mA (all inputs off)
Current draw on 24 Vdc internal bus		0 mA (all inputs on) 0 mA (all inputs off)
<p>(1) SV refers to the version and is printed on the product label.</p> <p>(2) The range depends on the configured filter value. If you use EcoStruxure Machine Expert - Basic, refer to the Modicon TM3 (EcoStruxure Machine Expert - Basic) Expansion Modules Configuration - Programming Guide. If you use EcoStruxure Machine Expert, refer to the Modicon TM3 Expansion Modules - Programming Guide.</p>		

I/O Re-rating

When using TM3DI16 / TM3DI16G:



X Input simultaneous ON ratio

Y Input voltage

TM3DI16 / TM3DI16G Wiring Diagram

Introduction


These expansion modules have a built-in removable screw or spring terminal block for the connection of inputs and power supply.

Wiring Rules

See Wiring Best Practices, page 36.

Wiring Diagram

The following figure illustrates the connection between the inputs, the sensors, and their commons:



The 4 COM terminals are connected internally

A Sink wiring (positive logic)

B Source wiring (negative logic)

For information about 24 Vdc power supply, refer to DC Power Supply Characteristics, page 41.

TM3DI16K Module 16 Regular Inputs 24 Vdc

What's in This Chapter

TM3DI16K Presentation..... 60
 TM3DI16K Characteristics 62
 TM3DI16K Wiring Diagram 65

Overview

This chapter describes the TM3DI16K expansion module, its characteristics and its connection to the different sensors.

TM3DI16K Presentation

Overview

TM3DI16K (HE10) digital expansion module:


- 16 channels
- 24 Vdc digital input
- 1 common line
- Sink/source
- HE10 (MIL 20) connector

Main Characteristics

Characteristic		Value
Number of input channels		16
Input type		Type 1 (IEC/EN 61131-2)
Logic type		Sink/Source
Rated input voltage		24 Vdc
Connection type		HE10 (MIL 20) connector
Cable type and length	Type	Unshielded
	Length	Maximum 30 m (98 ft)
Weight		65 g (2.30 oz)

Status LEDs

The following figure show the status LEDs:



This table describes the status LEDs:

LED	Color	Status	Description
0...15	Green	On	The input channel is activated
		Off	The input channel is deactivated

TM3DI16K Characteristics

Introduction


This section provides a description of the input characteristics of TM3DI16K expansion module.

See also Environmental Characteristics, page 25.

▲ WARNING
UNINTENDED EQUIPMENT OPERATION
Do not exceed any of the rated values specified in the environmental and electrical characteristics tables.
Failure to follow these instructions can result in death, serious injury, or equipment damage.

Dimensions

The following diagrams show the external dimensions for the TM3DI16K expansion module:



* 8.5 mm (0.33 in.) when the clamp is pulled out.


Input Characteristics

The table below describes the inputs characteristics of the TM3DI16K:

Characteristic		Value
Number of input channels		16 inputs
Number of channels groups		1 common line on 2 pins for 16 channels
Input type		Type 1 (IEC/EN 61131-2)
Logic type		Sink/Source
Rated input voltage		24 Vdc
Input voltage range		19.2...28.8 Vdc
Rated input current		5 mA
Input impedance		4.4 kΩ
Input limit values	Voltage at state 1	> 15 Vdc (15...28.8 Vdc)
	Voltage at state 0	< 5 Vdc (0...5 Vdc)
	Current at state 1	> 2.5 mA
	Current at state 0	< 1.0 mA
Turn on time		SV ⁽¹⁾ < 2.0: 4 ms
Turn off time		SV ⁽¹⁾ ≥ 2.0: 100 μs ⁽²⁾
Isolation	Between input and internal logic	500 Vac
	Between input groups	N/A
Connection type		HE10 (MIL 20) connector
Connector insertion/removal durability		Over 100 times
Current draw on 5 Vdc internal bus		34 mA (all inputs on) 5 mA (all inputs off)
Current draw on 24 Vdc internal bus		0 mA (all inputs on) 0 mA (all inputs off)
<p>(1) SV refers to the version and is printed on the product label.</p> <p>(2) The range depends on the configured filter value. If you use EcoStruxure Machine Expert - Basic, refer to the Modicon TM3 (EcoStruxure Machine Expert - Basic) Expansion Modules Configuration - Programming Guide. If you use EcoStruxure Machine Expert, refer to the Modicon TM3 Expansion Modules - Programming Guide.</p>		

I/O Re-rating

When using TM3DI16K:



X Input simultaneous ON ratio

Y Input voltage

TM3DI16K Wiring Diagram

Introduction


This expansion module has a built-in HE10 (MIL 20) connector for the connection of inputs and power supply.

Wiring Rules

See Wiring Best Practices, page 36.

Wiring Diagram with Free-Wire Cables

The following figure illustrates the connection between the inputs, the sensors, and their commons:



The COM0 terminals are connected internally

A Sink wiring (positive logic)

B Source wiring (negative logic)

For information about 24 Vdc power supply, refer to DC Power Supply Characteristics, page 41.

For more information on the TWDFCW••K cable colors, refer to TWDFCW••K Cable Description, page 23.

TM3DI32K Module 32 Regular Inputs 24 Vdc

What's in This Chapter

TM3DI32K Presentation.....	66
TM3DI32K Characteristics	68
TM3DI32K Wiring Diagram	71

Overview

This chapter describes the TM3DI32K expansion module, its characteristics, and its connection to the different sensors.

TM3DI32K Presentation

Overview

TM3DI32K (HE10) digital expansion module:


- 32 channels
- 24 Vdc digital input
- 2 common lines
- Sink/source
- HE10 (MIL 20) connector

Main Characteristics

Characteristic		Value
Number of input channels		32
Input type		Type 1 (IEC/EN 61131-2)
Logic type		Sink/Source
Rated input voltage		24 Vdc
Connection type		HE10 (MIL 20) connectors
Cable type and length	Type	Unshielded
	Length	Maximum 30 m (98 ft)
Weight		100 g (3.52 oz)

Status LEDs

The following figure shows the status LEDs:



This table describes the status LEDs:

LED	Color	Status	Description
0...31	Green	On	The input channel is activated
		Off	The input channel is deactivated

TM3DI32K Characteristics

Introduction


This section provides a description of the input characteristics of the TM3DI32K expansion module.

See also Environmental Characteristics, page 25.

▲ WARNING
UNINTENDED EQUIPMENT OPERATION
Do not exceed any of the rated values specified in the environmental and electrical characteristics tables.
Failure to follow these instructions can result in death, serious injury, or equipment damage.

Dimensions

The following diagrams show the external dimensions for the TM3DI32K expansion module:



* 8.5 mm (0.33 in.) when the clamp is pulled out.


Input Characteristics

The table below describes the inputs characteristics of the TM3DI32K:

Characteristic		Value
Number of input channels		32 inputs
Number of channels groups		2 groups of 16, 1 common line each on 2 pins
Input type		Type 1 (IEC/EN 61131-2)
Logic type		Sink/Source
Rated input voltage		24 Vdc
Input voltage range		19.2...28.8 Vdc
Rated input current		5 mA
Input impedance		4.4 kΩ
Input limit values	Voltage at state 1	> 15 Vdc (15...28.8 Vdc)
	Voltage at state 0	< 5 Vdc (0...5 Vdc)
	Current at state 1	> 2.5 mA
	Current at state 0	< 1.0 mA
Turn on time		SV ⁽¹⁾ < 2.0: 4 ms
Turn off time		SV ⁽¹⁾ ≥ 2.0: 100 μs ⁽²⁾
Isolation	Between input and internal logic	500 Vac
	Between input groups	500 Vac
Connection type		HE10 (MIL 20) connectors
Connector insertion/removal durability		Over 100 times
Current draw on 5 Vdc internal bus		46 mA (all inputs on)
		5 mA (all inputs off)
Current draw on 24 Vdc internal bus		0 mA (all inputs on)
		0 mA (all inputs off)
<p>(1) SV refers to the version and is printed on the product label.</p> <p>(2) The range depends on the configured filter value. If you use EcoStruxure Machine Expert - Basic, refer to the Modicon TM3 (EcoStruxure Machine Expert - Basic) Expansion Modules Configuration - Programming Guide. If you use EcoStruxure Machine Expert, refer to the Modicon TM3 Expansion Modules - Programming Guide.</p>		

I/O Re-rating

When using TM3DI32K:



X Input simultaneous ON ratio

Y Input voltage

TM3DI32K Wiring Diagram

Introduction



This expansion module has a built-in HE10 (MIL 20) connector for the connection of inputs and power supply.

Wiring Rules

See Wiring Best Practices, page 36.

Wiring Diagram with Free-Wire Cables

The following figure illustrates the connection between the inputs, the sensors, and their commons:



The COM0 terminals are connected internally

The COM1 terminals are connected internally

The COM0 and COM1 terminals are **not** connected internally

A Sink wiring (positive logic)

B Source wiring (negative logic)

For information about 24 Vdc power supply, refer to DC Power Supply Characteristics, page 41.

For more information on the TWDFCW••K cable colors, refer to TWDFCW••K Cable Description, page 23.

TM3 Digital Output Modules

What's in This Part

TM3DQ8R / TM3DQ8RG Module 8 Relay Outputs 2A 24 Vdc/240 Vac.....	73
TM3DQ8T / TM3DQ8TG Module 8 Regular Transistor Source Outputs 0.5A 24 Vdc.....	79
TM3DQ8U / TM3DQ8UG Module 8 Regular Transistor Sink Outputs 0.5A 24 Vdc	84
TM3DQ16R / TM3DQ16RG Module 16 Relay Outputs 2A 24 Vdc/240 Vac	89
TM3DQ16T / TM3DQ16TG Module 16 Regular Transistor Source Outputs 0.5A 24 Vdc	95
TM3DQ16TK Module 16 Regular Transistor Source Outputs 0.1A 24 Vdc	100
TM3DQ16U / TM3DQ16UG Module 16 Regular Transistor Sink Outputs 0.5A 24 Vdc.....	105
TM3DQ16UK Module 16 Regular Transistor Sink Outputs 0.1A 24 Vdc	110
TM3DQ32TK Module 32 Regular Transistor Outputs 0.1A 24 Vdc.....	115
TM3DQ32UK Module 32 Regular Transistor Outputs 0.1A 24 Vdc	120

TM3DQ8R / TM3DQ8RG Module 8 Relay Outputs 2A 24 Vdc/240 Vac

What's in This Chapter

TM3DQ8R / TM3DQ8RG Presentation73
 TM3DQ8R / TM3DQ8RG Characteristics75
 TM3DQ8R / TM3DQ8RG Wiring Diagram78

Overview

This chapter describes the TM3DQ8R / TM3DQ8RG expansion modules, its characteristics and its connection to the different actuators.

TM3DQ8R / TM3DQ8RG Presentation

Overview

TM3DQ8R (screw) and TM3DQ8RG (spring) digital expansion module:

- 8 channels
- 2 A relay outputs
- 1 common line
- Removable screw or spring terminal block

Main Characteristics

Characteristic		Value
Number of output channels		8 outputs
Contact type		NO (Normally Open)
Output type		Relay
Rated output voltage		24 Vdc / 240 Vac
Rated output current		2 A
Connection type	TM3DQ8R	Removable screw terminal block
	TM3DQ8RG	Removable spring terminal block
Cable type and length	Type	Unshielded
	Length	Maximum 30 m (98 ft)
Weight		110 g (3.90 oz)

Status LEDs

The following figure shows the status LEDs:



This table describes the status LEDs:

LED	Color	Status	Description
0...7	Green	On	The output channel is activated.
		Off	The output channel is deactivated.

TM3DQ8R / TM3DQ8RG Characteristics

Introduction

This section provides a description of the power limitation and the output characteristics of the TM3DQ8R / TM3DQ8RG expansion modules.

See also Environmental Characteristics, page 25.

⚠ DANGER

FIRE HAZARD

- Use only the correct wire sizes for the maximum current capacity of the I/O channels and power supplies.
- For relay output (2 A) wiring, use conductors of at least 0.5 mm² (AWG 20) with a temperature rating of at least 80 °C (176 °F).
- For common conductors of relay output wiring (7 A), or relay output wiring greater than 2 A, use conductors of at least 1.0 mm² (AWG 16) with a temperature rating of at least 80 °C (176 °F).

Failure to follow these instructions will result in death or serious injury.

⚠ WARNING


UNINTENDED EQUIPMENT OPERATION

Do not exceed any of the rated values specified in the environmental and electrical characteristics tables.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

Dimensions

The following diagrams show the external dimensions for the TM3DQ8R / TM3DQ8RG expansion modules:



* 8.5 mm (0.33 in.) when the clamp is pulled out.

Output Characteristics

The table below describes the outputs characteristics of the TM3DQ8R / TM3DQ8RG:

Characteristic		Value
Number of output channels		8
Number of channel groups		2 common lines, one for each group of 4 channels
Output type		Relay
Contact type		NO (Normally Open)
Rated output voltage		24 Vdc, 240 Vac
Maximum voltage		30 Vdc, 264 Vac
Minimum switching load		5 Vdc at 10 mA
Rated output current		2 A
Maximum output current		2 A per output
		7 A per common
Maximum output frequency with maximum load		20 operations per minute
Turn on time		Maximum 10 ms
De-rating	-10...55 °C	No de-rating
	(14...131 °F)	
Turn off time		Maximum 10 ms
Contact resistance		30 mΩ max
Mechanical life		20 million operations
Electrical life	Under resistive load	See Power limitation, page 76
	Under inductive load	
Protection against short circuit		No
Isolation	Between output and internal logic	500 Vac
	Between channel groups	1500 Vac
Connection type	TM3DQ8R	Removable screw terminal block
	TM3DQ8RG	Removable spring terminal block
Connector insertion/removal durability		Over 100 times
Current draw on 5 Vdc internal bus		25 mA (all outputs on)
		5 mA (all outputs off)
Current draw on 24 Vdc internal bus		40 mA (all outputs on)
		0 mA (all outputs off)
<p>NOTE: Refer to Protecting Outputs from Inductive Load Damage, page 39 for additional information concerning output protection.</p>		

Power Limitation

This table describes the power limitations of the TM3DQ8R / TM3DQ8RG expansion module depending on the voltage, the type of load, and the number of operations required.

These expansion modules do not support capacitive loads.

⚠ WARNING

RELAY OUTPUTS WELDED CLOSED

- Always protect relay outputs from inductive alternating current load damage using an appropriate external protective circuit or device.
- Do not connect relay outputs to capacitive loads.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

Power Limitations				
Voltage	24 Vdc	120 Vac	240 Vac	Number of operations
Power of resistive loads	–	240 VA	480 VA	100,000
AC-12		80 VA	160 VA	300,000
Power of inductive loads	–	60 VA	120 VA	100,000
AC-15 (cos ϕ = 0.35)		18 VA	36 VA	300,000
Power of inductive loads	–	120 VA	240 VA	100,000
AC-14 (cos ϕ = 0.7)		36 VA	72 VA	300,000
Power of resistive loads	48 W	–	–	100,000
DC-12	16 W			300,000
Power of inductive loads	24 W	–	–	100,000
DC-13 L/R = 7 ms	7.2 W			300,000

TM3DQ8R / TM3DQ8RG Wiring Diagram

Introduction


These expansion modules have a built-in removable screw or spring terminal block for the connection of outputs and power supply.

Wiring Rules

See Wiring Best Practices, page 36.

Wiring Diagram

The following figure illustrates the connections between the outputs, the actuators, and their commons:



* Type T fuse

(1) The COM0 and COM1 terminals are not connected internally

(2) To improve the life time of the contacts, and to protect from potential inductive load damage, connect a free wheeling diode in parallel to each inductive DC load or an RC snubber in parallel of each inductive AC load, or a varistor on either type of load.

A Source wiring (positive logic)

B Sink wiring (negative logic)

NOTE: When you use the TM3 expansion module with a TM3 Ethernet bus coupler, you must connect an RC snubber in parallel of each inductive AC load.

For information about 24 Vdc power supply, refer to DC Power Supply Characteristics, page 41.

▲ WARNING

UNINTENDED EQUIPMENT OPERATION

Do not connect wires to unused terminals and/or terminals indicated as “No Connection (N.C.)”.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

TM3DQ8T / TM3DQ8TG Module 8 Regular Transistor Source Outputs 0.5A 24 Vdc

What's in This Chapter

TM3DQ8T / TM3DQ8TG Presentation	79
TM3DQ8T / TM3DQ8TG Characteristics	81
TM3DQ8T / TM3DQ8TG Wiring Diagram	83

Overview

This chapter describes the TM3DQ8T / TM3DQ8TG module, its characteristics, and its connection to the different actuators.

TM3DQ8T / TM3DQ8TG Presentation

Overview

TM3DQ8T (screw) and TM3DQ8TG (spring) digital expansion module:

- 8 channels
- 0.5 A source outputs
- 1 common line
- Removable screw or spring terminal block

Main Characteristics

Characteristic		Value
Number of output channels		8
Logic type		Source
Rated output voltage		24 Vdc
Rated output current		0.5 A
Connection type	TM3DQ8T	Removable screw terminal block
	TM3DQ8TG	Removable spring terminal block
Cable type and length	Type	Unshielded
	Length	Maximum 30 m (98 ft)
Weight		76 g (2.7 oz)

Status LEDs

The following figure shows the status LEDs:



This table describes the status LEDs:

LED	Color	Status	Description
0...7	Green	On	The output channel is activated
		Off	The output channel is deactivated

TM3DQ8T / TM3DQ8TG Characteristics

Introduction


This section provides a description of the output characteristics of the TM3DQ8T / TM3DQ8TG expansion modules.

See also Environmental Characteristics, page 25.

⚠ WARNING
UNINTENDED EQUIPMENT OPERATION
Do not exceed any of the rated values specified in the environmental and electrical characteristics tables.
Failure to follow these instructions can result in death, serious injury, or equipment damage.

Dimensions

The following diagrams show the external dimensions for the TM3DQ8T / TM3DQ8TG expansion modules:



* 8.5 mm (0.33 in.) when the clamp is pulled out.

Output Characteristics

The table below describes the outputs characteristics of the TM3DQ8T / TM3DQ8TG:

Characteristic		Value
Number of output channels		8
Number of channel groups		1 common line for 8 channels
Output type		Transistor
Logic type		Source
Rated output voltage		24 Vdc
Output voltage range		19.2...28.8 Vdc
Rated output current		0.5 A maximum per channel
Total output current per group		4 A
Voltage drop		0.4 Vdc maximum
Leakage current when switched off		0.1 mA maximum
Maximum power of filament lamp		12 W
Inductive load		L/R = 10 ms
De-rating	- 10...55 °C (14...131 °F)	No de-rating
Turn on time		450 µs
Turn off time		450 µs
Protection against short circuit		Yes
Short circuit output peak current		1 A typically
Automatic rearming after short circuit or overload		Yes, time depending on the expansion module temperature
Protection against reverse polarity		Yes
Clamping voltage		Typically 50 Vdc
Switching frequency	Under resistive load	100 Hz maximum
Isolation	Between output and internal logic	500 Vac
	Between channel group	N/A
Connection type	TM3DQ8T	Removable screw terminal block
	TM3DQ8TG	Removable spring terminal block
Connector insertion/removal durability		Over 100 times
Current draw on 5 Vdc internal bus		17 mA (all outputs on) 5 mA (all outputs off)
Current draw on 24 Vdc internal bus		8 mA (all outputs on) 0 mA (all outputs off)
<p>NOTE: Refer to Protecting Outputs from Inductive Load Damage, page 39 for additional information concerning output protection.</p>		

TM3DQ8T / TM3DQ8TG Wiring Diagram

Introduction


These expansion modules have a built-in removable screw or spring terminal block for the connection of outputs and power supply.

Wiring Rules

See Wiring Best Practices, page 36.

Wiring Diagram

The following figure illustrates the connections between the outputs, the actuators, and their commons:



* Type T fuse

(1) The V+ terminals are connected internally.

For information about 24 Vdc power supply, refer to DC Power Supply Characteristics, page 41.

TM3DQ8U / TM3DQ8UG Module 8 Regular Transistor Sink Outputs 0.5A 24 Vdc

What's in This Chapter

TM3DQ8U / TM3DQ8UG Presentation	84
TM3DQ8U / TM3DQ8UG Characteristics	86
TM3DQ8U / TM3DQ8UG Wiring Diagram	88

Overview

This chapter describes the TM3DQ8U / TM3DQ8UG module, its characteristics, and its connection to the different actuators.

TM3DQ8U / TM3DQ8UG Presentation

Overview

TM3DQ8U (screw) and TM3DQ8UG (spring) digital expansion module:

- 8-channels
- 0.5 A sink outputs
- 1 common line
- Removable screw or spring terminal block

Main Characteristics

Characteristic		Value
Number of output channels		8
Logic type		Sink
Rated output voltage		24 Vdc
Rated output current		0.5 A
Connection type	TM3DQ8U	Removable screw terminal block
	TM3DQ8UG	Removable spring terminal block
Cable type and length	Type	Unshielded
	Length	Maximum 30 m (98 ft)
Weight		76 g (2.7 oz)

Status LEDs

The following figure shows the status LEDs:



This table describes the status LEDs:

LED	Color	Status	Description
0...7	Green	On	The output channel is activated.
		Off	The output channel is deactivated.

TM3DQ8U / TM3DQ8UG Characteristics

Introduction

This section provides a description of the electrical and output characteristics of the TM3DQ8U / TM3DQ8UG expansion modules.

See also Environmental Characteristics, page 25.

⚠ WARNING


UNINTENDED EQUIPMENT OPERATION

Do not exceed any of the rated values specified in the environmental and electrical characteristics tables.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

Dimensions

The following diagrams show the external dimensions for the TM3DQ8U / TM3DQ8UG expansion modules:



* 8.5 mm (0.33 in.) when the clamp is pulled out.

Output Characteristics

The table below describes the outputs characteristics of the TM3DQ8U / TM3DQ8UG:

Characteristic		Value
Number of output channels		8
Number of channel groups		1 common line for 8 channels
Output type		Transistor
Logic type		Sink
Rated output voltage		24 Vdc
Output voltage range		19.2...28.8 Vdc
Rated output current		0.5 A maximum per channel
Total output current per group		4 A
Voltage drop		0.4 V maximum
Leakage current when switched off		0.1 mA maximum
Maximum power of filament lamp		12 W
Inductive load		L/R = 10 ms
De-rating	- 10...55 °C (14...131 °F)	No de-rating
Turn on time		450 µs
Turn off time		450 µs
Protection against short circuit		No Fast external fuse required
Short circuit output peak current		N/A
Automatic rearming after short circuit or overload		N/A
Protection against reverse polarity		No
Clamping voltage		Typically 50 Vdc
Switching frequency	Under resistive load	100 Hz maximum
Isolation	Between output and internal logic	500 Vac
	Between channel group	N/A
Connection type	TM3DQ8U	Removable screw terminal block
	TM3DQ8UG	Removable spring terminal block
Connector insertion/removal durability		Over 100 times
Current draw on 5 Vdc internal bus		17 mA (all outputs on) 5 mA (all outputs off)
Current draw on 24 Vdc internal bus		8 mA (all outputs on) 0 mA (all outputs off)
<p>NOTE: Refer to Protecting Outputs from Inductive Load Damage, page 39 for additional information concerning output protection.</p>		

TM3DQ8U / TM3DQ8UG Wiring Diagram

Introduction


These expansion modules have a built-in removable screw or spring terminal block for the connection of outputs and power supply.

Wiring Rules

See Wiring Best Practices, page 36.

Wiring Diagram

The following figure illustrates the connections between the outputs, the actuators, and their commons:



* Type T fuse

** Type F fuse

(1) The V- terminals are connected internally.

For information about 24 Vdc power supply, refer to DC Power Supply Characteristics, page 41.

TM3DQ16R / TM3DQ16RG Module 16 Relay Outputs 2A 24 Vdc/240 Vac

What's in This Chapter

TM3DQ16R / TM3DQ16RG Presentation.....	89
TM3DQ16R / TM3DQ16RG Characteristics	91
TM3DQ16R / TM3DQ16RG Wiring Diagram.....	94

Overview

This chapter describes the TM3DQ16R / TM3DQ16RG expansion modules, its characteristics, and its connection to the different actuators.

TM3DQ16R / TM3DQ16RG Presentation

Overview

TM3DQ16R (screw) and TM3DQ16RG (spring) digital expansion module:


- 16 channels
- 2 A relay outputs
- 2 common lines
- Removable screw or spring terminal blocks

Main Characteristics

Characteristic		Value
Number of output channels		16 outputs
Contact type		NO (Normally Open)
Output type		Relay
Rated output voltage		24 Vdc, 240 Vac
Rated output current		2 A
Connection type	TM3DQ16R	Removable screw terminal blocks
	TM3DQ16RG	Removable spring terminal blocks
Cable type and length	Type	Unshielded
	Length	Maximum 30 m (98 ft)
Weight		145 g (5.11 oz)

Status LEDs

The following figure shows the status LEDs:



This table describes the status LEDs:

LED	Color	Status	Description
0...15	Green	On	The output channel is activated
		Off	The output channel is deactivated

TM3DQ16R / TM3DQ16RG Characteristics

Introduction


This section provides a description of the electrical and the output characteristics of the TM3DQ16R / TM3DQ16RG expansion modules.

See also Environmental Characteristics, page 25.

⚠ WARNING
UNINTENDED EQUIPMENT OPERATION
Do not exceed any of the rated values specified in the environmental and electrical characteristics tables.
Failure to follow these instructions can result in death, serious injury, or equipment damage.

Dimensions

The following diagrams show the external dimensions for the TM3DQ16R / TM3DQ16RG expansion modules:



* 8.5 mm (0.33 in.) when the clamp is pulled out.

Output Characteristics

The table below describes the outputs characteristics of the TM3DQ16R / TM3DQ16RG:

Characteristic		Value
Number of output channels		8
Number of channel groups		2 common lines, one on 2 terminals for each group of 8 channels
Output type		Relay
Contact type		NO (Normally Open)
Rated output voltage		24 Vdc, 240 Vac
Maximum voltage		30 Vdc, 264 Vac
Minimum switching load		5 Vdc at 10 mA
Rated output current		2 A
Maximum output current		2 A per output
		8 A per common
Maximum output frequency	With maximum load	20 operations per minute
De-rating	-10...55 °C (14...131 °F)	No de-rating
Turn on time		Maximum 10 ms
Turn off time		Maximum 10 ms
Contact resistance		30 mΩ max
Mechanical life		20 million operations
Electrical life	Under resistive load	See Power limitation, page 92
	Under inductive load	
Protection against short circuit		No
Isolation	Between output and internal logic	500 Vac
	Between channel groups	1500 Vac
Connection type	TM3DQ16R	Removable screw terminal block
	TM3DQ16RG	Removable spring terminal block
Connector insertion/removal durability		Over 100 times
Current draw on 5 Vdc internal bus		37 mA (all outputs on)
		5 mA (all outputs off)
Current draw on 24 Vdc internal bus		77 mA (all outputs on)
		0 mA (all outputs off)
<p>NOTE: Refer to Protecting Outputs from Inductive Load Damage, page 39 for additional information concerning output protection.</p>		

Power Limitation

This table describes the power limitation of the TM3DQ16R / TM3DQ16RG expansion modules depending on the voltage, the type of load, and the number of operations required.

These expansion modules do not support capacitive loads.

⚠ WARNING

RELAY OUTPUTS WELDED CLOSED

- Always protect relay outputs from inductive alternating current load damage using an appropriate external protective circuit or device.
- Do not connect relay outputs to capacitive loads.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

Power Limitations				
Voltage	24 Vdc	120 Vac	240 Vac	Number of operations
Power of resistive loads	–	240 VA	480 VA	100,000
AC-12		80 VA	160 VA	300,000
Power of inductive loads	–	60 VA	120 VA	100,000
AC-15 (cos ϕ = 0.35)		18 VA	36 VA	300,000
Power of inductive loads	–	120 VA	240 VA	100,000
AC-14 (cos ϕ = 0.7)		36 VA	72 VA	300,000
Power of resistive loads	48 W	–	–	100,000
DC-12	16 W			300,000
Power of inductive loads	24 W	–	–	100,000
DC-13 L/R = 7 ms	7.2 W			300,000

TM3DQ16R / TM3DQ16RG Wiring Diagram

Introduction


These expansion modules have a built-in removable screw or spring terminal block for the connection of the outputs and power supply.

Wiring Rules

See Wiring Best Practices, page 36.

Wiring Diagram

The following figure illustrates the connections between the outputs, the actuators, and their commons:



* Type T fuse

(1) The COM0 and COM1 terminals are **not** connected internally.

(2) To improve the life time of the contacts, and to protect from potential inductive load damage, connect a free wheeling diode in parallel to each inductive DC load or an RC snubber in parallel of each inductive AC load, or a varistor on either type of load.

A Source wiring (positive logic)

B Sink wiring (negative logic)

NOTE: When you use the TM3 expansion module with a TM3 Ethernet bus coupler, you must connect an RC snubber in parallel of each inductive AC load.

For information about 24 Vdc power supply, refer to DC Power Supply Characteristics, page 41.

TM3DQ16T / TM3DQ16TG Module 16 Regular Transistor Source Outputs 0.5A 24 Vdc

What's in This Chapter

TM3DQ16T / TM3DQ16TG Presentation	95
TM3DQ16T / TM3DQ16TG Characteristics	97
TM3DQ16T / TM3DQ16TG Wiring Diagram	99

Overview

This chapter describes the TM3DQ16T / TM3DQ16TG expansion module, its characteristics, and its connection to the different actuators.

TM3DQ16T / TM3DQ16TG Presentation

Overview

TM3DQ16T (screw), TM3DQ16TG (spring) digital expansion module:


- 16 channels
- 0.5 A source outputs
- 1 common line
- Removable screw or spring terminal block

Main Characteristics

Characteristic		Value
Number of output channels		16
Logic type		Source
Rated output voltage		24 Vdc
Rated output current		0.5 A
Connection type	TM3DQ16T	Removable screw terminal blocks
	TM3DQ16TG	Removable spring terminal blocks
Cable type and length	Type	Unshielded
	Length	Maximum 30 m (98 ft)
Weight		110 g (3.90 oz)

Status LEDs

The following figures show the status LEDs:



This table describes the status LEDs:

LED	Color	Status	Description
0...15	Green	On	The output channel is activated
		Off	The output channel is deactivated

TM3DQ16T / TM3DQ16TG Characteristics

Introduction


This section provides a description of the electrical and the output characteristics of the TM3DQ16T / TM3DQ16TG expansion modules.

See also Environmental Characteristics, page 25.

▲ WARNING
UNINTENDED EQUIPMENT OPERATION
Do not exceed any of the rated values specified in the environmental and electrical characteristics tables.
Failure to follow these instructions can result in death, serious injury, or equipment damage.

Dimensions

The following diagrams show the external dimensions for the TM3DQ16T / TM3DQ16TG expansion modules:



* 8.5 mm (0.33 in) when the clamp is pulled out.

Output Characteristics

The table below describes the outputs characteristics of the TM3DQ16T and TM3DQ16TG:

Characteristic		Value
Number of output channels		16
Number of channel groups		1 common line on 2 terminals for 16 channels
Output type		Transistor
Logic type		Source
Rated output voltage		24 Vdc
Output voltage range		19.2...28.8 Vdc
Rated output current		0.5 A
Total output current per group		8 A
Voltage drop		0.4 Vdc maximum
Leakage current when switched off		0.1 mA maximum
Maximum power of filament lamp		3 W
Inductive load		L/R = 10 ms
De-rating	- 10...55 °C (14...131 °F)	No de-rating
Turn on time		450 µs
Turn off time		450 µs
Protection against short circuit		Yes
Short circuit output peak current		1 A typically
Automatic rearming after short circuit or overload		Yes, time depending on component temperature
Protection against reverse polarity		Yes
Clamping voltage		Typically 50 Vdc
Switching frequency	Under resistive load	100 Hz maximum
Isolation	Between output and internal logic	500 Vac
	Between channel group	N/A
Connection type	TM3DQ16T	Removable screw terminal blocks
	TM3DQ16TG	Removable spring terminal blocks
Connector insertion/removal durability		Over 100 times
Current draw on 5 Vdc internal bus		20 mA (all outputs on) 5 mA (all outputs off)
Current draw on 24 Vdc internal bus		16 mA (all outputs on) 0 mA (all outputs off)
<p>NOTE: Refer to Protecting Outputs from Inductive Load Damage, page 39 for additional information concerning output protection.</p>		

TM3DQ16T / TM3DQ16TG Wiring Diagram

Introduction


These expansion modules have a built-in removable screw or spring terminal block for the connection of outputs and power supply.

Wiring Rules

See Wiring Best Practices, page 36.

Wiring Diagram

The following figure illustrates the connections between the outputs, the actuators, and their commons:



* Type T fuse

For information about 24 Vdc power supply, refer to DC Power Supply Characteristics, page 41.

TM3DQ16TK Module 16 Regular Transistor Source Outputs 0.1A 24 Vdc

What's in This Chapter

TM3DQ16TK Presentation	100
TM3DQ16TK Characteristics.....	102
TM3DQ16TK Wiring Diagram.....	104

Overview

This chapter describes the TM3DQ16TK expansion module, its characteristics, and its connection to the different actuators.

TM3DQ16TK Presentation

Overview

TM3DQ16TK (HE10) digital expansion module:


- 16 channels
- 0.1 A source outputs
- 1 common line
- HE10 (MIL 20) connector

Main Characteristics

Characteristic		Value
Number of output channels		16
Logic type		Source
Rated output voltage		24 Vdc
Rated output current		0.1 A
Connection type	TM3DQ16TK	HE10 (MIL 20) connector
Cable type and length	Type	Unshielded
	Length	Maximum 5 m (16 ft)
Weight		72 g (2.54 oz)

Status LEDs

The following figures show the status LEDs:



This table describes the status LEDs:

LED	Color	Status	Description
0...15	Green	On	The output channel is activated
		Off	The output channel is deactivated

TM3DQ16TK Characteristics

Introduction

This section provides a description of the electrical and the output characteristics of the TM3DQ16TK expansion module.

See also Environmental Characteristics, page 25.

⚠ WARNING


UNINTENDED EQUIPMENT OPERATION

Do not exceed any of the rated values specified in the environmental and electrical characteristics tables.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

Dimensions

The following diagrams show the external dimensions for the TM3DQ16TK expansion module:



* 8.5 mm (0.33 in) when the clamp is pulled out.

Output Characteristics

The table below describes the outputs characteristics of the TM3DQ16TK:

Characteristic		Value
Number of output channels		16
Number of channel groups		1 common line on 2 pins for 16 channels
Output type		Transistor
Logic type		Source
Rated output voltage		24 Vdc
Output voltage range		19.2...28.8 Vdc
Rated output current		0.1 A maximum per channel
Total output current per group		2 A
Voltage drop		0.4 Vdc maximum
Leakage current when switched off		0.1 mA maximum
Maximum power of filament lamp		9.6 W
Inductive load		L/R = 10 ms
De-rating	- 10...55 °C (14...131 °F)	No de-rating
Turn on time		450 µs
Turn off time		450 µs
Protection against short circuit		Yes
Short circuit output peak current		1 A typically
Automatic rearming after short circuit or overload		Yes, time depending on component temperature
Protection against reverse polarity		Yes
Clamping voltage		Typically 50 Vdc
Switching frequency	Under resistive load	100 Hz maximum
Isolation	Between output and internal logic	500 Vac
	Between channel group	N/A
Connection type		HE10 (MIL 20) connector
Connector insertion/removal durability		Over 100 times
Current draw on 5 Vdc internal bus		20 mA (all outputs on) 5 mA (all outputs off)
Current draw on 24 Vdc internal bus		16 mA (all outputs on) 0 mA (all outputs off)
<p>NOTE: Refer to Protecting Outputs from Inductive Load Damage, page 39 for additional information concerning output protection.</p>		

TM3DQ16TK Wiring Diagram

Introduction


This expansion module has a built-in HE10 (MIL 20) connector for the connection of outputs and power supply.

Wiring Rules

See Wiring Best Practices, page 36.

Wiring Diagram with Free-Wire Cables

The following figure illustrates the connections between the outputs, the actuators, and their commons:



* Type T fuse

For information about 24 Vdc power supply, refer to DC Power Supply Characteristics, page 41.

For more information on the TWDFCW••K cable colors, refer to TWDFCW••K Cable Description, page 23.

TM3DQ16U / TM3DQ16UG Module 16 Regular Transistor Sink Outputs 0.5A 24 Vdc

What's in This Chapter

TM3DQ16U / TM3DQ16UG Presentation.....	105
TM3DQ16U / TM3DQ16UG Characteristics	107
TM3DQ16U / TM3DQ16UG Wiring Diagram.....	109

Overview

This chapter describes the TM3DQ16U / TM3DQ16UG expansion module, its characteristics, and its connection to the different actuators.

TM3DQ16U / TM3DQ16UG Presentation

Overview

TM3DQ16U (screw) and TM3DQ16UG (spring) digital expansion module:


- 16 channels
- 0.5 A sink outputs
- 1 common line
- Removable screw or spring terminal block

Main Characteristics

Characteristic		Value
Number of output channels		16
Logic type		Sink
Rated output voltage		24 Vdc
Rated output current		0.5 A
Connection type	TM3DQ16U	Removable screw terminal blocks
	TM3DQ16UG	Removable spring terminal blocks
Cable type and length	Type	Unshielded
	Length	Maximum 30 m (98 ft)
Weight		76 g (2.70 oz)

Status LEDs

The following figures show the status LEDs:



This table describes the status LEDs:

LED	Color	Status	Description
0...15	Green	On	The output channel is activated
		Off	The output channel is deactivated

TM3DQ16U / TM3DQ16UG Characteristics

Introduction

This section provides a description of the electrical and the output characteristics of the TM3DQ16U / TM3DQ16UG expansion modules.

See also Environmental Characteristics, page 25.

⚠ WARNING


UNINTENDED EQUIPMENT OPERATION

Do not exceed any of the rated values specified in the environmental and electrical characteristics tables.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

Dimensions

The following diagrams show the external dimensions for the TM3DQ16U / TM3DQ16UG expansion modules:



* 8.5 mm (0.33 in) when the clamp is pulled out.

Output Characteristics

The table below describes the outputs characteristics of the TM3DQ16U and TM3DQ16UG:

Characteristic		Value
Number of output channels		16
Number of channel groups		1 common line on 2 pins for 16 channels
Output type		Transistor
Logic type		Sink
Rated output voltage		24 Vdc
Output voltage range		19.2...28.8 Vdc
Rated output current		0.5 A
Total output current		8 A
Voltage drop		0.4 Vdc maximum
Leakage current when switched off		0.1 mA maximum
Maximum power of filament lamp		12 W
Inductive load		L/R = 10 ms
De-rating	- 10...55 °C (14...131 °F)	No de-rating
Turn on time		450 µs
Turn off time		450 µs
Protection against short circuit		No Fast external fuse required
Short circuit output peak current		N/A
Automatic rearming after short circuit or overload		N/A
Protection against reverse polarity		No
Clamping voltage		Typically 50 Vdc
Switching frequency	Under resistive load	100 Hz maximum
Isolation	Between output and internal logic	500 Vac
	Between channel group	N/A
Connection type	TM3DQ16U	Removable screw terminal blocks
	TM3DQ16UG	Removable spring terminal blocks
Connector insertion/removal durability		Over 100 times
Current draw on 5 Vdc internal bus		20 mA (all outputs on) 5 mA (all outputs off)
Current draw on 24 Vdc internal bus		16 mA (all outputs on) 0 mA (all outputs off)
<p>NOTE: Refer to Protecting Outputs from Inductive Load Damage, page 39 for additional information concerning output protection.</p>		

TM3DQ16U / TM3DQ16UG Wiring Diagram

Introduction


These expansion modules have a built-in removable screw or spring terminal block connector for the connection of outputs and power supply.

Wiring Rules

See Wiring Best Practices, page 36.

Wiring Diagram

The following figure illustrates the connections between the outputs, the actuators, and their commons:



* Type T fuse

** Type F fuse

For information about 24 Vdc power supply, refer to DC Power Supply Characteristics, page 41.

TM3DQ16UK Module 16 Regular Transistor Sink Outputs 0.1A 24 Vdc

What's in This Chapter

TM3DQ16UK Presentation	110
TM3DQ16UK Characteristics	112
TM3DQ16UK Wiring Diagram	114

Overview

This chapter describes the TM3DQ16UK expansion module, its characteristics, and its connection to the different actuators.

TM3DQ16UK Presentation

Overview

TM3DQ16UK (HE10) digital expansion module:


- 16 channels
- 0.1 A sink outputs
- 1 common line
- HE10 (MIL 20) connector

Main Characteristics

Characteristic		Value
Number of output channels		16
Logic type		Sink
Rated output voltage		24 Vdc
Rated output current		0.1 A
Connection type		HE10 (MIL 20) connector
Cable type and length	Type	Unshielded
	Length	Maximum 5 m (16 ft)
Weight		111 g (3.90 oz)

Status LEDs

The following figures show the status LEDs:



This table describes the status LEDs:

LED	Color	Status	Description
0...15	Green	On	The output channel is activated
		Off	The output channel is deactivated

TM3DQ16UK Characteristics

Introduction

This section provides a description of the electrical and the output characteristics of the TM3DQ16UK expansion module.

See also Environmental Characteristics, page 25.

⚠ WARNING


UNINTENDED EQUIPMENT OPERATION

Do not exceed any of the rated values specified in the environmental and electrical characteristics tables.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

Dimensions

The following diagrams show the external dimensions for the TM3DQ16UK expansion module:



* 8.5 mm (0.33 in) when the clamp is pulled out.

Output Characteristics

The table below describes the outputs characteristics of the TM3DQ16UK:

Characteristic		Value
Number of output channels		16
Number of channel groups		1 common line on 2 pins for 16 channels
Output type		Transistor
Logic type		Sink
Rated output voltage		24 Vdc
Output voltage range		19.2...28.8 Vdc
Rated output current		0.1 A
Total output current per group		2 A
Voltage drop		0.4 Vdc maximum
Leakage current when switched off		0.1 mA maximum
Maximum power of filament lamp		2.4 W
Inductive load		L/R = 10 ms
De-rating	- 10...55 °C (14...131 °F)	No de-rating
Turn on time		450 µs
Turn off time		450 µs
Protection against short circuit		No Fast external fuse required
Short circuit output peak current		N/A
Automatic rearming after short circuit or overload		N/A
Protection against reverse polarity		No
Clamping voltage		Typically 50 Vdc
Switching frequency	Under resistive load	100 Hz maximum
Isolation	Between output and internal logic	500 Vac
	Between channel group	N/A
Connection type		HE10 (MIL 20) connector
Connector insertion/removal durability		Over 100 times
Current draw on 5 Vdc internal bus		20 mA (all outputs on) 5 mA (all outputs off)
Current draw on 24 Vdc internal bus		16 mA (all outputs on) 0 mA (all outputs off)
<p>NOTE: Refer to Protecting Outputs from Inductive Load Damage, page 39 for additional information concerning output protection.</p>		

TM3DQ16UK Wiring Diagram

Introduction

These expansion modules have a built-in HE10 (MIL 20) connector for the connection of outputs and power supply.


Telefast sub-bases are not compatible with this module.

Wiring Rules

See Wiring Best Practices, page 36.

Wiring Diagram

The following figure illustrates the connections between the outputs, the actuators, and their commons:



* Type T fuse

** Type F fuse

For information about 24 Vdc power supply, refer to DC Power Supply Characteristics, page 41.

TM3DQ32TK Module 32 Regular Transistor Outputs 0.1A 24 Vdc

What's in This Chapter

TM3DQ32TK Presentation..... 115
 TM3DQ32TK Characteristics..... 117
 TM3DQ32TK Wiring Diagram..... 119

Overview

This chapter describes the TM3DQ32TK expansion module, its characteristics, and its connection to the different actuators.

TM3DQ32TK Presentation

Overview

TM3DQ32TK (HE10) digital expansion module:


- 32 channels
- 0.1 A source outputs
- 2 common lines
- HE10 (MIL 20) connector

Main Characteristics

Characteristic		Value
Number of output channels		32
Logic type		Source
Rated output voltage		24 Vdc
Rated output current		0.1 A
Connection type		HE10 (MIL 20) connectors
Cable type and length	Type	Unshielded
	Length	Maximum 5 m (16 ft)
Weight		112 g (3.90 oz)

Status LEDs

The following figure shows the status LEDs:



This table describes the status LEDs:

LED	Color	Status	Description
0...31	Green	On	The output channel is activated
		Off	The output channel is deactivated

TM3DQ32TK Characteristics

Introduction


This section provides a description of the electrical and output characteristics of the TM3DQ32TK expansion module.

See also Environmental Characteristics, page 25.

⚠ WARNING
UNINTENDED EQUIPMENT OPERATION
Do not exceed any of the rated values specified in the environmental and electrical characteristics tables.
Failure to follow these instructions can result in death, serious injury, or equipment damage.

Dimensions

The following diagrams show the external dimensions for the TM3DQ32TK expansion modules:



* 8.5 mm (0.33 in) when the clamp is pulled out.

Output Characteristics

The table below describes the outputs characteristics of the TM3DQ32TK:

Characteristic	Value	
Number of output channels	32	
Number of channel groups	2 groups of 16 channels, 1 common line each on 2 pins	
Output type	Transistor	
Logic type	Source	
Rated output voltage	24 Vdc	
Output voltage range	19.2...28.8 Vdc	
Rated output current	0.1 A	
Total output current per group	2 A	
Voltage drop	0.4 Vdc maximum	
Leakage current when switched off	0.1 mA maximum	
Maximum power of filament lamp	2.4 W	
Inductive load	L/R = 10 ms	
De-rating	- 10...55 °C (14...131 °F)	No de-rating
Turn on time	450 µs	
Turn off time	450 µs	
Protection against short circuit	Yes	
Short circuit output peak current	1 A typically	
Automatic rearming after short circuit or overload	Yes, time depending on component temperature	
Protection against reverse polarity	Yes	
Clamping voltage	Typically 50 Vdc	
Switching frequency	Under resistive load	100 Hz maximum
Isolation	Between output and internal logic	500 Vac
Connection type	HE10 (MIL 20) connectors	
Connector insertion/removal durability	Over 100 times	
Current draw on 5 Vdc internal bus	27 mA (all outputs on) 5 mA (all outputs off)	
Current draw on 24 Vdc internal bus	31 mA (all outputs on) 0 mA (all outputs off)	
NOTE: Refer to Protecting Outputs from Inductive Load Damage, page 39 for additional information concerning output protection.		

TM3DQ32TK Wiring Diagram

Introduction


These expansion modules have two built-in HE10 (MIL 20) connectors for the connection of outputs and power supply.

Wiring Rules

See Wiring Best Practices, page 36.

Wiring Diagram with Free-Wire Cables

The following figure illustrates the connections between the outputs, the actuators, and their commons:



* Type T fuse

(1) The V0+ terminals are connected internally.

The V0- terminals are connected internally.

The V1+ terminals are connected internally.

The V1- terminals are connected internally.

The V0+ and V1+ terminals are not connected internally.

The V0- and V1- terminals are not connected internally.

For information about 24 Vdc power supply, refer to DC Power Supply Characteristics, page 41.

For more information on the TWDFCW••K cable colors, refer to TWDFCW••K Cable Description, page 23.

TM3DQ32UK Module 32 Regular Transistor Outputs 0.1A 24 Vdc

What's in This Chapter

TM3DQ32UK Presentation	120
TM3DQ32UK Characteristics	122
TM3DQ32UK Wiring Diagram	123

Overview

This chapter describes the TM3DQ32UK expansion module, its characteristics, and its connection to the different actuators.

TM3DQ32UK Presentation

Overview

TM3DQ32UK (HE10) digital expansion module:


- 32 channels
- 0.1 A sink outputs
- 2 common lines
- HE10 (MIL 20) connector

Main Characteristics

Characteristic		Value
Number of output channels		32
Logic type		Sink
Rated output voltage		24 Vdc
Rated output current		0.1 A
Connection type		HE10 (MIL 20) connectors
Cable type and length	Type	Unshielded
	Length	Maximum 5 m (16 ft)
Weight		112 g (3.90 oz)

Status LEDs

The following figure shows the status LEDs:



This table describes the status LEDs:

LED	Color	Status	Description
0...31	Green	On	The output channel is activated
		Off	The output channel is deactivated

TM3DQ32UK Characteristics

Introduction

This section provides a description of the electrical and output characteristics of the TM3DQ32UK expansion module.

See also Environmental Characteristics, page 25.

⚠ WARNING


UNINTENDED EQUIPMENT OPERATION

Do not exceed any of the rated values specified in the environmental and electrical characteristics tables.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

Dimensions

The following diagrams show the external dimensions for the TM3DQ32UK expansion module:



* 8.5 mm (0.33 in) when the clamp is pulled out.

Output Characteristics

The table below describes the outputs characteristics of the TM3DQ32UK:

Characteristic	Value
Number of output channels	32
Number of channel groups	2 groups of 16 channels, 1 common line each on 2 pins
Output type	Transistor
Logic type	Sink
Rated output voltage	24 Vdc
Output voltage range	19.2...28.8 Vdc
Rated output current	0.1 A
Total output current per group	2 A
Voltage drop	0.4 Vdc maximum
Leakage current when switched off	0.1 mA maximum
Maximum power of filament lamp	2.4 W
Inductive load	L/R = 10 ms
De-rating	- 10...55 °C (14...131 °F) No de-rating
Turn on time	450 µs
Turn off time	450 µs
Protection against short circuit	No Fast external fuse required
Short circuit output peak current	N/A
Automatic rearming after short circuit or overload	N/A
Protection against reverse polarity	Yes
Clamping voltage	Typically 50 Vdc
Switching frequency	Under resistive load 100 Hz maximum
Isolation	Between output and internal logic 500 Vac
Connection type	HE10 (MIL 20) connectors
Connector insertion/removal durability	Over 100 times
Current draw on 5 Vdc internal bus	27 mA (all outputs on) 5 mA (all outputs off)
Current draw on 24 Vdc internal bus	31 mA (all outputs on) 0 mA (all outputs off)

NOTE: Refer to Protecting Outputs from Inductive Load Damage, page 39 for additional information concerning output protection.

TM3DQ32UK Wiring Diagram

Introduction

These expansion modules have two built-in HE10 (MIL 20) connectors for the connection of outputs and power supply.


Telefast sub-bases are not compatible with this module.

Wiring Rules

See Wiring Best Practices, page 36.

Wiring Diagram

The following figure illustrates the connections between the outputs, the actuators, and their commons:



* Type T fuse

** Type F fuse

(1) The V0+ terminals are connected internally.

The V0- terminals are connected internally.

The V1+ terminals are connected internally.

The V1- terminals are connected internally.

The V0+ and V1+ terminals are not connected internally.

The V0- and V1- terminals are not connected internally.

For information about 24 Vdc power supply, refer to DC Power Supply Characteristics, page 41.

TM3 Digital Mixed Input/Output Modules

What's in This Part

TM3DM8R / TM3DM8RG Mixed I/O Module 4 Inputs/4 Outputs	126
TM3DM16R Mixed I/O Module 8 Inputs/8 Outputs	134
TM3DM24R / TM3DM24RG Mixed I/O Module 16 Inputs/8 Outputs	141
TM3DM32R Mixed I/O Module 16 Inputs/16 Outputs.....	149

TM3DM8R / TM3DM8RG Mixed I/O Module 4 Inputs/4 Outputs

What's in This Chapter

TM3DM8R / TM3DM8RG Presentation	126
TM3DM8R / TM3DM8RG Characteristics	128
TM3DM8R / TM3DM8RG Wiring Diagram	133

Overview

This chapter describes the TM3DM8R / TM3DM8RG expansion module, its characteristics, and its connection to the different sensors and actuators.

TM3DM8R / TM3DM8RG Presentation

Overview

TM3DM8R (screw) and TM3DM8RG (spring) digital expansion module:


- 4 channel 24 Vdc sink/source inputs
- 1 common line for inputs
- 4 channel 2 A relay outputs
- 1 common line for outputs
- Removable screw or spring terminal block

Main Characteristics

Characteristic	Value	
Input		
Number of input channels	4 inputs	
Input type	Type 1 (IEC/EN 61131-2)	
Input Logic type	Sink/Source	
Rated input voltage	24 Vdc	
Output		
Number of output channels	4 outputs	
Output type	Relay	
Contact type	NO (Normally Open)	
Rated output voltage	24 Vdc / 240 Vac	
Rated output current	2 A	
Connection and cable types		
Connection type	TM3DM8R	Removable screw terminal block
	TM3DM8RG	Removable spring terminal block
Cable type and length	Type	Unshielded
	Length	Maximum 30 m (98 ft)
Weight	95 g (3.35 oz)	

Status LEDs

The following figure shows the status LEDs:



This table describes the status LEDs:

LED	Color	Status	Type	Description
0...3	Green	On	Input	The channel is activated
		Off		The channel is deactivated
0...3	Green	On	Output	The channel is activated
		Off		The channel is deactivated

TM3DM8R / TM3DM8RG Characteristics

Introduction

This section describes the general characteristics of the TM3DM8R / TM3DM8RG expansion module.

See also Environmental Characteristics, page 25.

⚠ DANGER

FIRE HAZARD

- Use only the correct wire sizes for the maximum current capacity of the I/O channels and power supplies.
- For relay output (2 A) wiring, use conductors of at least 0.5 mm² (AWG 20) with a temperature rating of at least 80 °C (176 °F).
- For common conductors of relay output wiring (7 A), or relay output wiring greater than 2 A, use conductors of at least 1.0 mm² (AWG 16) with a temperature rating of at least 80 °C (176 °F).

Failure to follow these instructions will result in death or serious injury.

⚠ WARNING


UNINTENDED EQUIPMENT OPERATION

Do not exceed any of the rated values specified in the environmental and electrical characteristics tables.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

Dimensions

The following diagrams show the external dimensions for the TM3DM8R / TM3DM8RG expansion modules:



* 8.5 mm (0.33 in) when the clamp is pulled out.

Input Characteristics

The table below describes the inputs characteristics of the TM3DM8R / TM3DM8RG:

Characteristic		Value
Number of input channels		4 inputs
Number of channels groups		1 common line for 4 channels
Input type		Type 1 (IEC/EN 61131-2)
Logic type		Sink/Source
Rated input voltage		24 Vdc
Input voltage range		0...28.8 Vdc
Rated input current		7 mA
Input impedance		3.4 kΩ
Input limit values	Voltage at state 1	> 15 Vdc (15...28.8 Vdc)
	Voltage at state 0	< 5 Vdc (0...5 Vdc)
	Current at state 1	> 2.5 mA
	Current at state 0	< 1.0 mA
Turn on time		SV ⁽¹⁾ < 2.0: 4 ms
Turn off time		SV ⁽¹⁾ ≥ 2.0: 100 μs ⁽²⁾
Isolation	Between input and internal logic	500 Vac
	Between input group and output group	1500 Vac
	Between input groups	N/A
Connection type	TM3DM8R	Removable screw terminal block
	TM3DM8RG	Removable spring terminal block
Connector insertion/removal durability		Over 100 times
Current draw on 5 Vdc internal bus		24 mA (all inputs and outputs on)
		5 mA (all inputs and outputs off)
Current draw on 24 Vdc internal bus		20 mA (all inputs and outputs on)
		0 mA (all inputs and outputs off)
<p>(1) SV refers to the version and is printed on the product label.</p> <p>(2) The range depends on the configured filter value. If you use EcoStruxure Machine Expert - Basic, refer to the Modicon TM3 (EcoStruxure Machine Expert - Basic) Expansion Modules Configuration - Programming Guide. If you use EcoStruxure Machine Expert, refer to the Modicon TM3 Expansion Modules - Programming Guide.</p>		


Output Characteristics

The table below describes the outputs characteristics of the TM3DM8R / TM3DM8RG:

Characteristic		Value
Number of output channels		4 outputs
Number of channel groups		1 common line for 4 channels
Output type		Relay
Contact type		NO (Normally Open)
Rated output voltage		24 Vdc, 240 Vac
Maximum voltage		30 Vdc, 264 Vac
Minimum switching load		5 Vdc at 10 mA
Rated output current		2 A
Maximum output current		2 A per output
		7 A per common
Maximum output frequency		20 operations per minute
Turn on time		Maximum 10 ms
Turn off time		Maximum 10 ms
Contact resistance		30 mΩ maximum
Mechanical life		20 million operations
Electrical life	Under resistive load	See Power Limitation, page 131
	Under inductive load	
Protection against short circuit		No
Isolation	Between input and internal logic	500 Vac
	Between input group and output group	1500 Vac
	Between input groups	N/A
Connection type	TM3DM8R	Removable screw terminal block
	TM3DM8RG	Removable spring terminal block
Connector insertion/removal durability		Over 100 times
Current draw on 5 Vdc internal bus		24 mA (all inputs and outputs on)
		5 mA (all inputs and outputs off)
Current draw on 24 Vdc internal bus		20 mA (all inputs and outputs on)
		0 mA (all inputs and outputs off)
<p>NOTE: Refer to Protecting Outputs from Inductive Load Damage, page 36 for additional information on this topic.</p>		

I/O De-rating

When using TM3DM8R / TM3DM8RG:



At an ambient temperature of 55 °C (131 °F) in the horizontal mounting direction, limit the inputs and outputs, respectively, which turn on simultaneously as indicated by the X axis.

At 40 °C (104 °F), all inputs and outputs can be turned on simultaneously at 28.8 Vdc.

Power Limitation

This table describes the power limitation of the TM3DM8R / TM3DM8RG expansion module depending on the voltage, the type of load, and the number of operations required.

These expansion modules do not support capacitive loads.

⚠ WARNING

RELAY OUTPUTS WELDED CLOSED

- Always protect relay outputs from inductive alternating current load damage using an appropriate external protective circuit or device.
- Do not connect relay outputs to capacitive loads.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

Power Limitations				
Voltage	24 Vdc	120 Vac	240 Vac	Number of operations
Power of resistive loads	–	240 VA	480 VA	100,000
AC-12		80 VA	160 VA	300,000
Power of inductive loads	–	60 VA	120 VA	100,000
AC-15 ($\cos \phi = 0.35$)		18 VA	36 VA	300,000
Power of inductive loads	–	120 VA	240 VA	100,000
AC-14 ($\cos \phi = 0.7$)		36 VA	72 VA	300,000
Power of resistive loads	48 W	–	–	100,000
DC-12	16 W			300,000
Power of inductive loads	24 W	–	–	100,000
DC-13 L/R = 7 ms	7.2 W			300,000

TM3DM8R / TM3DM8RG Wiring Diagram

Introduction


These expansion modules have a built-in removable screw or spring terminal block for the connection of inputs, outputs, and power supply.

Wiring Rules

See Wiring Best Practices, page 36.

Wiring Diagram

The following figure illustrates the connections between the inputs and outputs, the sensors and actuators, and their commons:



* Type T Fuse

(1) The COM0 and COM1 terminals are **not** connected internally.

(2) To improve the life time of the contacts, and to protect from potential inductive load damage, connect a free wheeling diode in parallel to each inductive DC load or an RC snubber in parallel of each inductive AC load, or a varistor on either type of load.

C Source wiring (positive logic)

D Sink wiring (negative logic)

NOTE: When you use the TM3 expansion module with a TM3 Ethernet bus coupler, you must connect an RC snubber in parallel of each inductive AC load.

For information about 24 Vdc power supply, refer to DC Power Supply Characteristics, page 41.

⚠ WARNING

UNINTENDED EQUIPMENT OPERATION

Do not connect wires to unused terminals and/or terminals indicated as “No Connection (N.C.)”.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

TM3DM16R Mixed I/O Module 8 Inputs/8 Outputs

What's in This Chapter

TM3DM16R Presentation.....	134
TM3DM16R Characteristics	135
TM3DM16R Wiring Diagram	139

Overview

This chapter describes the TM3DM16R expansion module, its characteristics, and its connection to the different sensors and actuators.

TM3DM16R Presentation

Overview

TM3DM16R digital expansion module:

- 8 channel 24 Vdc sink/source inputs
- 1 common line for inputs
- 8 channel 2 A relay outputs
- 2 common lines for outputs
- Removable screw terminal block

Main Characteristics

Characteristic		Value
Input		
Number of input channels		8 inputs
Input type		Type 1 (IEC/EN 61131-2)
Input Logic type		Sink/Source
Rated input voltage		24 Vdc
Output		
Number of output channels		8 outputs
Output type		Relay
Contact type		NO (Normally Open)
Rated output voltage		24 Vdc / 240 Vac
Rated output current		2 A
Connection and cable types		
Connection type		Removable screw terminal block
Cable type and length	Type	Unshielded
	Length	Input: maximum 50 m (164 ft) Output: maximum 150 m (492 ft)
Weight		118 g (4.16 oz)

Status LEDs

The following figure shows the status LEDs:



This table describes the status LEDs:

LED	Color	Status	Type	Description
0...7	Green	On	Input	The channel is activated
		Off		The channel is deactivated
0...7	Green	On	Output	The channel is activated
		Off		The channel is deactivated

TM3DM16R Characteristics

Introduction

This section describes the general characteristics of the TM3DM16R expansion module.

See also Environmental Characteristics, page 25.

⚠ DANGER

FIRE HAZARD

- Use only the correct wire sizes for the maximum current capacity of the I/O channels and power supplies.
- For relay output (2 A) wiring, use conductors of at least 0.5 mm² (AWG 20) with a temperature rating of at least 80 °C (176 °F).
- For common conductors of relay output wiring (7 A), or relay output wiring greater than 2 A, use conductors of at least 1.0 mm² (AWG 16) with a temperature rating of at least 80 °C (176 °F).

Failure to follow these instructions will result in death or serious injury.

⚠ WARNING


UNINTENDED EQUIPMENT OPERATION

Do not exceed any of the rated values specified in the environmental and electrical characteristics tables.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

Dimensions

The following diagrams show the external dimensions for the TM3DM16R expansion modules:



* 8.5 mm (0.33 in) when the clamp is pulled out.

Input Characteristics

The table below describes the input characteristics of the TM3DM16R:

Characteristic		Value
Number of input channels		8 inputs
Number of channels groups		1 common line for 8 channels
Input type		Type 1 (IEC/EN 61131-2)
Logic type		Sink/Source
Rated input voltage		24 Vdc
Input voltage range		0...28.8 Vdc
Rated input current		5 mA
Input impedance		4.7 kΩ
Input limit values	Voltage at state 1	> 15 Vdc (15...28.8 Vdc)
	Voltage at state 0	< 5 Vdc (0...5 Vdc)
	Current at state 1	> 2.5 mA
	Current at state 0	< 1.5 mA
Turn on time		4 ms
Turn off time		4 ms
De-rating	0...55 °C (32...131 °F)	See Input de-rating, page 138
Isolation	Between input and internal logic	500 Vac / 800 Vdc
	Between input group and output group	1500 Vac / 2500 Vdc
	Between input groups	N/A
Connection type		Removable screw terminal block
Connector insertion/removal durability		Over 100 times
Current draw on 5 Vdc internal bus		70 mA
Current draw on 24 Vdc internal bus		40 mA


Output Characteristics

The table below describes the outputs characteristics of the TM3DM16R:

Characteristic		Value
Number of output channels		8 outputs
Number of channel groups		2 common lines for 8 channels
Output type		Relay
Contact type		NO (Normally Open)
Rated output voltage		24 Vdc, 220 Vac
Maximum voltage		30 Vdc, 250 Vac
Rated output current		2 A per output
Maximum output current		2 A per output 4 A per common
Maximum output frequency	With maximum load	0.1 Hz
	Without load	5 Hz
Turn on time		Maximum 10 ms
Turn off time		Maximum 10 ms
De-rating	0...55 °C (32...131 °F)	See Output de-rating, page 138
Mechanical life		20 million operations
Electrical life under resistive load 2 A		100,000 switching cycles at 45 °C (113 °F)
Protection against short circuit		No
Isolation	Between output and internal logic	1500 Vac / 2500 Vdc
	Between input group and output group	1500 Vac / 2500 Vdc
	Between output groups	1500 Vac / 2500 Vdc
Connection type		Removable screw terminal block
Connector insertion/removal durability		Over 100 times
Current draw on 5 Vdc internal bus		70 mA
Current draw on 24 Vdc internal bus		40 mA
<p>NOTE: Refer to Protecting Outputs from Inductive Load Damage, page 36 for additional information on this topic.</p>		

Input De-rating

When using TM3DM16R:




X Ambient temperature (°C / °F)

Y Input voltage (V)

At an ambient temperature of 55 °C (131 °F) in the horizontal mounting direction, limit the inputs and outputs, respectively, which turn on simultaneously as indicated by the X axis.

Output De-rating

When using TM3DM16R:



X Ambient temperature (°C / °F)

Y Output load current (%)

Power Limitation

This table describes the power limitation of the TM3DM16R expansion module depending on the voltage, the type of load, and the number of operations required.

These expansion modules do not support capacitive loads.

⚠ WARNING
<p>RELAY OUTPUTS WELDED CLOSED</p> <ul style="list-style-type: none"> • Always protect relay outputs from inductive alternating current load damage using an appropriate external protective circuit or device. • Do not connect relay outputs to capacitive loads. <p>Failure to follow these instructions can result in death, serious injury, or equipment damage.</p>

Power Limitations				
Voltage	24 Vdc	120 Vac	240 Vac	Number of operations
Power of resistive loads AC-12	–	240 VA 80 VA	480 VA 160 VA	100,000 300,000
Power of inductive loads AC-15 (cos φ = 0.35)	–	60 VA 18 VA	120 VA 36 VA	100,000 300,000
Power of inductive loads AC-14 (cos φ = 0.7)	–	120 VA 36 VA	240 VA 72 VA	100,000 300,000
Power of resistive loads DC-12	48 W 16 W	–	–	100,000 300,000
Power of inductive loads DC-13 L/R = 7 ms	24 W 7.2 W	–	–	100,000 300,000

TM3DM16R Wiring Diagram

Introduction


These expansion modules have a built-in removable screw terminal block for the connection of inputs, outputs, and power supply.

Wiring Rules

See Wiring Best Practices, page 36.

Wiring Diagram

The following figure illustrates the connections between the inputs and outputs, the sensors and actuators, and their commons:



* Type T Fuse

(1) The inputs COM0, outputs COM0 and COM1 terminals are **not** connected internally.

(2) To improve the life time of the contacts, and to protect from potential inductive load damage, connect a free wheeling diode in parallel to each inductive DC load or an RC snubber in parallel of each inductive AC load.

A Sink wiring (positive logic)

B Source wiring (negative logic)

C Source wiring (positive logic)

D Sink wiring (negative logic)

NOTE: When you use the TM3 expansion module with a TM3 Ethernet bus coupler, you must connect an RC snubber in parallel of each inductive AC load.

For information about 24 Vdc power supply, refer to DC Power Supply Characteristics, page 41.

⚠ WARNING
UNINTENDED EQUIPMENT OPERATION
Do not connect wires to unused terminals and/or terminals indicated as “No Connection (N.C.)”.
Failure to follow these instructions can result in death, serious injury, or equipment damage.

TM3DM24R / TM3DM24RG Mixed I/O Module 16 Inputs/8 Outputs

What's in This Chapter

TM3DM24R / TM3DM24RG Presentation 141
 TM3DM24R / TM3DM24RG Characteristics 143
 TM3DM24R / TM3DM24RG Wiring Diagram 147

Overview

This chapter describes the TM3DM24R / TM3DM24RG expansion modules, its characteristics, and its connection to the different sensors and actuators.

TM3DM24R / TM3DM24RG Presentation

Overview

TM3DM24R (screw) and TM3DM24RG (spring) digital expansion module:


- 16 channel 24 Vdc sink/source inputs
- 1 common line for inputs
- 8 channel 2 A relay outputs
- 2 common line for outputs
- Removable screw or spring terminal block

Main Characteristics

Characteristic		Value
Input		
Number of input channels		16 inputs
Input type		Type 1 (IEC/EN 61131-2)
Input Logic type		Sink/Source
Rated input voltage		24 Vdc
Output		
Number of output channels		8 outputs
Contact type		NO (Normally Open)
Rated output voltage		24 Vdc / 240 Vdc
Rated output current		2 A
Connection and cable types		
Connection type	TM3DM24R	Removable screw terminal blocks
	TM3DM24RG	Removable spring terminal blocks
Cable type and length	Type	Unshielded
	Length	Maximum 30 m (98 ft)
Weight		140 g (4.94 oz)

Status LEDs

The following figure shows the status LEDs:



This table describes the status LEDs:

LED	Color	Status	Type	Description
0...15	Green	On	Input	The channel is activated
		Off		The channel is deactivated
0...7	Green	On	Output	The channel is activated
		Off		The channel is deactivated

TM3DM24R / TM3DM24RG Characteristics

Introduction

This section provides a description of the electrical and input/output characteristics of the TM3DM24R / TM3DM24RG expansion modules.

See also Environmental Characteristics, page 25.

⚠ DANGER

FIRE HAZARD

- Use only the correct wire sizes for the maximum current capacity of the I/O channels and power supplies.
- For relay output (2 A) wiring, use conductors of at least 0.5 mm² (AWG 20) with a temperature rating of at least 80 °C (176 °F).
- For common conductors of relay output wiring (7 A), or relay output wiring greater than 2 A, use conductors of at least 1.0 mm² (AWG 16) with a temperature rating of at least 80 °C (176 °F).

Failure to follow these instructions will result in death or serious injury.

⚠ WARNING


UNINTENDED EQUIPMENT OPERATION

Do not exceed any of the rated values specified in the environmental and electrical characteristics tables.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

Dimensions

The following diagrams show the external dimensions for the TM3DM24R / TM3DM24RG expansion modules:



* 8.5 mm (0.33 in) when the clamp is pulled out.

Input Characteristics

The table below describes the inputs characteristics of the TM3DM24R / TM3DM24RG:

Characteristic		Value
Number of input channels		16 inputs
Number of channels groups		1 common line for 16 channels
Input type		Type 1 (IEC/EN 61131-2)
Logic type		Sink/Source
Rated input voltage		24 Vdc
Input voltage range		0...28.8 Vdc
Rated input current		7 mA
Input impedance		3.4 kΩ
Input limit values	Voltage at state 1	> 15 Vdc (15...28.8 Vdc)
	Voltage at state 0	< 5 Vdc (0...5 Vdc)
	Current at state 1	> 2.5 mA
	Current at state 0	< 1.0 mA
Turn on time		SV ⁽¹⁾ < 2.0: 4 ms
Turn off time		SV ⁽¹⁾ ≥ 2.0: 100 μs ⁽²⁾
Isolation	Between input and internal logic	500 Vac
	Between input group and output group	1500 Vac
	Between input groups	N/A
Connection type	TM3DM24R	Removable screw terminal block
	TM3DM24RG	Removable spring terminal block
Connector insertion/removal durability		Over 100 times
Current draw on 5 Vdc internal bus		42 mA (all inputs and outputs on)
		5 mA (all inputs and outputs off)
Current draw on 24 Vdc internal bus		39 mA (all inputs and outputs on)
		0 mA (all inputs and outputs off)
<p>(1) SV refers to the version and is printed on the product label.</p> <p>(2) The range depends on the configured filter value. If you use EcoStruxure Machine Expert - Basic, refer to the Modicon TM3 (EcoStruxure Machine Expert - Basic) Expansion Modules Configuration - Programming Guide. If you use EcoStruxure Machine Expert, refer to the Modicon TM3 Expansion Modules - Programming Guide.</p>		


Output Characteristics

The table below describes the outputs characteristics of the TM3DM24R / TM3DM24RG:

Characteristic		Value
Number of output channels		8
Number of channel groups		2 common line for 8 channels
Output type		Relay
Contact type		NO (Normally Open)
Rated output voltage		24 Vdc, 240 Vac
Maximum voltage		30 Vdc, 264 Vac
Minimum switching load		5 Vdc at 10 mA
Rated output current		2 A
Maximum output current		2 A per channels
		7 A per commons
Maximum output frequency	With maximum load	20 operations per minute
Turn on time		Maximum 10 ms
Turn off time		Maximum 10 ms
Contact resistance		30 mW
Mechanical life		20 million operations
Electrical life	Under resistive load	See Power limitation, page 76
	Under inductive load	
Protection against short circuit		No
Isolation	Between input and internal logic	500 Vac
	Between input group and output group	1500 Vac
	Between input groups	N/A
Connection type	TM3DM24R	Removable screw terminal block
	TM3DM24RG	Removable spring terminal block
Connector insertion/removal durability		Over 100 times
Current draw on 5 Vdc internal bus		42 mA (all inputs and outputs on)
		5 mA (all inputs and outputs off)
Current draw on 24 Vdc internal bus		39 mA (all inputs and outputs on)
		0 mA (all inputs and outputs off)
NOTE: Refer to Protecting Outputs from Inductive Load Damage, page 36 for additional information on this topic.		

I/O De-rating

When using TM3DM24R / TM3DM24RG:



X Input simultaneous ON ratio

Y Input voltage

Power Limitation

This table describes the power limitation of the TM3DM24R / TM3DM24RG expansion modules depending on the voltage, the type of load, and the number of operations required.

These expansion modules do not support capacitive loads.

⚠ WARNING

RELAY OUTPUTS WELDED CLOSED

- Always protect relay outputs from inductive alternating current load damage using an appropriate external protective circuit or device.
- Do not connect relay outputs to capacitive loads.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

Power Limitations

Voltage	24 Vdc	120 Vac	240 Vac	Number of operations
Power of resistive loads	–	240 VA	480 VA	100,000
AC-12		80 VA	160 VA	300,000
Power of inductive loads	–	60 VA	120 VA	100,000
AC-15 (cos ϕ = 0.35)		18 VA	36 VA	300,000
Power of inductive loads	–	120 VA	240 VA	100,000
AC-14 (cos ϕ = 0.7)		36 VA	72 VA	300,000
Power of resistive loads	48 W	–	–	100,000
DC-12	16 W			300,000
Power of inductive loads	24 W	–	–	100,000
DC-13 L/R = 7 ms	7.2 W			300,000

TM3DM24R / TM3DM24RG Wiring Diagram

Introduction


These expansion modules have a built-in removable screw or spring terminal block for the connection of inputs, outputs, and power supply.

Wiring Rules

See Wiring Best Practices, page 36.

Wiring Diagram

The following figure illustrates the connections between the inputs and outputs, the sensors and actuators, and their commons for a positive logic:



* Type T Fuse


(1) The COM0, COM1 and COM2 terminals are **not** connected internally.

(2) To improve the life time of the contacts, and to protect from potential inductive load damage, connect a free wheeling diode in parallel to each inductive DC load or an RC snubber in parallel of each inductive AC load, or a varistor on either type of load.

C Source wiring (positive logic)

NOTE: When you use the TM3 expansion module with a TM3 Ethernet bus coupler, you must connect an RC snubber in parallel of each inductive AC load.

The following figure illustrates the connections between the inputs and outputs, the sensors and actuators, and their commons for a negative logic:



* Type T Fuse

(1) The COM0, COM1 and COM2 terminals are **not** connected internally.

(2) To improve the life time of the contacts, and to protect from potential inductive load damage, connect a free wheeling diode in parallel to each inductive DC load or an RC snubber in parallel of each inductive AC load, or a varistor on either type of load.

D Sink wiring (negative logic)

NOTE: When you use the TM3 expansion module with a TM3 Ethernet bus coupler, you must connect an RC snubber in parallel of each inductive AC load.

For information about 24 Vdc power supply, refer to DC Power Supply Characteristics, page 41.

▲ WARNING

UNINTENDED EQUIPMENT OPERATION

Do not connect wires to unused terminals and/or terminals indicated as “No Connection (N.C.)”.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

TM3DM32R Mixed I/O Module 16 Inputs/16 Outputs

What's in This Chapter

TM3DM32R Presentation..... 149
 TM3DM32R Characteristics 151
 TM3DM32R Wiring Diagram 156

Overview

This chapter describes the TM3DM32R expansion module, its characteristics, and its connection to the different sensors and actuators.

TM3DM32R Presentation

Overview

TM3DM32R digital expansion module:


- 16 channel 24 Vdc sink/source inputs
- 2 common lines for inputs
- 16 channel 2 A relay outputs
- 4 common lines for outputs
- Removable screw terminal block

Main Characteristics

Characteristic		Value
Input		
Number of input channels		16 inputs
Input type		Type 1 (IEC/EN 61131-2)
Input Logic type		Sink/Source
Rated input voltage		24 Vdc
Output		
Number of output channels		16 outputs
Contact type		NO (Normally Open)
Rated output voltage		24 Vdc / 220 Vdc
Rated output current		2 A
Connection and cable types		
Connection type		Removable screw terminal blocks
Cable type and length	Type	Unshielded
	Length	Input: maximum 50 m (164 ft) Output: maximum 150 m (490 ft)
Weight		208 g (7.34 oz)

Status LEDs

The following figure shows the status LEDs:



This table describes the status LEDs:

LED	Color	Status	Type	Description
0...15	Green	On	Input	The channel is activated
		Off		The channel is deactivated
0...15	Green	On	Output	The channel is activated
		Off		The channel is deactivated

TM3DM32R Characteristics

Introduction

This section provides a description of the electrical and input/output characteristics of the TM3DM32R expansion modules.

See also Environmental Characteristics, page 25.

⚠ DANGER

FIRE HAZARD

- Use only the correct wire sizes for the maximum current capacity of the I/O channels and power supplies.
- For relay output (2 A) wiring, use conductors of at least 0.5 mm² (AWG 20) with a temperature rating of at least 80 °C (176 °F).
- For common conductors of relay output wiring (7 A), or relay output wiring greater than 2 A, use conductors of at least 1.0 mm² (AWG 16) with a temperature rating of at least 80 °C (176 °F).

Failure to follow these instructions will result in death or serious injury.

⚠ WARNING


UNINTENDED EQUIPMENT OPERATION

Do not exceed any of the rated values specified in the environmental and electrical characteristics tables.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

Dimensions

The following diagrams show the external dimensions for the TM3DM32R expansion modules:



* 8.5 mm (0.33 in) when the clamp is pulled out.

Input Characteristics

The table below describes the input characteristics of the TM3DM32R:

Characteristic		Value
Number of input channels		16 inputs
Number of channels groups		2 common lines for 16 channels
Input type		Type 1 (IEC/EN 61131-2)
Logic type		Sink/Source
Rated input voltage		24 Vdc
Input voltage range		0...28.8 Vdc
Rated input current		5 mA
Input impedance		4.7 kΩ
Input limit values	Voltage at state 1	> 15 Vdc (15...28.8 Vdc)
	Voltage at state 0	< 5 Vdc (0...5 Vdc)
	Current at state 1	> 2.5 mA
	Current at state 0	< 1.5 mA
Turn on time		4 ms
Turn off time		4 ms
De-rating	0...55 °C (32...131 °F)	See Input de-rating, page 154
Isolation	Between input and internal logic	500 Vac / 800 Vdc
	Between input group and output group	1500 Vac / 2500 Vdc
	Between input groups	500 Vac / 800 Vdc
Connection type		Removable screw terminal block
Connector insertion/removal durability		Over 100 times
Current draw on 5 Vdc internal bus		95 mA
Current draw on 24 Vdc internal bus		80 mA


Output Characteristics

The table below describes the output characteristics of the TM3DM32R:

Characteristic		Value
Number of output channels		16
Number of channel groups		4 common line for 16 channels
Output type		Relay
Contact type		NO (Normally Open)
Rated output current		2 A per output
Maximum output current		2 A per output 4 A per common
Maximum output frequency	With maximum load	0.1 Hz
	Without load	5 Hz
Turn on time		Maximum 10 ms
Turn off time		Maximum 10 ms
De-rating	0...55 °C (32...131 °F)	See Output de-rating, page 154
Mechanical life		20 million operations
Electrical life under resistive load 2 A		100,000 switching cycles at 45 °C (113 °F)
Protection against short circuit		No
Isolation	Between output and internal logic	1500 Vac / 2500 Vdc
	Between input group and output group	1500 Vac / 2500 Vdc
	Between output groups	1500 Vac / 2500 Vdc
Connection type		Removable screw terminal block
Connector insertion/removal durability		Over 100 times
Current draw on 5 Vdc internal bus		95 mA
Current draw on 24 Vdc internal bus		80 mA
<p>NOTE: Refer to Protecting Outputs from Inductive Load Damage, page 36 for additional information on this topic.</p>		

Input De-rating

When using TM3DM32R:




X Ambient temperature (°C / °F)

Y Input voltage

Output De-rating

When using TM3DM32R:



X Ambient temperature (°C / °F)

Y Output load current (%)

Power Limitation

This table describes the power limitation of the TM3DM32R expansion modules depending on the voltage, the type of load, and the number of operations required.

These expansion modules do not support capacitive loads.

⚠ WARNING**RELAY OUTPUTS WELDED CLOSED**

- Always protect relay outputs from inductive alternating current load damage using an appropriate external protective circuit or device.
- Do not connect relay outputs to capacitive loads.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

Power Limitations				
Voltage	24 Vdc	120 Vac	240 Vac	Number of operations
Power of resistive loads	–	240 VA	480 VA	100,000
AC-12		80 VA	160 VA	300,000
Power of inductive loads	–	60 VA	120 VA	100,000
AC-15 (cos ϕ = 0.35)		18 VA	36 VA	300,000
Power of inductive loads	–	120 VA	240 VA	100,000
AC-14 (cos ϕ = 0.7)		36 VA	72 VA	300,000
Power of resistive loads	48 W	–	–	100,000
DC-12	16 W			300,000
Power of inductive loads	24 W	–	–	100,000
DC-13 L/R = 7 ms	7.2 W			300,000

TM3DM32R Wiring Diagram

Introduction


These expansion modules have a built-in removable screw terminal block for the connection of inputs, outputs, and power supply.

Wiring Rules

See Wiring Best Practices, page 36.

Wiring Diagram

The following figure illustrates the connections between the inputs and outputs, the sensors and actuators, and their commons for a positive logic:



* Type T Fuse

(1) The inputs COM0, COM1, outputs COM0, COM1, COM2, and COM3 terminals are **not** connected internally.


(2) To improve the life time of the contacts, and to protect from potential inductive load damage, connect a free wheeling diode in parallel to each inductive DC load or an RC snubber in parallel of each inductive AC load.

A Sink wiring (positive logic)

C Source wiring (positive logic)

NOTE: When you use the TM3 expansion module with a TM3 Ethernet bus coupler, you must connect an RC snubber in parallel of each inductive AC load.

The following figure illustrates the connections between the inputs and outputs, the sensors and actuators, and their commons for a negative logic:



* Type T Fuse

(1) The inputs COM0, COM1 and outputs COM0, COM1, COM2, and COM3 terminals are **not** connected internally.

(2) To improve the life time of the contacts, and to protect from potential inductive load damage, connect a free wheeling diode in parallel to each inductive DC load or an RC snubber in parallel of each inductive AC load.

B Source wiring (negative logic)

D Sink wiring (negative logic)

NOTE: When you use the TM3 expansion module with a TM3 Ethernet bus coupler, you must connect an RC snubber in parallel of each inductive AC load.

For information about 24 Vdc power supply, refer to DC Power Supply Characteristics, page 41.

▲ WARNING
UNINTENDED EQUIPMENT OPERATION
Do not connect wires to unused terminals and/or terminals indicated as “No Connection (N.C.)”.
Failure to follow these instructions can result in death, serious injury, or equipment damage.

Glossary

A

application:

A program including configuration data, symbols, and documentation.

C

controller:

Automates industrial processes (also known as programmable logic controller or programmable controller).

E

EIA rack:

(*electronic industries alliance rack*) A standardized (EIA 310-D, IEC 60297, and DIN 41494 SC48D) system for mounting various electronic modules in a stack or rack that is 19 inches (482.6 mm) wide.

EN:

EN identifies one of many European standards maintained by CEN (*European Committee for Standardization*), CENELEC (*European Committee for Electrotechnical Standardization*), or ETSI (*European Telecommunications Standards Institute*).

expansion bus:

An electronic communication bus between expansion I/O modules and a controller or bus coupler.

expansion connector:

A connector to attach expansion I/O modules.

H

HE10:

Rectangular connector for electrical signals with frequencies below 3 MHz, complying with IEC 60807-2.

I

I/O:

(*input/output*)

IEC:

(*international electrotechnical commission*) A non-profit and non-governmental international standards organization that prepares and publishes international standards for electrical, electronic, and related technologies.

IP 20:

(*ingress protection*) The protection classification according to IEC 60529 offered by an enclosure, shown by the letter IP and 2 digits. The first digit indicates 2 factors: helping protect persons and for equipment. The second digit indicates helping protect against water. IP 20 devices help protect against electric contact of objects larger than 12.5 mm, but not against water.

N

N/O:

(normally open) A contact pair that opens when the actuator is de-energized (no power is applied) and closes when the actuator is energized (power is applied).

NEMA:

(national electrical manufacturers association) The standard for the performance of various classes of electrical enclosures. The NEMA standards cover corrosion resistance, ability to help protect from rain, submersion, and so on. For IEC member countries, the IEC 60529 standard classifies the ingress protection rating for enclosures.

P

program:

The component of an application that consists of compiled source code capable of being installed in the memory of a logic controller.

R

RJ45:

A standard type of 8-pin connector for network cables defined for Ethernet.

T

terminal block:

(terminal block) The component that mounts in an electronic module and provides electrical connections between the controller and the field devices.

Index

A

accessories	22
assembling to a controller	33

C

certifications and standards	27
characteristics	
TM3DI16/TM3DI16G	56
TM3DI16K	62
TM3DI32K	68
TM3DI8/TM3DI8G	51
TM3DI8A	46
TM3DM16R	135
TM3DM24R/TM3DM24RG	143
TM3DM32R	151
TM3DM8R/TM3DM8RG	128
TM3DQ16R/TM3DQ16RG	91
TM3DQ16T/TM3DQ16TG	97
TM3DQ16TK	102
TM3DQ16U/TMQ3DQ16UG	107
TM3DQ16UK	112
TM3DQ32TK	117
TM3DQ32UK	122
TM3DQ8R/TM3DQ8RG	75
TM3DQ8T/TM3DQ8TG	81
TM3DQ8U/TM3DQ8UG	86
controllers	
disassembling a module	34

D

DIN rail	31
----------------	----

E

electromagnetic susceptibility	27
environmental characteristics	25

G

general description	16
grounding	42

I

inductive load	39
intended use	8

M

minimum clearances	29
mounting position	29

O

output protection	39
-------------------------	----

P

physical description	
TM3 I/O expansion modules	20
power supply	41
presentation	
TM3DI16/TM3DI16G	54
TM3DI16K	60
TM3DI32K	66
TM3DI8/TM3DI8G	49
TM3DI8A	45
TM3DM16R	134
TM3DM24R/TM3DM24RG	141
TM3DM32R	149
TM3DM8R/TM3DM8RG	126
TM3DQ16R/TM3DQ16RG	89
TM3DQ16T/TM3DQ16TG	95
TM3DQ16TK	100
TM3DQ16U/TMQ3DQ16UG	105
TM3DQ16UK	110
TM3DQ32TK	115
TM3DQ32UK	120
TM3DQ8R/TM3DQ8RG	73
TM3DQ8T/TM3DQ8TG	79
TM3DQ8U/TM3DQ8UG	84

Q

qualification of personnel	7
----------------------------------	---

T

TM3 digital input modules	
TM3DI16/TM3DI16G	54
TM3DI16K	60
TM3DI32K	66
TM3DI8/TM3DI8G	49
TM3DI8A	45
TM3 digital mixed I/O modules	
TM3DM16R	134
TM3DM24R/TM3DM24RG	141
TM3DM32R	149
TM3DM8R/TM3DM8RG	126
TM3 digital output modules	
TM3DQ16R/TM3DQ16RG	89
TM3DQ16T/TM3DQ16TG	95
TM3DQ16TK	100
TM3DQ16U/TMQ3DQ16UG	105
TM3DQ16UK	110
TM3DQ32TK	115
TM3DQ32UK	120
TM3DQ8R/TM3DQ8RG	73
TM3DQ8T/TM3DQ8TG	79
TM3DQ8U/TM3DQ8UG	84
TM3 I/O expansion modules	
physical description	20
TM3DI16/TM3DI16G	
characteristics	56
presentation	54
wiring diagram	59
TM3DI16K	
characteristics	62
presentation	60
wiring diagram	65
TM3DI32K	
characteristics	68
presentation	66
wiring diagram	71
TM3DI8/TM3DI8G	

characteristics	51	TM3DI32K.....	71
presentation	49	TM3DI8/TM3DI8G	53
wiring diagram	53	TM3DI8A.....	48
TM3DI8A		TM3DM16R.....	139
characteristics	46	TM3DM24R/TM3DM24RG	147
presentation	45	TM3DM32R.....	156
wiring diagram	48	TM3DM8R/TM3DM8RG	133
TM3DM16R		TM3DQ16R/TM3DQ16RG	94
characteristics	135	TM3DQ16T/TM3DQ16TG	99
presentation	134	TM3DQ16TK	104
wiring diagram	139	TM3DQ16U/TMQ3DQ16UG	109
TM3DM24R/TM3DM24RG		TM3DQ16UK.....	114
characteristics	143	TM3DQ32TK	119
presentation	141	TM3DQ32UK.....	123
wiring diagram	147	TM3DQ8R/TM3DQ8RG	78
TM3DM32R		TM3DQ8T/TM3DQ8TG	83
characteristics	151	TM3DQ8U/TM3DQ8UG	88
presentation	149	wiring rules	36
wiring diagram	156		
TM3DM8R/TM3DM8RG			
characteristics	128		
presentation	126		
wiring diagram	133		
TM3DQ16R/TM3DQ16RG			
characteristics	91		
presentation	89		
wiring diagram	94		
TM3DQ16T/TM3DQ16TG			
characteristics	97		
presentation	95		
wiring diagram	99		
TM3DQ16TK			
characteristics	102		
presentation	100		
wiring diagram	104		
TM3DQ16U/TMQ3DQ16UG			
characteristics	107		
presentation	105		
wiring diagram	109		
TM3DQ16UK			
characteristics	112		
presentation	110		
wiring diagram	114		
TM3DQ32TK			
characteristics	117		
presentation	115		
wiring diagram	119		
TM3DQ32UK			
characteristics	122		
presentation	120		
wiring diagram	123		
TM3DQ8R/TM3DQ8RG			
characteristics	75		
presentation	73		
wiring diagram	78		
TM3DQ8T/TM3DQ8TG			
characteristics	81		
presentation	79		
wiring diagram	83		
TM3DQ8U/TM3DQ8UG			
characteristics	86		
presentation	84		
wiring diagram	88		

W

wiring diagram	
TM3DI16/TM3DI16G.....	59
TM3DI16K.....	65

Schneider Electric
35 rue Joseph Monier
92500 Rueil Malmaison
France

+ 33 (0) 1 41 29 70 00

www.se.com

As standards, specifications, and design change from time to time,
please ask for confirmation of the information given in this publication.

© 2024 Schneider Electric. All rights reserved.

EIO0000003125.05