



A versatile UPS developed for unstable power conditions worldwide

Smart-UPS™ On-Line provides high-density, double-conversion online power protection for servers, voice/data networks, medical labs, and light industrial applications. The Smart-UPS On-Line is capable of supporting loads from 1 kVA to 10 kVA in a rack/tower convertible chassis. The 6 kVA, 8 kVA, and 10 kVA models feature unity output power factor enabling them to support power-hungry blade servers or heavily loaded equipment racks. When business-critical systems require runtime in hours, not minutes, Smart-UPS On-Line can be configured with multiple battery packs to meet aggressive runtime demands.

The included PowerChute™ Network Shutdown management software provides unattended graceful shutdown of network operating systems. Models 5 kVA to 10 kVA include an integrated network management card for remote management. The entire Smart-UPS On-Line family provides value to customers with demanding power conditions, including a very wide input voltage window, extremely tight output voltage regulation, frequency regulation, internal bypass, and input power factor correction.



Smart-UPS On-Line

Industry-leading power factor maximizing UPS density Rackmount and Tower SRT 1 kVA – 10 kVA



SRT5KXLT shown

Standard features

Best-in-class power density

More real power in watts, 0.82 pf on the 2.2 kVA, 0.9 pf on the 1kVA, 1.5 kVA, and 3 kVA, 0.85 pf on 5 kVA, Unity on 6 kVA - 10 kVA units.

High-efficiency "Green Mode"

Achieves 97% efficiency, which helps save utility and cooling costs without compromising performance or reliability. Energy Star® compliant.

Graphical LCD display with multicolor backlight

Intuitive interface provides detailed and accurate information with ability to configure locally.

Intelligent battery management

Temperature-compensated charging extends battery life and advanced algorithms recommend replacement date. The UPS can inform the user which batteries need to be replaced and auto detect when additional battery packs are added.

Built-in energy meter

Measures energy use and displays UPS efficiency in various modes of operation for easy energy tracking.

Operate without battery

Ability to immediately help protect equipment when power returns after a complete discharge of the battery.

Three-year warranty on electronics

Additional year of warranty protection for electronics provides peace of mind.





Smart-UPS On-Line

Proven performance with the world's largest installed base of single-phase, double-conversion products

Rackmount and Tower SRT 1 kVA – 10 kVA



SRT10KXLT shown

Additional features

Embedded network management card with environmental monitoring (on the NC and 5 kVA – 10 kVA models)

Remote monitoring and control of the UPS and the environment via Ethernet connection while freeing up the SmartSlot™ so customers can add accessories for additional communication options.

Switched outlet group(s)

Ability to control a group of output load receptacles independent from the main UPS. Enables:

- Rebooting hung device without cycling the entire UPS
- Sequenced turn on/off
- Shedding of noncritical loads based on a variety of parameters (battery time, runtime remaining, and overload)
- · Scheduled time off to conserve energy

Emergency power off (EPO)

Remote UPS shutoff in the event of a fire or other emergency. The UPS can accept normally open (NO) or normally closed (NC) contacts.

Communication ports

Serial, USB, Ethernet, and SmartSlot for network accessory cards.

Communication protocols

Modbus Serial, USB PowerSummary, HTTP, SNMP, and Telnet.

Intuitive, easy-to-use LCD provides clear and accurate information in multiple languages







Backlight screens:

Amber: Indication of condition that requires attention

Red: Indication of UPS alarm that requires immediate attention

Standard features

LCD display screen

Accurately provides real-time status updates in your choice of basic or advanced menus.

UPS status (scrolling)

- Output voltage
- · Input voltage
- Output frequency
- Run time
- Load
- Battery health

Control

- UPS and outlet group settings
- · Bypass control

Configuration

- · Output voltage, frequency
- · Language, brightness, contrast
- Alarm volume
- IP address

Test and diagnostics

 Initiate battery and runtime calibration tests

About

- UPS serial number, battery part number
- Battery install and suggested replacement dates

Product accessories

Management cards

- AP9640: UPS Network Management Card
- AP9641: UPS Network Management Card with Environmental Monitoring
- AP9643: UPS Network Management Card with Environmental Monitoring and Modbus Support
- AP9810: APC dry contact I/O accessory
- · AP9624: UPS interface expander
- · AP9613: dry contact I/O SmartSlot card

Battery packs

- SRT192BP: APC Smart-UPS SRT 192 V 5 kVA and 6 kVA battery pack
- SRT192RMBP: APC Smart-UPS SRT 192 V 5 kVA and 6 kVA RM battery pack
- SRT192BP2: APC Smart-UPS SRT 192 V 8 kVA and 10 kVA battery pack
- SRT192RMBP2: APC Smart-UPS SRT 192 V 8 kVA and 10 kVA RM battery pack
- SRT48BP: APC Smart-UPS SRT 48 V 1 kVA and 1.5 kVA battery pack
- SRT48RMBP: APC Smart-UPS SRT 48 V 1 kVA and 1.5 kVA RM battery pack
- SRT72BP: APC Smart-UPS SRT 72 V 2.2 kVA battery pack
- SRT72RMBP: APC Smart-UPS SRT 72 V 2.2 kVA RM battery pack
- SRT96BP: APC Smart-UPS SRT 96 V 3 kVA battery pack
- SRT96RMBP: APC Smart-UPS SRT 96 V 3 kVA RM battery pack
- SRT002: APC Smart-UPS SRT 15 ft. extension cable for 192 VDC external battery packs 5/6 kVA UPS
- SRT003: APC Smart-UPS SRT 15 ft. extension cable for 192 VDC external battery packs 8/10 kVA UPS

- SRT009: APC Smart-UPS SRT 15 ft. extension cable for 72 VDC external battery pack 2.2 kVA UPS
- SRT010: APC Smart-UPS SRT 15 ft. extension cable for 96 VDC external battery pack 3 kVA UPS
- SRT013: APC Smart-UPS SRT 15 ft. extension cable for 48 VDC external battery pack

Rail kits

- SRTRK2: APC Smart-UPS SRT 19 inch rail kit for Smart-UPS SRT 5/6/8/10 kVA
- SRTRK3: APC Smart-UPS SRT 2 post mounting rail kit for Smart-UPS SRT 2.2/3/5/8/10 kVA
- SRTRK4: APC Smart-UPS SRT 19 inch rail kit for Smart-UPS SRT 2.2/3 kVA

Backplate kit

- SRT001: APC Smart-UPS SRT 5 kVA output HW kit
- SRT004: APC Smart-UPS SRT 5 kVA PDU, 208 V (4) L6-20
- SRT005: APC Smart-UPS SRT 6 kVA PDU, 208 V (4) L6-20, (1) L6-30
- SRT008: APC Smart-UPS SRT 8/10 kVA PDU, 208 V (6) L6-30
- SRT011: APC Smart-UPS SRT 3 kVA PDU, 208 V (3) L6-30
- SRT012: APC Smart-UPS SRT 2.2/3 kVA input/output HW kit

Service bypass panels

- SBP1500RM: APC service bypass panel 120 V; 15 A; BBM; (8) 5-15R
- SBP2200RM: APC service bypass panel 120 V; 20 A; BBM; (6) 5-15R (2) 5-20R

- SBP3000RM: APC service bypass panel 120 V; 16 A; BBM; (4) 5-20R (1) L5-30R
- SBP5KRMT2U: APC service bypass panel — 200/208/240 V; 30 A; BBM; L6-30P input; (2) L6-30R (2) L6-20R output
- SBP6KRMT2U: APC service bypass panel
 200/208/240 V; 50 A; MBB; L6-30P/HW input; (1) L6-30R (2) L6-20R output
- SBP10KRMT4U: APC service bypass panel
 — 200/208/240 V; 100 A; MBB; hardwire
 input; (3) L6-30R (3) L6-20R output

Step-down transformers

- SRT5KTF: APC Smart-UPS SRT 3/5/6 kVA 3Utower isolation/step-down transformer
- SRT5KRMTF: APC Smart-UPS 3/5/6 kVA 2U RM step-down transformer
- SRT10KRMTF: APC Smart-UPS SRT 10 kVA 4U RM step-down transformer

Other

· SURT013: SURT equipment cart

Replacement battery cartridge

- APCRBC140: RBC for SRT 5 kVA
 —10 kVA UPS
- APCRBC155: RBC for SRT 1-1.5 kVA
- APCRBC141: RBC for SRT 2.2 kVA UPS
- APCRBC152: RBC for SRT 3 kVA UPS

Runtime estimates at half and full load (minutes)

UPS Half/Full Loads	SRT1000XLA (RM) (RM-NC) 450 W/900 W	SRT1500XLA (RM) (RM-NC) 675 W/1350 W	SRT2200XLA (RM) (RM-NC) 900 W/1800 W	SRT3000XLA (RM) (RM-NC) 1350 W/2700 W	SRT3000XLT (RM) SRT3000XLW-IEC (RM) SRT3000RMXLT-NC 1350 W/2700 W	SRT5KRMXLW-HW 2250 W/4500 W	SRT5KXLT (RM) SRT5KXLT-IEC (RM) 2125 W/4250 W	SRT6KXLT (RM) SRT6KXLT-IEC (RM) 3000 W/6000 W	SRT8KXLT (RM) SRT8KXLT-IEC (RM) 4000 W/8000 W	SRT10KXLT (RM) SRT10KXLT-IEC (RM) 5000 W/10000 W
Internal	25.36/10.48	13.16/4.61	10.3/3.26	10.28/3.21	11.36/3.8	11.75/3.98	10.53/3.8	8.3/2.4	14.4/5.16	11.4/3.73
(1) Battery pack	88/40	50/22.58	41/18.1	37/16	44/19.9	46/20.46	42/19	34/14.86	37/15	27.83/11.5
(2) Battery packs	156/73	91/41	74/33	68/31	80/37	83/38	76/35	62/28.28	54/24.41	45/19.65
(3) Battery packs	226/106	132/61	109/50	99/45	117/54	121/56	112/52	92/42	76/34	62/28.05
(4) Battery packs	299/141	175/82	144/67	132/61	156/73	160/75	148/69	122/56	98/44	81/36

Smart-UPS On-Line SRT 1000 VA and SRT 1500 VA 120 V

Product features	SRT1000XLA - SRT1000RMXLA SRT1000RMXLA-NC (Pre-installed NMC, AP9641)	SRT1500XLA - SRT1500RMXLA SRT1500RMXLA-NC (Pre-installed NMC, AP9641)		
Output				
Power rating	1000 VA/900 W	1500 VA/1350 W		
Nominal output voltage	120) V		
Output frequency	50/60 Hz \pm 3 Hz (auto sense) 50/	$60~\mathrm{Hz}\pm0.1~\mathrm{Hz}$ (user selectable)		
Topology	Double-conve	ersion Online		
Online efficiency at full load (typical)	91.5% (ENE	RGY STAR)		
Green mode efficiency at full load (typical)	97	%		
Output connections (switched groups)	(6) NEMA 5-15R	(6) NEMA 5-15R		
Input				
Nominal input voltage	12	0 V		
Input voltage range full load (half load)	80 V - 150 VAC ±5V (50 - 150 VAC ±5V)	108 V - 150 VAC ±5V (50 - 150 VAC ±5V)		
Input frequency	40 - 7	70 Hz		
Input connection	5-1	5P		
Batteries and runtime				
Battery type	Sealed maintenance-free valve regulated lead-acid battery with suspended electrolyte, leak proof			
Typical backup time at 1/2 load (min.)	25.4	13.2		
Typical backup time at full load (min.)	10.5	4.6		
Replacement battery (quantity)	APCRBC155 (1)			
External battery pack (tower/rackmount)	SRT48BP/SRT48RMBP			
Communication and management				
Interface ports	Serial (RJ45), USB (Type A) and SmartSlot			
Control panel	High resolution graphical LCD display			
Emergency power off (EPO)	Yes (NO/NC connections)			
Physical				
Rack height	3" (85 mm), 2U			
Maximum width (RM)	17" (432 mm)			
Maximum depth (RM)	21.5 inches/545 mm			
Net weight	48.5 lb (22.0 kg)			
Conformance				
Regulatory	UL-1778, FCC Part 15 Class A, CSA			
Warranty	3 years electronics, 2 years battery			



Smart-UPS On-Line SRT 2200 VA and SRT 3000 VA 120 V

Product features	SRT2200XLA - SRT2200RMXLA SRT2200RMXLA-NC (Pre-installed NMC, AP9641)	SRT3000XLA - SRT3000RMXLA SRT3000RMXLA-NC (Pre-installed NMC, AP9641)			
Output					
Power rating	2200 VA/1800 W	3000 VA/2700 W			
Nominal output voltage	120	0 V			
Output frequency	50/60 Hz \pm 3 Hz (auto sense) 50/	$/60 \text{ Hz} \pm 0.1 \text{ Hz}$ (user selectable)			
Topology	Double-conv	ersion Online			
Online efficiency at full load (typical)	91.5% (ENE	RGY STAR)			
Green mode efficiency at full load (typical)	97	%			
Output connections (switched groups)	(6) 5-20, (1) L5-20R	(8) 5-20, (1) L5-30R			
Input					
Nominal input voltage	12	0 V			
Input voltage range full load (half load)	108 V - 150 VAC ±5\	/ (50 – 150 VAC ±5V)			
Input frequency	40 – 7	70 Hz			
Input connection	5-20P	L5-30P			
Batteries and runtime					
Battery type	Sealed maintenance-free valve regulated lead-acid battery with suspended electrolyte, leak proof				
Typical backup time at 1/2 load (min.)	10.3	10.4			
Typical backup time at full load (min.)	3.2	3.1			
Replacement battery (quantity)	APCRBC141 (1)	APCRBC152 (1)			
External battery pack (tower/rackmount)	SRT72BP/SRT72RMBP	SRT96BP/SRT96RMBP			
Communication and management					
Interface ports	Serial (RJ45), USB (Type A) and SmartSlot				
Control panel	High resolution gra	phical LCD display			
Emergency power off (EPO)	Yes (NO/NC connections)				
Physical					
Rack height	3.35" (85 mm), 2U	3.35" (85 mm), 2U			
Maximum width (RM)	17" (432 mm)	17" (432 mm)			
Maximum depth (RM)	23 " (559 mm)	25 " (636 mm)			
Net weight	55 lb (24.95 kg)	69 lb (31.3 kg)			
Conformance					
Regulatory	UL-1778, FCC Part 15 Class A, CSA				
Warranty	3 years electronics, 2 years battery				



Smart-UPS On-Line SRT 3000 VA 208 V

Product features	SRT3000XLW-IEC SRT3000RMXLW-IEC	SRT3000XLT - SRT3000RMXLT SRT3000RMXLT-NC (Pre-installed NMC, AP9641)			
Output					
Power rating	3000 VA/2700 W				
Nominal output voltage	230 V (208 V, 220 V, 230 V, 240 V user selectable)	208 V (240 V user selectable)			
Output frequency	50/60 Hz ± 3 Hz (auto sense) 50/	/60 Hz ± 0.1 Hz (user selectable)			
Topology	Double-conv	ersion Online			
Online efficiency at full load (typical)	91% (ENE	RGY STAR)			
Green mode efficiency at full load (typical)	97	%			
Output connections (switched groups)	(6) IEC 320 C13 (2) IEC 320 C19	(2) L6-20R (1) L6-30R			
Input					
Nominal input voltage	230 V (208 V, 220 V, 240 V user selectable)	208 V (240 V user selectable)			
Input voltage range full load (half load)	160 – 275 V	(100 – 275 V)			
Input frequency	40 –	70 Hz			
Input connection	IEC 60320 C20, Schuko CEE 7/EU1-16P, British BS1363A	L6-20P			
Batteries and runtime					
Battery type	Sealed maintenance-free valve regulated lead-acid battery with suspended electrolyte, leak proof				
Typical backup time at 1/2 load (min.)	11.8 min	11.4 min			
Typical backup time at full load (min.)	4.0 min	3.8 min			
Replacement battery (quantity)	APCRB	C152 (1)			
External battery pack (tower/rackmount)	SRT96BP/S	SRT96RMBP			
Communication and management					
Interface ports	Serial (RJ45), USB (T	ype A) and SmartSlot			
Control panel	High resolution graphical LCD display				
Emergency power off (EPO)	Yes (NO/NC connections)				
Physical					
Rack height	3.35" (85	mm), 2U			
Maximum width (RM)	17" (43	17" (432 mm)			
Maximum depth (RM)	25" (63	25" (636 mm)			
Net weight	69 lb (31 kg)				
Conformance					
Regulatory	CE, VDE, RCM, and EAC, IEC/EN 62040-1, IEC/EN 62040-2, UL-1778, FCC Part 15 Class A, CSA	UL-1778, FCC Part 15 Class A, CSA			
Warranty	3 years electronics, 2 years battery				



Smart-UPS On-Line SRT 3000 VA 120/208 V with Transformer

Product features	SRT3000XLT-5KTF	SRT3000RMXLT-5KTF				
Output						
Power rating	3000 VA/2	3000 VA/2700 W				
Nominal output voltage (UPS)	208 V (240 V us	er selectable)				
Nominal output voltage (transformer)	120 V, 208 V, 240 V	120 V				
Output frequency	50/60 Hz ± 3 Hz	z (auto sense)				
Output connections (UPS)	(2) L6-20R, (1) L6-30R (for transformer)	(2) L6-20R, (1) L6-30R (for transformer)				
Output connections (transformer)	(8) 5-20R, (2) L6-20R, (1) L6-30R, (1) L14-30R	(12) 5-20R				
Input						
Nominal input voltage	208 V (240 V us	208 V (240 V user selectable)				
Input connection	L6-2	L6-20P				
Physical						
Rack height	Tower	6.7" (170 mm) 4U				
Maximum width (RM)	8.45" (215 mm)	17" (432 mm)				
Maximum depth (RM)	26" (660 mm)	25" (636 mm)				
Net weight	194 lb (87.82 kg)	164 lb (74.18 kg)				
Conformance						
Regulatory	UL-1778, FCC Part	UL-1778, FCC Part 15 Class A, CSA				
Warranty	3 years electronics	3 years electronics, 2 years battery				

^{*} Transformer must be connected to UPS output with constant input voltage.

Smart-UPS On-Line SRT 5 kVA and 6 kVA 208 V

Product features	SRT5KRMXLW-HW	SRT5KXLT SRT5KRMXLT	SRT5KXLT-IEC SRT5KRMXLT-IEC	SRT6KXLT SRT6KRMXLT	SRT6KXLT-IEC SRT6KRMXLT-IEC			
Output	Output							
Power rating	5000 VA/4500 W	208VAC: 5400 VA/4800 W 240VAC: 6000 VA/4800		6000 VA/6000 W				
Nominal output voltage	230 V (208, 220, 230, 240 V user selectable)	· · · · · · · · · · · · · · · · · · ·						
Output frequency		50/60 Hz \pm 3 Hz (auto sense) 50/60 Hz \pm 0.1 Hz (user selectable)						
Topology	Double-conversion Online							
Online efficiency at full load (typical)			94% (ENERGY STAR)					
Green mode efficiency at full load (typical)			98%					
Output connections	HW	(2) L6-20R (2) L6-30R	(6) IEC 320 C13 (4) IEC 320 C19	(2) L6-20R (3) L6-30R, HW	(6) IEC 320 C13 (4) IEC 320 C19, HW			
Input								
Nominal input voltage	230 V (208, 220, 230, 240 V user selectable)		208 V (240 \	/ user selectable)				
Input voltage range full load (half load)			160 – 275 V (100 – 275 V	V)				
Input frequency			40 – 70 Hz					
Input connection	Hardwire 3-wire (L1+L2/N+G)	L6-30P		Hardwire 3-wire (L1+L2+G)				
Batteries and runtime								
Battery type	Sealed maintenance-free valve regulated lead-acid battery with suspended electrolyte, leak proof							
Typical backup time at 1/2 load (min.)	11.75 min.	10	0.53 min.	8.3 min.				
Typical backup time at full load (min.)	3.98 min.	3	3.8 min.	2.4 min.				
Replacement battery (quantity)		APCRBC140						
External battery pack (tower/rackmount)	SRT192BP/SRT192RMBP							
Communication and management								
Interface ports	RJ-4	45 with status LEDs (1	10/100 Base-T), serial (RJ45)), USB (Type B), and Smart	Slot			
Control panel	High-resolution graphical LCD display							
Emergency power off (EPO)	Yes (NO/NC connections)							
Embedded network management with environmental monitoring	Yes							
Physical								
Rack height	3 U			4 U				
Maximum height rackmount SKU	5.1" (130 mm)			6.85" (174 mm)				
Maximum width rackmount SKU	17" (432 mm)			17" (432 mm)				
Maximum depth rackmount SKU	28.32" (719 mm)		28.32" (719 mm)					
Net weight	123 lbs (55.8 kg)			135 lbs (61.25 kg)				
Conformance								
Regulatory	CE, VDE, UL-1778, FCC Part 15 Class A, cUL		UL-1778, FCC Par	UL-1778, FCC Part 15 Class A, cUL, NOM				
Warranty	3 years for electronics, 2 years for battery							



Smart-UPS On-Line SRT 5 kVA and 6 kVA 120/208 V with Transformers

Product features	SRT5KXLT-5KTF	SRT5RMKXLT-5KTF	SRT6KXLT-5KTF	SRT6RMKXLT-5KTF		
Output						
Power rating	208VAC: 540 240VAC: 600		6,000 VA/6,000 W			
Nominal output voltage	208 V (240 V user selectable)					
Nominal output voltage (transformer)	120 V, 208 V, 240 V	120 V	120 V, 208 V, 240 V	120 V		
Output frequency		50/60 Hz \pm 3 H	dz (auto sense)			
Output connections (UPS)	(2) L6-20R, (2) L6-30	R (1 for transformer)	(2) L6-20R, (2) L6-30R (1 for transformer), HW			
Output connections (transformer)	(8) 5-20R, (2) L6-20R, (1) L6-30R, (1) L14-30R	(12) 5-20R	(8) 5-20R, (2) L6-20R, (1) L6-30R, (1) L14-30R	(12) 5-20R		
Input						
Nominal input voltage	208 V (240 V user selectable)					
Input voltage range full load (half load)	160 – 275 V (100 – 275 V)					
Input frequency	40 – 70 Hz					
Input connection	Hardwire 3-wire (L1 + L2/N + G)					
Physical						
Rack height	Tower	5U	Tower	6U		
Maximum height	17" (432 mm)	8.6" (219 mm)	17" (432 mm)	10.35" (263 mm)		
Maximum width	10.2" (260 mm)	17" (432 mm)	11.95" (304 mm)	17" (432 mm)		
Maximum depth	28.32" (719.4 mm)	28.32" (719.4 mm)	28.32" (719.4 mm)	28.32" (719.4 mm)		
Net weight	248 lbs (112.62 kg)	218 lbs (98.98 kg)	260 lbs (118.07 kg)	230 lbs (104.43 kg)		
Conformance						
Regulatory	UL-1778, FCC Part 15 Class A, cUL					
Warranty		3 years electronic	ics, 2 years battery			

Smart-UPS On-Line SRT 8 kVA and 10 kVA 208 V

Product features	SRT8KXLT SRT8KRMXLT	SRT8KXLT30 SRT8KRMXLT30	SRT8KXLT-IEC SRT8KRMXLT-IEC	SRT10KXLT SRT10KRMXLT	SRT10KXLT30 SRT10KRMXLT30	SRT10KXLT-IEC SRT10KRMXLT-IEC
Output						
Power rating		8,000 VA/8,000 W		10,000 VA/10,000 W		
Nominal output voltage			208 V (240 V u	ser selectable)		
Output frequency		50/60 Hz \pm 3 Hz (auto sense) 50/60 Hz \pm 0.1 Hz (user selectable)				
Topology			Double-conv	ersion Online		
Online efficiency at full load (typical)		94% (ENERGY STAR)		93% (ENERGY STAF	₹)
Green mode efficiency at full load (typical)		98.5%			99%	
Output connections	(4) L6-20R (2) L6-30R, HW	(6) L6-30R, HW	(6) IEC 320 C13 (4) IEC 320 C19, HW	(4) L6-20R (2) L6-30R, HW	(6) L6-30R, HW	(6) IEC 320 C13 (4) IEC 320 C19, HW
Input						
Nominal input voltage			208 V (240 V u	ser selectable)		
Input voltage range full load (half load)			160 – 275 V	(100 – 275 V)		
Input frequency			40 –	70 Hz		
Input connection			Hardwire 3-wire	e (L1+L2/N+G)		
Batteries and runtime						
Battery type		Sealed maintenance-fre	e valve regulated lead-ac	cid battery with suspen	nded electrolyte, leak p	proof
Typical backup time at 1/2 load (min.)		14.4 min.		11.4 min.		
Typical backup time at full load (min.)		5.2 min.		3.7 min.		
Replacement battery (quantity)			APCRBO	C140 (2)		
External battery pack (tower/rackmount)			SRT192BP2/S	RT192RMBP2		
Communication and manager	nent					
Interface ports		RJ-45 with status	s LEDs (10/100 Base-T), s	serial (RJ45), USB (Typ	oe B), and SmartSlot	
Control panel			High-resolution gra	aphical LCD display		
Emergency power off (EPO)			Yes (NO/NC	connections)		
Embedded network management with environmental monitoring			Ye	es		
Physical						
Rack height			6	U		
Maximum height rackmount SKU	10.35" (263 mm)					
Maximum width rackmount SKU	17" (432 mm)					
Maximum depth rackmount SKU	28.15" (715 mm)					
Net weight	246 lbs (111.82 kg)					
Conformance						
Regulatory	UL-1778, FCC Part 15 Class A, CSA C22.2 No.107.3-05, NOM					
Warranty	3 years electronics, 2 years battery					



Smart-UPS On-Line SRT 8 kVA and 10 kVA 120/208 V with Transformers

Product features	SRT8KXLT-5KTF	SRT8KRMXLT-5KTF	SRT10KRMXLT-10KTF	SRT10KXLT-5KTF2	SRT10KRMXLT-5KTF2			
Output								
Power rating (UPS)	8,000 V	√8,000 W	10,000 VA/10,000 W					
Power rating (transformer)	500	00 VA	10 kVA	500	00 VA			
Nominal output voltage			208 V (240 V user sel	lectable)				
Nominal output voltage (transformer)	120 V, 208 V, 240 V	120V	120 V, 208 V, 240 V		120 V			
Output frequency			50/60 Hz ± 3 Hz (aut	o sense)				
Output connections (UPS)	(4) L6-20R, (1) L6-	30R (for transformer)	(4) L6-20R, (2) L6-30R	(4) L6-20R, (2) L6-30R, (1) Hardwire 3-wire (2P + E)	(4) L6-20R, (2) L6-30R, (1) Hardwire 3-wire (2P + E)			
Output connections (transformer)	(8) 5-20R, (2) L6- 20R, (1) L6-30R, (1) L14-30R	(12) 5-20R	(2) L5-20R, (2) L14-30R, (2) Hardwire 3-wire (2P + E), (1) Hardwire 4-wire (2P + N + E)	(16) 5-20R, (4) L6-20R, (2) L6-30R, (2) L14-30R	(24) 5-20R			
Input								
Nominal input voltage	208 V (240 V user selectable)							
Input voltage range full load (half load)		160 – 275 V (100 – 275 V)						
Input frequency		40 – 70 Hz						
Input connection	Hardwire 3-wire (L1+L2+G)							
Physical								
Rack height	Tower	8U	10U	Tower	10U			
Maximum height	17" (432 mm)	13.85" (352 mm)	17.25" (438 mm)	17" (432 mm)	17.35" (441 mm)			
Maximum width	15.45" (393 mm)	17" (432 mm)	17" (432 mm)	20.55" (523 mm)	17" (432 mm)			
Maximum depth	28.15" (715 mm)	28.15" (715 mm)	29.5" (749 mm)	28.15" (715 mm)	28.15" (715 mm)			
Net weight	371 lbs (168.4 kg)	341 lbs (154.76 kg)	466 lbs (211.58 kg)	496 lbs (225.22 kg)	436 lbs (197.94 kg)			
Conformance								
Regulatory	UL-1778, FCC Part 15 Class A, CSA C22.2 No.107.3-05							
Warranty		3 years electronics, 2 years	ears battery					



Schneider Electric

One Boston Place Floor 27 Boston, MA 02108 United States (857)205-9626

www.apc.com

September 2022

