

# MiCOM P743

## Numerical Busbar Protection

### P743/EN PM/K96

Version:        Software: E2.0  
                  Hardware: K

### PICS & MICS

Content:    Protocol Implementation Conformance Statement  
                  & Model Implementation Conformance Statement

**Note:** The technical manual for this device gives instructions for its installation, commissioning, and operation. However, the manual cannot cover all conceivable circumstances or include detailed information on all topics. In the event of questions or specific problems, do not take any action without proper authorization. Contact the appropriate Schneider Electric technical sales office and request the necessary information.

Any agreements, commitments, and legal relationships and any obligations on the part of Schneider Electric including settlements of warranties, result solely from the applicable purchase contract, which is not affected by the contents of the technical manual.

This device **MUST NOT** be modified. If any modification is made without the express permission of Schneider Electric, it will invalidate the warranty, and may render the product unsafe.

The Schneider Electric logo and any alternative version thereof are trademarks and service marks of Schneider Electric.

MiCOM is a registered trademark of Schneider Electric. All trade names or trademarks mentioned herein whether registered or not, are the property of their owners.

This manual is provided for informational use only and is subject to change without notice.

© 2012, Schneider Electric. All rights reserved.

## CONTENTS

---

<b>1.</b>	<b>PROTOCOL IMPLEMENTATION CONFORMANCE STATEMENT (PICS)</b>	<b>5</b>
1.1	Introduction .....	5
1.2	ACSI basic conformance statement.....	5
1.3	ACSI models conformance statement .....	5
1.4	ACSI service conformance statement.....	7

---

<b>2.</b>	<b>MODEL IMPLEMENTATION CONFORMANCE STATEMENT (MICS)</b>	<b>10</b>
2.1	Introduction .....	10
2.2	Objective .....	10
2.3	Logical Device definitions.....	10
2.4	Logical Node definitions .....	13
2.5	Common Data Class definitions .....	29
2.6	Common data attribute type definitions .....	39
2.7	Enumerated type definitions.....	41
2.8	MMS data-type conversions.....	44

## TABLES

TABLE 1: BASIC CONFORMANCE STATEMENT	5
TABLE 2: MODELS CONFORMANCE STATEMENT	6
TABLE 3: SERVICE CONFORMANCE STATEMENT	9

BLANK PAGE

# 1. PROTOCOL IMPLEMENTATION CONFORMANCE STATEMENT (PICS)

## 1.1 Introduction

This specification is the Protocol Implementation Conformance Statement (PICS) and presents the ACSI conformance statements as defined in Annex A of Part 7-2 of the IEC 61850 standard specifications.

## 1.2 ACSI basic conformance statement

The basic conformance statement shall be as defined in Table 1.

Client-Server roles		Client/ subscriber	Server/ publisher	Value/ comments
B11	Server side (of TWO-PARTY-APPLICATION-ASSOCIATION)		Y	
B12	Client side of (TWO-PARTY-APPLICATION-ASSOCIATION)			
<b>SCSMs supported</b>				
B21	SCSM: IEC 6185-8-1 used		Y	
B22	SCSM: IEC 6185-9-1 used			
B23	SCSM: IEC 6185-9-2 used			
B24	SCSM: other			
<b>Generic substation event model (GSE)</b>				
B31	<b>Publisher</b> side		Y	
B32	<b>Subscriber</b> side	Y		
<b>Transmission of sampled value model (SVC)</b>				
B41	<b>Publisher</b> side			
B42	<b>Subscriber</b> side			
–				
Y = supported				
N or empty = not supported				

**Table 1: Basic conformance statement**

## 1.3 ACSI models conformance statement

The ACSI models conformance statement shall be as defined in Table 2.

		Client/ subscriber	Server/ publisher	Value/ comments
<b>If Server or Client side (B11/12) is supported</b>				
M1	Logical Device		Y	
M2	Logical Node		Y	
M3	Data		Y	
M4	Data set		Y	
M5	Substitution			
M6	Setting group control		Y	
	Reporting			
M7	Buffered report control		Y	
M7-1	sequence-number		Y	
M7-2	report-time-stamp		Y	

		Client/ subscriber	Server/ publisher	Value/ comments
M7-3	reason-for-inclusion		Y	
M7-4	data-set-name		Y	
M7-5	data-reference		Y	
M7-6	buffer-overflow		Y	
M7-7	entryID		Y	
M7-8	BufTim		Y	
M7-9	IntgPd		Y	
M7-10	GI		Y	
M7-11	conf-revision		Y	
M8	Unbuffered report control		Y	
M8-1	sequence-number		Y	
M8-2	report-time-stamp		Y	
M8-3	reason-for-inclusion		Y	
M8-4	data-set-name		Y	
M8-5	data-reference		Y	
M8-6	BufTim		Y	
M8-7	IntgPd		Y	
M8-8	GI		Y	
M8-9	conf-revision		Y	
	Logging			
M9	Log control			
M9-1	IntgPd			
M10	Log			
M11	Control		Y	
<b>If GSE (B31/32) is supported</b>				
M12	GOOSE	Y	Y	
M13	GSSE			
<b>If SVC (41/42) is supported</b>				
M14	Multicast SVC			
M15	Unicast SVC			
<b>If Server or Client side (B11/12) is supported</b>				
M16	Time	Y	Y	Time source with required accuracy shall be available.
M17	File Transfer		Y	
Y = service is supported N or empty = service is not supported				

**Table 2: Models conformance statement**

## 1.4 ACSI service conformance statement

The ACSI service conformance statement shall be as defined in Table 3 (depending on the statements in Table 1).

	Services	AA: TP/MC	Client (C)	Server (S)	Comments
<b>Server</b>					
S1	ServerDirectory	TP		Y	

<b>Application association</b>					
S2	Associate			Y	
S3	Abort			Y	
S4	Release			Y	

<b>Logical Device</b>					
S5	LogicalDeviceDirectory	TP		Y	

<b>Logical Node</b>					
S6	LogicalNodeDirectory	TP		Y	
S7	GetDataValues	TP		Y	

<b>Data</b>					
S8	GetDataValues	TP		Y	
S9	SetDataValues	TP		Y	
S10	GetDataDirectory	TP		Y	
S11	GetDataDefinition	TP		Y	

<b>Data set</b>					
S12	GetDataSetValues	TP		Y	
S13	SetDataSetValues	TP			
S14	CreateDataSet	TP			
S15	DeleteDataSet	TP			
S16	GetDataSetDirectory	TP		Y	

<b>Substitution</b>					
S17	SetDataValues	TP			

<b>Setting group control</b>					
S18	SelectActiveSG	TP		Y	
S19	SelectEditSG	TP			
S20	SetSGValues	TP			
S21	ConfirmEditSGValues	TP			
S22	GetSGValues	TP		Y	
S23	GetSGCBValues	TP		Y	

	Services	AA: TP/MC	Client (C)	Server (S)	Comments
<b>Reporting</b>					
	Buffered report control block (BRCB)				
S24	Report	TP		Y	
S24-1	data-change (dchg)			Y	
S24-2	qchg-change (qchg)				
S24-3	data-update (dupd)				
S25	GetBRCBValues	TP		Y	
S26	SetBRCBValues	TP		Y	

<b>Unbuffered report control block (URCB)</b>					
S27	Report	TP		Y	
S27-1	data-change (dchg)			Y	
S27-2	qchg-change (qchg)				
S27-3	data-update (dup)				
S28	GetURCBValues	TP		Y	
S29	SetURCBValues	TP		Y	

<b>Logging</b>					
	Log control block				
S30	GetLCBValues	TP			
S31	SetLCBValues	TP			
	Log				
S32	QueryLogByTime	TP			
S33	QueryLogByEntry	TP			
S34	GetLogStatusValues	TP			

<b>Generic substation event model (GSE)</b>					
<b>GOOSE-CONTROL-BLOCK</b>					
S35	SendGOOSEMessage	MC		Y	IED supports GOOSE publish & subscription.
S36	GetReference	TP			
S37	GetGOOSEElementNumber	TP			
S38	GetGoCBValues	TP		Y	
S39	SetGoCBValues	TP		Y	
<b>GSSE-CONTROL-BLOCK</b>					
S40	SendGSSEMessage	MC			
S41	GetReference	TP			
S42	GetGSSEElementNumber	TP			
S43	GetGsCBValues	TP			



	Services	AA: TP/MC	Client (C)	Server (S)	Comments
S44	SetGsCBValues	TP			
<b>Transmission of sampled value model (SVC)</b>					
<b>Multicast SVC</b>					
S45	SendMSVMessage	MC			
S46	GetMSVCBValues	TP			
S47	SetMSVCBValues	TP			
<b>Unicast SVC</b>					
S48	SendUSVMessage	TP			
S49	GetUSVCBValues	TP			
S50	SetUSVCBValues	TP			
<b>Control</b>					
S51	Select			Y	
S52	SelectWithValue	TP		Y	
S53	Cancel	TP		Y	
S54	Operate	TP		Y	
S55	Command-Termination	TP		Y	
S56	TimeActivated-Operate	TP			
<b>File transfer</b>					
S57	GetFile	TP		Y	
S58	SetFile	TP			
S59	DeleteFile	TP		Y	Only from /dr_unextracted/ Operation may only be performed on .cfg files.
S60	GetFileAttributeValues	TP		Y	
<b>Time</b>					
T1	Time resolution of internal clock			1 ms	Nearest negative power of 2 in seconds.
T2	Time accuracy of internal clock				T0
				1 ms	T1
					T2
					T3
					T4
					T5
T3	Supported TimeStamp resolution	-		10	Nearest value of 2 ** -n in seconds

**Table 3: Service conformance statement**

AA: Application association type

TP: Two part (for MMS)

MC: Multicast (for GOOSE and SMV)

## 2. MODEL IMPLEMENTATION CONFORMANCE STATEMENT (MICS)

### 2.1 Introduction

This specification is the Model Implementation Conformance Statement (MICS) and presents the top-level IEC61850 data model that has been implemented. The definitions of all used Logical Nodes and their associated Common Data Classes, components and associated enumerated values are also included for completeness.

The reader is expected to be conversant with the terminology presented within the IEC61850 part 7 series of specifications.

### 2.2 Objective

To provide comprehensive details of the standard data object model elements supported by the device. The MICS is conformant to the devices associated ICD (Substation Configuration Language) file, according to part 6 of the IEC61850 standards. The layout of the presented tables within this document are conformant to the part 7 series of the IEC61850 standard specifications with the following exceptions:

- • The "Trigger Options" field is not presented
- • The "M/O" field is not present as the definitions are as deployed within the model
- • An additional column "X" is used to signify AREVA custom attributes

### 2.3 Logical Device definitions

The MiCOM relay implements an IEC61850 server that can contain one or more Logical Devices. Each Logical Device contains a data model built from instances of specific Logical Nodes and must consist of at least an instance of the LPHD Logical Node (which is responsible for providing physical device information) and an instance of the LLN0 Logical Node (for addressing common issues across the Logical Device).

The IEC61850 data model is contained within the Logical Devices detailed in the table below. All MiCOM devices will name the supported Logical Devices consistently to ensure that data model variables with the same purpose will have the same name within each MiCOM server.

Logical Device	Comment/Usage
Control	Commands and controls
Measurements	Power System Measurements
Protection	Protection Elements
Records	Recording Data
System	Global System Data

#### 2.3.1 IEC61850 logical device data model

The IEC61850 Logical Device top-level data model consists of instances of Logical Nodes. The data model name for a Logical Node instance is constructed from an optional prefix (known as the wrapper), the Logical Node name, and an instance ID (or suffix).

The presented data model is in an alphabetically sorted order, rather than a logical order, because this is the natural order of the data when presented by a native MMS browser. (Higher level browsers can of course impart any ordering that they desire).

LD	LN Instance	LN Type	Description
<b>Control</b>			
	CtICILO1	CILO_BASIC	Interlocking Circuit Breaker Tri Phases
	CtICSWI1	CSWI_GENERAL	CB Control
	LLN0	LLN0_STANDARD	Controls Logical Device
	LPHD1	LPHD_STANDARD	Physical Device
<b>Information</b>			
	PhsXCBR1	XCBR_BASIC	Circuit Breaker Phase A
	PhsXCBR2	XCBR_BASIC	Circuit Breaker Phase B
	PhsXCBR3	XCBR_BASIC	Circuit Breaker Phase C
	TriXCBR1	XCBR_BASIC	Circuit Breaker Tri Phases
<b>Measurements</b>			
	LLN0	LLN0_STANDARD	Measurements Logical Device
	LPHD1	LPHD_STANDARD	Physical Device Information
	PriMMXU1	MMXU_P743	P743 Primary Measurements
	SecMMXU1	MMXU_P743	P743 Secondary Measurements
<b>Protection</b>			
	BbcEfmPIOC1	PIOC_NEU_OP_NOSEG	IN>BB Earth Fault Busbar Trip Confirm
	BbcOcpPIOC1	PIOC_STR_SEG_OP_NOSEG	I>BB Phases Busbar Trip Confirm
	CbfBbpRBRF1	RBRF_INTTRIP_NOSEG	CB Fail 1 for Busbar Protection (Internal Trip)
	CbfBbpRBRF2	RBRF_EXTTRIP_NOSEG	CB Fail 2 for Busbar Protection (External Trip)
	CbfBbpRBRF3	RBRF_INTTRIP_SEG	CB Fail 3 for Busbar Protection (Internal Trip)
	CbfBbpRBRF4	RBRF_EXTTRIP_NOSEG	CB Fail 4 for Busbar Protection (External Trip)
	CbfCupPTRC1	PTRC_NO_SEG	CB Fail Trip to CU
	DzpEfmPTOC1	PTOC_NEU_OP_NOSEG	IN>DZ Dead Zone Earth Fault Protection
	DzpPhsPTOC1	PTOC_STR_SEG_OP_NOSEG	I>DZ Phases Dead Zone Protection
	EfmBbbPIOC1	PIOC_NEU_OP_NOSEG	IN>2 Earth Fault Blocking Busbar
	EfmPTOC1	PTOC_NEU_OP_NOSEG	IN>1 Earth Fault Protection
	EfmPTOC2	PTOC_NEU_OP_NOSEG	IN>2 Earth Fault Protection
	LLN0	LLN0_PROT_P743	Protection Logical Device for P743
	LogPTRC1	PTRC_NOSEG_NOTR	Logic Protection for P743
	LPHD1	LPHD_STANDARD	Physical Device Information
	OcpBbbPIOC1	PIOC_STR_SEG_OP_NOSEG	I>2 Overcurrent Blocking Busbar
	OcpPTOC1	PTOC_STR_SEG_OP_NOSEG	I>1 Phases Overcurrent Protection
	OcpPTOC2	PTOC_STR_SEG_OP_NOSEG	I>2 Phases Overcurrent Protection
	PlpPTRC1	PTRC_NOSEG_NOTR	Programmable Logic Protection for P743
	TrpCupPDIF1	PDIF_STR_SEG_NEU_OP_NOS EG__	87BB Trip confirmation by external criteria
	TrpPhsPTRC1	PTRC_NOOP_TRNOSEG	Trip Phase A
	TrpPhsPTRC2	PTRC_NOOP_TRNOSEG	Trip Phase B
	TrpPhsPTRC3	PTRC_NOOP_TRNOSEG	Trip Phase C
<b>Records</b>			
	LLN0	LLN0_STANDARD	Records Logical Device
	LPHD1	LPHD_STANDARD	Physical Device
<b>Information</b>			
	RDRE1	RDRE_BASIC	Disturbance Recorder
<b>System</b>			
	AlmGGIO1	GGIO_ALM_96	Alarms
	FnkGGIO1	GGIO_IND_10	Function Keys
	GosGGIO1	GGIO_IND_64	GOOSE Input Signals
	GosGGIO2	GGIO_IND_32	GOOSE Output Signals
	LckGGIO1	GGIO_IND_6	87BB External Blocking
	LedGGIO1	GGIO_IND_18	Red LED Signals
	LedGGIO2	GGIO_IND_18	Green LED Signals
	LLN0	LLN0_SYSTEM	System Logical Device (with Ordrun)
	LPHD1	LPHD_STANDARD	Physical Device

LD	LN Instance	LN Type	Description
<b>Information</b>			
	OptGGIO1	GGIO_IND_24	P743 : Opto Inputs
	OptVirGGIO1	GGIO_IND_16_WD	P740 : virtual opto
	OrdRunGGIO1	GGIO_IND_64	Uniqueness of control "Order Running" indications for Control operations
	PloGGIO1	GGIO_SPCSO_32	PSL Control Inputs
	RlyGGIO1	GGIO_IND_20	P743 : 20 Output
<b>Contacts</b>			
	RlyVirGGIO1	GGIO_IND_16_WD	P740 : virtual relay
	TrpCupGGIO1	GGIO_IND_3	Trip Order from CU

## 2.4 Logical Node definitions

The definition tables for each of the Logical Nodes in the top-level data model are presented in the following sub-sections.

The following table presents a summary of the Logical Node templates used across the Logical Devices within the overall IEC61850 product data model:

LN Type	(LN Class)	Description	Name Space
CILO_BASIC	(CILO)	Interlocking	IEC 61850-7-4:2003
CSWI_GENERAL	(CSWI)	Switch controller General	IEC 61850-7-4:2003
GGIO_ALM_96	(GGIO)	Generic Process I/O (w.r.t 96 Alarm Elements)	IEC 61850-7-4:2003
GGIO_IND_10	(GGIO)	Generic Process I/O (w.r.t 10 Indication Elements)	IEC 61850-7-4:2003
GGIO_IND_16_WD	(GGIO)	Generic process I/O	IEC 61850-7-4:2003
GGIO_IND_18	(GGIO)	Generic Process I/O (w.r.t 18 Indication Elements)	IEC 61850-7-4:2003
GGIO_IND_20	(GGIO)	Generic process I/O	IEC 61850-7-4:2003
GGIO_IND_24	(GGIO)	Generic process I/O (w.r.t 24 Indication Elements)	IEC 61850-7-4:2003
GGIO_IND_3	(GGIO)	Generic process I/O (w.r.t 3 Indication Elements)	IEC 61850-7-4:2003
GGIO_IND_32	(GGIO)	Generic Process I/O (w.r.t 32 Indication Elements)	IEC 61850-7-4:2003
GGIO_IND_6	(GGIO)	Generic process I/O	IEC 61850-7-4:2003
GGIO_IND_64	(GGIO)	Generic process I/O (w.r.t 64 Indication Elements)	IEC 61850-7-4:2003
GGIO_SPCSO_32	(GGIO)	Generic process I/O (w.r.t 32 Controllable Elements)	IEC 61850-7-4:2003
LLN0_SYSTEM	(LLN0)	Logical Node 0 (with Ordrun, SyncSt, LEDRs)	IEC 61850-7-4:2003
LLN0_PROT_P743	(LLN0)	Protection Domain Logical Node 0 for P743	AREVA-SII:PCS-Px40
LLN0_STANDARD	(LLN0)	General Logical Node 0	IEC 61850-7-4:2003
LPHD_STANDARD	(LPHD)	Px40 Physical Device Information	IEC 61850-7-4:2003
MMXU_P743	(MMXU)	Standard measurements (w.r.t P743)	IEC 61850-7-4:2003
PDIF_STR_SEG_NEU_OP_NOSEG	(PDIF)	Differential	IEC 61850-7-4:2003
PIOC_NEU_OP_NOSEG	(PIOC)	Instantaneous overcurrent (w.r.t Neutral)	IEC 61850-7-4:2003
PIOC_STR_SEG_OP_NOSEG	(PIOC)	Instantaneous overcurrent	IEC 61850-7-4:2003
PTOC_STR_SEG_OP_NOSEG	(PTOC)	Timed Overcurrent	IEC 61850-7-4:2003
PTOC_NEU_OP_NOSEG	(PTOC)	Timed Overcurrent (w.r.t Neutral)	IEC 61850-7-4:2003
PTRC_NOSEG_NOTR	(PTRC)	Protection trip conditioning	IEC 61850-7-4:2003
PTRC_NO_SEG	(PTRC)	Protection trip conditioning (w.r.t No Phase Segregation)	IEC 61850-7-4:2003
PTRC_NOOP_TRNOS EG	(PTRC)	Protection trip conditioning with no Operate and Trip no phase segregation	IEC 61850-7-4:2003
RBRF_EXTTRIP_NOS EG	(RBRF)	Breaker Failure (w.r.t External Tripping, No Phase Segregation)	IEC 61850-7-4:2003
RBRF_INTTRIP_NOS EG	(RBRF)	Breaker Failure (w.r.t Internal Tripping, No Phase Segregation)	IEC 61850-7-4:2003
RBRF_INTTRIP_SEG	(RBRF)	Breaker Failure (w.r.t Internal Tripping, Phase Segregation)	IEC 61850-7-4:2003

LN Type	(LN Class)	Description	Name Space
RDRE_BASIC	(RDRE)	Disturbance Recorder function (w.r.t Mandatory Attributes only)	IEC 61850-7-4:2003
XCBR_BASIC	(XCBR)	Circuit Breaker (w.r.t Mandatory Attributes Only)	IEC 61850-7-4:2003

#### 2.4.1 Logical Node: CILO\_BASIC

**Description:** Interlocking

**LN Class:** CILO

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		
NamPlt	LPL_LN	Name Plate		
EnaOpn	SPS_WD	Enable Open	T	
EnaCls	SPS_WD	Enable Close	T	

#### 2.4.2 Logical Node: CSWI\_GENERAL

**Description:** Switch controller General

**LN Class:** CSWI

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		
NamPlt	LPL_LN	Name Plate		
Pos	DPC_CONTROL	Switch, general		
OpOpn	ACT_NO_SEG	Operation "open switch"	T	
OpCls	ACT_NO_SEG	Operation "close switch"	T	

#### 2.4.3 Logical Node: GGIO\_ALM\_96

**Description:** Generic Process I/O (w.r.t 96 Alarm Elements)

**LN Class:** GGIO

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		
NamPlt	LPL_LN	Name Plate		
Alm1	SPS_D	General single alarm		
Alm2	SPS_D	General single alarm		
Alm3	SPS_D	General single alarm		
Alm4	SPS_D	General single alarm		
Alm5	SPS_D	General single alarm		
Alm6	SPS_D	General single alarm		
Alm7	SPS_D	General single alarm		
Alm8	SPS_D	General single alarm		
Alm9	SPS_D	General single alarm		
Alm10	SPS_D	General single alarm		
Alm11	SPS_D	General single alarm		
Alm12	SPS_D	General single alarm		
Alm13	SPS_D	General single alarm		
Alm14	SPS_D	General single alarm		
Alm15	SPS_D	General single alarm		
Alm16	SPS_D	General single alarm		

Attribute	Attr. Type	Explanation	T	X
Alm17	SPS_D	General single alarm		
Alm18	SPS_D	General single alarm		
Alm19	SPS_D	General single alarm		
Alm20	SPS_D	General single alarm		
Alm21	SPS_D	General single alarm		
Alm22	SPS_D	General single alarm		
Alm23	SPS_D	General single alarm		
Alm24	SPS_D	General single alarm		
Alm25	SPS_D	General single alarm		
Alm26	SPS_D	General single alarm		
Alm27	SPS_D	General single alarm		
Alm28	SPS_D	General single alarm		
Alm29	SPS_D	General single alarm		
Alm30	SPS_D	General single alarm		
Alm31	SPS_D	General single alarm		
Alm32	SPS_D	General single alarm		
Alm33	SPS_D	General single alarm		
Alm34	SPS_D	General single alarm		
Alm35	SPS_D	General single alarm		
Alm36	SPS_D	General single alarm		
Alm37	SPS_D	General single alarm		
Alm38	SPS_D	General single alarm		
Alm39	SPS_D	General single alarm		
Alm40	SPS_D	General single alarm		
Alm41	SPS_D	General single alarm		
Alm42	SPS_D	General single alarm		
Alm43	SPS_D	General single alarm		
Alm44	SPS_D	General single alarm		
Alm45	SPS_D	General single alarm		
Alm46	SPS_D	General single alarm		
Alm47	SPS_D	General single alarm		
Alm48	SPS_D	General single alarm		
Alm49	SPS_D	General single alarm		
Alm50	SPS_D	General single alarm		
Alm51	SPS_D	General single alarm		
Alm52	SPS_D	General single alarm		
Alm53	SPS_D	General single alarm		
Alm54	SPS_D	General single alarm		
Alm55	SPS_D	General single alarm		
Alm56	SPS_D	General single alarm		
Alm57	SPS_D	General single alarm		
Alm58	SPS_D	General single alarm		
Alm59	SPS_D	General single alarm		
Alm60	SPS_D	General single alarm		
Alm61	SPS_D	General single alarm		
Alm62	SPS_D	General single alarm		
Alm63	SPS_D	General single alarm		
Alm64	SPS_D	General single alarm		
Alm65	SPS_D	General single alarm		
Alm66	SPS_D	General single alarm		
Alm67	SPS_D	General single alarm		
Alm68	SPS_D	General single alarm		
Alm69	SPS_D	General single alarm		
Alm70	SPS_D	General single alarm		
Alm71	SPS_D	General single alarm		
Alm72	SPS_D	General single alarm		
Alm73	SPS_D	General single alarm		
Alm74	SPS_D	General single alarm		
Alm75	SPS_D	General single alarm		
Alm76	SPS_D	General single alarm		
Alm77	SPS_D	General single alarm		
Alm78	SPS_D	General single alarm		
Alm79	SPS_D	General single alarm		
Alm80	SPS_D	General single alarm		
Alm81	SPS_D	General single alarm		
Alm82	SPS_D	General single alarm		
Alm83	SPS_D	General single alarm		

Attribute	Attr. Type	Explanation	T	X
Alm84	SPS_D	General single alarm		
Alm85	SPS_D	General single alarm		
Alm86	SPS_D	General single alarm		
Alm87	SPS_D	General single alarm		
Alm88	SPS_D	General single alarm		
Alm89	SPS_D	General single alarm		
Alm90	SPS_D	General single alarm		
Alm91	SPS_D	General single alarm		
Alm92	SPS_D	General single alarm		
Alm93	SPS_D	General single alarm		
Alm94	SPS_D	General single alarm		
Alm95	SPS_D	General single alarm		
Alm96	SPS_D	General single alarm		

#### 2.4.4 Logical Node: GGIO\_IND\_10

**Description:** Generic Process I/O (w.r.t 10 Indication Elements)

**LN Class:** GGIO

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		
NamPlt	LPL_LN	Name Plate		
Ind1	SPS_D	General indication (binary input)		
Ind2	SPS_D	General indication (binary input)		
Ind3	SPS_D	General indication (binary input)		
Ind4	SPS_D	General indication (binary input)		
Ind5	SPS_D	General indication (binary input)		
Ind6	SPS_D	General indication (binary input)		
Ind7	SPS_D	General indication (binary input)		
Ind8	SPS_D	General indication (binary input)		
Ind9	SPS_D	General indication (binary input)		
Ind10	SPS_D	General indication (binary input)		

#### 2.4.5 Logical Node: GGIO\_IND\_16\_WD

**Description:** Generic process I/O

**LN Class:** GGIO

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		
NamPlt	LPL_LN	Name Plate		
Ind1	SPS_WD	General indication (binary input)		
Ind2	SPS_WD	General indication (binary input)		
Ind3	SPS_WD	General indication (binary input)		
Ind4	SPS_WD	General indication (binary input)		
Ind5	SPS_WD	General indication (binary input)		



Attribute	Attr. Type	Explanation	T	X
Ind6	SPS_WD	General indication (binary input)		
Ind7	SPS_WD	General indication (binary input)		
Ind8	SPS_WD	General indication (binary input)		
Ind9	SPS_WD	General indication (binary input)		
Ind10	SPS_WD	General indication (binary input)		
Ind11	SPS_WD	General indication (binary input)		
Ind12	SPS_WD	General indication (binary input)		
Ind13	SPS_WD	General indication (binary input)		
Ind14	SPS_WD	General indication (binary input)		
Ind15	SPS_WD	General indication (binary input)		
Ind16	SPS_WD	General indication (binary input)		

2.4.6 Logical Node: GGIO\_IND\_18

**Description:** Generic Process I/O (w.r.t 18 Indication Elements)

**LN Class:** GGIO

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		
NamPlt	LPL_LN	Name Plate		
Ind1	SPS_D	General indication (binary input)		
Ind2	SPS_D	General indication (binary input)		
Ind3	SPS_D	General indication (binary input)		
Ind4	SPS_D	General indication (binary input)		
Ind5	SPS_D	General indication (binary input)		
Ind6	SPS_D	General indication (binary input)		
Ind7	SPS_D	General indication (binary input)		
Ind8	SPS_D	General indication (binary input)		
Ind9	SPS_D	General indication (binary input)		
Ind10	SPS_D	General indication (binary input)		
Ind11	SPS_D	General indication (binary input)		
Ind12	SPS_D	General indication (binary input)		
Ind13	SPS_D	General indication (binary input)		
Ind14	SPS_D	General indication (binary input)		
Ind15	SPS_D	General indication (binary input)		
Ind16	SPS_D	General indication (binary input)		
Ind17	SPS_D	General indication (binary input)		

Attribute	Attr. Type	Explanation	T	X
Ind18	SPS_D	General indication (binary input)		

2.4.7 Logical Node: GGIO\_IND\_20

**Description:** Generic process I/O

**LN Class:** GGIO

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		
NamPlt	LPL_LN	Name Plate		
Ind1	SPS_D	General indication (binary input)		
Ind2	SPS_D	General indication (binary input)		
Ind3	SPS_D	General indication (binary input)		
Ind4	SPS_D	General indication (binary input)		
Ind5	SPS_D	General indication (binary input)		
Ind6	SPS_D	General indication (binary input)		
Ind7	SPS_D	General indication (binary input)		
Ind8	SPS_D	General indication (binary input)		
Ind9	SPS_D	General indication (binary input)		
Ind10	SPS_D	General indication (binary input)		
Ind11	SPS_D	General indication (binary input)		
Ind12	SPS_D	General indication (binary input)		
Ind13	SPS_D	General indication (binary input)		
Ind14	SPS_D	General indication (binary input)		
Ind15	SPS_D	General indication (binary input)		
Ind16	SPS_D	General indication (binary input)		
Ind17	SPS_D	General indication (binary input)		
Ind18	SPS_D	General indication (binary input)		
Ind19	SPS_D	General indication (binary input)		
Ind20	SPS_D	General indication (binary input)		

2.4.8 Logical Node: GGIO\_IND\_24

**Description:** Generic process I/O (w.r.t 24 Indication Elements)

**LN Class:** GGIO

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		
NamPlt	LPL_LN	Name Plate		
Ind1	SPS_D	General indication (binary input)		

Attribute	Attr. Type	Explanation	T	X
Ind2	SPS_D	General indication (binary input)		
Ind3	SPS_D	General indication (binary input)		
Ind4	SPS_D	General indication (binary input)		
Ind5	SPS_D	General indication (binary input)		
Ind6	SPS_D	General indication (binary input)		
Ind7	SPS_D	General indication (binary input)		
Ind8	SPS_D	General indication (binary input)		
Ind9	SPS_D	General indication (binary input)		
Ind10	SPS_D	General indication (binary input)		
Ind11	SPS_D	General indication (binary input)		
Ind12	SPS_D	General indication (binary input)		
Ind13	SPS_D	General indication (binary input)		
Ind14	SPS_D	General indication (binary input)		
Ind15	SPS_D	General indication (binary input)		
Ind16	SPS_D	General indication (binary input)		
Ind17	SPS_D	General indication (binary input)		
Ind18	SPS_D	General indication (binary input)		
Ind19	SPS_D	General indication (binary input)		
Ind20	SPS_D	General indication (binary input)		
Ind21	SPS_D	General indication (binary input)		
Ind22	SPS_D	General indication (binary input)		
Ind23	SPS_D	General indication (binary input)		
Ind24	SPS_D	General indication (binary input)		

2.4.9 Logical Node: GGIO\_IND\_3

**Description:** Generic process I/O (w.r.t 3 Indication Elements)

**LN Class:** GGIO

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		
NamPlt	LPL_LN	Name Plate		
Ind1	SPS_D	87BB Trip Order indication		
Ind2	SPS_D	50BF Trip Order indication		
Ind3	SPS_D	Manual Trip Order indication		

2.4.10 Logical Node: GGIO\_IND\_32

**Description:** Generic Process I/O (w.r.t 32 Indication Elements)

**LN Class:** GGIO

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		
NamPlt	LPL_LN	Name Plate		
Ind1	SPS_D	General indication (binary input)		
Ind2	SPS_D	General indication (binary input)		
Ind3	SPS_D	General indication (binary input)		
Ind4	SPS_D	General indication (binary input)		
Ind5	SPS_D	General indication (binary input)		
Ind6	SPS_D	General indication (binary input)		
Ind7	SPS_D	General indication (binary input)		
Ind8	SPS_D	General indication (binary input)		
Ind9	SPS_D	General indication (binary input)		
Ind10	SPS_D	General indication (binary input)		
Ind11	SPS_D	General indication (binary input)		
Ind12	SPS_D	General indication (binary input)		
Ind13	SPS_D	General indication (binary input)		
Ind14	SPS_D	General indication (binary input)		
Ind15	SPS_D	General indication (binary input)		
Ind16	SPS_D	General indication (binary input)		
Ind17	SPS_D	General indication (binary input)		
Ind18	SPS_D	General indication (binary input)		
Ind19	SPS_D	General indication (binary input)		
Ind20	SPS_D	General indication (binary input)		
Ind21	SPS_D	General indication (binary input)		
Ind22	SPS_D	General indication (binary input)		
Ind23	SPS_D	General indication (binary input)		
Ind24	SPS_D	General indication (binary input)		
Ind25	SPS_D	General indication (binary input)		
Ind26	SPS_D	General indication (binary input)		
Ind27	SPS_D	General indication (binary input)		
Ind28	SPS_D	General indication (binary input)		
Ind29	SPS_D	General indication (binary input)		
Ind30	SPS_D	General indication (binary input)		
Ind31	SPS_D	General indication (binary input)		
Ind32	SPS_D	General indication (binary input)		

## 2.4.11 Logical Node: GGIO\_IND\_6

**Description:** Generic process I/O**LN Class:** GGIO

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		
NamPlt	LPL_LN	Name Plate		
Ind1	SPS_D	General indication (binary input)		
Ind2	SPS_D	General indication (binary input)		
Ind3	SPS_D	General indication (binary input)		
Ind4	SPS_D	General indication (binary input)		
Ind5	SPS_D	General indication (binary input)		
Ind6	SPS_D	General indication (binary input)		

## 2.4.12 Logical Node: GGIO\_IND\_64

**Description:** Generic process I/O (w.r.t 64 Indication Elements)**LN Class:** GGIO

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		
NamPlt	LPL_LN	Name Plate		
Ind1	SPS_D	General indication (binary input)		
Ind2	SPS_D	General indication (binary input)		
Ind3	SPS_D	General indication (binary input)		
Ind4	SPS_D	General indication (binary input)		
Ind5	SPS_D	General indication (binary input)		
Ind6	SPS_D	General indication (binary input)		
Ind7	SPS_D	General indication (binary input)		
Ind8	SPS_D	General indication (binary input)		
Ind9	SPS_D	General indication (binary input)		
Ind10	SPS_D	General indication (binary input)		
Ind11	SPS_D	General indication (binary input)		
Ind12	SPS_D	General indication (binary input)		
Ind13	SPS_D	General indication (binary input)		
Ind14	SPS_D	General indication (binary input)		
Ind15	SPS_D	General indication (binary input)		
Ind16	SPS_D	General indication (binary input)		
Ind17	SPS_D	General indication (binary input)		
Ind18	SPS_D	General indication (binary input)		

Attribute	Attr. Type	Explanation	T	X
		input)		
Ind19	SPS_D	General indication (binary input)		
Ind20	SPS_D	General indication (binary input)		
Ind21	SPS_D	General indication (binary input)		
Ind22	SPS_D	General indication (binary input)		
Ind23	SPS_D	General indication (binary input)		
Ind24	SPS_D	General indication (binary input)		
Ind25	SPS_D	General indication (binary input)		
Ind26	SPS_D	General indication (binary input)		
Ind27	SPS_D	General indication (binary input)		
Ind28	SPS_D	General indication (binary input)		
Ind29	SPS_D	General indication (binary input)		
Ind30	SPS_D	General indication (binary input)		
Ind31	SPS_D	General indication (binary input)		
Ind32	SPS_D	General indication (binary input)		
Ind33	SPS_D	General indication (binary input)		
Ind34	SPS_D	General indication (binary input)		
Ind35	SPS_D	General indication (binary input)		
Ind36	SPS_D	General indication (binary input)		
Ind37	SPS_D	General indication (binary input)		
Ind38	SPS_D	General indication (binary input)		
Ind39	SPS_D	General indication (binary input)		
Ind40	SPS_D	General indication (binary input)		
Ind41	SPS_D	General indication (binary input)		
Ind42	SPS_D	General indication (binary input)		
Ind43	SPS_D	General indication (binary input)		
Ind44	SPS_D	General indication (binary input)		
Ind45	SPS_D	General indication (binary input)		
Ind46	SPS_D	General indication (binary input)		
Ind47	SPS_D	General indication (binary input)		
Ind48	SPS_D	General indication (binary input)		
Ind49	SPS_D	General indication (binary input)		
Ind50	SPS_D	General indication (binary input)		
Ind51	SPS_D	General indication (binary input)		
Ind52	SPS_D	General indication (binary input)		

Attribute	Attr. Type	Explanation	T	X
		input)		
Ind53	SPS_D	General indication (binary input)		
Ind54	SPS_D	General indication (binary input)		
Ind55	SPS_D	General indication (binary input)		
Ind56	SPS_D	General indication (binary input)		
Ind57	SPS_D	General indication (binary input)		
Ind58	SPS_D	General indication (binary input)		
Ind59	SPS_D	General indication (binary input)		
Ind60	SPS_D	General indication (binary input)		
Ind61	SPS_D	General indication (binary input)		
Ind62	SPS_D	General indication (binary input)		
Ind63	SPS_D	General indication (binary input)		
Ind64	SPS_D	General indication (binary input)		

#### 2.4.13 Logical Node: GGIO\_SPCSO\_32

**Description:** Generic process I/O (w.r.t 32 Controllable Elements)

**LN Class:** GGIO

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		
NamPlt	LPL_LN	Name Plate		
SPCSO1	SPC_CONTROL	Single point controllable status output		
SPCSO2	SPC_CONTROL	Single point controllable status output		
SPCSO3	SPC_CONTROL	Single point controllable status output		
SPCSO4	SPC_CONTROL	Single point controllable status output		
SPCSO5	SPC_CONTROL	Single point controllable status output		
SPCSO6	SPC_CONTROL	Single point controllable status output		
SPCSO7	SPC_CONTROL	Single point controllable status output		
SPCSO8	SPC_CONTROL	Single point controllable status output		
SPCSO9	SPC_CONTROL	Single point controllable status output		
SPCSO10	SPC_CONTROL	Single point controllable status output		
SPCSO11	SPC_CONTROL	Single point controllable status output		
SPCSO12	SPC_CONTROL	Single point controllable status output		
SPCSO13	SPC_CONTROL	Single point controllable status output		
SPCSO14	SPC_CONTROL	Single point controllable status output		
SPCSO15	SPC_CONTROL	Single point controllable status output		

Attribute	Attr. Type	Explanation	T	X
SPCSO16	SPC_CONTROL	Single point controllable status output		
SPCSO17	SPC_CONTROL	Single point controllable status output		
SPCSO18	SPC_CONTROL	Single point controllable status output		
SPCSO19	SPC_CONTROL	Single point controllable status output		
SPCSO20	SPC_CONTROL	Single point controllable status output		
SPCSO21	SPC_CONTROL	Single point controllable status output		
SPCSO22	SPC_CONTROL	Single point controllable status output		
SPCSO23	SPC_CONTROL	Single point controllable status output		
SPCSO24	SPC_CONTROL	Single point controllable status output		
SPCSO25	SPC_CONTROL	Single point controllable status output		
SPCSO26	SPC_CONTROL	Single point controllable status output		
SPCSO27	SPC_CONTROL	Single point controllable status output		
SPCSO28	SPC_CONTROL	Single point controllable status output		
SPCSO29	SPC_CONTROL	Single point controllable status output		
SPCSO30	SPC_CONTROL	Single point controllable status output		
SPCSO31	SPC_CONTROL	Single point controllable status output		
SPCSO32	SPC_CONTROL	Single point controllable status output		

#### 2.4.14 Logical Node: LLN0\_PROT\_P743

**Description:** Protection Domain Logical Node 0 for P743

**LN Class:** LLN0

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		
NamPlt	LPL_LLNO	Name Plate		
DzpMod	INC_MODE_PRIVAT E	Dead Zone Protection Mode		X
DzpBeh	INS_BEH_PRIVATE	Dead Zone Protection Behaviour		X
BbcMod	INC_MODE_PRIVAT E	Busbar Trip Confirm Mode		X
BbcBeh	INS_BEH_PRIVATE	Busbar Trip Confirm Behaviour		X
CbfMod	INC_MODE_PRIVAT E	CB Fail Mode		X
CbfBeh	INS_BEH_PRIVATE	CB Fail Behaviour		X
OcpMod	INC_MODE_PRIVAT E	Overcurrent Protection Mode		X
OcpBeh	INS_BEH_PRIVATE	Overcurrent Protection Behaviour		X
EfmMod	INC_MODE_PRIVAT E	Earth Fault Protection Mode		X
EfmBeh	INS_BEH_PRIVATE	Earth Fault Protection Behaviour		X



## 2.4.15 Logical Node: LLN0\_STANDARD

**Description:** General Logical Node 0**LN Class:** LLN0

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		
NamPlt	LPL_LLNO	Name Plate		

## 2.4.16 Logical Node: LLN0\_SYSTEM

**Description:** Logical Node 0 (with Ordrun, SyncSt, LEDRs)**LN Class:** LLN0

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		
NamPlt	LPL_LLNO	Name Plate		
LEDRs	SPC_CONTROL	LED reset	T	
OrdRun	SPS_WD_NS	Order Running		X
SyncSt	SPS_WD_NS	IED time synchronisation state		X

## 2.4.17 Logical Node: LPHD\_STANDARD

**Description:** Px40 Physical Device Information**LN Class:** LPHD

Attribute	Attr. Type	Explanation	T	X
PhyNam	DPL_STANDARD	Physical device name plate		
PhyHealth	INS_HEALTH	Physical device health		
Proxy	SPS_D	Indicates if this LN is a proxy		
PwrUp	SPS_D	Power up detected		

## 2.4.18 Logical Node: MMXU\_P743

**Description:** Standard measurements (w.r.t P743)**LN Class:** MMXU

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		
NamPlt	LPL_LN	Name Plate		
Hz	MV_FLOAT	Frequency		
A	WYE_SEG_RES_D	Phase currents		

## 2.4.19 Logical Node: PDIF\_STR\_SEG\_NEU\_OP\_NOSEG\_\_

**Description:** Differential**LN Class:** PDIF

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		
NamPlt	LPL_LN	Name Plate		
Str	ACD_SEG_NEU	Start		
Op	ACT_NO_SEG	Operate	T	

## 2.4.20 Logical Node: PIOC\_NEU\_OP\_NOSEG

**Description:** Instantaneous overcurrent (w.r.t Neutral)**LN Class:** PIOC

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		
NamPlt	LPL_LN	Name Plate		
Str	ACD_NEU	Start		
Op	ACT_NO_SEG	Operate	T	

## 2.4.21 Logical Node: PIOC\_STR\_SEG\_OP\_NOSEG

**Description:** Instantaneous overcurrent**LN Class:** PIOC

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		
NamPlt	LPL_LN	Name Plate		
Str	ACD_SEG	Start		
Op	ACT_NO_SEG	Operate	T	

## 2.4.22 Logical Node: PTOC\_NEU\_OP\_NOSEG

**Description:** Timed Overcurrent (w.r.t Neutral)**LN Class:** PTOC

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		
NamPlt	LPL_LN	Name Plate		
Str	ACD_NEU	Start		
Op	ACT_NO_SEG	Operate	T	

## 2.4.23 Logical Node: PTOC\_STR\_SEG\_OP\_NOSEG

**Description:** Timed Overcurrent**LN Class:** PTOC

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		
NamPlt	LPL_LN	Name Plate		
Str	ACD_SEG	Start		
Op	ACT_NO_SEG	Operate	T	

## 2.4.24 Logical Node: PTRC\_NO\_SEG

**Description:** Protection trip conditioning (w.r.t No Phase Segregation)**LN Class:** PTRC

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		
NamPlt	LPL_LN	Name Plate		
Tr	ACT_NO_SEG	Trip		
Str	ACD_NO_SEG	Sum of all starts of all connected Logical Nodes		

## 2.4.25 Logical Node: PTRC\_NOOP\_TRNOSEG

**Description:** Protection trip conditioning with no Operate and Trip no phase segregation**LN Class:** PTRC

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		
NamPlt	LPL_LN	Name Plate		
Tr	ACT_NO_SEG	Trip		

## 2.4.26 Logical Node: PTRC\_NOSEG\_NOTR

**Description:** Protection trip conditioning**LN Class:** PTRC

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		
NamPlt	LPL_LN	Name Plate		
Op	ACT_NO_SEG	Operate (combination of subscribed Op from protection functions)		
Str	ACD_NO_SEG	Sum of all starts of all connected Logical Nodes		

## 2.4.27 Logical Node: RBRF\_EXTTRIP\_NOSEG

**Description:** Breaker Failure (w.r.t External Tripping, No Phase Segregation)**LN Class:** RBRF

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		
NamPlt	LPL_LN	Name Plate		
OpEx	ACT_NO_SEG	Breaker failure trip ("External trip")	T	

## 2.4.28 Logical Node: RBRF\_INTTRIP\_NOSEG

**Description:** Breaker Failure (w.r.t Internal Tripping, No Phase Segregation)**LN Class:** RBRF

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Opln	ACT_NO_SEG	Operate, retrip ("Internal trip")	T	

## 2.4.29 Logical Node: RBRF\_INTTRIP\_SEG

**Description:** Breaker Failure (w.r.t Internal Tripping, Phase Segregation)

**LN Class:** RBRF

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		
NamPlt	LPL_LN	Name Plate		
Opln	ACT_SEG	Operate, retrip ("Internal trip")	T	

## 2.4.30 Logical Node: RDRE\_BASIC

**Description:** Disturbance Recorder function (w.r.t Mandatory Attributes only)

**LN Class:** RDRE

Attribute	Attr. Type	Explanation	T	X
Mod	INC_MOD	Mode		
Beh	INS_BEH	Behaviour		
Health	INS_HEALTH	Health		
NamPlt	LPL_LN	Name Plate		
RcdMade	SPS_WD	Recording made		
FitNum	INS_BASIC	Fault number		

## 2.4.31 Logical Node: XCBR\_BASIC

**Description:** Circuit Breaker (w.r.t Mandatory Attributes Only)

**LN Class:** XCBR

Attribute	Attr. Type	Explanation	T	X
Beh	INS_BEH	Behaviour		
Mod	INC_MOD	Mode		
Health	INS_HEALTH	Health		
NamPlt	LPL_LN	Name Plate		
Loc	SPS_WD	Local operation		
EEHealth	INS_HEALTH	External equipment health		
OpCnt	INS_BASIC	Operation counter		
Pos	DPC_CONTROL	Switch position		
BlkOpn	SPC_STATUS	Block opening		
BlkCls	SPC_STATUS	Block closing		
CBOpCap	INS_BASIC	Circuit Breaker operating capability		
Lock	SPC_CONTROL_NS	Handle Circuit Breaker locks		X

## 2.5 Common Data Class definitions

The definition tables for each of the Common Data Classes used in the Logical Node definitions are presented in the following sub-sections.

From an application point-of-view the data attributes of a Common Data Class are classified according to their specific use. The characterization of data attributes, and the services that they support/provide, will be through the use of 'Functional Constraints'. The Functional Constraints are specified by the table below:

FC Name	Semantic	Source Definition
BR	Buffered reports	IEC61850-7-2
CF	Configuration	IEC61850-7-2
CO	Control	IEC61850-7-2
DC	Description	IEC61850-7-2
EX	Extended Definition	IEC61850-7-2
GO	GOOSE Control	IEC61850-7-2
GS	GSSE Control (UCA2 GOOSE)	IEC61850-7-2
LG	Logging	IEC61850-7-2
MS	Multicast sampled value control	IEC61850-7-2
MX	Measurands (Analogue values)	IEC61850-7-2
RP	Unbuffered reports	IEC61850-7-2
SE	Setting Group Editable	IEC61850-7-2
SG	Setting Group	IEC61850-7-2
SP	Set Point	IEC61850-7-2
ST	Status Information	IEC61850-7-2
SV	Substitution Values	IEC61850-7-2
US	Unicast sampled value control	IEC61850-7-2
XX	Data attribute service parameters	IEC61850-7-2

### 2.5.1 Common Data Class: ACD\_NEU

**Description:** Directional Protection Activation Information (w.r.t Neutral)

**CDC Class:** ACD

Attribute	Type	FC	Enumeration	Comment	X
general	BOOLEAN	ST		Trip or start has happened	
dirGeneral	ENUMERATED 8*(MMS Type: INT8)	ST	dir	General direction (unknown, forward, backward or both)	
neut	BOOLEAN	ST		Trip or start event with earth current has happened	
dirNeut	ENUMERATED 8*(MMS Type: INT8)	ST	dir	Earth current direction (unknown, forward or backward)	
q	Quality	ST		Quality of the protection activation information	
t	TimeStamp	ST		Timestamp of the last change in state of protection activation information	

## 2.5.2 Common Data Class: ACD\_NO\_SEG

**Description:** Directional Protection Activation Information (w,r,t No Phase Segregation)**CDC Class:** ACD

Attribute	Type	FC	Enumeration	Comment	X
general	BOOLEAN	ST		Trip or start has happened	
dirGeneral	ENUMERATED 8*(MMS Type: INT8)	ST	dir	General direction (unknown, forward, backward or both)	
q	Quality	ST		Quality of the protection activation information	
t	TimeStamp	ST		Timestamp of the last change in state of protection activation information	

## 2.5.3 Common Data Class: ACD\_SEG

**Description:** Directional Protection Activation Information (w.r.t Phase Segregation)**CDC Class:** ACD

Attribute	Type	FC	Enumeration	Comment	X
general	BOOLEAN	ST		Trip or start has happened	
dirGeneral	ENUMERATED 8*(MMS Type: INT8)	ST	dir	General direction (unknown, forward, backward or both)	
phsA	BOOLEAN	ST		Trip or start event of Phase A has happened	
dirPhsA	ENUMERATED 8*(MMS Type: INT8)	ST	dir	Phase A direction (unknown, forward or backward)	
phsB	BOOLEAN	ST		Trip or start event of Phase B has happened	
dirPhsB	ENUMERATED 8*(MMS Type: INT8)	ST	dir	Phase B direction (unknown, forward or backward)	
phsC	BOOLEAN	ST		Trip or start event of Phase C has happened	
dirPhsC	ENUMERATED 8*(MMS Type: INT8)	ST	dir	Phase C direction (unknown, forward or backward)	
q	Quality	ST		Quality of the protection activation information	
t	TimeStamp	ST		Timestamp of the last change in state of protection activation information	

2.5.4 Common Data Class: ACD\_SEG\_NEU

**Description:** Directional Protection Activation Information

**CDC Class:** ACD

Attribute	Type	FC	Enumeration	Comment	X
general	BOOLEAN	ST		Trip or start has happened	
dirGeneral	ENUMERATED 8*(MMS Type: INT8)	ST	dir	General direction (unknown, forward, backward or both)	
phsA	BOOLEAN	ST		Trip or start event of Phase A has happened	
dirPhsA	ENUMERATED 8*(MMS Type: INT8)	ST	dir	Phase A direction (unknown, forward or backward)	
phsB	BOOLEAN	ST		Trip or start event of Phase B has happened	
dirPhsB	ENUMERATED 8*(MMS Type: INT8)	ST	dir	Phase B direction (unknown, forward or backward)	
phsC	BOOLEAN	ST		Trip or start event of Phase C has happened	
dirPhsC	ENUMERATED 8*(MMS Type: INT8)	ST	dir	Phase C direction (unknown, forward or backward)	
neut	BOOLEAN	ST		Trip or start event with earth current has happened	
dirNeut	ENUMERATED 8*(MMS Type: INT8)	ST	dir	Earth current direction (unknown, forward or backward)	
q	Quality	ST		Quality of the protection activation information	
t	TimeStamp	ST		Timestamp of the last change in state of protection activation information	

2.5.5 Common Data Class: ACT\_NO\_SEG

**Description:** Protection Activation Information (w.r.t No Phase Segregation)

**CDC Class:** ACT

Attribute	Type	FC	Enumeration	Comment	X
general	BOOLEAN	ST		Trip or start has happened	
q	Quality	ST		Quality of the protection activation information	
t	TimeStamp	ST		Timestamp of the last change in state of protection activation information	

## 2.5.6 Common Data Class: ACT\_SEG

**Description:** Protection Activation Information (w.r.t Phase Segregation)**CDC Class:** ACT

Attribute	Type	FC	Enumeration	Comment	X
general	BOOLEAN	ST		Trip or start has happened	
phsA	BOOLEAN	ST		Trip or start event of Phase A has happened	
phsB	BOOLEAN	ST		Trip or start event of Phase B has happened	
phsC	BOOLEAN	ST		Trip or start event of Phase C has happened	
q	Quality	ST		Quality of the protection activation information	
t	TimeStamp	ST		Timestamp of the last change in state of protection activation information	

## 2.5.7 Common Data Class: CMV\_MAG\_ANG\_FLOAT

**Description:** Complex Measured value (w.r.t Floating Point Magnitude and Angle)**CDC Class:** CMV

Attribute	Type	FC	Enumeration	Comment	X
cVal	Vector_MagnitudeAngle_Float	MX		Deadbanded complex measured vector. Updated to the current value of instCVal when the value has changed according to the configuration parameter db.	
q	Quality	MX		Quality of the measurement value	
t	TimeStamp	MX		Time deadbanded magnitude last exceeded its db configuration parameter	
units	Unit_Multiplier	CF		Unit of the attribute representing the data	
db	INT32U	CF		Measurement deadband	
rangeC	RangeC	CF		Measurement range configuration attributes	



2.5.8 Common Data Class: DPC\_CONTROL

**Description:** Controllable Double Point (with ctIVal)

**CDC Class:** DPC

Attribute	Type	FC	Enumeration	Comment	X
ctIVal	BOOLEAN	CO		Control value (Off - FALSE, On - TRUE)	
origin	Originator	ST		Originator of the last change of the controllable data	
stVal	CODED_ENUM *(MMS Type: _BSTR2)	ST	Dbpos	Status value of the data (Intermediate state, Off, On or Bad-state)	
q	Quality	ST		Quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state of status value	
ctlModel	ENUMERATED 8*(MMS Type: INT8)	CF	ctlModel	Control model (Corresponding to the behaviour of the data)	
sboTimeout	INT32U	CF		Select Before Operate timeout period (in milliseconds)	
Bypass	ENUMERATED 8 (MMS Type: bitstring)	CO	Bypass	Bypass	

2.5.9 Common Data Class: DPL\_STANDARD

**Description:** Standard Device Name Plate

**CDC Class:** DPL

Attribute	Type	FC	Enumeration	Comment	X
vendor	VISIBLE_STRING255	DC		Name of the vendor	
hwRev	VISIBLE_STRING255	DC		Hardware revision	
swRev	VISIBLE_STRING255	DC		Software revision	
serNum	VISIBLE_STRING255	DC		Serial Number	
model	VISIBLE_STRING255	DC		Model Number	
location	VISIBLE_STRING255	DC		Physical location of device	

2.5.10 Common Data Class: INC\_MOD

**Description:** Controllable Integer Status (w.r.t Mode)

**CDC Class:** INC

Attribute	Type	FC	Enumeration	Comment	X
stVal	INT32*(MMS Type: INT8)	ST	Mod	Status value of the data	
q	Quality	ST		Quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state of status value	
ctlModel	ENUMERATED 8*(MMS Type: INT8)	CF	ctlModel	Control model (Corresponding to the behaviour of the data)	

## 2.5.11 Common Data Class: INC\_MODE\_PRIVATE

**Description:** Controllable Integer Status**CDC Class:** INC

Attribute	Type	FC	Enumeration	Comment	X
stVal	INT32*(MMS Type: INT8)	ST	Mod	Status value of the data	
q	Quality	ST		Quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state of status value	
ctlModel	ENUMERATED 8*(MMS Type: INT8)	CF	ctlModel	Control model (Corresponding to the behaviour of the data)	
dataNs	VISIBLE_STRING255	EX		Data name space	

## 2.5.12 Common Data Class: INS\_BASIC

**Description:** Integer Status (w.r.t Mandatory Options Only)**CDC Class:** INS

Attribute	Type	FC	Enumeration	Comment	X
stVal	INT32	ST		The element status	
q	Quality	ST		The quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state	

## 2.5.13 Common Data Class: INS\_BEH

**Description:** Integer Status (w.r.t Behaviour)**CDC Class:** INS

Attribute	Type	FC	Enumeration	Comment	X
stVal	INT32*(MMS Type: INT8)	ST	Beh	The element status	
q	Quality	ST		The quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state	

## 2.5.14 Common Data Class: INS\_BEH\_PRIVATE

**Description:** Integer Status**CDC Class:** INS

Attribute	Type	FC	Enumeration	Comment	X
stVal	INT32*(MMS Type: INT8)	ST	Beh	The element status	
q	Quality	ST		The quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state	
dataNs	VISIBLE_STRING255	EX		Data name space	

2.5.15 Common Data Class: INS\_HEALTH

**Description:** Integer Status (w.r.t health)

**CDC Class:** INS

Attribute	Type	FC	Enumeration	Comment	X
stVal	INT32*(MMS Type: INT8)	ST	Health	The element status	
q	Quality	ST		The quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state	

2.5.16 Common Data Class: LPL\_LLNO

**Description:** Logical Node 0 Name Plate

**CDC Class:** LPL

Attribute	Type	FC	Enumeration	Comment	X
vendor	VISIBLE_STRI NG255	DC		Name of the vendor	
swRev	VISIBLE_STRI NG255	DC		Software revision	
d	VISIBLE_STRI NG255	DC		Description	
configRev	VISIBLE_STRI NG255	DC		Uniquely identifies the configuration of a local device instance	
ldNs	VISIBLE_STRI NG255	EX		Logical Device name space	

2.5.17 Common Data Class: LPL\_LN

**Description:** Standard Logical Node Name Plate

**CDC Class:** LPL

Attribute	Type	FC	Enumeration	Comment	X
vendor	VISIBLE_STRI NG255	DC		Name of the vendor	
swRev	VISIBLE_STRI NG255	DC		Software revision	
d	VISIBLE_STRI NG255	DC		Description	

2.5.18 Common Data Class: MV\_FLOAT

**Description:** Measured value (w.r.t. Floating Point value)

**CDC Class:** MV

Attribute	Type	FC	Enumeration	Comment	X
mag	AnalogueValue_Float	MX		Deadbanded magnitude of the instantaneous value of a measured value or harmonic value. Updated to the current value of instMag when the value has changed according to the configuration parameter db.	
q	Quality	MX		Quality of the measurement value	
t	TimeStamp	MX		Time deadbanded magnitude last exceeded its db	

Attribute	Type	FC	Enumeration	Comment	X
				configuration parameter	
units	Unit_Multiplier	CF		Unit of the attribute representing the data	
db	INT32U	CF		Measurement deadband	
rangeC	RangeC	CF		Measurement range configuration attributes	

## 2.5.19 Common Data Class: SPC\_CONTROL

**Description:** Controllable Single Point**CDC Class:** SPC

Attribute	Type	FC	Enumeration	Comment	X
ctlVal	BOOLEAN	CO		Control value (Off - FALSE, On - TRUE)	
origin	Originator	ST		Originator of the last change of the controllable data	
stVal	BOOLEAN	ST		Status value of the data	
q	Quality	ST		Quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state of status value	
ctlModel	ENUMERATED 8*(MMS Type: INT8)	CF	ctlModel	Control model (Corresponding to the behaviour of the data)	
sboTimeout	INT32U	CF		Select Before Operate timeout period (in milliseconds)	
Bypass	ENUMERATED 8 (MMS Type: bitstring)	CO	Bypass	Bypass	

## 2.5.20 Common Data Class: SPC\_CONTROL\_NS

**Description:** Controllable Single Point (with DataNS)**CDC Class:** SPC

Attribute	Type	FC	Enumeration	Comment	X
ctlVal	BOOLEAN	CO		Control value (Off - FALSE, On - TRUE)	
origin	Originator	ST		Originator of the last change of the controllable data	
stVal	BOOLEAN	ST		Status value of the data	
q	Quality	ST		Quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state of status value	
ctlModel	ENUMERATED 8*(MMS Type: INT8)	CF	ctlModel	Control model (Corresponding to the behaviour of the data)	
sboTimeout	INT32U	CF		Select Before Operate timeout period (in milliseconds)	
dataNs	VISIBLE_STRING255	EX		Data name space	
Bypass	ENUMERATED 8 (MMS Type: bitstring)	CO	Bypass	Bypass	

2.5.21 Common Data Class: SPC\_STATUS

**Description:** Controllable Single Point (w.r.t Status Only)

**CDC Class:** SPC

Attribute	Type	FC	Enumeration	Comment	X
stVal	BOOLEAN	ST		Status value of the data	
q	Quality	ST		Quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state of status value	
ctlModel	ENUMERATED 8*(MMS Type: INT8)	CF	ctlModel	Control model (Corresponding to the behaviour of the data)	

2.5.22 Common Data Class: SPS\_D

**Description:** Standard Single Point Status (with Description)

**CDC Class:** SPS

Attribute	Type	FC	Enumeration	Comment	X
stVal	BOOLEAN	ST		The element status (TRUE or FALSE)	
q	Quality	ST		The quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state	
d	VISIBLE_STRING255	DC		Description of the status element	

2.5.23 Common Data Class: SPS\_WD

**Description:** Single Point Status (without Description)

**CDC Class:** SPS

Attribute	Type	FC	Enumeration	Comment	X
stVal	BOOLEAN	ST		The element status (TRUE or FALSE)	
q	Quality	ST		The quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state	

2.5.24 Common Data Class: SPS\_WD\_NS

**Description:** Single Point Status (without Description, with namespace)

**CDC Class:** SPS

Attribute	Type	FC	Enumeration	Comment	X
stVal	BOOLEAN	ST		The element status (TRUE or FALSE)	
q	Quality	ST		The quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state	
dataNs	VISIBLE_STRING255	EX		Data name space	

## 2.5.25 Common Data Class: WYE\_SEG\_RES\_D

**Description:** Phase to ground measurements for a 3-Phase system (w.r.t Phase Segregation + Residual + Description)

**CDC Class:** WYE

Attribute	Type	FC	Enumeration	Comment	X
phsA	CMV_MAG_AN G_FLOAT	--		Measurement values for Phase A	
phsB	CMV_MAG_AN G_FLOAT	--		Measurement values for Phase B	
phsC	CMV_MAG_AN G_FLOAT	--		Measurement values for Phase C	
neut	CMV_MAG_AN G_FLOAT	--		Measurement values for neutral input	
d	VISIBLE_STRI NG255	DC		Description of the status element	

## 2.6 Common data attribute type definitions

Common data attribute types, known herein as components, are defined for use in the Common Data Classes defined in the sections above.

### 2.6.1 Component: AnalogueValue\_Float

**Comment:** General analogue value (w.r.t Floating Point value)

**Parent Type:** AnalogueValue

Attribute	Type		Enumeration	Comment	X
f	FLOAT32		Floating point value		

### 2.6.2 Component: Originator

**Comment:** Originator of the last change of data attribute representing the value of a controllable data object

**Parent Type:**

Attribute	Type		Enumeration	Comment	X
orIdent	OCTET_STRING64		Originator identification (Null value indicates unknown or not reported)		
orCat	ENUMERATED8*(MMS Type: INT8)	orCategory	Originator category (Not-supported, bay-control, station-control, remote-control, automatic-bay, automatic-station, automatic-remote, maintenance or process)		

### 2.6.3 Component: RangeC

**Comment:** Measurement range configuration

**Parent Type:** RangeConfig

Attribute	Type		Enumeration	Comment	X
min	AnalogueValue_Float		Minimum process measurement for which values of i and f are considered within limits		
max	AnalogueValue_Float		Maximum process measurement for which values of i and f are considered within limits		
lLim	AnalogueValue_Float		Low Low range limit		
lLim	AnalogueValue_Float		Low range limit		
hLim	AnalogueValue_Float		High range limit		
hhLim	AnalogueValue_Float		High High range limit		

2.6.4 Component: Unit\_Multiplier

**Comment:** SI Unit definitions

**Parent Type:** Unit

Attribute	Type		Enumeration	Comment	X
SIUnit	ENUMERATED8*(MMS Type: INT8)	SIUnit	SI Unit		
multiplier	ENUMERATED16*(MMS Type: INT8)	multiplier	Multiplier value, the default of which is 0 (i.e. multiplier = 1)		

2.6.5 Component: Vector\_MagnitudeAngle\_Float

**Comment:** Complex vector (w.r.t Floating Point Magnitude and Angle values)

**Parent Type:** Vector

Attribute	Type		Enumeration	Comment	X
mag	AnalogueValue_Float		The magnitude of the complex value		
ang	AnalogueValue_Float		The angle of the complex value (the unit is degrees)		



## 2.7 Enumerated type definitions

The following sub-sections specify the enumerations that are associated to some Common Data Class attributes. The definition of the enumerations are according to IEC61850-7-3 and IEC61850-7-4 unless otherwise stated.

### 2.7.1 Enumerated type: AddCause

**Description:** Additional Cause diagnosis

Ordinal	Semantic
0	Unknown
1	Not-supported
2	Blocked-by-switching-hierarchy
3	Select-failed
4	Invalid-position
5	Position-reached
6	Parameter-change-in-execution
7	Step-limit
8	Blocked-by-Mode
9	Blocked-by-process
10	Blocked-by-interlocking
11	Blocked-by-synchrocheck
12	Command-already-in-execution
13	Blocked-by-health
14	1-of-n-control
15	Abortion-by-cancel
16	Time-limit-over
17	Abortion-by-trip
18	Object-not-selected

### 2.7.2 Enumerated type: Beh

**Description:** Behaviour

Ordinal	Semantic
1	on
2	blocked
3	test
4	test/blocked
5	off

### 2.7.3 Enumerated type: Bypass

**Description:** Cause of Bypass

Ordinal	Semantic
0	locking-bypass
1	mode-bypass
2	automation-bypass
3	uniqueness-bypass
4	select-bypass
5	status-bypass

### 2.7.4 Enumerated type: ctlModel

**Description:** Control Model

Ordinal	Semantic
0	status-only
1	direct-with-normal-security
2	sbo-with-normal-security
3	direct-with-enhanced-security
4	sbo-with-enhanced-security

## 2.7.5 Enumerated type: Dbpos

**Description:** Circuit Breaker position

Ordinal	Semantic
0	intermediate
1	off
2	on
3	bad

## 2.7.6 Enumerated type: dir

**Description:** Direction

Ordinal	Semantic
0	unknown
1	forward
2	backward
3	both

## 2.7.7 Enumerated type: Health

**Description:** Health

Ordinal	Semantic
1	Ok
2	Warning
3	Alarm

## 2.7.8 Enumerated type: Mod

**Description:** Mode

Ordinal	Semantic
1	on
2	blocked
3	test
4	test/blocked
5	off

## 2.7.9 Enumerated type: multiplier

**Description:** Exponents of the multiplier value in base 10.

Ordinal	Semantic
-24	y
-21	z
-18	a
-15	f
-12	p
-9	n
-6	μ
-3	m
-2	c
-1	d
0	
1	da
2	h
3	k
6	M
9	G
12	T
15	P
18	E
21	Z
24	Y

## 2.7.10 Enumerated type: orCategory

**Description:** Control mode and Place mode

Ordinal	Semantic
0	not-supported
1	bay-control
2	station-control
3	remote-control
4	automatic-bay
5	automatic-station
6	automatic-remote
7	maintenance
8	process

## 2.7.11 Enumerated type: SIUnit

**Description:** SI Units derived from ISO/IEC 1000

Ordinal	Semantic
1	none
2	m
3	kg
4	s
5	A
6	K
7	mol
8	cd
9	deg
10	rad
11	sr
21	Gy
22	q
23	°C
24	Sv
25	F
26	C
27	S
28	H
29	V
30	ohm
31	J
32	N
33	Hz
34	lx
35	Lm
36	Wb
37	T
38	W
39	Pa
41	m <sup>2</sup>
42	m <sup>3</sup>
43	m/s
44	m/s <sup>2</sup>
45	m <sup>3</sup> /s
46	m/m <sup>3</sup>
47	M
48	kg/m <sup>3</sup>
49	m <sup>2</sup> /s
50	W/m K
51	J/K
52	ppm
53	1/s
54	rad/s
61	VA
62	Watts
63	VA <sub>r</sub>
64	phi

Ordinal	Semantic
65	cos(phi)
66	Vs
67	V <sup>2</sup>
68	As
69	A <sup>2</sup>
70	A <sup>2t</sup>
71	VAh
72	Wh
73	VArh
74	V/Hz

## 2.8 MMS data-type conversions

The following table shows the relationships between the Part 7 and Part 8-1 data types. The definitions presented above use Part 7 data types, however these are subject to 'translation' when exposed over an MMS (Part 8-1) interface:

Part 7 Type	MMS Type	Part 7 Description
BOOLEAN	Bool	Logical TRUE/FALSE value
BSTR16	Bstring16	Bit string 16
BVstring13	BVstring13	Variable bit string (upto 13 bits)
Check	BVstring2	Control Object check flags
CODED_ENUM	Byte	Coded enumeration
CODED_ENUM2	Byte	Coded enumeration (2)
EntryTime	Btime6	8.1 Section 8.1.3.7
ENUMERATED16	Short	16 bit enumerated value
ENUMERATED8	Byte	8 bit enumerated value
FLOAT32	Float	32 bit floating point value
FLOAT64	Double	64 bit floating point value
INT128	Int64	128 bit signed integer value
INT16	Short	16 bit signed integer value
INT16U	Ushort	16 bit unsigned integer value
INT24U	Ulong	24 bit unsigned integer value
INT32	Long	32 bit signed integer value
INT32U	Ulong	32 bit unsigned integer value
INT8	Byte	8 bit signed integer value
INT8U	Ubyte	8 bit unsigned integer value
OCTET_STRING6	Ostring6	6 character string (8 bits per character)
OCTET_STRING64	OVstring64	64 character string (8 bits per character)
OCTET_STRING8	OVstring8	8 character string (8 bits per character)
Quality	BVstring13	IEC61850 Quality
TimeStamp	Utctime	IEC61850 Time stamp
UNICODE_STRING255	UTF8Vstring255	255 character string (16 bits per unicode character)
UTC_TM	Utctime	UTC Timestamp
VISIBLE_STRING255	Vstring255	255 character string
VISIBLE_STRING64	Vstring64	64 character string
VISIBLE_STRING65	Vstring65	65 character string
VISIBLE_STRING97	Vstring97	97 character string





## Customer Care Centre

<http://www.schneider-electric.com/CCC>

**Schneider Electric**

35 rue Joseph Monier  
92506 Rueil-Malmaison  
FRANCE

Phone: +33 (0) 1 41 29 70 00

Fax: +33 (0) 1 41 29 71 00

[www.schneider-electric.com](http://www.schneider-electric.com)

**Publication: P743/EN PM/K96**

Publishing: Schneider Electric

10/2012